

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P561545

Luminaire Tested: **SQ4-PC3-075U-100D-92765-1D-UNV-STD-W-4 (3500K)**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P561545
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2106-289-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PC3-075U-100D-92765-1D-UNV-STD-W-4 (3500K)
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS
DOWNLIGHT 1000 LUMENS PER FOOT
UPLIGHT 750 LUMENS PER FOOT
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7259.4 lumens
Efficiency: N/A
Efficacy: 109.8 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 66.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P561545
CATALOG NUMBER: SQ4-PC3-075U-100D-92765-1D-UNV-STD-W-4 (3500K)

Luminous Intensity Polar Plot





TEST NUMBER: P561545

CATALOG NUMBER: SQ4-PC3-075U-100D-92765-1D-UNV-STD-W-4 (3500K)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61	55
1	99	95	91	87	92	88	85	82	76	73	71	64	63	61	54	53	51	46
2	90	83	76	71	83	77	72	67	66	62	59	56	53	51	47	45	43	39
3	82	73	65	59	76	68	61	56	58	53	49	50	46	43	42	39	37	33
4	75	64	56	50	70	60	53	47	52	46	42	44	40	37	37	34	32	28
5	69	57	49	43	64	54	46	41	46	41	36	40	35	32	34	30	28	24
6	64	51	43	37	59	48	41	35	42	36	32	36	31	28	31	27	24	21
7	59	46	38	33	54	43	36	31	38	32	28	33	28	25	28	24	22	19
8	55	42	34	29	51	39	32	27	35	29	25	30	25	22	26	22	19	17
9	51	38	31	26	47	36	29	24	32	26	22	27	23	20	24	20	17	15
10	47	35	28	23	44	33	26	22	29	24	20	25	21	18	22	18	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13495	13495	13495
5°	13597	13509	13459
10°	13564	13500	13463
15°	13493	13493	13479
20°	13404	13444	13444
25°	13277	13373	13333
30°	13116	13274	13217
35°	12920	13118	13027
40°	12706	12886	12756
45°	12476	12564	12369
50°	12150	12150	11955
55°	11765	11612	11437
60°	11197	10972	10797
65°	10348	10141	10053
70°	9061	9134	9096
75°	7290	8063	8110
80°	5180	6838	6907
85°	3155	5738	5738



TEST NUMBER: P561545

CATALOG NUMBER: SQ4-PC3-075U-100D-92765-1D-UNV-STD-W-4 (3500K)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	138.4	1.9
10°-20°	397.3	5.5
20°-30°	601.6	8.3
30°-40°	721.2	9.9
40°-50°	735.4	10.1
50°-60°	642.0	8.8
60°-70°	459.6	6.3
70°-80°	236.7	3.3
80°-90°	59.9	0.8
90°-100°	239.7	3.3
100°-110°	682.0	9.4
110°-120°	653.4	9.0
120°-130°	517.2	7.1
130°-140°	415.1	5.7
140°-150°	325.0	4.5
150°-160°	237.8	3.3
160°-170°	147.3	2.0
170°-180°	50.0	0.7
0°-30°	1137.3	15.7
0°-40°	1858.5	25.6
0°-60°	3235.8	44.6
0°-90°	3992.0	55.0
90°-120°	1575.1	21.7
90°-150°	2832.3	39.0
90°-180°	3267.0	45.0
0°-180°	7259.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1463	1463	1463	1463	1463	
5°	1468	1454	1459	1454	1453	139
15°	1413	1401	1413	1413	1411	398
25°	1304	1295	1314	1310	1310	600
35°	1147	1144	1165	1157	1157	717
45°	956	954	963	951	948	736
55°	731	722	722	711	711	652
65°	474	463	464	460	460	469
75°	204	214	226	228	228	221
85°	30	46	54	56	54	40
90°	0	0	0	0	0	2
95°	26	103	464	161	99	30
105°	106	161	695	1228	1167	112
115°	197	238	527	1116	1311	194
125°	278	308	503	835	998	249
135°	340	368	497	705	797	262
145°	401	422	501	610	665	250
155°	458	469	513	552	574	212
165°	506	508	519	530	538	142
175°	530	527	525	522	518	50
180°	526	526	526	526	526	

TEST NUMBER: P561545

CATALOG NUMBER: SQ4-PC3-075U-100D-92765-1D-UNV-STD-W-4 (3500K)

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1462.7	1462.7	1462.7	1462.7	1462.7
2.5°	1471.4	1458.7	1462.7	1459.3	1454.0
5°	1468.1	1453.6	1458.6	1454.5	1453.2
7.5°	1457.6	1443.0	1449.7	1447.0	1445.6
10°	1447.8	1433.2	1441.0	1438.3	1437.0
12.5°	1434.8	1421.3	1430.2	1427.5	1427.2
15°	1412.6	1400.7	1412.6	1412.6	1411.2
17.5°	1384.7	1373.8	1386.6	1387.4	1386.6
20°	1365.2	1353.3	1369.3	1367.9	1369.3
22.5°	1341.4	1331.6	1348.7	1345.2	1346.5
25°	1304.2	1295.0	1313.7	1309.7	1309.7
27.5°	1260.4	1253.7	1274.2	1269.8	1269.8
30°	1231.1	1224.5	1246.0	1240.6	1240.6
32.5°	1198.6	1194.1	1214.6	1208.1	1208.1
35°	1147.1	1144.5	1164.7	1156.6	1156.6
37.5°	1094.0	1091.7	1110.0	1100.2	1097.0
40°	1055.0	1053.7	1069.9	1059.1	1059.1
42.5°	1016.0	1014.7	1028.8	1015.8	1015.8
45°	956.2	953.5	962.9	950.7	948.0
47.5°	890.9	888.2	894.1	880.8	879.5
50°	846.5	843.8	846.5	834.3	832.9
52.5°	801.0	796.2	796.6	784.4	784.2
55°	731.4	722.1	721.9	711.0	711.0
57.5°	657.7	645.5	646.6	637.3	636.0
60°	606.8	593.5	594.6	586.4	585.1
62.5°	556.9	541.5	544.7	535.5	535.2
65°	474.0	463.4	464.5	460.5	460.5
67.5°	394.4	384.6	391.7	388.4	388.2
70°	335.9	329.3	338.6	338.6	337.2
72.5°	281.7	281.4	293.1	293.1	293.9
75°	204.5	213.8	226.2	227.5	227.5
77.5°	136.5	152.9	166.6	167.1	166.9
80°	97.5	116.1	128.7	131.3	130.0
82.5°	66.1	85.7	96.2	98.8	97.5
85°	29.8	45.7	54.2	55.5	54.2
87.5°	8.7	18.2	21.7	21.6	19.5
90°	0.0	0.0	0.0	0.0	0.0
92.5°	8.0	42.4	98.4	28.6	21.6
95°	26.0	103.2	464.0	160.6	99.0
97.5°	47.8	120.9	714.6	511.3	350.4
100°	63.0	131.4	769.0	778.9	600.0
102.5°	79.8	142.8	757.0	997.0	840.8
105°	106.0	160.8	695.0	1227.6	1167.0
107.5°	132.6	181.7	622.6	1292.6	1346.6
110°	151.0	197.0	581.0	1267.8	1389.0

TEST NUMBER: P561545

CATALOG NUMBER: SQ4-PC3-075U-100D-92765-1D-UNV-STD-W-4 (3500K)

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	168.6	212.2	553.0	1208.9	1381.8
115°	197.0	238.1	527.0	1116.4	1311.0
117.5°	222.0	260.5	511.6	1015.3	1221.4
120°	242.0	274.3	510.0	957.5	1155.0
122.5°	258.0	290.3	506.0	906.8	1090.2
125°	278.0	308.3	503.0	834.7	998.0
127.5°	299.8	328.2	501.4	791.7	926.2
130°	311.0	339.4	499.0	761.7	879.0
132.5°	323.0	350.6	499.0	738.3	846.2
135°	340.0	368.4	497.0	705.1	797.0
137.5°	356.0	383.6	496.8	677.0	756.4
140°	368.0	396.4	496.0	653.7	730.0
142.5°	381.6	405.3	498.4	635.2	703.6
145°	401.0	421.5	501.0	610.2	665.0
147.5°	417.6	437.5	505.4	585.1	632.4
150°	432.0	445.7	507.0	576.8	610.0
152.5°	443.2	457.7	508.6	565.5	596.4
155°	458.0	468.8	513.0	551.5	574.0
157.5°	476.4	482.9	514.0	545.2	561.2
160°	486.0	490.9	518.0	540.3	554.0
162.5°	491.6	497.3	518.8	536.2	546.8
165°	506.0	508.0	519.0	530.2	538.0
167.5°	515.8	514.0	523.6	528.7	531.8
170°	519.0	518.0	522.0	523.1	527.0
172.5°	526.2	522.9	524.4	521.5	524.6
175°	530.0	527.1	525.0	521.9	518.0
177.5°	531.6	526.9	524.4	521.2	522.0
180°	526.0	526.0	526.0	526.0	526.0

(END OF REPORT)