

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P561547

Luminaire Tested: **SQ4-PC3-075U-100D-92765-1D-UNV-STD-W-4 (4500K)**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P561547
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2106-289-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PC3-075U-100D-92765-1D-UNV-STD-W-4 (4500K)
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS
DOWNLIGHT 1000 LUMENS PER FOOT
UPLIGHT 750 LUMENS PER FOOT
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 4500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7511.4 lumens
Efficiency: N/A
Efficacy: 113.8 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 66
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P561547
CATALOG NUMBER: SQ4-PC3-075U-100D-92765-1D-UNV-STD-W-4 (4500K)

Luminous Intensity Polar Plot





TEST NUMBER: P561547

CATALOG NUMBER: SQ4-PC3-075U-100D-92765-1D-UNV-STD-W-4 (4500K)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61	55
1	99	95	91	87	92	88	85	82	76	73	71	64	63	61	54	53	51	46
2	90	83	76	71	83	77	72	67	66	62	59	56	53	51	47	45	43	39
3	82	73	65	59	76	68	61	56	58	53	49	50	46	43	42	39	37	33
4	75	64	56	50	70	60	53	47	52	46	42	44	40	37	37	34	32	28
5	69	57	49	43	64	54	46	41	46	41	36	40	35	32	34	30	28	24
6	64	51	43	37	59	48	41	35	42	36	32	36	31	28	31	27	24	21
7	59	46	38	33	54	43	36	31	38	32	28	33	28	25	28	24	22	19
8	55	42	34	29	51	39	32	27	35	29	25	30	25	22	26	22	19	17
9	51	38	31	26	47	36	29	24	32	26	22	27	23	20	24	20	17	15
10	47	35	28	23	44	33	26	22	29	24	20	25	21	18	22	18	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13964	13964	13964
5°	14069	13978	13926
10°	14035	13969	13930
15°	13961	13961	13947
20°	13869	13911	13911
25°	13738	13838	13795
30°	13571	13736	13676
35°	13369	13574	13480
40°	13148	13334	13199
45°	12910	13001	12800
50°	12572	12572	12370
55°	12172	12014	11834
60°	11584	11352	11171
65°	10708	10494	10402
70°	9374	9450	9412
75°	7543	8341	8391
80°	5361	7072	7146
85°	3260	5939	5939



TEST NUMBER: P561547

CATALOG NUMBER: SQ4-PC3-075U-100D-92765-1D-UNV-STD-W-4 (4500K)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	143.2	1.9
10°-20°	411.0	5.5
20°-30°	622.5	8.3
30°-40°	746.3	9.9
40°-50°	760.9	10.1
50°-60°	664.2	8.8
60°-70°	475.5	6.3
70°-80°	244.9	3.3
80°-90°	61.9	0.8
90°-100°	248.0	3.3
100°-110°	705.7	9.4
110°-120°	676.1	9.0
120°-130°	535.1	7.1
130°-140°	429.5	5.7
140°-150°	336.2	4.5
150°-160°	246.0	3.3
160°-170°	152.4	2.0
170°-180°	51.7	0.7
0°-30°	1176.7	15.7
0°-40°	1923.0	25.6
0°-60°	3348.2	44.6
0°-90°	4130.6	55.0
90°-120°	1629.8	21.7
90°-150°	2930.6	39.0
90°-180°	3381.0	45.0
0°-180°	7511.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1514	1514	1514	1514	1514	
5°	1519	1504	1509	1505	1504	144
15°	1462	1449	1462	1462	1460	412
25°	1350	1340	1359	1355	1355	621
35°	1187	1184	1205	1197	1197	742
45°	989	987	996	984	981	762
55°	757	747	747	736	736	675
65°	490	480	481	476	476	485
75°	212	221	234	235	235	229
85°	31	47	56	57	56	42
90°	0	0	0	0	0	2
95°	27	107	480	166	102	31
105°	110	166	719	1270	1208	116
115°	204	246	545	1155	1356	201
125°	288	319	520	864	1033	257
135°	352	381	514	730	825	271
145°	415	436	518	631	688	259
155°	474	485	531	571	594	219
165°	524	526	537	549	557	147
175°	548	545	543	540	536	52
180°	544	544	544	544	544	

TEST NUMBER: P561547

CATALOG NUMBER: SQ4-PC3-075U-100D-92765-1D-UNV-STD-W-4 (4500K)

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1513.5	1513.5	1513.5	1513.5	1513.5
2.5°	1522.5	1509.3	1513.5	1510.0	1504.5
5°	1519.1	1504.0	1509.3	1505.0	1503.7
7.5°	1508.2	1493.1	1500.0	1497.2	1495.8
10°	1498.1	1483.0	1491.1	1488.2	1486.9
12.5°	1484.6	1470.6	1479.9	1477.0	1476.8
15°	1461.6	1449.3	1461.6	1461.6	1460.2
17.5°	1432.8	1421.5	1434.7	1435.6	1434.7
20°	1412.6	1400.3	1416.8	1415.4	1416.8
22.5°	1387.9	1377.8	1395.5	1391.9	1393.2
25°	1349.5	1339.9	1359.3	1355.1	1355.1
27.5°	1304.1	1297.3	1318.4	1313.9	1313.9
30°	1273.9	1267.0	1289.3	1283.7	1283.7
32.5°	1240.2	1235.6	1256.8	1250.0	1250.0
35°	1187.0	1184.2	1205.2	1196.8	1196.8
37.5°	1132.0	1129.6	1148.6	1138.4	1135.1
40°	1091.7	1090.3	1107.1	1095.9	1095.9
42.5°	1051.3	1049.9	1064.5	1051.0	1051.0
45°	989.4	986.6	996.4	983.7	981.0
47.5°	921.8	919.1	925.2	911.4	910.1
50°	875.9	873.1	875.9	863.2	861.8
52.5°	828.8	823.8	824.3	811.7	811.4
55°	756.7	747.2	746.9	735.7	735.7
57.5°	680.5	667.9	669.0	659.5	658.1
60°	627.8	614.1	615.2	606.8	605.4
62.5°	576.2	560.4	563.6	554.1	553.8
65°	490.5	479.5	480.7	476.5	476.5
67.5°	408.1	397.9	405.3	401.9	401.6
70°	347.5	340.7	350.3	350.3	348.9
72.5°	291.5	291.2	303.3	303.3	304.1
75°	211.6	221.2	234.0	235.4	235.4
77.5°	141.3	158.2	172.4	172.9	172.6
80°	100.9	120.1	133.1	135.9	134.5
82.5°	68.4	88.7	99.5	102.3	100.9
85°	30.8	47.3	56.1	57.4	56.1
87.5°	9.0	18.8	22.4	22.4	20.2
90°	0.0	0.0	0.0	0.0	0.0
92.5°	8.3	43.9	101.8	29.6	22.3
95°	26.9	106.8	480.1	166.2	102.4
97.5°	49.5	125.1	739.4	529.1	362.6
100°	65.2	136.0	795.7	806.0	620.8
102.5°	82.6	147.7	783.3	1031.7	870.0
105°	109.7	166.3	719.1	1270.2	1207.5
107.5°	137.2	188.0	644.2	1337.5	1393.4
110°	156.2	203.8	601.2	1311.8	1437.2

TEST NUMBER: P561547

CATALOG NUMBER: SQ4-PC3-075U-100D-92765-1D-UNV-STD-W-4 (4500K)

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	174.5	219.6	572.2	1250.9	1429.8
115°	203.8	246.3	545.3	1155.2	1356.5
117.5°	229.7	269.6	529.4	1050.5	1263.8
120°	250.4	283.8	527.7	990.7	1195.1
122.5°	267.0	300.3	523.6	938.3	1128.1
125°	287.7	319.0	520.5	863.7	1032.7
127.5°	310.2	339.5	518.8	819.1	958.4
130°	321.8	351.1	516.3	788.1	909.5
132.5°	334.2	362.7	516.3	763.9	875.6
135°	351.8	381.1	514.3	729.6	824.7
137.5°	368.4	396.9	514.0	700.5	782.7
140°	380.8	410.1	513.2	676.4	755.3
142.5°	394.8	419.3	515.7	657.2	728.0
145°	414.9	436.2	518.4	631.4	688.1
147.5°	432.1	452.7	522.9	605.4	654.4
150°	447.0	461.2	524.6	596.8	631.2
152.5°	458.6	473.6	526.3	585.1	617.1
155°	473.9	485.0	530.8	570.7	593.9
157.5°	492.9	499.6	531.8	564.1	580.7
160°	502.9	507.9	536.0	559.1	573.2
162.5°	508.7	514.5	536.8	554.9	565.8
165°	523.6	525.6	537.0	548.6	556.7
167.5°	533.7	531.9	541.8	547.0	550.3
170°	537.0	536.0	540.1	541.3	545.3
172.5°	544.5	541.0	542.6	539.6	542.8
175°	548.4	545.4	543.2	540.0	536.0
177.5°	550.1	545.2	542.6	539.3	540.1
180°	544.3	544.3	544.3	544.3	544.3

(END OF REPORT)