

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P561569

Luminaire Tested: **SQ4-PC3-0U-050D-92765-1D-UNV-STD-W-4 (2700K)**

Issue Date: 7/30/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P561569  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-289-1)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/30/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PC3-0U-050D-92765-1D-UNV-STD-W-4 (2700K)  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS  
DOWNLIGHT 500 LUMENS PER FOOT  
DIRECT ONLY  
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 2700K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1940.0 lumens  
Efficiency: N/A  
Efficacy: 94.2 lumens/watt  
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37  
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')  
CIE Type: Direct


Input Watts (W): 20.6  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P561569

CATALOG NUMBER: SQ4-PC3-0U-050D-92765-1D-UNV-STD-W-4 (2700K)

### Luminous Intensity Polar Plot





TEST NUMBER: P561569

CATALOG NUMBER: SQ4-PC3-0U-050D-92765-1D-UNV-STD-W-4 (2700K)

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	109	105	100	97	106	102	98	95	98	95	92	94	92	89	91	88	87	85
2	99	91	85	79	97	90	83	78	86	81	76	83	78	75	80	76	73	71
3	91	80	72	66	88	79	71	65	76	70	64	73	68	63	71	66	62	60
4	83	71	63	56	81	70	62	56	68	61	55	65	59	54	63	58	53	51
5	77	64	55	48	74	63	54	48	61	53	48	59	52	47	57	51	47	44
6	71	58	49	42	69	57	48	42	55	47	42	53	46	41	52	46	41	39
7	66	52	43	37	64	51	43	37	50	42	37	48	42	37	47	41	36	34
8	61	48	39	33	60	47	39	33	46	38	33	44	38	33	43	37	33	31
9	57	44	36	30	56	43	35	30	42	35	30	41	34	30	40	34	29	28
10	54	40	32	27	52	40	32	27	39	32	27	38	31	27	37	31	27	25

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	6558	6558	6558
5°	6608	6565	6540
10°	6592	6561	6542
15°	6557	6557	6551
20°	6513	6533	6533
25°	6452	6499	6479
30°	6374	6451	6423
35°	6279	6375	6331
40°	6175	6263	6199
45°	6063	6106	6011
50°	5905	5905	5810
55°	5717	5643	5558
60°	5442	5331	5246
65°	5030	4929	4886
70°	4402	4437	4421
75°	3543	3918	3943
80°	2518	3321	3358
85°	1535	2784	2784



TEST NUMBER: P561569

CATALOG NUMBER: SQ4-PC3-OU-050D-92765-1D-UNV-STD-W-4 (2700K)

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	67.3	3.5
10°-20°	193.0	10.0
20°-30°	292.3	15.1
30°-40°	350.5	18.1
40°-50°	357.4	18.4
50°-60°	312.0	16.1
60°-70°	223.3	11.5
70°-80°	115.0	5.9
80°-90°	29.1	1.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	552.7	28.5
0°-40°	903.2	46.6
0°-60°	1572.5	81.1
0°-90°	1940.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1940.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	711	711	711	711	711	
5°	714	706	709	707	706	68
15°	686	681	686	686	686	194
25°	634	629	638	636	636	292
35°	558	556	566	562	562	349
45°	465	463	468	462	461	358
55°	355	351	351	346	346	317
65°	230	225	226	224	224	228
75°	99	104	110	111	111	107
85°	14	22	26	27	26	20
90°	0	0	0	0	0	



TEST NUMBER: P561569

CATALOG NUMBER: SQ4-PC3-OU-050D-92765-1D-UNV-STD-W-4 (2700K)

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	710.8	710.8	710.8	710.8	710.8
2.5°	715.0	708.9	710.8	709.2	706.6
5°	713.5	706.4	708.8	706.9	706.2
7.5°	708.3	701.2	704.5	703.2	702.5
10°	703.6	696.5	700.3	699.0	698.3
12.5°	697.3	690.7	695.0	693.7	693.6
15°	686.5	680.7	686.5	686.5	685.8
17.5°	672.9	667.6	673.8	674.2	673.8
20°	663.4	657.6	665.4	664.8	665.4
22.5°	651.8	647.1	655.4	653.7	654.3
25°	633.8	629.3	638.4	636.4	636.4
27.5°	612.5	609.3	619.2	617.1	617.1
30°	598.3	595.1	605.5	602.9	602.9
32.5°	582.5	580.3	590.2	587.1	587.1
35°	557.5	556.2	566.0	562.1	562.1
37.5°	531.7	530.5	539.4	534.7	533.1
40°	512.7	512.1	520.0	514.7	514.7
42.5°	493.8	493.1	499.9	493.6	493.6
45°	464.7	463.4	468.0	462.0	460.7
47.5°	432.9	431.7	434.5	428.1	427.4
50°	411.4	410.1	411.4	405.4	404.8
52.5°	389.2	386.9	387.1	381.2	381.1
55°	355.4	350.9	350.8	345.5	345.5
57.5°	319.6	313.7	314.2	309.7	309.1
60°	294.9	288.4	288.9	285.0	284.3
62.5°	270.6	263.2	264.7	260.2	260.1
65°	230.4	225.2	225.8	223.8	223.8
67.5°	191.7	186.9	190.3	188.8	188.6
70°	163.2	160.0	164.5	164.5	163.9
72.5°	136.9	136.8	142.4	142.4	142.8
75°	99.4	103.9	109.9	110.6	110.6
77.5°	66.3	74.3	81.0	81.2	81.1
80°	47.4	56.4	62.5	63.8	63.2
82.5°	32.1	41.6	46.7	48.0	47.4
85°	14.5	22.2	26.3	27.0	26.3
87.5°	4.2	8.8	10.5	10.5	9.5
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)