

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: CORELITE

Report Number: P561613

Luminaire Tested: **SQ4-PC3-0U-125D-92765-1D-UNV-STD-W-4 (5000K)**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P561613
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-289-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PC3-0U-125D-92765-1D-UNV-STD-W-4 (5000K)
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS
DOWNLIGHT 1250 LUMENS PER FOOT
DIRECT ONLY
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5287.5 lumens
Efficiency: N/A
Efficacy: 94.9 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 55.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P561613
CATALOG NUMBER: SQ4-PC3-0U-125D-92765-1D-UNV-STD-W-4 (5000K)

Luminous Intensity Polar Plot





TEST NUMBER: P561613

CATALOG NUMBER: SQ4-PC3-0U-125D-92765-1D-UNV-STD-W-4 (5000K)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	109	105	100	97	106	102	98	95	98	95	92	94	92	89	91	88	87	85
2	99	91	85	79	97	90	83	78	86	81	76	83	78	75	80	76	73	71
3	91	80	72	66	88	79	71	65	76	70	64	73	68	63	71	66	62	60
4	83	71	63	56	81	70	62	56	68	61	55	65	59	54	63	58	53	51
5	77	64	55	48	74	63	54	48	61	53	48	59	52	47	57	51	47	44
6	71	58	49	42	69	57	48	42	55	47	42	53	46	41	52	46	41	39
7	66	52	43	37	64	51	43	37	50	42	37	48	42	37	47	41	36	34
8	61	48	39	33	60	47	39	33	46	38	33	44	38	33	43	37	33	31
9	57	44	36	30	56	43	35	30	42	35	30	41	34	30	40	34	29	28
10	54	40	32	27	52	40	32	27	39	32	27	38	31	27	37	31	27	25

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17875	17875	17875
5°	18010	17893	17826
10°	17966	17882	17831
15°	17871	17871	17854
20°	17753	17807	17807
25°	17586	17714	17659
30°	17372	17583	17506
35°	17113	17376	17255
40°	16830	17069	16895
45°	16525	16641	16384
50°	16093	16093	15835
55°	15582	15379	15149
60°	14830	14531	14301
65°	13708	13433	13315
70°	12001	12099	12050
75°	9657	10680	10744
80°	6865	9054	9149
85°	4181	7601	7601



TEST NUMBER: P561613

CATALOG NUMBER: SQ4-PC3-OU-125D-92765-1D-UNV-STD-W-4 (5000K)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	183.4	3.5
10°-20°	526.2	10.0
20°-30°	796.8	15.1
30°-40°	955.3	18.1
40°-50°	974.0	18.4
50°-60°	850.3	16.1
60°-70°	608.7	11.5
70°-80°	313.5	5.9
80°-90°	79.3	1.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1506.3	28.5
0°-40°	2461.6	46.6
0°-60°	4286.0	81.1
0°-90°	5287.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5287.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1937	1937	1937	1937	1937	
5°	1945	1925	1932	1927	1925	185
15°	1871	1855	1871	1871	1869	528
25°	1728	1715	1740	1735	1735	795
35°	1519	1516	1543	1532	1532	950
45°	1266	1263	1275	1259	1256	975
55°	969	956	956	942	942	864
65°	628	614	615	610	610	621
75°	271	283	300	301	301	293
85°	40	60	72	74	72	55
90°	0	0	0	0	0	



TEST NUMBER: P561613

CATALOG NUMBER: SQ4-PC3-0U-125D-92765-1D-UNV-STD-W-4 (5000K)

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1937.4	1937.4	1937.4	1937.4	1937.4
2.5°	1948.9	1932.0	1937.4	1932.9	1925.9
5°	1944.6	1925.3	1932.0	1926.6	1924.8
7.5°	1930.6	1911.3	1920.2	1916.5	1914.8
10°	1917.7	1898.4	1908.7	1905.1	1903.3
12.5°	1900.4	1882.5	1894.3	1890.7	1890.4
15°	1871.0	1855.2	1871.0	1871.0	1869.2
17.5°	1834.1	1819.7	1836.6	1837.6	1836.6
20°	1808.2	1792.4	1813.6	1811.9	1813.6
22.5°	1776.7	1763.7	1786.3	1781.7	1783.5
25°	1727.5	1715.2	1740.1	1734.7	1734.7
27.5°	1669.4	1660.6	1687.7	1681.9	1681.9
30°	1630.6	1621.9	1650.4	1643.2	1643.2
32.5°	1587.6	1581.6	1608.7	1600.1	1600.1
35°	1519.4	1515.9	1542.7	1532.0	1532.0
37.5°	1449.1	1445.9	1470.3	1457.2	1453.0
40°	1397.4	1395.7	1417.2	1402.8	1402.8
42.5°	1345.8	1344.0	1362.6	1345.4	1345.4
45°	1266.5	1263.0	1275.4	1259.2	1255.7
47.5°	1180.0	1176.5	1184.3	1166.7	1164.9
50°	1121.2	1117.7	1121.2	1105.0	1103.2
52.5°	1060.9	1054.6	1055.2	1039.0	1038.7
55°	968.7	956.4	956.1	941.8	941.8
57.5°	871.1	855.0	856.4	844.2	842.4
60°	803.7	786.1	787.5	776.7	775.0
62.5°	737.6	717.3	721.5	709.3	708.9
65°	627.9	613.8	615.3	609.9	609.9
67.5°	522.4	509.4	518.8	514.5	514.1
70°	444.9	436.1	448.5	448.4	446.7
72.5°	373.1	372.8	388.2	388.2	389.3
75°	270.9	283.2	299.6	301.4	301.4
77.5°	180.8	202.6	220.6	221.4	221.0
80°	129.2	153.7	170.4	174.0	172.2
82.5°	87.5	113.5	127.4	130.9	129.2
85°	39.5	60.5	71.8	73.5	71.8
87.5°	11.5	24.1	28.7	28.6	25.8
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)