

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P938328

Luminaire Tested: SQ4-FB-150U-075D-92765-1D-UNV-STD-W-12-4000K

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P938328
REPORT IS A COMBINATION OF REPORTS P933622 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-150U-075D-92765-1D-UNV-STD-W-12-4000K
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 23015.6 lumens
Efficiency: N/A
Efficacy: 120.6 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 12' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 190.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P938328
CATALOG NUMBER: SQ4-FB-150U-075D-92765-1D-UNV-STD-W-12-4000K

Luminous Intensity Polar Plot





TEST NUMBER: P938328

CATALOG NUMBER: SQ4-FB-150U-075D-92765-1D-UNV-STD-W-12-4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	102	102	102	102	91	91	91	91	71	71	71	53	53	53	36	36	36	29			29
1	93	88	84	81	83	79	76	73	62	60	58	46	45	43	32	31	30	23			23
2	84	77	71	66	75	69	64	59	54	50	47	40	38	36	27	26	25	19			19
3	76	67	60	54	68	60	54	49	47	43	39	35	32	30	24	22	21	16			16
4	70	59	51	45	62	53	46	41	42	37	33	31	28	25	21	19	17	13			13
5	64	52	44	38	57	47	40	35	37	32	28	28	24	21	19	17	15	11			11
6	58	47	39	33	52	42	35	30	33	28	24	25	21	18	17	15	13	10			10
7	54	42	34	28	48	38	31	26	30	25	21	22	19	16	15	13	11	8			8
8	50	38	30	25	44	34	27	23	27	22	18	20	17	14	14	12	10	7			7
9	46	34	27	22	41	31	24	20	24	20	16	18	15	12	13	10	9	6			6
10	43	31	24	19	38	28	22	18	22	18	14	17	13	11	12	9	8	6			6

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2625	2625	2625
5°	2566	3035	3529
10°	2328	4425	5850
15°	1979	5783	7064
20°	1612	6703	7199
25°	1345	7016	7053
30°	1135	7062	7039
35°	1004	6947	7221
40°	875	6796	7410
45°	793	6686	7439
50°	728	6588	7315
55°	698	6444	6991
60°	715	6164	6479
65°	746	5736	5776
70°	797	5006	4879
75°	885	4085	3807
80°	975	2837	2566
85°	885	1507	1313

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 45°
 Luminance: 7439 cd/sqm



TEST NUMBER: P938328

CATALOG NUMBER: SQ4-FB-150U-075D-92765-1D-UNV-STD-W-12-4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	109.8	0.5
10°-20°	486.6	2.1
20°-30°	851.1	3.7
30°-40°	1095.6	4.8
40°-50°	1223.8	5.3
50°-60°	1172.1	5.1
60°-70°	928.9	4.0
70°-80°	546.2	2.4
80°-90°	161.4	0.7
90°-100°	1236.2	5.4
100°-110°	3250.0	14.1
110°-120°	3369.9	14.6
120°-130°	2703.1	11.7
130°-140°	2121.0	9.2
140°-150°	1627.9	7.1
150°-160°	1172.4	5.1
160°-170°	717.3	3.1
170°-180°	242.3	1.1
0°-30°	1447.5	6.3
0°-40°	2543.1	11.0
0°-60°	4938.9	21.5
0°-90°	6575.4	28.6
90°-120°	7856.1	34.1
90°-150°	14308.1	62.2
90°-180°	16440.0	71.4
0°-180°	23015.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	849	849	849	849	849	
5°	827	887	999	1130	1171	76
15°	620	1144	1927	2336	2410	172
25°	396	1296	2295	2396	2399	182
35°	267	1239	2161	2284	2374	167
45°	183	988	1910	2189	2287	141
55°	131	628	1621	1883	1935	119
65°	104	333	1204	1354	1373	103
75°	76	205	660	726	729	80
85°	27	63	164	180	183	29
90°	17	48	129	65	65	16
95°	163	640	2129	1098	747	181
105°	586	887	3593	5455	5089	621
115°	1040	1263	2878	5741	6553	1027
125°	1447	1622	2618	4424	5218	1284
135°	1724	1898	2536	3571	4049	1334
145°	2000	2128	2504	3047	3285	1253
155°	2260	2323	2504	2749	2829	1039
165°	2439	2471	2504	2602	2635	688
175°	2536	2536	2521	2553	2553	241
180°	2536	2536	2536	2536	2536	



TEST NUMBER: P938328

CATALOG NUMBER: SQ4-FB-150U-075D-92765-1D-UNV-STD-W-12-4000K

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	848.7	848.7	848.7	848.7	848.7	848.7	848.7	848.7	848.7	848.7	848.7
2.5°	848.7	848.7	854.1	856.9	862.3	865.1	870.5	876.0	892.4	895.1	900.5
5°	826.9	837.8	873.3	886.9	925.1	977.0	998.8	1034.3	1108.0	1129.9	1143.5
7.5°	794.1	818.7	906.0	927.8	1023.3	1159.9	1217.2	1293.6	1410.9	1468.2	1514.6
10°	742.3	794.1	949.7	1001.5	1157.1	1364.5	1471.0	1577.4	1754.8	1833.9	1863.9
12.5°	685.0	769.6	996.1	1067.1	1290.9	1593.8	1722.0	1839.4	2041.3	2147.7	2164.1
15°	619.5	734.1	1039.8	1143.5	1432.8	1784.8	1926.7	2071.3	2259.6	2336.0	2355.1
17.5°	562.2	706.8	1080.7	1189.9	1541.9	1956.7	2101.4	2221.4	2374.2	2426.1	2439.7
20°	491.2	663.1	1108.0	1249.9	1656.5	2082.3	2221.4	2314.2	2417.9	2450.7	2456.1
22.5°	439.4	616.7	1124.4	1271.8	1732.9	2158.7	2276.0	2349.7	2420.6	2431.6	2434.3
25°	395.7	564.9	1121.7	1296.3	1798.4	2205.1	2295.1	2349.7	2390.6	2396.1	2396.1
27.5°	354.8	507.6	1110.8	1301.8	1847.6	2216.0	2286.9	2325.1	2344.2	2355.1	2355.1
30°	319.3	453.0	1083.5	1290.9	1869.4	2205.1	2262.4	2281.5	2300.6	2316.9	2325.1
32.5°	292.0	401.1	1042.5	1269.0	1872.1	2177.8	2218.7	2229.6	2256.9	2295.1	2308.7
35°	267.4	349.3	996.1	1239.0	1855.8	2134.1	2161.4	2172.3	2226.9	2284.2	2303.3
37.5°	242.9	311.1	936.0	1187.2	1831.2	2082.3	2101.4	2120.5	2205.1	2273.3	2295.1
40°	218.3	278.3	865.1	1129.9	1793.0	2019.5	2035.9	2065.9	2177.8	2256.9	2278.7
42.5°	199.2	251.1	788.7	1069.8	1743.9	1948.5	1973.1	2016.8	2145.0	2229.6	2254.2
45°	182.8	223.8	706.8	987.9	1681.1	1874.9	1910.3	1970.4	2106.8	2188.7	2210.5
47.5°	166.5	204.7	622.2	903.3	1612.9	1801.2	1847.6	1915.8	2055.0	2134.1	2153.2
50°	152.8	185.6	537.6	813.2	1539.2	1722.0	1776.6	1847.6	1989.5	2063.1	2087.7
52.5°	141.9	169.2	458.5	723.2	1454.6	1640.2	1702.9	1776.6	1910.3	1981.3	1997.7
55°	131.0	155.5	390.2	627.6	1367.3	1552.8	1621.1	1692.0	1823.0	1883.0	1894.0
57.5°	125.5	144.6	332.9	537.6	1274.5	1454.6	1531.0	1596.5	1719.3	1765.7	1776.6
60°	117.3	136.4	289.3	461.2	1173.5	1361.8	1427.3	1492.8	1596.5	1634.7	1642.9
62.5°	109.2	131.0	256.5	387.5	1069.8	1252.7	1318.2	1378.2	1465.5	1492.8	1503.7
65°	103.7	125.5	232.0	332.9	963.3	1138.0	1203.5	1255.4	1326.3	1353.6	1359.1
67.5°	98.2	120.1	212.9	286.5	856.9	1023.3	1072.6	1121.7	1176.3	1203.5	1206.3
70°	90.1	114.6	196.5	253.8	747.7	892.4	933.3	985.1	1028.8	1042.5	1050.7
72.5°	84.6	106.4	185.6	229.2	635.8	766.8	805.0	835.0	873.3	886.9	886.9
75°	76.4	95.5	174.7	204.7	521.2	627.6	660.4	690.4	720.4	725.9	717.7
77.5°	68.2	84.6	150.1	171.9	406.6	496.7	524.0	540.3	564.9	570.3	573.1
80°	57.3	73.7	117.3	133.7	294.7	365.7	384.8	398.4	420.3	420.3	425.7
82.5°	43.7	57.3	84.6	95.5	199.2	251.1	267.4	275.6	289.3	289.3	289.3
85°	27.3	35.5	54.6	62.8	120.1	152.8	163.7	166.5	177.4	180.1	180.1
87.5°	13.6	19.1	35.5	38.2	62.8	79.1	79.1	84.6	84.6	81.9	79.1
90°	17.0	30.7	44.3	47.7	74.9	111.2	129.4	115.0	86.2	64.7	64.7
92.5°	68.0	183.7	299.5	328.5	461.8	639.6	728.4	638.4	458.4	323.4	310.6
95°	163.4	375.1	587.0	639.9	1136.4	1798.4	2129.3	1900.0	1441.7	1097.8	1058.9
97.5°	282.5	469.4	656.2	703.0	1530.7	2634.4	3186.2	3041.4	2751.7	2534.3	2460.2
100°	374.4	543.9	713.3	755.7	1674.3	2898.9	3511.3	3521.8	3543.0	3559.0	3470.6
102.5°	452.7	610.8	768.9	808.5	1740.0	2982.2	3603.3	3787.8	4157.0	4433.8	4358.2
105°	585.5	719.4	853.3	886.8	1788.9	2991.6	3593.0	4006.8	4834.4	5455.0	5414.3
107.5°	721.7	846.5	971.3	1002.5	1797.9	2858.4	3388.8	3965.9	5120.3	5986.0	5995.9
110°	813.6	926.3	1039.0	1067.2	1784.3	2740.5	3218.6	3863.9	5154.4	6122.2	6164.6



TEST NUMBER: P938328

CATALOG NUMBER: SQ4-FB-150U-075D-92765-1D-UNV-STD-W-12-4000K

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	903.8	1011.2	1118.7	1145.5	1784.9	2637.4	3063.7	3724.1	5044.8	6035.4	6100.5
115°	1040.0	1139.0	1238.2	1262.9	1801.4	2519.2	2878.2	3514.4	4786.7	5741.0	5831.2
117.5°	1174.4	1264.4	1354.4	1376.9	1834.7	2445.2	2750.5	3324.6	4473.0	5334.2	5434.3
120°	1252.7	1337.4	1422.1	1443.3	1862.0	2420.3	2699.4	3224.0	4273.2	5060.1	5157.4
122.5°	1329.3	1414.8	1500.3	1521.6	1901.2	2407.3	2660.3	3132.7	4077.5	4786.1	4882.0
125°	1446.8	1524.6	1602.6	1622.1	1954.0	2396.5	2617.8	3019.1	3821.7	4423.6	4511.9
127.5°	1542.0	1620.7	1699.4	1719.0	2006.7	2390.3	2582.0	2926.6	3615.7	4132.6	4207.1
130°	1593.1	1677.8	1762.5	1783.7	2045.2	2394.0	2568.4	2875.1	3488.6	3948.7	4017.6
132.5°	1645.9	1730.6	1815.3	1836.5	2076.4	2396.4	2556.4	2831.1	3380.3	3792.2	3853.9
135°	1724.1	1801.3	1878.5	1897.8	2110.5	2394.3	2536.1	2766.0	3225.9	3570.9	3624.0
137.5°	1804.2	1880.6	1957.0	1976.1	2161.6	2408.9	2532.6	2727.0	3115.9	3407.5	3451.0
140°	1870.6	1940.9	2011.3	2028.9	2192.8	2411.4	2520.7	2688.6	3024.5	3276.4	3317.1
142.5°	1921.6	1986.6	2051.7	2068.0	2218.9	2420.1	2520.7	2668.2	2963.2	3184.5	3219.6
145°	1999.9	2056.7	2113.4	2127.5	2252.9	2420.1	2503.7	2624.3	2865.6	3046.6	3073.1
147.5°	2078.2	2133.4	2188.6	2202.4	2302.8	2436.7	2503.7	2598.7	2788.5	2930.9	2952.9
150°	2129.3	2179.2	2229.2	2241.6	2328.9	2445.5	2503.7	2583.9	2744.3	2864.5	2882.3
152.5°	2182.0	2219.9	2257.6	2267.1	2346.0	2451.1	2503.7	2572.2	2709.1	2811.8	2825.2
155°	2260.4	2288.4	2316.3	2323.3	2383.4	2463.6	2503.7	2558.2	2667.1	2748.8	2757.7
157.5°	2318.2	2345.4	2372.6	2379.4	2420.8	2476.0	2503.7	2546.1	2630.8	2694.3	2700.6
160°	2357.3	2378.5	2399.7	2405.0	2437.9	2481.8	2503.7	2540.0	2612.6	2667.1	2670.7
162.5°	2396.4	2412.4	2428.2	2432.2	2456.0	2487.8	2503.7	2534.3	2595.6	2641.6	2645.0
165°	2439.0	2453.4	2467.8	2471.4	2482.1	2496.5	2503.7	2525.6	2569.5	2602.4	2606.0
167.5°	2478.2	2485.0	2491.8	2493.5	2502.6	2514.7	2520.7	2535.1	2563.8	2585.4	2586.9
170°	2503.7	2510.5	2517.3	2519.1	2519.6	2520.3	2520.7	2535.1	2563.8	2585.4	2585.4
172.5°	2517.3	2518.8	2520.3	2520.7	2520.7	2520.7	2520.7	2532.1	2554.8	2571.8	2570.5
175°	2536.1	2536.1	2536.1	2536.1	2531.0	2524.2	2520.7	2527.9	2542.3	2553.1	2553.1
177.5°	2536.1	2536.1	2536.1	2536.1	2532.1	2526.8	2524.2	2529.8	2541.2	2549.6	2548.1
180°	2536.1	2536.1	2536.1	2536.1	2536.1	2536.1	2536.1	2536.1	2536.1	2536.1	2536.1



TEST NUMBER: P938328

CATALOG NUMBER: SQ4-FB-150U-075D-92765-1D-UNV-STD-W-12-4000K

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	848.7	848.7
2.5°	906.0	900.5
5°	1165.3	1170.8
7.5°	1569.2	1566.5
10°	1951.3	1975.8
12.5°	2229.6	2235.1
15°	2398.8	2409.7
17.5°	2464.3	2467.0
20°	2467.0	2461.6
22.5°	2437.0	2431.6
25°	2401.5	2398.8
27.5°	2368.8	2371.5
30°	2355.1	2363.3
32.5°	2355.1	2368.8
35°	2360.6	2374.2
37.5°	2357.9	2374.2
40°	2347.0	2366.1
42.5°	2316.9	2330.6
45°	2270.5	2286.9
47.5°	2210.5	2221.4
50°	2134.1	2145.0
52.5°	2038.6	2041.3
55°	1924.0	1934.9
57.5°	1801.2	1803.9
60°	1664.7	1672.9
62.5°	1520.1	1520.1
65°	1367.3	1372.7
67.5°	1209.0	1222.6
70°	1048.0	1050.7
72.5°	889.6	889.6
75°	725.9	728.6
77.5°	570.3	570.3
80°	423.0	425.7
82.5°	292.0	297.5
85°	182.8	182.8
87.5°	84.6	76.4
90°	64.7	64.7
92.5°	259.1	207.7
95°	903.0	747.2
97.5°	2163.7	1867.1
100°	3117.4	2764.1
102.5°	4055.6	3753.0
105°	5251.8	5089.1
107.5°	6035.3	6074.6
110°	6334.1	6503.5



TEST NUMBER: P938328

CATALOG NUMBER: SQ4-FB-150U-075D-92765-1D-UNV-STD-W-12-4000K

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	6360.7	6621.0
115°	6192.0	6552.8
117.5°	5834.4	6234.6
120°	5546.1	5935.0
122.5°	5265.6	5649.1
125°	4865.2	5218.5
127.5°	4505.2	4803.2
130°	4292.9	4568.3
132.5°	4100.4	4347.0
135°	3836.6	4049.2
137.5°	3625.0	3798.9
140°	3479.7	3642.4
142.5°	3359.5	3499.4
145°	3179.1	3285.0
147.5°	3040.6	3128.3
150°	2953.4	3024.5
152.5°	2878.9	2932.6
155°	2793.2	2828.8
157.5°	2725.5	2750.5
160°	2685.1	2699.4
162.5°	2658.6	2672.2
165°	2620.4	2634.8
167.5°	2592.9	2599.0
170°	2585.4	2585.4
172.5°	2565.2	2559.9
175°	2553.1	2553.1
177.5°	2542.1	2536.1
180°	2536.1	2536.1



TEST NUMBER: P938328
 CATALOG NUMBER: SQ4-FB-150U-075D-92765-1D-UNV-STD-W-12-4000K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	1.97	2.69	3.09	3.80	5.35	15.17	15.88	16.28	17.00	18.54
	3H	2.67	3.31	3.79	4.43	5.99	17.00	17.64	18.12	18.76	20.33
	4H	2.96	3.57	4.09	4.69	6.26	17.64	18.25	18.78	19.37	20.94
	6H	3.20	3.76	4.34	4.89	6.47	18.07	18.63	19.21	19.76	21.33
	8H	3.26	3.80	4.41	4.94	6.51	18.19	18.72	19.33	19.86	21.43
	12H	3.28	3.79	4.43	4.92	6.51	18.25	18.76	19.40	19.90	21.49
4H	2H	9.18	9.79	10.32	10.91	12.48	15.42	16.03	16.56	17.16	18.72
	3H	10.73	11.24	11.88	12.39	13.97	17.46	17.97	18.61	19.12	20.70
	4H	10.82	11.29	11.97	12.43	14.03	18.22	18.69	19.37	19.83	21.43
	6H	10.82	11.23	11.98	12.39	13.97	18.76	19.16	19.91	20.32	21.91
	8H	10.80	11.17	11.95	12.32	13.93	18.92	19.29	20.07	20.45	22.05
	12H	10.74	11.09	11.92	12.25	13.86	19.01	19.35	20.18	20.51	22.12
8H	4H	12.26	12.63	13.41	13.78	15.39	18.27	18.65	19.43	19.80	21.40
	6H	12.49	12.80	13.67	14.00	15.60	18.90	19.21	20.07	20.40	22.00
	8H	12.51	12.78	13.69	13.95	15.57	19.12	19.39	20.30	20.56	22.18
	12H	12.47	12.71	13.65	13.88	15.53	19.26	19.50	20.44	20.67	22.32
12H	4H	12.39	12.73	13.57	13.90	15.51	18.22	18.56	19.39	19.72	21.33
	6H	12.75	13.02	13.93	14.19	15.82	18.88	19.15	20.06	20.32	21.95
	8H	12.81	13.05	14.00	14.22	15.88	19.10	19.34	20.29	20.51	22.17