

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: CORELITE

Report Number: P561662

Luminaire Tested: **SQ4-PC3-100U-125D-92765-1D-UNV-STD-W-4 (3500K)**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P561662
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2106-289-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PC3-100U-125D-92765-1D-UNV-STD-W-4 (3500K)
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 1000 LUMENS PER FOOT
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9426.7 lumens
Efficiency: N/A
Efficacy: 106.9 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 88.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P561662
CATALOG NUMBER: SQ4-PC3-100U-125D-92765-1D-UNV-STD-W-4 (3500K)

Luminous Intensity Polar Plot





TEST NUMBER: P561662

CATALOG NUMBER: SQ4-PC3-100U-125D-92765-1D-UNV-STD-W-4 (3500K)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	59	59	59	54
1	99	94	90	87	91	88	84	81	75	73	70	63	62	60	53	51	50	45
2	90	82	76	71	83	77	71	67	66	62	58	56	53	50	46	44	42	38
3	82	72	65	59	76	67	61	56	58	53	49	49	45	42	41	38	36	32
4	75	64	56	50	69	60	53	47	51	46	42	44	40	36	37	34	31	28
5	69	57	49	43	63	53	46	40	46	40	36	39	35	31	33	30	27	24
6	63	51	43	37	59	48	40	35	41	36	31	35	31	27	30	26	24	21
7	59	46	38	33	54	43	36	31	38	32	28	32	28	24	27	24	21	18
8	54	42	34	29	50	39	32	27	34	28	24	29	25	22	25	21	19	16
9	51	38	31	26	47	36	29	24	31	26	22	27	23	19	23	20	17	15
10	47	35	28	23	44	33	26	22	29	23	20	25	21	18	21	18	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17086	17086	17086
5°	17214	17103	17040
10°	17173	17092	17044
15°	17082	17082	17066
20°	16970	17021	17021
25°	16810	16932	16879
30°	16606	16806	16733
35°	16359	16609	16494
40°	16088	16315	16150
45°	15796	15908	15661
50°	15383	15383	15136
55°	14893	14700	14480
60°	14175	13891	13670
65°	13101	12839	12728
70°	11470	11564	11519
75°	9229	10209	10270
80°	6562	8655	8745
85°	3991	7262	7262



TEST NUMBER: P561662

CATALOG NUMBER: SQ4-PC3-100U-125D-92765-1D-UNV-STD-W-4 (3500K)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	175.3	1.9
10°-20°	502.9	5.3
20°-30°	761.6	8.1
30°-40°	913.1	9.7
40°-50°	931.1	9.9
50°-60°	812.8	8.6
60°-70°	581.9	6.2
70°-80°	299.7	3.2
80°-90°	75.8	0.8
90°-100°	320.7	3.4
100°-110°	912.7	9.7
110°-120°	874.4	9.3
120°-130°	692.1	7.3
130°-140°	555.5	5.9
140°-150°	434.9	4.6
150°-160°	318.2	3.4
160°-170°	197.1	2.1
170°-180°	66.9	0.7
0°-30°	1439.9	15.3
0°-40°	2353.0	25.0
0°-60°	4096.8	43.5
0°-90°	5054.1	53.6
90°-120°	2107.9	22.4
90°-150°	3790.4	40.2
90°-180°	4373.0	46.4
0°-180°	9426.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1852	1852	1852	1852	1852	
5°	1859	1840	1847	1842	1840	176
15°	1788	1773	1788	1788	1787	504
25°	1651	1640	1663	1658	1658	760
35°	1452	1449	1475	1464	1464	908
45°	1211	1207	1219	1204	1200	932
55°	926	914	914	900	900	825
65°	600	587	588	583	583	594
75°	259	271	286	288	288	280
85°	38	58	69	70	69	51
90°	0	0	0	0	0	3
95°	35	138	621	215	132	40
105°	142	215	930	1643	1562	150
115°	264	319	705	1494	1754	260
125°	372	413	673	1117	1336	333
135°	455	493	665	944	1067	351
145°	537	564	670	817	890	335
155°	613	627	686	738	768	283
165°	677	680	695	710	720	190
175°	709	705	703	698	693	67
180°	704	704	704	704	704	

TEST NUMBER: P561662

CATALOG NUMBER: SQ4-PC3-100U-125D-92765-1D-UNV-STD-W-4 (3500K)

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1851.9	1851.9	1851.9	1851.9	1851.9
2.5°	1862.9	1846.8	1851.9	1847.6	1840.9
5°	1858.7	1840.3	1846.7	1841.6	1839.9
7.5°	1845.4	1826.9	1835.4	1832.0	1830.3
10°	1833.0	1814.6	1824.4	1821.0	1819.3
12.5°	1816.6	1799.5	1810.7	1807.3	1807.0
15°	1788.4	1773.4	1788.4	1788.4	1786.7
17.5°	1753.1	1739.4	1755.5	1756.5	1755.5
20°	1728.4	1713.3	1733.6	1731.9	1733.6
22.5°	1698.2	1685.8	1707.5	1703.1	1704.8
25°	1651.3	1639.5	1663.3	1658.1	1658.1
27.5°	1595.7	1587.3	1613.2	1607.7	1607.7
30°	1558.7	1550.3	1577.5	1570.7	1570.7
32.5°	1517.5	1511.8	1537.8	1529.5	1529.5
35°	1452.4	1449.0	1474.6	1464.4	1464.4
37.5°	1385.1	1382.1	1405.4	1392.9	1388.9
40°	1335.8	1334.1	1354.6	1340.9	1340.9
42.5°	1286.4	1284.7	1302.5	1286.0	1286.0
45°	1210.6	1207.2	1219.2	1203.6	1200.3
47.5°	1127.9	1124.6	1132.1	1115.2	1113.5
50°	1071.7	1068.3	1071.7	1056.2	1054.5
52.5°	1014.1	1008.0	1008.6	993.2	992.8
55°	925.9	914.2	913.9	900.2	900.2
57.5°	832.7	817.2	818.6	806.9	805.2
60°	768.2	751.4	752.8	742.4	740.8
62.5°	705.1	685.6	689.7	678.0	677.7
65°	600.1	586.7	588.1	583.0	583.0
67.5°	499.3	486.9	495.9	491.8	491.4
70°	425.2	416.9	428.7	428.6	427.0
72.5°	356.7	356.3	371.1	371.1	372.1
75°	258.9	270.7	286.4	288.1	288.1
77.5°	172.8	193.6	210.9	211.6	211.3
80°	123.5	146.9	162.9	166.3	164.6
82.5°	83.7	108.5	121.7	125.1	123.5
85°	37.7	57.8	68.6	70.3	68.6
87.5°	11.0	23.0	27.4	27.4	24.7
90°	0.0	0.0	0.0	0.0	0.0
92.5°	10.7	56.8	131.7	38.3	28.9
95°	34.8	138.2	620.9	214.9	132.5
97.5°	64.0	161.8	956.3	684.3	468.9
100°	84.3	175.9	1029.1	1042.4	802.9
102.5°	106.8	191.1	1013.1	1334.3	1125.2
105°	141.9	215.1	930.1	1642.9	1561.7
107.5°	177.5	243.1	833.2	1729.9	1802.1
110°	202.1	263.6	777.5	1696.6	1858.8

TEST NUMBER: P561662

CATALOG NUMBER: SQ4-PC3-100U-125D-92765-1D-UNV-STD-W-4 (3500K)

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	225.6	284.0	740.1	1617.8	1849.2
115°	263.6	318.6	705.3	1494.1	1754.4
117.5°	297.1	348.6	684.6	1358.7	1634.5
120°	323.9	367.0	682.5	1281.4	1545.7
122.5°	345.3	388.4	677.2	1213.5	1459.0
125°	372.0	412.6	673.1	1117.1	1335.6
127.5°	401.2	439.2	671.0	1059.4	1239.5
130°	416.2	454.1	667.8	1019.3	1176.3
132.5°	432.3	469.2	667.8	988.0	1132.4
135°	455.0	493.0	665.1	943.6	1066.6
137.5°	476.4	513.3	664.8	906.0	1012.3
140°	492.5	530.4	663.8	874.9	976.9
142.5°	510.7	542.3	667.0	850.0	941.6
145°	536.6	564.1	670.5	816.7	889.9
147.5°	558.9	585.5	676.4	783.0	846.3
150°	578.1	596.4	678.5	771.8	816.3
152.5°	593.1	612.5	680.6	756.8	798.1
155°	612.9	627.3	686.5	738.1	768.2
157.5°	637.5	646.2	687.9	729.6	751.0
160°	650.4	656.9	693.2	723.1	741.4
162.5°	657.9	665.5	694.3	717.6	731.8
165°	677.2	679.8	694.6	709.5	720.0
167.5°	690.3	687.9	700.7	707.5	711.7
170°	694.6	693.2	698.6	700.0	705.3
172.5°	704.2	699.7	701.8	697.9	702.0
175°	709.3	705.3	702.6	698.4	693.2
177.5°	711.4	705.1	701.8	697.5	698.6
180°	703.9	703.9	703.9	703.9	703.9

(END OF REPORT)