

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: CORELITE

Report Number: P561664

Luminaire Tested: **SQ4-PC3-100U-125D-92765-1D-UNV-STD-W-4 (4500K)**

Issue Date: 7/30/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P561664  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2106-289-1)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/30/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PC3-100U-125D-92765-1D-UNV-STD-W-4 (4500K)  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS  
DOWNLIGHT 1250 LUMENS PER FOOT  
UPLIGHT 1000 LUMENS PER FOOT  
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 4500K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 9753.9 lumens  
Efficiency: N/A  
Efficacy: 110.7 lumens/watt  
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37  
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 88.1  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P561664  
CATALOG NUMBER: SQ4-PC3-100U-125D-92765-1D-UNV-STD-W-4 (4500K)

### Luminous Intensity Polar Plot





TEST NUMBER: P561664

CATALOG NUMBER: SQ4-PC3-100U-125D-92765-1D-UNV-STD-W-4 (4500K)

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20										
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR	0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	59	59	59	54	54	54	54	54	54		
	1	99	94	90	87	91	88	84	81	75	73	70	63	62	60	53	51	50	45	45	45	45	45	45		
	2	90	82	76	71	83	77	71	67	66	62	58	56	53	50	46	44	42	38	38	38	38	38	38		
	3	82	72	65	59	76	67	61	56	58	53	49	49	45	42	41	38	36	32	32	32	32	32	32		
	4	75	64	56	50	69	60	53	47	51	46	42	44	40	36	37	34	31	28	28	28	28	28	28		
	5	69	57	49	43	63	53	46	40	46	40	36	39	35	31	33	30	27	24	24	24	24	24	24		
	6	63	51	43	37	59	48	40	35	41	36	31	35	31	27	30	26	24	21	21	21	21	21	21		
	7	59	46	38	33	54	43	36	31	38	32	28	32	28	24	27	24	21	18	18	18	18	18	18		
	8	54	42	34	29	50	39	32	27	34	28	24	29	25	22	25	21	19	16	16	16	16	16	16		
	9	51	38	31	26	47	36	29	24	31	26	22	27	23	19	23	20	17	15	15	15	15	15	15		
	10	47	35	28	23	44	33	26	22	29	23	20	25	21	18	21	18	15	13	13	13	13	13	13		

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	17679	17679	17679
5°	17813	17698	17632
10°	17769	17686	17636
15°	17675	17675	17659
20°	17559	17612	17612
25°	17394	17520	17466
30°	17182	17390	17314
35°	16926	17185	17066
40°	16646	16882	16711
45°	16344	16460	16205
50°	15917	15917	15662
55°	15411	15212	14984
60°	14668	14373	14144
65°	13557	13286	13168
70°	11869	11966	11918
75°	9550	10562	10626
80°	6785	8958	9048
85°	4128	7516	7516



TEST NUMBER: P561664

CATALOG NUMBER: SQ4-PC3-100U-125D-92765-1D-UNV-STD-W-4 (4500K)

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	181.3	1.9
10°-20°	520.4	5.3
20°-30°	788.1	8.1
30°-40°	944.8	9.7
40°-50°	963.4	9.9
50°-60°	841.0	8.6
60°-70°	602.1	6.2
70°-80°	310.1	3.2
80°-90°	78.4	0.8
90°-100°	331.9	3.4
100°-110°	944.4	9.7
110°-120°	904.8	9.3
120°-130°	716.1	7.3
130°-140°	574.8	5.9
140°-150°	450.0	4.6
150°-160°	329.3	3.4
160°-170°	203.9	2.1
170°-180°	69.2	0.7
0°-30°	1489.9	15.3
0°-40°	2434.7	25.0
0°-60°	4239.0	43.5
0°-90°	5229.6	53.6
90°-120°	2181.1	22.4
90°-150°	3921.9	40.2
90°-180°	4524.0	46.4
0°-180°	9753.9	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1916	1916	1916	1916	1916	
5°	1923	1904	1911	1906	1904	183
15°	1850	1835	1850	1850	1849	522
25°	1709	1696	1721	1716	1716	786
35°	1503	1499	1526	1515	1515	940
45°	1253	1249	1262	1245	1242	964
55°	958	946	946	932	932	854
65°	621	607	609	603	603	614
75°	268	280	296	298	298	289
85°	39	60	71	73	71	53
90°	0	0	0	0	0	3
95°	36	143	642	222	137	41
105°	147	223	962	1700	1616	155
115°	273	330	730	1546	1815	269
125°	385	427	696	1156	1382	345
135°	471	510	688	976	1104	363
145°	555	584	694	845	921	347
155°	634	649	710	764	795	293
165°	701	703	719	734	745	197
175°	734	730	727	723	717	70
180°	728	728	728	728	728	

TEST NUMBER: P561664

CATALOG NUMBER: SQ4-PC3-100U-125D-92765-1D-UNV-STD-W-4 (4500K)

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1916.2	1916.2	1916.2	1916.2	1916.2
2.5°	1927.5	1910.9	1916.2	1911.8	1904.8
5°	1923.3	1904.2	1910.9	1905.5	1903.8
7.5°	1909.4	1890.4	1899.2	1895.6	1893.8
10°	1896.7	1877.6	1887.8	1884.2	1882.5
12.5°	1879.6	1861.9	1873.6	1870.0	1869.7
15°	1850.5	1834.9	1850.5	1850.5	1848.8
17.5°	1814.0	1799.8	1816.5	1817.5	1816.5
20°	1788.4	1772.8	1793.8	1792.0	1793.8
22.5°	1757.2	1744.4	1766.8	1762.2	1764.0
25°	1708.6	1696.5	1721.0	1715.7	1715.7
27.5°	1651.1	1642.4	1669.2	1663.5	1663.5
30°	1612.8	1604.1	1632.3	1625.2	1625.2
32.5°	1570.2	1564.3	1591.1	1582.6	1582.6
35°	1502.8	1499.3	1525.8	1515.2	1515.2
37.5°	1433.2	1430.1	1454.2	1441.3	1437.1
40°	1382.1	1380.4	1401.7	1387.5	1387.5
42.5°	1331.0	1329.3	1347.7	1330.7	1330.7
45°	1252.6	1249.1	1261.5	1245.4	1242.0
47.5°	1167.1	1163.6	1171.4	1153.9	1152.2
50°	1108.9	1105.4	1108.9	1092.9	1091.2
52.5°	1049.3	1043.0	1043.6	1027.6	1027.3
55°	958.1	945.9	945.7	931.5	931.5
57.5°	861.6	845.6	847.0	834.9	833.2
60°	794.9	777.5	778.9	768.2	766.5
62.5°	729.6	709.4	713.6	701.5	701.2
65°	621.0	607.1	608.6	603.2	603.2
67.5°	516.7	503.8	513.1	508.8	508.5
70°	440.0	431.3	443.6	443.5	441.8
72.5°	369.0	368.7	383.9	384.0	385.0
75°	267.9	280.1	296.3	298.1	298.1
77.5°	178.8	200.4	218.2	218.9	218.6
80°	127.7	152.0	168.6	172.1	170.3
82.5°	86.6	112.3	126.0	129.5	127.7
85°	39.0	59.9	71.0	72.7	71.0
87.5°	11.4	23.8	28.4	28.3	25.5
90°	0.0	0.0	0.0	0.0	0.0
92.5°	11.1	58.7	136.3	39.7	29.9
95°	36.0	143.0	642.5	222.4	137.1
97.5°	66.2	167.5	989.5	708.1	485.2
100°	87.2	182.0	1064.8	1078.6	830.8
102.5°	110.5	197.7	1048.2	1380.6	1164.3
105°	146.8	222.6	962.4	1699.9	1616.0
107.5°	183.6	251.6	862.1	1789.9	1864.7
110°	209.1	272.7	804.5	1755.5	1923.4

TEST NUMBER: P561664

CATALOG NUMBER: SQ4-PC3-100U-125D-92765-1D-UNV-STD-W-4 (4500K)

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	233.5	293.8	765.7	1674.0	1913.4
115°	272.8	329.7	729.7	1545.9	1815.4
117.5°	307.4	360.8	708.4	1405.9	1691.3
120°	335.1	379.8	706.2	1325.8	1599.3
122.5°	357.3	401.9	700.7	1255.6	1509.6
125°	385.0	426.9	696.5	1155.8	1381.9
127.5°	415.1	454.4	694.3	1096.2	1282.5
130°	430.6	469.9	691.0	1054.7	1217.2
132.5°	447.3	485.4	691.0	1022.3	1171.7
135°	470.8	510.1	688.2	976.3	1103.6
137.5°	493.0	531.1	687.9	937.5	1047.4
140°	509.6	548.8	686.8	905.2	1010.8
142.5°	528.4	561.2	690.1	879.5	974.3
145°	555.3	583.7	693.7	845.0	920.8
147.5°	578.3	605.9	699.8	810.2	875.7
150°	598.2	617.2	702.0	798.6	844.7
152.5°	613.7	633.7	704.3	783.1	825.8
155°	634.2	649.1	710.4	763.7	794.8
157.5°	659.7	668.6	711.7	754.9	777.1
160°	673.0	679.7	717.3	748.2	767.1
162.5°	680.7	688.6	718.4	742.5	757.2
165°	700.7	703.4	718.7	734.1	745.0
167.5°	714.2	711.8	725.0	732.1	736.4
170°	718.7	717.3	722.8	724.3	729.7
172.5°	728.6	724.0	726.1	722.1	726.4
175°	733.9	729.8	727.0	722.7	717.3
177.5°	736.1	729.6	726.1	721.7	722.8
180°	728.4	728.4	728.4	728.4	728.4

(END OF REPORT)