

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P561676

Luminaire Tested: **SQ4-PC3-125U-050D-92765-1D-UNV-STD-W-4 (4000K)**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P561676
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2106-289-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PC3-125U-050D-92765-1D-UNV-STD-W-4 (4000K)
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS
DOWNLIGHT 500 LUMENS PER FOOT
UPLIGHT 1250 LUMENS PER FOOT
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7657.1 lumens
Efficiency: N/A
Efficacy: 123.1 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 62.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P561676

CATALOG NUMBER: SQ4-PC3-125U-050D-92765-1D-UNV-STD-W-4 (4000K)

Luminous Intensity Polar Plot





TEST NUMBER: P561676

CATALOG NUMBER: SQ4-PC3-125U-050D-92765-1D-UNV-STD-W-4 (4000K)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	91	91	91	91	71	71	71	52	52	52	35	35	35	27
1	93	89	85	81	83	79	76	73	62	60	58	46	44	43	31	30	30	23
2	84	77	71	66	75	69	64	60	54	51	48	40	38	36	27	26	25	19
3	77	68	61	55	68	61	55	50	48	43	40	35	33	30	24	22	21	16
4	70	60	52	47	62	54	47	42	42	38	34	31	28	26	21	20	18	14
5	64	53	45	40	57	48	41	36	38	33	29	28	25	22	19	17	16	12
6	59	48	40	34	53	43	36	31	34	29	25	25	22	19	17	15	14	11
7	55	43	35	30	49	38	32	27	30	26	22	23	20	17	16	14	12	9
8	50	39	31	26	45	35	28	24	28	23	19	21	18	15	15	12	11	8
9	47	35	28	23	42	32	25	21	25	21	17	19	16	14	13	11	10	7
10	44	32	25	20	39	29	23	19	23	19	15	18	14	12	12	10	9	7

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6981	6981	6981
5°	7033	6988	6962
10°	7015	6982	6963
15°	6978	6978	6972
20°	6933	6953	6953
25°	6867	6917	6896
30°	6784	6866	6836
35°	6682	6785	6738
40°	6572	6665	6598
45°	6453	6499	6399
50°	6284	6284	6183
55°	6085	6006	5916
60°	5790	5674	5584
65°	5353	5246	5200
70°	4686	4723	4705
75°	3771	4171	4196
80°	2678	3533	3570
85°	1630	2964	2964



TEST NUMBER: P561676

CATALOG NUMBER: SQ4-PC3-125U-050D-92765-1D-UNV-STD-W-4 (4000K)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	71.6	0.9
10°-20°	205.5	2.7
20°-30°	311.2	4.1
30°-40°	373.0	4.9
40°-50°	380.4	5.0
50°-60°	332.0	4.3
60°-70°	237.7	3.1
70°-80°	122.4	1.6
80°-90°	30.9	0.4
90°-100°	410.2	5.4
100°-110°	1167.3	15.2
110°-120°	1118.4	14.6
120°-130°	885.2	11.6
130°-140°	710.5	9.3
140°-150°	556.2	7.3
150°-160°	407.0	5.3
160°-170°	252.1	3.3
170°-180°	85.5	1.1
0°-30°	588.2	7.7
0°-40°	961.3	12.6
0°-60°	1673.7	21.9
0°-90°	2064.8	27.0
90°-120°	2695.9	35.2
90°-150°	4847.7	63.3
90°-180°	5592.0	73.0
0°-180°	7657.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	757	757	757	757	757	
5°	759	752	754	752	752	72
15°	731	724	731	731	730	206
25°	675	670	680	677	677	310
35°	593	592	602	598	598	371
45°	495	493	498	492	490	381
55°	378	374	373	368	368	337
65°	245	240	240	238	238	242
75°	106	111	117	118	118	114
85°	15	24	28	29	28	21
90°	0	0	0	0	0	2
95°	44	177	794	275	169	51
105°	181	275	1190	2101	1997	192
115°	337	408	902	1911	2244	332
125°	476	528	861	1429	1708	426
135°	582	630	851	1207	1364	449
145°	686	722	858	1044	1138	429
155°	784	802	878	944	982	362
165°	866	869	888	907	921	244
175°	907	902	899	893	887	86
180°	900	900	900	900	900	



TEST NUMBER: P561676

CATALOG NUMBER: SQ4-PC3-125U-050D-92765-1D-UNV-STD-W-4 (4000K)

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	756.6	756.6	756.6	756.6	756.6
2.5°	761.0	754.5	756.6	754.8	752.1
5°	759.4	751.8	754.5	752.3	751.7
7.5°	753.9	746.4	749.8	748.4	747.7
10°	748.8	741.3	745.3	743.9	743.2
12.5°	742.1	735.1	739.7	738.3	738.2
15°	730.6	724.5	730.6	730.6	729.9
17.5°	716.2	710.6	717.2	717.6	717.2
20°	706.1	700.0	708.2	707.5	708.2
22.5°	693.8	688.7	697.6	695.8	696.5
25°	674.6	669.8	679.5	677.4	677.4
27.5°	651.9	648.5	659.0	656.8	656.8
30°	636.8	633.3	644.5	641.7	641.7
32.5°	620.0	617.6	628.2	624.9	624.9
35°	593.3	592.0	602.4	598.2	598.2
37.5°	565.9	564.6	574.1	569.1	567.4
40°	545.7	545.0	553.4	547.8	547.8
42.5°	525.5	524.8	532.1	525.4	525.4
45°	494.6	493.2	498.1	491.7	490.4
47.5°	460.8	459.4	462.5	455.6	454.9
50°	437.8	436.5	437.8	431.5	430.8
52.5°	414.3	411.8	412.0	405.7	405.6
55°	378.3	373.5	373.4	367.8	367.8
57.5°	340.2	333.9	334.4	329.6	329.0
60°	313.8	307.0	307.5	303.3	302.6
62.5°	288.1	280.1	281.7	277.0	276.8
65°	245.2	239.7	240.3	238.2	238.2
67.5°	204.0	198.9	202.6	200.9	200.8
70°	173.7	170.3	175.1	175.1	174.4
72.5°	145.7	145.6	151.6	151.6	152.0
75°	105.8	110.6	117.0	117.7	117.7
77.5°	70.6	79.1	86.2	86.4	86.3
80°	50.4	60.0	66.5	67.9	67.2
82.5°	34.2	44.3	49.7	51.1	50.4
85°	15.4	23.6	28.0	28.7	28.0
87.5°	4.5	9.4	11.2	11.2	10.1
90°	0.0	0.0	0.0	0.0	0.0
92.5°	13.7	72.6	168.4	49.0	37.0
95°	44.5	176.7	794.2	274.9	169.4
97.5°	81.8	207.0	1223.1	875.2	599.7
100°	107.8	225.0	1316.2	1333.2	1026.9
102.5°	136.6	244.4	1295.7	1706.5	1439.1
105°	181.4	275.1	1189.5	2101.2	1997.4
107.5°	227.0	311.0	1065.6	2212.4	2304.8
110°	258.4	337.1	994.4	2169.9	2377.4

TEST NUMBER: P561676

CATALOG NUMBER: SQ4-PC3-125U-050D-92765-1D-UNV-STD-W-4 (4000K)

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	288.6	363.2	946.5	2069.2	2365.0
115°	337.2	407.5	902.0	1910.8	2243.9
117.5°	380.0	445.9	875.6	1737.7	2090.5
120°	414.2	469.4	872.9	1638.8	1976.9
122.5°	441.6	496.8	866.1	1552.0	1866.0
125°	475.8	527.7	860.9	1428.7	1708.1
127.5°	513.1	561.7	858.2	1355.0	1585.3
130°	532.3	580.8	854.1	1303.6	1504.5
132.5°	552.8	600.0	854.1	1263.6	1448.3
135°	581.9	630.5	850.7	1206.8	1364.1
137.5°	609.3	656.5	850.3	1158.7	1294.6
140°	629.9	678.4	848.9	1118.9	1249.4
142.5°	653.1	693.6	853.0	1087.1	1204.3
145°	686.3	721.5	857.5	1044.5	1138.2
147.5°	714.8	748.9	865.0	1001.4	1082.4
150°	739.4	762.8	867.8	987.2	1044.1
152.5°	758.6	783.3	870.5	967.9	1020.8
155°	783.9	802.3	878.0	943.9	982.4
157.5°	815.4	826.4	879.7	933.1	960.5
160°	831.8	840.2	886.6	924.8	948.2
162.5°	841.4	851.1	888.0	917.8	935.9
165°	866.1	869.4	888.3	907.4	920.8
167.5°	882.8	879.8	896.2	904.9	910.2
170°	888.3	886.6	893.4	895.3	902.0
172.5°	900.6	894.9	897.5	892.5	897.9
175°	907.1	902.1	898.6	893.3	886.6
177.5°	909.9	901.8	897.5	892.1	893.4
180°	900.3	900.3	900.3	900.3	900.3

(END OF REPORT)