

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P561453

Luminaire Tested: **SQ4-PC3-025U-125D-92765-1D-UNV-STD-W-4 (3000K)**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P561453
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2106-289-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PC3-025U-125D-92765-1D-UNV-STD-W-4 (3000K)
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 250 LUMENS PER FOOT
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6827.1 lumens
Efficiency: N/A
Efficacy: 97.9 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 69.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P561453
CATALOG NUMBER: SQ4-PC3-025U-125D-92765-1D-UNV-STD-W-4 (3000K)

Luminous Intensity Polar Plot





TEST NUMBER: P561453

CATALOG NUMBER: SQ4-PC3-025U-125D-92765-1D-UNV-STD-W-4 (3000K)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	112	112	112	112	107	107	107	107	96	96	96	86	86	86	77	77	77	72
1	103	98	94	91	97	93	90	87	84	82	79	76	74	72	68	66	65	61
2	94	86	80	74	89	82	76	71	74	69	66	67	63	60	60	57	55	51
3	86	76	68	62	81	72	65	60	65	60	55	59	54	51	53	49	47	43
4	78	67	59	52	74	64	56	51	58	52	47	52	47	43	47	43	40	37
5	72	60	51	45	68	57	49	44	52	45	41	47	42	38	43	38	35	32
6	66	54	45	39	63	51	44	38	47	40	35	43	37	33	39	34	31	28
7	61	49	40	34	58	46	39	33	42	36	31	39	33	29	35	31	27	25
8	57	44	36	31	54	42	35	30	39	32	28	35	30	26	32	28	24	22
9	53	40	33	27	50	39	32	27	36	29	25	33	27	24	30	25	22	20
10	50	37	30	25	47	36	29	24	33	27	23	30	25	21	28	23	20	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16686	16686	16686
5°	16811	16703	16641
10°	16771	16692	16645
15°	16682	16682	16667
20°	16572	16621	16621
25°	16416	16535	16484
30°	16216	16413	16341
35°	15974	16220	16106
40°	15711	15933	15772
45°	15425	15535	15295
50°	15022	15022	14781
55°	14544	14356	14141
60°	13843	13564	13348
65°	12795	12540	12428
70°	11203	11292	11249
75°	9015	9967	10028
80°	6408	8453	8544
85°	3896	7093	7093



TEST NUMBER: P561453

CATALOG NUMBER: SQ4-PC3-025U-125D-92765-1D-UNV-STD-W-4 (3000K)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	171.2	2.5
10°-20°	491.2	7.2
20°-30°	743.8	10.9
30°-40°	891.7	13.1
40°-50°	909.2	13.3
50°-60°	793.7	11.6
60°-70°	568.2	8.3
70°-80°	292.7	4.3
80°-90°	74.0	1.1
90°-100°	138.8	2.0
100°-110°	394.8	5.8
110°-120°	378.2	5.5
120°-130°	299.4	4.4
130°-140°	240.3	3.5
140°-150°	188.1	2.8
150°-160°	137.6	2.0
160°-170°	85.3	1.2
170°-180°	28.9	0.4
0°-30°	1406.1	20.6
0°-40°	2297.8	33.7
0°-60°	4000.8	58.6
0°-90°	4935.7	72.3
90°-120°	911.8	13.4
90°-150°	1639.5	24.0
90°-180°	1891.0	27.7
0°-180°	6827.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1808	1808	1808	1808	1808	
5°	1815	1797	1804	1798	1797	172
15°	1746	1732	1746	1746	1745	492
25°	1613	1601	1624	1619	1619	742
35°	1418	1415	1440	1430	1430	887
45°	1182	1179	1191	1175	1172	910
55°	904	893	892	879	879	806
65°	586	573	574	569	569	580
75°	253	264	280	281	281	273
85°	37	56	67	69	67	50
90°	0	0	0	0	0	2
95°	15	60	269	93	57	17
105°	61	93	402	711	676	65
115°	114	138	305	646	759	112
125°	161	178	291	483	578	144
135°	197	213	288	408	461	152
145°	232	244	290	353	385	145
155°	265	271	297	319	332	123
165°	293	294	300	307	311	82
175°	307	305	304	302	300	29
180°	304	304	304	304	304	

TEST NUMBER: P561453

CATALOG NUMBER: SQ4-PC3-025U-125D-92765-1D-UNV-STD-W-4 (3000K)

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1808.5	1808.5	1808.5	1808.5	1808.5
2.5°	1819.2	1803.5	1808.5	1804.3	1797.8
5°	1815.2	1797.2	1803.5	1798.4	1796.8
7.5°	1802.1	1784.1	1792.4	1789.0	1787.4
10°	1790.1	1772.1	1781.7	1778.3	1776.7
12.5°	1774.0	1757.3	1768.3	1764.9	1764.6
15°	1746.5	1731.8	1746.5	1746.5	1744.9
17.5°	1712.0	1698.6	1714.4	1715.4	1714.4
20°	1687.9	1673.2	1692.9	1691.3	1692.9
22.5°	1658.5	1646.3	1667.5	1663.2	1664.8
25°	1612.6	1601.1	1624.3	1619.3	1619.3
27.5°	1558.3	1550.1	1575.4	1570.0	1570.0
30°	1522.1	1514.0	1540.6	1533.9	1533.9
32.5°	1482.0	1476.4	1501.7	1493.7	1493.7
35°	1418.3	1415.0	1440.1	1430.0	1430.0
37.5°	1352.7	1349.7	1372.4	1360.3	1356.4
40°	1304.5	1302.8	1322.9	1309.5	1309.5
42.5°	1256.2	1254.6	1272.0	1255.9	1255.9
45°	1182.2	1178.9	1190.6	1175.4	1172.2
47.5°	1101.5	1098.2	1105.5	1089.1	1087.4
50°	1046.6	1043.3	1046.6	1031.5	1029.8
52.5°	990.3	984.4	985.0	969.9	969.6
55°	904.2	892.8	892.5	879.1	879.1
57.5°	813.1	798.1	799.4	788.0	786.4
60°	750.2	733.8	735.1	725.0	723.4
62.5°	688.6	669.6	673.5	662.1	661.8
65°	586.1	573.0	574.4	569.3	569.3
67.5°	487.6	475.5	484.3	480.2	479.9
70°	415.3	407.1	418.6	418.6	417.0
72.5°	348.3	348.0	362.4	362.4	363.4
75°	252.9	264.3	279.6	281.3	281.3
77.5°	168.8	189.1	206.0	206.6	206.3
80°	120.6	143.5	159.1	162.4	160.8
82.5°	81.7	105.9	118.9	122.2	120.6
85°	36.8	56.5	67.0	68.6	67.0
87.5°	10.7	22.5	26.8	26.7	24.1
90°	0.0	0.0	0.0	0.0	0.0
92.5°	4.6	24.6	57.0	16.6	12.5
95°	15.1	59.8	268.6	93.0	57.3
97.5°	27.7	70.0	413.7	296.0	202.8
100°	36.5	76.1	445.1	450.9	347.3
102.5°	46.2	82.6	438.2	577.2	486.7
105°	61.4	93.1	402.3	710.6	675.5
107.5°	76.8	105.2	360.4	748.3	779.5
110°	87.4	114.0	336.3	733.9	804.0

TEST NUMBER: P561453

CATALOG NUMBER: SQ4-PC3-025U-125D-92765-1D-UNV-STD-W-4 (3000K)

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	97.6	122.8	320.1	699.8	799.9
115°	114.0	137.8	305.1	646.3	758.9
117.5°	128.5	150.8	296.1	587.7	707.0
120°	140.1	158.8	295.2	554.3	668.6
122.5°	149.3	168.0	292.9	524.9	631.1
125°	160.9	178.5	291.2	483.2	577.7
127.5°	173.5	190.0	290.2	458.3	536.1
130°	180.0	196.4	288.9	440.9	508.8
132.5°	187.0	202.9	288.9	427.3	489.8
135°	196.8	213.2	287.7	408.2	461.4
137.5°	206.1	222.0	287.6	391.9	437.9
140°	213.0	229.4	287.1	378.4	422.6
142.5°	220.9	234.6	288.5	367.7	407.3
145°	232.1	244.0	290.0	353.2	384.9
147.5°	241.7	253.3	292.6	338.7	366.1
150°	250.1	258.0	293.5	333.9	353.1
152.5°	256.6	264.9	294.4	327.3	345.2
155°	265.1	271.3	297.0	319.3	332.3
157.5°	275.8	279.5	297.5	315.6	324.9
160°	281.3	284.2	299.9	312.8	320.7
162.5°	284.6	287.9	300.3	310.4	316.5
165°	292.9	294.0	300.4	306.9	311.4
167.5°	298.6	297.6	303.1	306.0	307.8
170°	300.4	299.9	302.2	302.8	305.1
172.5°	304.6	302.7	303.6	301.9	303.7
175°	306.8	305.1	303.9	302.1	299.9
177.5°	307.7	305.0	303.6	301.7	302.2
180°	304.5	304.5	304.5	304.5	304.5

(END OF REPORT)