

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P561719

Luminaire Tested: **SQ4-PC3-125U-125D-92765-1D-UNV-STD-W-4 (6500K)**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P561719
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2106-289-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PC3-125U-125D-92765-1D-UNV-STD-W-4 (6500K)
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 1250 LUMENS PER FOOT
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 6500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 11296.1 lumens
Efficiency: N/A
Efficacy: 116.9 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 96.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P561719
CATALOG NUMBER: SQ4-PC3-125U-125D-92765-1D-UNV-STD-W-4 (6500K)

Luminous Intensity Polar Plot





TEST NUMBER: P561719

CATALOG NUMBER: SQ4-PC3-125U-125D-92765-1D-UNV-STD-W-4 (6500K)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	98	98	98	98	82	82	82	68	68	68	54	54	54	48
1	97	93	89	86	89	86	83	80	72	70	68	60	58	56	48	47	46	41
2	89	81	75	70	81	75	70	65	63	59	56	52	50	47	42	40	39	34
3	81	71	64	58	74	66	60	54	56	51	47	46	43	40	37	35	33	29
4	74	63	55	49	68	58	51	46	49	44	40	41	37	34	33	31	28	25
5	68	56	48	42	62	52	45	40	44	39	34	37	33	29	30	27	25	21
6	62	50	42	36	57	47	40	34	40	34	30	33	29	26	27	24	22	19
7	58	45	37	32	53	42	35	30	36	30	26	30	26	23	25	22	19	17
8	53	41	33	28	49	38	31	27	33	27	23	28	23	20	23	20	17	15
9	50	38	30	25	46	35	28	24	30	25	21	25	21	18	21	18	15	13
10	46	34	27	22	43	32	26	21	28	22	19	23	19	16	19	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	18301	18301	18301
5°	18440	18320	18252
10°	18394	18308	18256
15°	18298	18298	18280
20°	18178	18232	18232
25°	18005	18137	18081
30°	17786	18001	17923
35°	17522	17790	17666
40°	17232	17476	17299
45°	16919	17039	16776
50°	16476	16476	16214
55°	15953	15746	15511
60°	15183	14878	14640
65°	14033	13754	13633
70°	12287	12387	12336
75°	9885	10933	11001
80°	7024	9271	9367
85°	4277	7781	7781



TEST NUMBER: P561719

CATALOG NUMBER: SQ4-PC3-125U-125D-92765-1D-UNV-STD-W-4 (6500K)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	187.7	1.7
10°-20°	538.7	4.8
20°-30°	815.8	7.2
30°-40°	978.1	8.7
40°-50°	997.3	8.8
50°-60°	870.6	7.7
60°-70°	623.3	5.5
70°-80°	321.0	2.8
80°-90°	81.2	0.7
90°-100°	431.5	3.8
100°-110°	1227.8	10.9
110°-120°	1176.4	10.4
120°-130°	931.1	8.2
130°-140°	747.3	6.6
140°-150°	585.1	5.2
150°-160°	428.1	3.8
160°-170°	265.2	2.3
170°-180°	90.0	0.8
0°-30°	1542.3	13.7
0°-40°	2520.4	22.3
0°-60°	4388.2	38.8
0°-90°	5413.7	47.9
90°-120°	2835.8	25.1
90°-150°	5099.2	45.1
90°-180°	5882.0	52.1
0°-180°	11296.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1984	1984	1984	1984	1984	
5°	1991	1971	1978	1973	1971	189
15°	1916	1900	1916	1916	1914	540
25°	1769	1756	1782	1776	1776	814
35°	1556	1552	1580	1568	1568	973
45°	1297	1293	1306	1289	1286	998
55°	992	979	979	964	964	884
65°	643	628	630	624	624	636
75°	277	290	307	309	309	300
85°	40	62	74	75	74	55
90°	0	0	0	0	0	4
95°	47	186	835	289	178	54
105°	191	289	1251	2210	2101	202
115°	355	429	949	2010	2360	349
125°	500	555	906	1503	1797	448
135°	612	663	895	1269	1435	472
145°	722	759	902	1099	1197	451
155°	825	844	924	993	1033	381
165°	911	914	934	954	969	256
175°	954	949	945	940	933	90
180°	947	947	947	947	947	



TEST NUMBER: P561719

CATALOG NUMBER: SQ4-PC3-125U-125D-92765-1D-UNV-STD-W-4 (6500K)

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1983.6	1983.6	1983.6	1983.6	1983.6
2.5°	1995.4	1978.1	1983.6	1979.0	1971.9
5°	1991.0	1971.2	1978.1	1972.6	1970.8
7.5°	1976.6	1956.9	1966.0	1962.3	1960.5
10°	1963.4	1943.7	1954.2	1950.5	1948.7
12.5°	1945.8	1927.5	1939.5	1935.9	1935.5
15°	1915.7	1899.5	1915.7	1915.6	1913.8
17.5°	1877.8	1863.1	1880.4	1881.5	1880.4
20°	1851.4	1835.2	1856.9	1855.1	1856.9
22.5°	1819.0	1805.8	1829.0	1824.2	1826.0
25°	1768.7	1756.2	1781.6	1776.1	1776.1
27.5°	1709.2	1700.2	1727.9	1722.1	1722.1
30°	1669.5	1660.6	1689.7	1682.4	1682.4
32.5°	1625.5	1619.4	1647.1	1638.3	1638.3
35°	1555.7	1552.1	1579.5	1568.5	1568.5
37.5°	1483.7	1480.4	1505.3	1492.0	1487.7
40°	1430.8	1429.0	1451.0	1436.3	1436.3
42.5°	1377.9	1376.1	1395.1	1377.5	1377.5
45°	1296.7	1293.1	1305.9	1289.3	1285.7
47.5°	1208.2	1204.6	1212.6	1194.5	1192.7
50°	1147.9	1144.3	1147.9	1131.4	1129.6
52.5°	1086.2	1079.7	1080.3	1063.8	1063.4
55°	991.8	979.2	978.9	964.3	964.3
57.5°	891.9	875.4	876.8	864.3	862.5
60°	822.8	804.9	806.3	795.2	793.4
62.5°	755.2	734.4	738.7	726.2	725.9
65°	642.8	628.5	630.0	624.5	624.5
67.5°	534.8	521.6	531.2	526.8	526.4
70°	455.5	446.5	459.2	459.1	457.3
72.5°	382.0	381.7	397.5	397.5	398.6
75°	277.3	289.9	306.7	308.6	308.6
77.5°	185.1	207.4	225.9	226.6	226.3
80°	132.2	157.4	174.5	178.1	176.3
82.5°	89.6	116.2	130.4	134.0	132.2
85°	40.4	62.0	73.5	75.3	73.5
87.5°	11.8	24.7	29.4	29.3	26.4
90°	0.0	0.0	0.0	0.0	0.0
92.5°	14.4	76.4	177.2	51.6	38.9
95°	46.8	185.9	835.4	289.1	178.2
97.5°	86.1	217.7	1286.6	920.6	630.9
100°	113.4	236.6	1384.5	1402.4	1080.2
102.5°	143.7	257.0	1362.9	1795.1	1513.8
105°	190.8	289.4	1251.3	2210.2	2101.0
107.5°	238.7	327.1	1120.9	2327.2	2424.4
110°	271.9	354.6	1046.0	2282.4	2500.7

TEST NUMBER: P561719

CATALOG NUMBER: SQ4-PC3-125U-125D-92765-1D-UNV-STD-W-4 (6500K)

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	303.5	382.1	995.6	2176.5	2487.8
115°	354.7	428.6	948.8	2010.0	2360.3
117.5°	399.7	469.0	921.1	1827.9	2199.0
120°	435.7	493.8	918.2	1723.8	2079.4
122.5°	464.5	522.6	911.0	1632.5	1962.8
125°	500.5	555.1	905.6	1502.8	1796.8
127.5°	539.8	590.8	902.7	1425.3	1667.5
130°	559.9	611.0	898.4	1371.3	1582.5
132.5°	581.5	631.2	898.4	1329.1	1523.5
135°	612.1	663.2	894.8	1269.4	1434.9
137.5°	640.9	690.6	894.4	1218.9	1361.8
140°	662.5	713.6	893.0	1177.0	1314.3
142.5°	687.0	729.6	897.3	1143.5	1266.7
145°	722.0	758.9	902.0	1098.7	1197.3
147.5°	751.8	787.8	909.9	1053.4	1138.6
150°	777.8	802.4	912.8	1038.4	1098.2
152.5°	797.9	824.0	915.7	1018.1	1073.7
155°	824.6	843.9	923.6	992.9	1033.4
157.5°	857.7	869.3	925.4	981.5	1010.4
160°	875.0	883.8	932.6	972.8	997.4
162.5°	885.1	895.3	934.0	965.4	984.4
165°	911.0	914.5	934.4	954.5	968.6
167.5°	928.6	925.5	942.7	951.8	957.4
170°	934.4	932.6	939.8	941.8	948.8
172.5°	947.4	941.4	944.1	938.8	944.5
175°	954.2	948.9	945.2	939.6	932.6
177.5°	957.1	948.6	944.1	938.4	939.8
180°	947.0	947.0	947.0	947.0	947.0

(END OF REPORT)