

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P561732

Luminaire Tested: **SQ4-PC3-150U-050D-92765-1D-UNV-STD-W-4 (6500K)**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P561732
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2106-289-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PC3-150U-050D-92765-1D-UNV-STD-W-4 (6500K)
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS
DOWNLIGHT 500 LUMENS PER FOOT
UPLIGHT 1500 LUMENS PER FOOT
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 6500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9261.2 lumens
Efficiency: N/A
Efficacy: 129.9 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 71.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P561732
CATALOG NUMBER: SQ4-PC3-150U-050D-92765-1D-UNV-STD-W-4 (6500K)

Luminous Intensity Polar Plot





TEST NUMBER: P561732

CATALOG NUMBER: SQ4-PC3-150U-050D-92765-1D-UNV-STD-W-4 (6500K)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	101	101	101	101	90	90	90	90	69	69	69	49	49	49	32	32	32	23				
1	92	88	84	81	81	78	75	72	60	58	56	43	42	41	28	27	27	20				
2	84	77	71	66	74	68	63	59	53	49	46	38	36	34	25	24	23	17				
3	76	67	60	55	67	60	54	49	46	42	39	34	31	29	22	20	19	14				
4	70	59	52	46	62	53	47	42	41	37	33	30	27	25	19	18	16	12				
5	64	53	45	39	56	47	40	36	36	32	28	27	24	21	17	16	14	10				
6	59	47	39	34	52	42	35	31	33	28	24	24	21	18	16	14	12	9				
7	54	42	35	29	48	38	31	27	30	25	21	22	19	16	14	12	11	8				
8	50	38	31	26	44	34	28	23	27	22	19	20	17	14	13	11	10	7				
9	46	35	28	23	41	31	25	21	24	20	17	18	15	13	12	10	9	6				
10	43	32	25	20	38	28	22	18	22	18	15	17	14	11	11	9	8	6				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7342	7342	7342
5°	7398	7350	7323
10°	7380	7345	7324
15°	7340	7340	7334
20°	7293	7315	7315
25°	7224	7277	7253
30°	7136	7222	7191
35°	7029	7137	7088
40°	6913	7011	6940
45°	6787	6836	6730
50°	6610	6610	6505
55°	6400	6317	6223
60°	6091	5969	5873
65°	5630	5517	5469
70°	4928	4969	4950
75°	3968	4388	4413
80°	2821	3719	3756
85°	1715	3123	3123



TEST NUMBER: P561732

CATALOG NUMBER: SQ4-PC3-150U-050D-92765-1D-UNV-STD-W-4 (6500K)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	75.3	0.8
10°-20°	216.1	2.3
20°-30°	327.3	3.5
30°-40°	392.4	4.2
40°-50°	400.1	4.3
50°-60°	349.3	3.8
60°-70°	250.0	2.7
70°-80°	128.8	1.4
80°-90°	32.6	0.4
90°-100°	520.1	5.6
100°-110°	1479.7	16.0
110°-120°	1417.7	15.3
120°-130°	1122.1	12.1
130°-140°	900.6	9.7
140°-150°	705.1	7.6
150°-160°	515.9	5.6
160°-170°	319.6	3.5
170°-180°	108.4	1.2
0°-30°	618.8	6.7
0°-40°	1011.1	10.9
0°-60°	1760.5	19.0
0°-90°	2171.9	23.5
90°-120°	3417.5	36.9
90°-150°	6145.3	66.4
90°-180°	7089.0	76.5
0°-180°	9261.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	796	796	796	796	796	
5°	799	791	794	791	791	76
15°	768	762	768	768	768	217
25°	710	705	715	712	712	327
35°	624	623	634	629	629	390
45°	520	519	524	517	516	400
55°	398	393	393	387	387	355
65°	258	252	253	250	250	255
75°	111	116	123	124	124	120
85°	16	25	30	30	30	22
90°	0	0	0	0	0	3
95°	56	224	1007	348	215	64
105°	230	349	1508	2664	2532	243
115°	427	516	1143	2422	2844	421
125°	603	669	1091	1811	2165	540
135°	738	799	1078	1530	1729	569
145°	870	915	1087	1324	1443	544
155°	994	1017	1113	1197	1245	459
165°	1098	1102	1126	1150	1167	309
175°	1150	1144	1139	1132	1124	109
180°	1141	1141	1141	1141	1141	

TEST NUMBER: P561732

CATALOG NUMBER: SQ4-PC3-150U-050D-92765-1D-UNV-STD-W-4 (6500K)

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	795.8	795.8	795.8	795.8	795.8
2.5°	800.5	793.6	795.8	794.0	791.1
5°	798.8	790.8	793.6	791.4	790.7
7.5°	793.0	785.1	788.7	787.2	786.5
10°	787.7	779.8	784.0	782.5	781.8
12.5°	780.6	773.3	778.1	776.6	776.5
15°	768.5	762.1	768.5	768.5	767.8
17.5°	753.4	747.5	754.4	754.8	754.4
20°	742.8	736.3	745.0	744.2	745.0
22.5°	729.8	724.5	733.8	731.9	732.6
25°	709.6	704.6	714.8	712.5	712.5
27.5°	685.7	682.1	693.2	690.9	690.9
30°	669.8	666.2	677.9	675.0	675.0
32.5°	652.1	649.7	660.8	657.3	657.3
35°	624.1	622.7	633.7	629.3	629.3
37.5°	595.2	593.9	603.9	598.6	596.9
40°	574.0	573.3	582.1	576.2	576.2
42.5°	552.8	552.1	559.7	552.6	552.6
45°	520.2	518.8	523.9	517.2	515.8
47.5°	484.7	483.3	486.5	479.2	478.5
50°	460.5	459.1	460.5	453.9	453.2
52.5°	435.8	433.2	433.4	426.8	426.6
55°	397.9	392.9	392.7	386.9	386.9
57.5°	357.8	351.2	351.8	346.8	346.0
60°	330.1	322.9	323.5	319.0	318.3
62.5°	303.0	294.6	296.4	291.4	291.2
65°	257.9	252.1	252.7	250.5	250.5
67.5°	214.6	209.2	213.1	211.3	211.2
70°	182.7	179.1	184.2	184.2	183.5
72.5°	153.3	153.1	159.5	159.5	159.9
75°	111.3	116.3	123.1	123.8	123.8
77.5°	74.3	83.2	90.6	90.9	90.8
80°	53.1	63.1	70.0	71.5	70.7
82.5°	36.0	46.6	52.3	53.8	53.1
85°	16.2	24.9	29.5	30.2	29.5
87.5°	4.7	9.9	11.8	11.8	10.6
90°	0.0	0.0	0.0	0.0	0.0
92.5°	17.4	92.0	213.5	62.1	46.9
95°	56.4	224.0	1006.8	348.5	214.8
97.5°	103.7	262.4	1550.5	1109.5	760.3
100°	136.7	285.2	1668.5	1690.1	1301.8
102.5°	173.1	309.8	1642.5	2163.3	1824.3
105°	230.0	348.8	1508.0	2663.6	2532.1
107.5°	287.7	394.2	1350.9	2804.6	2921.8
110°	327.6	427.3	1260.6	2750.7	3013.7

TEST NUMBER: P561732

CATALOG NUMBER: SQ4-PC3-150U-050D-92765-1D-UNV-STD-W-4 (6500K)

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	365.8	460.4	1199.9	2623.0	2998.1
115°	427.4	516.5	1143.4	2422.3	2844.5
117.5°	481.7	565.3	1110.0	2202.9	2650.1
120°	525.1	595.1	1106.6	2077.5	2506.0
122.5°	559.8	629.8	1097.9	1967.4	2365.4
125°	603.2	669.0	1091.4	1811.1	2165.4
127.5°	650.5	712.0	1087.9	1717.7	2009.6
130°	674.8	736.3	1082.7	1652.6	1907.2
132.5°	700.8	760.6	1082.7	1601.8	1836.0
135°	737.7	799.2	1078.4	1529.8	1729.3
137.5°	772.4	832.2	1077.9	1468.9	1641.2
140°	798.5	860.0	1076.2	1418.4	1583.9
142.5°	828.0	879.3	1081.4	1378.1	1526.6
145°	870.1	914.6	1087.0	1324.1	1442.9
147.5°	906.1	949.4	1096.6	1269.5	1372.1
150°	937.3	967.0	1100.1	1251.4	1323.5
152.5°	961.6	993.0	1103.5	1227.0	1294.0
155°	993.7	1017.1	1113.1	1196.6	1245.4
157.5°	1033.7	1047.7	1115.2	1182.9	1217.7
160°	1054.5	1065.1	1123.9	1172.3	1202.0
162.5°	1066.6	1078.9	1125.7	1163.5	1186.4
165°	1097.9	1102.1	1126.1	1150.3	1167.3
167.5°	1119.1	1115.3	1136.1	1147.1	1153.9
170°	1126.1	1124.0	1132.6	1135.0	1143.4
172.5°	1141.7	1134.5	1137.8	1131.4	1138.2
175°	1150.0	1143.6	1139.1	1132.4	1123.9
177.5°	1153.4	1143.2	1137.8	1130.9	1132.6
180°	1141.3	1141.3	1141.3	1141.3	1141.3

(END OF REPORT)