

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P523624

Luminaire Tested: **SQ4-PP3-025U-050D-92765-1D-UNV-STD-W-4 (5000K)**

Issue Date: 5/24/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P523624  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2103-172-1)  
Test Lab: INNOVATION CENTER  
Issue Date: 5/24/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PP3-025U-050D-92765-1D-UNV-STD-W-4 (5000K)  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS  
DOWNLIGHT 500 LUMENS PER FOOT  
UPLIGHT 250 LUMENS PER FOOT  
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 5000K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4127.4 lumens  
Efficiency: N/A  
Efficacy: 118.9 lumens/watt  
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33  
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 34.7  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P523624

CATALOG NUMBER: SQ4-PP3-025U-050D-92765-1D-UNV-STD-W-4 (5000K)

### Luminous Intensity Polar Plot





TEST NUMBER: P523624

CATALOG NUMBER: SQ4-PP3-025U-050D-92765-1D-UNV-STD-W-4 (5000K)

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20									
RC	80					70					50					30					10				
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0				
RCR																									
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	51	51	51	51				
1	98	94	90	87	91	87	84	81	74	71	69	62	60	59	51	50	49	43	43	43	43				
2	90	82	76	71	83	76	71	67	65	61	58	54	52	49	45	43	41	37	37	37	37				
3	82	72	65	59	75	67	61	56	57	53	49	48	45	42	40	37	35	31	31	31	31				
4	75	64	56	50	69	60	53	47	51	46	42	43	39	36	36	33	30	27	27	27	27				
5	69	57	49	43	63	53	46	41	46	40	36	39	34	31	32	29	27	23	23	23	23				
6	63	51	43	37	58	48	41	35	41	36	31	35	31	27	29	26	23	21	21	21	21				
7	59	46	38	33	54	43	36	31	37	32	28	32	27	24	27	23	21	18	18	18	18				
8	54	42	34	29	50	39	32	28	34	29	25	29	25	22	24	21	19	16	16	16	16				
9	51	38	31	26	47	36	29	25	31	26	22	27	22	19	23	19	17	15	15	15	15				
10	47	35	28	23	44	33	26	22	29	23	20	25	21	18	21	18	15	13	13	13	13				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	7575	7575	7575
5°	7630	7583	7556
10°	7618	7563	7529
15°	7567	7526	7485
20°	7517	7475	7418
25°	7427	7376	7303
30°	7290	7252	7159
35°	7099	7051	6962
40°	6872	6829	6751
45°	6684	6637	6572
50°	6445	6403	6341
55°	6111	6030	5984
60°	5563	5403	5377
65°	4901	4696	4681
70°	4232	4057	4057
75°	3643	3590	3540
80°	3209	3252	3172
85°	2509	2742	2742



TEST NUMBER: P523624

CATALOG NUMBER: SQ4-PP3-025U-050D-92765-1D-UNV-STD-W-4 (5000K)

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	77.6	1.9
10°-20°	221.7	5.4
20°-30°	332.0	8.0
30°-40°	389.5	9.4
40°-50°	390.7	9.5
50°-60°	333.3	8.1
60°-70°	217.3	5.3
70°-80°	109.0	2.6
80°-90°	30.2	0.7
90°-100°	148.6	3.6
100°-110°	422.9	10.2
110°-120°	405.2	9.8
120°-130°	320.7	7.8
130°-140°	257.4	6.2
140°-150°	201.5	4.9
150°-160°	147.4	3.6
160°-170°	91.3	2.2
170°-180°	31.0	0.8
0°-30°	631.3	15.3
0°-40°	1020.8	24.7
0°-60°	1744.7	42.3
0°-90°	2101.3	50.9
90°-120°	976.8	23.7
90°-150°	1756.4	42.6
90°-180°	2026.0	49.1
0°-180°	4127.4	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	821	821	821	821	821	
5°	824	816	819	816	816	78
15°	792	784	788	785	784	223
25°	730	721	725	718	717	336
35°	630	624	626	619	618	394
45°	512	509	509	504	504	394
55°	380	378	375	373	372	338
65°	224	220	215	214	214	224
75°	102	102	101	100	99	111
85°	24	26	26	26	26	28
90°	0	0	0	0	0	2
95°	16	64	288	100	61	18
105°	66	100	431	761	724	70
115°	122	148	327	692	813	120
125°	172	191	312	518	619	154
135°	211	228	308	437	494	163
145°	249	261	311	378	412	155
155°	284	291	318	342	356	131
165°	314	315	322	329	334	88
175°	329	327	326	324	321	31
180°	326	326	326	326	326	

TEST NUMBER: P523624

CATALOG NUMBER: SQ4-PP3-025U-050D-92765-1D-UNV-STD-W-4 (5000K)

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	821.0	821.0	821.0	821.0	821.0
2.5°	826.2	819.4	821.0	819.7	816.4
5°	823.8	816.1	818.8	815.9	815.9
7.5°	818.2	809.8	812.5	809.6	809.5
10°	813.1	804.6	807.3	804.4	803.7
12.5°	805.6	797.1	800.4	796.9	796.8
15°	792.2	784.5	787.9	785.0	783.6
17.5°	777.1	768.6	772.8	768.7	768.2
20°	765.6	757.1	761.3	755.5	755.5
22.5°	751.8	743.3	748.0	740.5	740.5
25°	729.6	721.1	724.6	718.1	717.4
27.5°	703.3	695.0	698.5	691.2	691.0
30°	684.3	676.5	680.7	672.7	672.0
32.5°	663.5	656.4	659.4	651.4	650.7
35°	630.3	624.0	626.0	618.8	618.1
37.5°	595.3	588.9	591.2	585.0	584.7
40°	570.6	566.4	567.0	561.9	560.5
42.5°	547.6	542.8	543.4	538.3	538.1
45°	512.3	508.8	508.7	503.7	503.7
47.5°	474.9	472.2	471.4	467.3	467.1
50°	449.0	446.9	446.1	442.5	441.8
52.5°	421.9	420.9	418.5	415.4	415.3
55°	379.9	378.5	374.9	372.7	372.0
57.5°	334.3	331.5	327.4	324.2	324.8
60°	301.5	298.7	292.8	291.4	291.4
62.5°	269.8	266.4	260.6	258.6	259.7
65°	224.5	220.3	215.1	213.7	214.4
67.5°	183.3	179.5	174.0	174.0	173.4
70°	156.9	154.7	150.4	150.4	150.4
72.5°	133.3	132.3	129.1	129.1	128.5
75°	102.2	102.2	100.7	100.0	99.3
77.5°	76.6	76.8	76.1	75.4	74.1
80°	60.4	61.8	61.2	60.4	59.7
82.5°	45.5	46.9	46.8	45.5	45.3
85°	23.7	25.9	25.9	25.9	25.9
87.5°	6.3	8.6	9.2	9.2	9.8
90°	0.0	0.0	0.0	0.0	0.0
92.5°	5.0	26.3	61.0	17.8	13.4
95°	16.1	64.0	287.7	99.6	61.4
97.5°	29.6	75.0	443.1	317.1	217.3
100°	39.1	81.5	476.9	483.0	372.1
102.5°	49.5	88.5	469.4	618.3	521.4
105°	65.7	99.7	431.0	761.3	723.7
107.5°	82.2	112.7	386.1	801.6	835.1
110°	93.6	122.1	360.3	786.2	861.3



TEST NUMBER: P523624

CATALOG NUMBER: SQ4-PP3-025U-050D-92765-1D-UNV-STD-W-4 (5000K)

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	104.6	131.6	342.9	749.7	856.9
115°	122.2	147.6	326.8	692.3	813.0
117.5°	137.7	161.6	317.3	629.6	757.4
120°	150.1	170.1	316.3	593.8	716.2
122.5°	160.0	180.0	313.8	562.3	676.1
125°	172.4	191.2	311.9	517.6	618.9
127.5°	185.9	203.5	310.9	490.9	574.4
130°	192.9	210.4	309.4	472.3	545.1
132.5°	200.3	217.4	309.4	457.8	524.7
135°	210.8	228.4	308.2	437.2	494.2
137.5°	220.8	237.9	308.1	419.8	469.1
140°	228.2	245.8	307.6	405.4	452.7
142.5°	236.6	251.3	309.1	393.9	436.3
145°	248.7	261.4	310.7	378.4	412.4
147.5°	259.0	271.3	313.4	362.8	392.2
150°	267.9	276.4	314.4	357.7	378.3
152.5°	274.8	283.8	315.4	350.7	369.8
155°	284.0	290.7	318.1	342.0	355.9
157.5°	295.4	299.4	318.7	338.1	348.0
160°	301.4	304.4	321.2	335.1	343.5
162.5°	304.9	308.4	321.7	332.5	339.1
165°	313.8	315.0	321.8	328.8	333.6
167.5°	319.9	318.8	324.7	327.8	329.8
170°	321.8	321.2	323.7	324.4	326.8
172.5°	326.3	324.2	325.2	323.4	325.3
175°	328.7	326.8	325.6	323.6	321.2
177.5°	329.7	326.7	325.2	323.2	323.7
180°	326.2	326.2	326.2	326.2	326.2

(END OF REPORT)