

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: CORELITE

Report Number: P561498

Luminaire Tested: **SQ4-PC3-050U-100D-92765-1D-UNV-STD-W-4 (6500K)**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P561498
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2106-289-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PC3-050U-100D-92765-1D-UNV-STD-W-4 (6500K)
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS
DOWNLIGHT 1000 LUMENS PER FOOT
UPLIGHT 500 LUMENS PER FOOT
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 6500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6613.9 lumens
Efficiency: N/A
Efficacy: 114.4 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 57.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P561498

CATALOG NUMBER: SQ4-PC3-050U-100D-92765-1D-UNV-STD-W-4 (6500K)

Luminous Intensity Polar Plot





TEST NUMBER: P561498

CATALOG NUMBER: SQ4-PC3-050U-100D-92765-1D-UNV-STD-W-4 (6500K)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	104	104	104	104	91	91	91	80	80	80	70	70	70	65
1	101	97	93	89	95	91	88	85	80	78	75	71	69	67	62	60	59	55
2	92	85	78	73	86	80	74	69	71	66	63	62	59	56	54	52	50	46
3	84	74	67	61	79	70	63	58	62	57	53	55	51	47	48	45	42	39
4	77	66	58	51	72	62	55	49	55	49	45	49	44	41	43	39	36	33
5	71	59	50	44	66	55	48	42	49	43	39	44	39	35	39	35	32	29
6	65	53	44	38	61	50	42	37	45	38	34	40	35	31	35	31	28	25
7	60	48	39	34	56	45	38	32	40	34	30	36	31	27	32	28	25	22
8	56	43	35	30	52	41	34	29	37	31	26	33	28	24	29	25	22	20
9	52	40	32	27	49	38	31	26	34	28	24	30	25	22	27	23	20	18
10	49	36	29	24	46	35	28	23	31	25	21	28	23	20	25	21	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	14455	14455	14455
5°	14564	14470	14416
10°	14529	14460	14420
15°	14453	14453	14438
20°	14357	14400	14400
25°	14221	14325	14280
30°	14049	14218	14156
35°	13839	14052	13954
40°	13611	13802	13663
45°	13364	13458	13250
50°	13014	13014	12806
55°	12601	12437	12251
60°	11992	11752	11564
65°	11084	10863	10767
70°	9706	9784	9744
75°	7810	8637	8687
80°	5547	7322	7401
85°	3377	6140	6140



TEST NUMBER: P561498

CATALOG NUMBER: SQ4-PC3-050U-100D-92765-1D-UNV-STD-W-4 (6500K)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	148.3	2.2
10°-20°	425.5	6.4
20°-30°	644.4	9.7
30°-40°	772.5	11.7
40°-50°	787.7	11.9
50°-60°	687.6	10.4
60°-70°	492.3	7.4
70°-80°	253.5	3.8
80°-90°	64.1	1.0
90°-100°	171.5	2.6
100°-110°	488.0	7.4
110°-120°	467.6	7.1
120°-130°	370.1	5.6
130°-140°	297.0	4.5
140°-150°	232.5	3.5
150°-160°	170.1	2.6
160°-170°	105.4	1.6
170°-180°	35.8	0.5
0°-30°	1218.2	18.4
0°-40°	1990.7	30.1
0°-60°	3466.0	52.4
0°-90°	4275.9	64.7
90°-120°	1127.1	17.0
90°-150°	2026.7	30.6
90°-180°	2338.0	35.3
0°-180°	6613.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1567	1567	1567	1567	1567	
5°	1572	1557	1562	1558	1557	149
15°	1513	1500	1513	1513	1512	427
25°	1397	1387	1407	1403	1403	643
35°	1229	1226	1248	1239	1239	768
45°	1024	1021	1031	1018	1016	788
55°	783	773	773	762	762	698
65°	508	496	498	493	493	502
75°	219	229	242	244	244	237
85°	32	49	58	59	58	43
90°	0	0	0	0	0	2
95°	19	74	332	115	71	21
105°	76	115	497	878	835	80
115°	141	170	377	799	938	139
125°	199	221	360	597	714	178
135°	243	264	356	504	570	188
145°	287	302	358	437	476	179
155°	328	335	367	395	411	151
165°	362	364	371	379	385	102
175°	379	377	376	374	371	36
180°	376	376	376	376	376	

TEST NUMBER: P561498

CATALOG NUMBER: SQ4-PC3-050U-100D-92765-1D-UNV-STD-W-4 (6500K)

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1566.7	1566.7	1566.7	1566.7	1566.7
2.5°	1576.0	1562.4	1566.7	1563.1	1557.5
5°	1572.5	1556.9	1562.4	1558.0	1556.6
7.5°	1561.2	1545.6	1552.8	1549.9	1548.5
10°	1550.8	1535.2	1543.5	1540.6	1539.2
12.5°	1536.9	1522.4	1531.9	1529.0	1528.7
15°	1513.1	1500.3	1513.1	1513.0	1511.6
17.5°	1483.2	1471.6	1485.2	1486.1	1485.2
20°	1462.3	1449.5	1466.6	1465.2	1466.6
22.5°	1436.8	1426.3	1444.6	1440.9	1442.3
25°	1397.0	1387.1	1407.2	1402.8	1402.8
27.5°	1350.0	1342.9	1364.8	1360.2	1360.2
30°	1318.7	1311.6	1334.6	1328.8	1328.8
32.5°	1283.9	1279.0	1301.0	1294.0	1294.0
35°	1228.7	1225.9	1247.6	1238.9	1238.9
37.5°	1171.9	1169.3	1189.0	1178.5	1175.1
40°	1130.1	1128.7	1146.0	1134.4	1134.4
42.5°	1088.3	1086.9	1101.9	1088.0	1088.0
45°	1024.2	1021.4	1031.4	1018.3	1015.5
47.5°	954.3	951.4	957.7	943.5	942.1
50°	906.7	903.8	906.7	893.6	892.2
52.5°	857.9	852.8	853.3	840.2	840.0
55°	783.4	773.4	773.2	761.6	761.6
57.5°	704.5	691.4	692.6	682.7	681.2
60°	649.9	635.7	636.9	628.1	626.7
62.5°	596.5	580.1	583.5	573.6	573.3
65°	507.7	496.4	497.6	493.2	493.2
67.5°	422.4	411.9	419.5	416.1	415.8
70°	359.8	352.7	362.7	362.6	361.2
72.5°	301.7	301.5	313.9	313.9	314.8
75°	219.1	229.0	242.3	243.7	243.7
77.5°	146.2	163.8	178.4	179.0	178.7
80°	104.4	124.3	137.8	140.7	139.3
82.5°	70.8	91.8	103.0	105.9	104.4
85°	31.9	48.9	58.0	59.4	58.0
87.5°	9.3	19.5	23.2	23.2	20.9
90°	0.0	0.0	0.0	0.0	0.0
92.5°	5.7	30.4	70.4	20.5	15.5
95°	18.6	73.9	332.0	114.9	70.8
97.5°	34.2	86.5	511.3	365.9	250.7
100°	45.1	94.1	550.3	557.4	429.3
102.5°	57.1	102.2	541.7	713.5	601.6
105°	75.8	115.0	497.3	878.4	835.1
107.5°	94.9	130.0	445.5	925.0	963.6
110°	108.1	140.9	415.7	907.2	993.9

TEST NUMBER: P561498

CATALOG NUMBER: SQ4-PC3-050U-100D-92765-1D-UNV-STD-W-4 (6500K)

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	120.6	151.8	395.7	865.1	988.8
115°	141.0	170.4	377.1	798.9	938.1
117.5°	158.9	186.4	366.1	726.5	874.0
120°	173.2	196.3	364.9	685.1	826.5
122.5°	184.6	207.7	362.1	648.9	780.1
125°	198.9	220.6	359.9	597.3	714.1
127.5°	214.5	234.8	358.8	566.5	662.8
130°	222.5	242.8	357.1	545.0	629.0
132.5°	231.1	250.9	357.1	528.3	605.5
135°	243.3	263.6	355.6	504.5	570.3
137.5°	254.7	274.5	355.5	484.4	541.3
140°	263.3	283.6	354.9	467.8	522.4
142.5°	273.1	290.0	356.6	454.5	503.5
145°	286.9	301.6	358.5	436.7	475.8
147.5°	298.8	313.1	361.6	418.7	452.5
150°	309.1	318.9	362.8	412.7	436.5
152.5°	317.1	327.5	363.9	404.7	426.8
155°	327.7	335.4	367.1	394.6	410.7
157.5°	340.9	345.5	367.8	390.1	401.6
160°	347.8	351.3	370.7	386.6	396.4
162.5°	351.8	355.8	371.2	383.7	391.3
165°	362.1	363.5	371.4	379.4	385.0
167.5°	369.1	367.8	374.7	378.3	380.5
170°	371.4	370.7	373.5	374.3	377.1
172.5°	376.5	374.2	375.2	373.1	375.4
175°	379.2	377.1	375.7	373.5	370.7
177.5°	380.4	377.0	375.2	373.0	373.5
180°	376.4	376.4	376.4	376.4	376.4

(END OF REPORT)