

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P523635

Luminaire Tested: **SQ4-PP3-025U-075D-92765-1D-UNV-STD-W-4 (4000K)**

Issue Date: 5/24/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P523635  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2103-172-1)  
Test Lab: INNOVATION CENTER  
Issue Date: 5/24/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PP3-025U-075D-92765-1D-UNV-STD-W-4 (4000K)  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS  
DOWNLIGHT 750 LUMENS PER FOOT  
UPLIGHT 250 LUMENS PER FOOT  
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 4000K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5035.2 lumens  
Efficiency: N/A  
Efficacy: 109.7 lumens/watt  
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33  
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')  
CIE Type: Semi-Direct

Input Watts (W): 45.9  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P523635  
CATALOG NUMBER: SQ4-PP3-025U-075D-92765-1D-UNV-STD-W-4 (4000K)

### Luminous Intensity Polar Plot





TEST NUMBER: P523635

CATALOG NUMBER: SQ4-PP3-025U-075D-92765-1D-UNV-STD-W-4 (4000K)

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	110	110	110	110	103	103	103	103	89	89	89	77	77	77	66	66	66	66	66	66	66	66	66	61		
1	100	96	92	89	94	90	87	84	79	76	74	68	67	65	59	58	56	56	56	56	56	56	56	52		
2	92	84	78	73	86	79	74	69	69	65	62	60	57	55	52	50	48	48	48	48	48	48	48	44		
3	84	74	67	61	78	70	63	58	61	56	52	54	50	46	46	43	41	41	41	41	41	41	41	37		
4	77	66	58	52	72	62	55	49	55	49	45	48	43	40	41	38	35	35	35	35	35	35	35	32		
5	71	59	51	45	66	55	48	42	49	43	39	43	38	35	37	34	31	31	31	31	31	31	31	28		
6	65	53	45	39	61	50	42	37	44	38	34	39	34	30	34	30	27	27	27	27	27	27	27	25		
7	60	48	40	34	56	45	38	33	40	34	30	35	31	27	31	27	24	24	24	24	24	24	24	22		
8	56	43	36	30	52	41	34	29	37	31	27	32	28	24	28	25	22	22	22	22	22	22	22	19		
9	52	40	32	27	49	38	31	26	34	28	24	30	25	22	26	22	20	20	20	20	20	20	20	18		
10	49	36	29	24	46	35	28	23	31	25	21	28	23	20	24	21	18	18	18	18	18	18	18	16		

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	11042	11042	11042
5°	11122	11054	11016
10°	11104	11025	10976
15°	11030	10970	10910
20°	10957	10895	10813
25°	10826	10752	10645
30°	10627	10570	10436
35°	10349	10278	10148
40°	10017	9954	9841
45°	9744	9675	9580
50°	9394	9334	9244
55°	8908	8791	8723
60°	8110	7877	7839
65°	7143	6846	6824
70°	6169	5913	5913
75°	5308	5233	5158
80°	4681	4739	4628
85°	3663	4001	4001



TEST NUMBER: P523635

CATALOG NUMBER: SQ4-PP3-025U-075D-92765-1D-UNV-STD-W-4 (4000K)

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	113.2	2.2
10°-20°	323.1	6.4
20°-30°	484.0	9.6
30°-40°	567.7	11.3
40°-50°	569.5	11.3
50°-60°	485.8	9.6
60°-70°	316.8	6.3
70°-80°	158.9	3.2
80°-90°	44.0	0.9
90°-100°	144.7	2.9
100°-110°	411.6	8.2
110°-120°	394.4	7.8
120°-130°	312.1	6.2
130°-140°	250.5	5.0
140°-150°	196.1	3.9
150°-160°	143.5	2.9
160°-170°	88.9	1.8
170°-180°	30.2	0.6
0°-30°	920.3	18.3
0°-40°	1488.0	29.6
0°-60°	2543.2	50.5
0°-90°	3063.0	60.8
90°-120°	950.7	18.9
90°-150°	1709.6	34.0
90°-180°	1972.0	39.2
0°-180°	5035.2	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1197	1197	1197	1197	1197	
5°	1201	1190	1194	1189	1189	114
15°	1155	1144	1148	1144	1142	326
25°	1064	1051	1056	1047	1046	489
35°	919	910	912	902	901	574
45°	747	742	742	734	734	575
55°	554	552	546	543	542	492
65°	327	321	314	312	313	327
75°	149	149	147	146	145	162
85°	35	38	38	38	38	41
90°	0	0	0	0	0	2
95°	16	62	280	97	60	18
105°	64	97	420	741	704	68
115°	119	144	318	674	791	117
125°	168	186	304	504	602	150
135°	205	222	300	426	481	158
145°	242	254	302	368	401	151
155°	276	283	310	333	346	128
165°	305	307	313	320	325	86
175°	320	318	317	315	313	30
180°	318	318	318	318	318	

TEST NUMBER: P523635

CATALOG NUMBER: SQ4-PP3-025U-075D-92765-1D-UNV-STD-W-4 (4000K)

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1196.8	1196.8	1196.8	1196.8	1196.8
2.5°	1204.3	1194.5	1196.8	1195.0	1190.0
5°	1200.9	1189.7	1193.6	1189.4	1189.4
7.5°	1192.8	1180.5	1184.4	1180.2	1180.0
10°	1185.2	1172.9	1176.8	1172.6	1171.6
12.5°	1174.3	1162.0	1166.8	1161.7	1161.5
15°	1154.8	1143.5	1148.5	1144.3	1142.2
17.5°	1132.8	1120.5	1126.5	1120.6	1119.8
20°	1116.0	1103.7	1109.7	1101.3	1101.3
22.5°	1095.9	1083.5	1090.4	1079.5	1079.5
25°	1063.5	1051.2	1056.2	1046.7	1045.7
27.5°	1025.2	1013.1	1018.2	1007.5	1007.3
30°	997.5	986.2	992.2	980.7	979.6
32.5°	967.3	956.8	961.2	949.6	948.6
35°	918.8	909.6	912.5	902.0	901.0
37.5°	867.8	858.4	861.7	852.7	852.3
40°	831.7	825.6	826.5	819.1	817.1
42.5°	798.2	791.2	792.1	784.7	784.3
45°	746.8	741.7	741.5	734.2	734.2
47.5°	692.2	688.4	687.2	681.1	680.9
50°	654.5	651.4	650.3	645.0	644.0
52.5°	615.1	613.6	610.0	605.6	605.4
55°	553.8	551.7	546.5	543.3	542.3
57.5°	487.3	483.2	477.2	472.6	473.5
60°	439.5	435.4	426.9	424.8	424.8
62.5°	393.3	388.4	379.9	377.0	378.6
65°	327.2	321.1	313.6	311.5	312.6
67.5°	267.3	261.7	253.6	253.6	252.8
70°	228.7	225.6	219.2	219.2	219.2
72.5°	194.2	192.8	188.2	188.1	187.3
75°	148.9	148.9	146.8	145.8	144.7
77.5°	111.6	112.0	111.0	109.9	108.0
80°	88.1	90.2	89.2	88.1	87.1
82.5°	66.3	68.3	68.2	66.3	66.1
85°	34.6	37.7	37.8	37.8	37.8
87.5°	9.2	12.5	13.4	13.4	14.3
90°	0.0	0.0	0.0	0.0	0.0
92.5°	4.8	25.6	59.4	17.3	13.0
95°	15.7	62.3	280.1	96.9	59.8
97.5°	28.9	73.0	431.3	308.6	211.5
100°	38.0	79.3	464.2	470.2	362.2
102.5°	48.2	86.2	456.9	601.8	507.5
105°	64.0	97.0	419.5	741.0	704.4
107.5°	80.0	109.7	375.8	780.2	812.8
110°	91.1	118.9	350.7	765.2	838.4

TEST NUMBER: P523635

CATALOG NUMBER: SQ4-PP3-025U-075D-92765-1D-UNV-STD-W-4 (4000K)

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	101.8	128.1	333.8	729.7	834.1
115°	118.9	143.7	318.1	673.9	791.3
117.5°	134.0	157.3	308.8	612.8	737.2
120°	146.1	165.5	307.8	577.9	697.2
122.5°	155.7	175.2	305.4	547.3	658.0
125°	167.8	186.1	303.6	503.8	602.4
127.5°	181.0	198.1	302.6	477.8	559.1
130°	187.7	204.8	301.2	459.7	530.6
132.5°	195.0	211.6	301.2	445.6	510.8
135°	205.2	222.3	300.0	425.6	481.1
137.5°	214.9	231.5	299.9	408.6	456.6
140°	222.1	239.2	299.4	394.6	440.6
142.5°	230.3	244.6	300.8	383.4	424.7
145°	242.0	254.4	302.4	368.3	401.4
147.5°	252.1	264.1	305.1	353.2	381.7
150°	260.8	269.0	306.0	348.1	368.2
152.5°	267.5	276.2	307.0	341.3	360.0
155°	276.4	282.9	309.6	332.9	346.5
157.5°	287.6	291.4	310.2	329.1	338.7
160°	293.3	296.3	312.7	326.1	334.4
162.5°	296.7	300.2	313.1	323.7	330.0
165°	305.4	306.6	313.3	320.0	324.7
167.5°	311.3	310.3	316.0	319.1	321.0
170°	313.3	312.7	315.1	315.7	318.1
172.5°	317.6	315.6	316.5	314.8	316.6
175°	319.9	318.1	316.9	315.0	312.7
177.5°	320.9	318.0	316.5	314.6	315.1
180°	317.5	317.5	317.5	317.5	317.5

(END OF REPORT)