

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P561507

Luminaire Tested: **SQ4-PC3-050U-125D-92765-1D-UNV-STD-W-4 (4000K)**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P561507
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2106-289-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PC3-050U-125D-92765-1D-UNV-STD-W-4 (4000K)
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 500 LUMENS PER FOOT
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7369.3 lumens
Efficiency: N/A
Efficacy: 102.9 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 71.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P561507
CATALOG NUMBER: SQ4-PC3-050U-125D-92765-1D-UNV-STD-W-4 (4000K)

Luminous Intensity Polar Plot





TEST NUMBER: P561507

CATALOG NUMBER: SQ4-PC3-050U-125D-92765-1D-UNV-STD-W-4 (4000K)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	112	112	112	112	106	106	106	106	94	94	94	84	84	84	74	74	74	70
1	102	98	94	90	97	93	89	86	83	80	78	74	72	70	66	64	63	59
2	93	86	79	74	88	81	75	71	73	68	65	65	62	59	58	55	53	49
3	85	75	68	62	80	71	65	59	64	59	54	58	53	50	51	48	45	42
4	78	67	58	52	73	63	56	50	57	51	46	51	46	43	46	42	39	36
5	71	59	51	45	67	57	49	43	51	45	40	46	41	37	41	37	34	31
6	66	53	45	39	62	51	43	38	46	40	35	42	36	32	37	33	30	27
7	61	48	40	34	58	46	38	33	42	35	31	38	33	29	34	30	26	24
8	57	44	36	30	53	42	35	29	38	32	27	35	29	26	31	27	24	21
9	53	40	32	27	50	38	31	26	35	29	25	32	27	23	29	25	21	19
10	49	37	29	24	47	35	28	24	32	26	22	30	24	21	27	23	19	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17399	17399	17399
5°	17529	17416	17351
10°	17487	17405	17356
15°	17395	17395	17378
20°	17280	17332	17332
25°	17118	17242	17189
30°	16909	17114	17039
35°	16657	16913	16796
40°	16382	16613	16445
45°	16084	16199	15948
50°	15664	15664	15413
55°	15167	14971	14745
60°	14433	14144	13919
65°	13341	13075	12961
70°	11680	11775	11729
75°	9400	10395	10455
80°	6679	8815	8905
85°	4065	7389	7389



TEST NUMBER: P561507

CATALOG NUMBER: SQ4-PC3-050U-125D-92765-1D-UNV-STD-W-4 (4000K)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	178.5	2.4
10°-20°	512.2	6.9
20°-30°	775.6	10.5
30°-40°	929.8	12.6
40°-50°	948.1	12.9
50°-60°	827.6	11.2
60°-70°	592.5	8.0
70°-80°	305.2	4.1
80°-90°	77.2	1.0
90°-100°	163.0	2.2
100°-110°	463.9	6.3
110°-120°	444.5	6.0
120°-130°	351.8	4.8
130°-140°	282.4	3.8
140°-150°	221.1	3.0
150°-160°	161.8	2.2
160°-170°	100.2	1.4
170°-180°	34.0	0.5
0°-30°	1466.2	19.9
0°-40°	2396.0	32.5
0°-60°	4171.8	56.6
0°-90°	5146.6	69.8
90°-120°	1071.5	14.5
90°-150°	1926.7	26.1
90°-180°	2223.0	30.2
0°-180°	7369.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1886	1886	1886	1886	1886	
5°	1893	1874	1880	1875	1874	180
15°	1821	1806	1821	1821	1819	513
25°	1682	1670	1694	1688	1688	774
35°	1479	1476	1502	1491	1491	925
45°	1233	1229	1242	1226	1222	949
55°	943	931	931	917	917	841
65°	611	598	599	594	594	604
75°	264	276	292	293	293	285
85°	38	59	70	72	70	52
90°	0	0	0	0	0	2
95°	18	70	316	109	67	20
105°	72	109	473	835	794	76
115°	134	162	358	760	892	132
125°	189	210	342	568	679	169
135°	231	251	338	480	542	178
145°	273	287	341	415	452	170
155°	312	319	349	375	390	144
165°	344	346	353	361	366	97
175°	360	358	357	355	352	34
180°	358	358	358	358	358	



TEST NUMBER: P561507

CATALOG NUMBER: SQ4-PC3-050U-125D-92765-1D-UNV-STD-W-4 (4000K)

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1885.8	1885.8	1885.8	1885.8	1885.8
2.5°	1896.9	1880.5	1885.8	1881.4	1874.6
5°	1892.7	1874.0	1880.5	1875.2	1873.5
7.5°	1879.1	1860.3	1869.0	1865.5	1863.8
10°	1866.6	1847.8	1857.8	1854.3	1852.6
12.5°	1849.8	1832.4	1843.9	1840.4	1840.0
15°	1821.2	1805.8	1821.2	1821.1	1819.4
17.5°	1785.2	1771.2	1787.6	1788.7	1787.6
20°	1760.0	1744.7	1765.3	1763.6	1765.3
22.5°	1729.3	1716.7	1738.7	1734.2	1736.0
25°	1681.5	1669.5	1693.7	1688.5	1688.5
27.5°	1624.9	1616.4	1642.7	1637.1	1637.1
30°	1587.2	1578.6	1606.4	1599.4	1599.4
32.5°	1545.3	1539.5	1565.9	1557.5	1557.5
35°	1478.9	1475.5	1501.6	1491.2	1491.2
37.5°	1410.5	1407.4	1431.1	1418.4	1414.3
40°	1360.2	1358.5	1379.4	1365.4	1365.4
42.5°	1309.9	1308.2	1326.3	1309.6	1309.6
45°	1232.7	1229.3	1241.5	1225.7	1222.3
47.5°	1148.6	1145.2	1152.8	1135.6	1133.9
50°	1091.3	1087.9	1091.3	1075.5	1073.8
52.5°	1032.6	1026.5	1027.0	1011.3	1011.0
55°	942.9	930.9	930.7	916.7	916.7
57.5°	847.9	832.2	833.6	821.7	820.0
60°	782.2	765.2	766.5	756.0	754.3
62.5°	718.0	698.2	702.3	690.4	690.0
65°	611.1	597.5	598.9	593.7	593.7
67.5°	508.5	495.8	505.0	500.8	500.4
70°	433.0	424.5	436.5	436.5	434.8
72.5°	363.2	362.8	377.9	377.9	378.9
75°	263.7	275.6	291.6	293.3	293.3
77.5°	176.0	197.2	214.8	215.5	215.1
80°	125.7	149.6	165.9	169.3	167.6
82.5°	85.2	110.5	124.0	127.4	125.7
85°	38.4	58.9	69.8	71.6	69.8
87.5°	11.2	23.5	27.9	27.9	25.1
90°	0.0	0.0	0.0	0.0	0.0
92.5°	5.4	28.9	66.9	19.5	14.7
95°	17.7	70.2	315.6	109.3	67.3
97.5°	32.5	82.3	486.1	347.8	238.4
100°	42.9	89.4	523.1	529.9	408.2
102.5°	54.3	97.1	515.0	678.3	572.0
105°	72.1	109.4	472.8	835.1	793.9
107.5°	90.2	123.6	423.5	879.3	916.0
110°	102.7	134.0	395.2	862.4	944.9



TEST NUMBER: P561507

CATALOG NUMBER: SQ4-PC3-050U-125D-92765-1D-UNV-STD-W-4 (4000K)

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	114.7	144.4	376.2	822.4	940.0
115°	134.0	161.9	358.5	759.5	891.8
117.5°	151.0	177.2	348.0	690.7	830.9
120°	164.6	186.6	346.9	651.3	785.7
122.5°	175.5	197.5	344.2	616.8	741.6
125°	189.1	209.7	342.2	567.8	678.9
127.5°	203.9	223.2	341.1	538.5	630.1
130°	211.6	230.9	339.5	518.1	598.0
132.5°	219.7	238.5	339.5	502.2	575.6
135°	231.3	250.6	338.1	479.6	542.2
137.5°	242.2	260.9	338.0	460.5	514.6
140°	250.3	269.6	337.4	444.7	496.6
142.5°	259.6	275.7	339.0	432.1	478.6
145°	272.8	286.8	340.8	415.1	452.4
147.5°	284.1	297.6	343.8	398.0	430.2
150°	293.9	303.2	344.9	392.3	415.0
152.5°	301.5	311.3	346.0	384.7	405.7
155°	311.6	318.9	349.0	375.2	390.5
157.5°	324.1	328.5	349.7	370.9	381.8
160°	330.6	333.9	352.4	367.6	376.9
162.5°	334.4	338.3	352.9	364.8	372.0
165°	344.2	345.5	353.1	360.7	366.0
167.5°	350.9	349.7	356.2	359.6	361.8
170°	353.1	352.4	355.1	355.8	358.5
172.5°	358.0	355.7	356.7	354.7	356.9
175°	360.5	358.5	357.1	355.0	352.4
177.5°	361.6	358.4	356.7	354.6	355.1
180°	357.8	357.8	357.8	357.8	357.8

(END OF REPORT)