

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P523636

Luminaire Tested: **SQ4-PP3-025U-075D-92765-1D-UNV-STD-W-4 (4500K)**

Issue Date: 5/24/2021

Test Information

Test Method: LM-79-2019
Report Number: P523636
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2103-172-1)
Test Lab: INNOVATION CENTER
Issue Date: 5/24/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PP3-025U-075D-92765-1D-UNV-STD-W-4 (4500K)
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 250 LUMENS PER FOOT
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 4500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5116.4 lumens
Efficiency: N/A
Efficacy: 111.5 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 45.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P523636

CATALOG NUMBER: SQ4-PP3-025U-075D-92765-1D-UNV-STD-W-4 (4500K)

Luminous Intensity Polar Plot





TEST NUMBER: P523636

CATALOG NUMBER: SQ4-PP3-025U-075D-92765-1D-UNV-STD-W-4 (4500K)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20				
RC	80					70					50					30				
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	110	110	110	110	103	103	103	103	89	89	89	77	77	77	66	66	66	61		
1	100	96	92	89	94	90	87	84	79	76	74	68	67	65	59	58	56	52		
2	92	84	78	73	86	79	74	69	69	65	62	60	57	55	52	50	48	44		
3	84	74	67	61	78	70	63	58	61	56	52	54	50	46	46	43	41	37		
4	77	66	58	52	72	62	55	49	55	49	45	48	43	40	41	38	35	32		
5	71	59	51	45	66	55	48	42	49	43	39	43	38	35	37	34	31	28		
6	65	53	45	39	61	50	42	37	44	38	34	39	34	30	34	30	27	25		
7	60	48	40	34	56	45	38	33	40	34	30	35	31	27	31	27	24	22		
8	56	43	36	30	52	41	34	29	37	31	26	32	28	24	28	25	22	19		
9	52	40	32	27	49	38	31	26	34	28	24	30	25	22	26	22	20	18		
10	49	36	29	24	46	35	28	23	31	25	21	28	23	20	24	21	18	16		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11220	11220	11220
5°	11302	11233	11193
10°	11283	11203	11153
15°	11208	11147	11086
20°	11134	11071	10988
25°	11002	10925	10817
30°	10798	10741	10604
35°	10515	10443	10311
40°	10180	10115	9999
45°	9901	9832	9734
50°	9545	9485	9393
55°	9051	8932	8863
60°	8241	8005	7964
65°	7259	6958	6934
70°	6266	6007	6007
75°	5393	5319	5244
80°	4755	4814	4702
85°	3726	4065	4065



TEST NUMBER: P523636

CATALOG NUMBER: SQ4-PP3-025U-075D-92765-1D-UNV-STD-W-4 (4500K)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	115.0	2.2
10°-20°	328.3	6.4
20°-30°	491.8	9.6
30°-40°	576.8	11.3
40°-50°	578.7	11.3
50°-60°	493.6	9.6
60°-70°	321.9	6.3
70°-80°	161.5	3.2
80°-90°	44.7	0.9
90°-100°	147.0	2.9
100°-110°	418.3	8.2
110°-120°	400.8	7.8
120°-130°	317.2	6.2
130°-140°	254.6	5.0
140°-150°	199.3	3.9
150°-160°	145.8	2.9
160°-170°	90.3	1.8
170°-180°	30.7	0.6
0°-30°	935.1	18.3
0°-40°	1512.0	29.6
0°-60°	2584.3	50.5
0°-90°	3112.4	60.8
90°-120°	966.1	18.9
90°-150°	1737.2	34.0
90°-180°	2004.0	39.2
0°-180°	5116.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1216	1216	1216	1216	1216	
5°	1220	1209	1213	1209	1209	116
15°	1173	1162	1167	1163	1161	331
25°	1081	1068	1073	1064	1063	497
35°	934	924	927	916	916	583
45°	759	754	754	746	746	584
55°	563	561	555	552	551	500
65°	332	326	319	317	318	332
75°	151	151	149	148	147	164
85°	35	38	38	38	38	41
90°	0	0	0	0	0	2
95°	16	63	285	98	61	18
105°	65	99	426	753	716	69
115°	121	146	323	685	804	119
125°	170	189	308	512	612	153
135°	208	226	305	432	489	161
145°	246	258	307	374	408	154
155°	281	288	315	338	352	130
165°	310	312	318	325	330	87
175°	325	323	322	320	318	31
180°	323	323	323	323	323	

TEST NUMBER: P523636

CATALOG NUMBER: SQ4-PP3-025U-075D-92765-1D-UNV-STD-W-4 (4500K)

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1216.1	1216.1	1216.1	1216.1	1216.1
2.5°	1223.7	1213.7	1216.1	1214.2	1209.2
5°	1220.3	1208.9	1212.9	1208.6	1208.6
7.5°	1212.0	1199.5	1203.5	1199.2	1199.0
10°	1204.3	1191.8	1195.8	1191.5	1190.5
12.5°	1193.2	1180.7	1185.6	1180.5	1180.2
15°	1173.4	1162.0	1167.0	1162.7	1160.6
17.5°	1151.0	1138.5	1144.6	1138.7	1137.8
20°	1134.0	1121.5	1127.6	1119.1	1119.1
22.5°	1113.5	1101.0	1108.0	1096.9	1096.9
25°	1080.7	1068.2	1073.2	1063.6	1062.6
27.5°	1041.7	1029.4	1034.7	1023.8	1023.6
30°	1013.6	1002.1	1008.2	996.5	995.4
32.5°	982.9	972.2	976.7	964.9	963.9
35°	933.6	924.2	927.2	916.5	915.5
37.5°	881.8	872.2	875.6	866.5	866.1
40°	845.2	838.9	839.8	832.3	830.2
42.5°	811.1	804.0	804.9	797.4	797.0
45°	758.8	753.6	753.5	746.0	746.0
47.5°	703.4	699.5	698.3	692.1	691.9
50°	665.0	661.9	660.8	655.4	654.4
52.5°	625.0	623.5	619.9	615.4	615.2
55°	562.7	560.6	555.3	552.1	551.0
57.5°	495.2	491.0	484.9	480.3	481.1
60°	446.6	442.4	433.8	431.6	431.6
62.5°	399.7	394.7	386.0	383.1	384.7
65°	332.5	326.3	318.7	316.6	317.6
67.5°	271.6	265.9	257.7	257.7	256.9
70°	232.3	229.2	222.7	222.7	222.7
72.5°	197.4	195.9	191.2	191.2	190.3
75°	151.3	151.3	149.2	148.1	147.1
77.5°	113.4	113.8	112.8	111.7	109.8
80°	89.5	91.6	90.6	89.5	88.5
82.5°	67.4	69.4	69.3	67.4	67.1
85°	35.2	38.3	38.4	38.4	38.4
87.5°	9.4	12.7	13.6	13.7	14.5
90°	0.0	0.0	0.0	0.0	0.0
92.5°	4.9	26.0	60.4	17.6	13.2
95°	15.9	63.3	284.6	98.5	60.7
97.5°	29.3	74.2	438.3	313.6	214.9
100°	38.6	80.6	471.7	477.7	368.0
102.5°	48.9	87.6	464.3	611.5	515.7
105°	65.0	98.6	426.3	752.9	715.8
107.5°	81.3	111.4	381.9	792.8	825.9
110°	92.6	120.8	356.3	777.6	851.9



TEST NUMBER: P523636

CATALOG NUMBER: SQ4-PP3-025U-075D-92765-1D-UNV-STD-W-4 (4500K)

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	103.4	130.2	339.2	741.5	847.5
115°	120.8	146.0	323.2	684.7	804.1
117.5°	136.2	159.8	313.8	622.7	749.1
120°	148.4	168.2	312.8	587.3	708.4
122.5°	158.2	178.0	310.3	556.2	668.7
125°	170.5	189.1	308.5	512.0	612.1
127.5°	183.9	201.3	307.5	485.6	568.1
130°	190.7	208.1	306.1	467.2	539.1
132.5°	198.1	215.0	306.1	452.8	519.0
135°	208.5	225.9	304.8	432.5	488.8
137.5°	218.3	235.3	304.7	415.2	463.9
140°	225.7	243.1	304.2	401.0	447.7
142.5°	234.0	248.6	305.7	389.6	431.5
145°	245.9	258.5	307.3	374.3	407.9
147.5°	256.1	268.4	310.0	358.8	387.9
150°	265.0	273.4	311.0	353.7	374.1
152.5°	271.8	280.7	311.9	346.8	365.8
155°	280.9	287.5	314.6	338.3	352.1
157.5°	292.2	296.2	315.3	334.4	344.2
160°	298.1	301.1	317.7	331.4	339.8
162.5°	301.5	305.0	318.2	328.9	335.4
165°	310.3	311.5	318.3	325.2	330.0
167.5°	316.4	315.3	321.1	324.3	326.2
170°	318.3	317.7	320.2	320.8	323.2
172.5°	322.7	320.7	321.6	319.8	321.8
175°	325.1	323.3	322.0	320.1	317.7
177.5°	326.0	323.2	321.6	319.7	320.2
180°	322.6	322.6	322.6	322.6	322.6

(END OF REPORT)