

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P561518

Luminaire Tested: **SQ4-PC3-075U-050D-92765-1D-UNV-STD-W-4 (3000K)**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P561518
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2106-289-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PC3-075U-050D-92765-1D-UNV-STD-W-4 (3000K)
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS
DOWNLIGHT 500 LUMENS PER FOOT
UPLIGHT 750 LUMENS PER FOOT
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5171.0 lumens
Efficiency: N/A
Efficacy: 116.5 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 44.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P561518
CATALOG NUMBER: SQ4-PC3-075U-050D-92765-1D-UNV-STD-W-4 (3000K)

Luminous Intensity Polar Plot





TEST NUMBER: P561518

CATALOG NUMBER: SQ4-PC3-075U-050D-92765-1D-UNV-STD-W-4 (3000K)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	95	95	95	95	77	77	77	60	60	60	45	45	45	38
1	95	91	87	84	86	83	80	77	67	65	63	53	52	50	40	39	38	32
2	87	79	73	68	78	72	67	63	59	55	52	47	44	42	35	34	32	27
3	79	70	63	57	71	64	57	52	52	48	44	41	38	36	31	29	27	23
4	72	62	54	48	65	56	50	44	46	41	37	37	33	30	28	26	24	20
5	66	55	47	41	60	50	43	38	41	36	32	33	29	26	25	23	21	17
6	61	49	41	35	55	45	38	33	37	32	28	30	26	23	23	20	18	15
7	56	44	36	31	51	40	34	29	33	28	24	27	23	20	21	18	16	13
8	52	40	32	27	47	37	30	25	30	25	22	25	21	18	19	16	14	12
9	48	36	29	24	44	33	27	22	28	23	19	23	19	16	17	15	13	11
10	45	33	26	22	41	31	24	20	26	21	17	21	17	14	16	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6695	6695	6695
5°	6744	6701	6676
10°	6728	6697	6678
15°	6693	6693	6686
20°	6649	6669	6669
25°	6586	6634	6613
30°	6506	6585	6556
35°	6409	6508	6462
40°	6303	6392	6328
45°	6189	6233	6136
50°	6027	6027	5931
55°	5836	5760	5673
60°	5554	5442	5355
65°	5132	5030	4986
70°	4494	4532	4513
75°	3615	4000	4025
80°	2572	3390	3427
85°	1567	2848	2848



TEST NUMBER: P561518

CATALOG NUMBER: SQ4-PC3-075U-050D-92765-1D-UNV-STD-W-4 (3000K)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	68.7	1.3
10°-20°	197.1	3.8
20°-30°	298.4	5.8
30°-40°	357.8	6.9
40°-50°	364.8	7.1
50°-60°	318.4	6.2
60°-70°	228.0	4.4
70°-80°	117.4	2.3
80°-90°	29.7	0.6
90°-100°	234.1	4.5
100°-110°	666.0	12.9
110°-120°	638.1	12.3
120°-130°	505.0	9.8
130°-140°	405.4	7.8
140°-150°	317.4	6.1
150°-160°	232.2	4.5
160°-170°	143.8	2.8
170°-180°	48.8	0.9
0°-30°	564.1	10.9
0°-40°	921.9	17.8
0°-60°	1605.1	31.0
0°-90°	1980.2	38.3
90°-120°	1538.2	29.7
90°-150°	2766.0	53.5
90°-180°	3191.0	61.7
0°-180°	5171.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	726	726	726	726	726	
5°	728	721	724	722	721	69
15°	701	695	701	701	700	198
25°	647	642	652	650	650	298
35°	569	568	578	574	574	356
45°	474	473	478	472	470	365
55°	363	358	358	353	353	323
65°	235	230	230	228	228	233
75°	101	106	112	113	113	110
85°	15	23	27	28	27	20
90°	0	0	0	0	0	2
95°	25	101	453	157	97	29
105°	104	157	679	1199	1140	110
115°	192	232	515	1090	1280	189
125°	272	301	491	815	975	243
135°	332	360	485	689	778	256
145°	392	412	489	596	649	245
155°	447	458	501	539	560	207
165°	494	496	507	518	525	139
175°	518	515	513	510	506	49
180°	514	514	514	514	514	



TEST NUMBER: P561518

CATALOG NUMBER: SQ4-PC3-075U-050D-92765-1D-UNV-STD-W-4 (3000K)

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	725.6	725.6	725.6	725.6	725.6
2.5°	729.9	723.5	725.6	723.9	721.3
5°	728.2	721.0	723.5	721.5	720.8
7.5°	723.0	715.8	719.1	717.7	717.1
10°	718.2	710.9	714.8	713.4	712.8
12.5°	711.7	705.0	709.4	708.1	708.0
15°	700.7	694.8	700.7	700.7	700.0
17.5°	686.9	681.5	687.8	688.2	687.8
20°	677.2	671.3	679.2	678.5	679.2
22.5°	665.4	660.5	669.0	667.3	667.9
25°	647.0	642.4	651.7	649.6	649.6
27.5°	625.2	621.9	632.0	629.9	629.9
30°	610.7	607.4	618.1	615.4	615.4
32.5°	594.5	592.3	602.5	599.3	599.3
35°	569.0	567.7	577.8	573.7	573.7
37.5°	542.7	541.5	550.6	545.7	544.2
40°	523.3	522.7	530.7	525.4	525.4
42.5°	504.0	503.3	510.3	503.9	503.9
45°	474.3	473.0	477.7	471.6	470.3
47.5°	441.9	440.6	443.5	436.9	436.3
50°	419.9	418.6	419.9	413.8	413.2
52.5°	397.3	394.9	395.2	389.1	389.0
55°	362.8	358.2	358.1	352.7	352.7
57.5°	326.2	320.2	320.7	316.1	315.5
60°	301.0	294.4	294.9	290.9	290.2
62.5°	276.2	268.6	270.2	265.6	265.5
65°	235.1	229.9	230.4	228.4	228.4
67.5°	195.6	190.8	194.3	192.7	192.5
70°	166.6	163.3	168.0	167.9	167.3
72.5°	139.7	139.6	145.4	145.4	145.8
75°	101.4	106.0	112.2	112.9	112.9
77.5°	67.7	75.9	82.6	82.9	82.8
80°	48.4	57.6	63.8	65.2	64.5
82.5°	32.8	42.5	47.7	49.0	48.4
85°	14.8	22.7	26.9	27.5	26.9
87.5°	4.3	9.0	10.7	10.7	9.7
90°	0.0	0.0	0.0	0.0	0.0
92.5°	7.8	41.4	96.1	28.0	21.1
95°	25.4	100.8	453.1	156.8	96.7
97.5°	46.7	118.1	697.9	499.4	342.2
100°	61.5	128.4	751.0	760.7	585.9
102.5°	77.9	139.4	739.3	973.7	821.1
105°	103.5	157.0	678.7	1198.9	1139.7
107.5°	129.5	177.4	608.0	1262.3	1315.0
110°	147.5	192.3	567.4	1238.0	1356.5



TEST NUMBER: P561518

CATALOG NUMBER: SQ4-PC3-075U-050D-92765-1D-UNV-STD-W-4 (3000K)

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	164.6	207.2	540.0	1180.6	1349.4
115°	192.4	232.5	514.7	1090.3	1280.3
117.5°	216.8	254.4	499.6	991.5	1192.8
120°	236.3	267.8	498.0	935.1	1127.9
122.5°	252.0	283.5	494.1	885.5	1064.7
125°	271.5	301.1	491.2	815.2	974.6
127.5°	292.8	320.5	489.7	773.1	904.5
130°	303.7	331.4	487.3	743.8	858.4
132.5°	315.4	342.4	487.3	721.0	826.4
135°	332.0	359.7	485.4	688.6	778.3
137.5°	347.7	374.6	485.2	661.1	738.7
140°	359.4	387.1	484.4	638.4	712.9
142.5°	372.7	395.8	486.7	620.3	687.1
145°	391.6	411.7	489.3	595.9	649.4
147.5°	407.8	427.3	493.6	571.4	617.6
150°	421.9	435.2	495.1	563.2	595.7
152.5°	432.8	446.9	496.7	552.3	582.4
155°	447.3	457.8	501.0	538.6	560.5
157.5°	465.2	471.5	502.0	532.4	548.0
160°	474.6	479.4	505.9	527.6	541.0
162.5°	480.1	485.6	506.6	523.7	534.0
165°	494.1	496.1	506.8	517.8	525.4
167.5°	503.7	502.0	511.3	516.3	519.3
170°	506.8	505.9	509.8	510.8	514.7
172.5°	513.9	510.6	512.1	509.3	512.3
175°	517.6	514.7	512.7	509.7	505.9
177.5°	519.1	514.6	512.1	509.0	509.8
180°	513.7	513.7	513.7	513.7	513.7

(END OF REPORT)