

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P561521

Luminaire Tested: **SQ4-PC3-075U-050D-92765-1D-UNV-STD-W-4 (4500K)**

Issue Date: 7/30/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P561521  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2106-289-1)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/30/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PC3-075U-050D-92765-1D-UNV-STD-W-4 (4500K)  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS  
DOWNLIGHT 500 LUMENS PER FOOT  
UPLIGHT 750 LUMENS PER FOOT  
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 4500K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5478.9 lumens  
Efficiency: N/A  
Efficacy: 123.4 lumens/watt  
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37  
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')  
CIE Type: Semi-Indirect

Input Watts (W): 44.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P561521  
CATALOG NUMBER: SQ4-PC3-075U-050D-92765-1D-UNV-STD-W-4 (4500K)

### Luminous Intensity Polar Plot





TEST NUMBER: P561521

CATALOG NUMBER: SQ4-PC3-075U-050D-92765-1D-UNV-STD-W-4 (4500K)

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	104	104	104	104	95	95	95	95	77	77	77	60	60	60	45	45	45	38				
1	95	91	87	84	86	83	80	77	67	65	63	53	52	50	40	39	38	32				
2	87	79	73	68	78	72	67	63	59	55	52	47	44	42	35	34	32	27				
3	79	70	63	57	71	64	57	52	52	48	44	41	38	36	31	29	27	23				
4	72	62	54	48	65	56	50	44	46	41	37	37	33	30	28	26	24	20				
5	66	55	47	41	60	50	43	38	41	36	32	33	29	26	25	23	21	17				
6	61	49	41	35	55	45	38	33	37	32	28	30	26	23	23	20	18	15				
7	56	44	36	31	51	40	34	29	33	28	24	27	23	20	21	18	16	13				
8	52	40	32	27	47	37	30	25	30	25	22	25	21	18	19	16	14	12				
9	48	36	29	24	44	33	27	22	28	23	19	23	19	16	17	15	13	11				
10	45	33	26	22	41	31	24	20	26	21	17	21	17	14	16	14	12	10				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	7093	7093	7093
5°	7146	7100	7074
10°	7129	7096	7075
15°	7091	7091	7084
20°	7045	7065	7065
25°	6978	7029	7007
30°	6893	6977	6946
35°	6791	6895	6847
40°	6678	6772	6704
45°	6557	6604	6502
50°	6386	6386	6284
55°	6183	6103	6011
60°	5884	5766	5674
65°	5438	5331	5283
70°	4761	4802	4780
75°	3832	4238	4263
80°	2726	3592	3629
85°	1662	3017	3017



TEST NUMBER: P561521

CATALOG NUMBER: SQ4-PC3-075U-050D-92765-1D-UNV-STD-W-4 (4500K)

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	72.8	1.3
10°-20°	208.8	3.8
20°-30°	316.2	5.8
30°-40°	379.1	6.9
40°-50°	386.5	7.1
50°-60°	337.4	6.2
60°-70°	241.5	4.4
70°-80°	124.4	2.3
80°-90°	31.5	0.6
90°-100°	248.0	4.5
100°-110°	705.7	12.9
110°-120°	676.1	12.3
120°-130°	535.1	9.8
130°-140°	429.5	7.8
140°-150°	336.2	6.1
150°-160°	246.0	4.5
160°-170°	152.4	2.8
170°-180°	51.7	0.9
0°-30°	597.7	10.9
0°-40°	976.8	17.8
0°-60°	1700.7	31.0
0°-90°	2098.1	38.3
90°-120°	1629.8	29.7
90°-150°	2930.6	53.5
90°-180°	3381.0	61.7
0°-180°	5478.9	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	769	769	769	769	769	
5°	772	764	767	764	764	73
15°	742	736	742	742	742	209
25°	686	681	690	688	688	315
35°	603	602	612	608	608	377
45°	502	501	506	500	498	387
55°	384	380	379	374	374	343
65°	249	244	244	242	242	246
75°	108	112	119	120	120	116
85°	16	24	28	29	28	21
90°	0	0	0	0	0	2
95°	27	107	480	166	102	31
105°	110	166	719	1270	1208	116
115°	204	246	545	1155	1356	201
125°	288	319	520	864	1033	257
135°	352	381	514	730	825	271
145°	415	436	518	631	688	259
155°	474	485	531	571	594	219
165°	524	526	537	549	557	147
175°	548	545	543	540	536	52
180°	544	544	544	544	544	

TEST NUMBER: P561521

CATALOG NUMBER: SQ4-PC3-075U-050D-92765-1D-UNV-STD-W-4 (4500K)

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	768.8	768.8	768.8	768.8	768.8
2.5°	773.3	766.6	768.8	767.0	764.2
5°	771.6	764.0	766.6	764.5	763.8
7.5°	766.1	758.4	761.9	760.5	759.8
10°	760.9	753.3	757.4	755.9	755.2
12.5°	754.1	747.0	751.7	750.2	750.1
15°	742.4	736.2	742.4	742.4	741.7
17.5°	727.8	722.1	728.8	729.2	728.8
20°	717.5	711.2	719.6	718.9	719.6
22.5°	705.0	699.8	708.8	707.0	707.7
25°	685.5	680.6	690.5	688.3	688.3
27.5°	662.4	658.9	669.7	667.4	667.4
30°	647.0	643.6	654.9	652.0	652.0
32.5°	630.0	627.6	638.4	634.9	634.9
35°	602.9	601.5	612.2	607.9	607.9
37.5°	575.0	573.8	583.4	578.2	576.6
40°	554.5	553.8	562.3	556.6	556.6
42.5°	534.0	533.3	540.7	533.9	533.9
45°	502.5	501.1	506.1	499.7	498.3
47.5°	468.2	466.8	469.9	462.9	462.3
50°	444.9	443.5	444.9	438.5	437.8
52.5°	421.0	418.5	418.7	412.3	412.1
55°	384.4	379.5	379.4	373.7	373.7
57.5°	345.7	339.3	339.8	335.0	334.3
60°	318.9	311.9	312.5	308.2	307.5
62.5°	292.7	284.6	286.3	281.4	281.3
65°	249.1	243.6	244.2	242.0	242.0
67.5°	207.3	202.1	205.9	204.1	204.0
70°	176.5	173.0	178.0	177.9	177.2
72.5°	148.1	147.9	154.0	154.0	154.5
75°	107.5	112.4	118.9	119.6	119.6
77.5°	71.8	80.4	87.6	87.8	87.7
80°	51.3	61.0	67.6	69.0	68.3
82.5°	34.7	45.0	50.5	51.9	51.3
85°	15.7	24.0	28.5	29.2	28.5
87.5°	4.6	9.6	11.4	11.4	10.3
90°	0.0	0.0	0.0	0.0	0.0
92.5°	8.3	43.9	101.8	29.6	22.3
95°	26.9	106.8	480.1	166.2	102.4
97.5°	49.5	125.1	739.4	529.1	362.6
100°	65.2	136.0	795.7	806.0	620.8
102.5°	82.6	147.7	783.3	1031.7	870.0
105°	109.7	166.3	719.1	1270.2	1207.5
107.5°	137.2	188.0	644.2	1337.5	1393.4
110°	156.2	203.8	601.2	1311.8	1437.2

TEST NUMBER: P561521

CATALOG NUMBER: SQ4-PC3-075U-050D-92765-1D-UNV-STD-W-4 (4500K)

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	174.5	219.6	572.2	1250.9	1429.8
115°	203.8	246.3	545.3	1155.2	1356.5
117.5°	229.7	269.6	529.4	1050.5	1263.8
120°	250.4	283.8	527.7	990.7	1195.1
122.5°	267.0	300.3	523.6	938.3	1128.1
125°	287.7	319.0	520.5	863.7	1032.7
127.5°	310.2	339.5	518.8	819.1	958.4
130°	321.8	351.1	516.3	788.1	909.5
132.5°	334.2	362.7	516.3	763.9	875.6
135°	351.8	381.1	514.3	729.6	824.7
137.5°	368.4	396.9	514.0	700.5	782.7
140°	380.8	410.1	513.2	676.4	755.3
142.5°	394.8	419.3	515.7	657.2	728.0
145°	414.9	436.2	518.4	631.4	688.1
147.5°	432.1	452.7	522.9	605.4	654.4
150°	447.0	461.2	524.6	596.8	631.2
152.5°	458.6	473.6	526.3	585.1	617.1
155°	473.9	485.0	530.8	570.7	593.9
157.5°	492.9	499.6	531.8	564.1	580.7
160°	502.9	507.9	536.0	559.1	573.2
162.5°	508.7	514.5	536.8	554.9	565.8
165°	523.6	525.6	537.0	548.6	556.7
167.5°	533.7	531.9	541.8	547.0	550.3
170°	537.0	536.0	540.1	541.3	545.3
172.5°	544.5	541.0	542.6	539.6	542.8
175°	548.4	545.4	543.2	540.0	536.0
177.5°	550.1	545.2	542.6	539.3	540.1
180°	544.3	544.3	544.3	544.3	544.3

(END OF REPORT)