

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P561530

Luminaire Tested: **SQ4-PC3-075U-075D-92765-1D-UNV-STD-W-4 (2700K)**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P561530
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2106-289-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PC3-075U-075D-92765-1D-UNV-STD-W-4 (2700K)
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 750 LUMENS PER FOOT
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6031.3 lumens
Efficiency: N/A
Efficacy: 108.9 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 55.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P561530
CATALOG NUMBER: SQ4-PC3-075U-075D-92765-1D-UNV-STD-W-4 (2700K)

Luminous Intensity Polar Plot





TEST NUMBER: P561530

CATALOG NUMBER: SQ4-PC3-075U-075D-92765-1D-UNV-STD-W-4 (2700K)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	98	98	98	98	82	82	82	68	68	68	54	54	54	48
1	97	93	89	86	90	86	83	80	72	70	68	60	58	57	48	47	46	41
2	89	81	75	70	81	75	70	65	63	59	56	52	50	47	42	41	39	34
3	81	71	64	58	74	66	60	55	56	51	47	46	43	40	38	35	33	29
4	74	63	55	49	68	58	52	46	50	44	40	41	37	34	34	31	28	25
5	68	56	48	42	62	52	45	40	44	39	35	37	33	30	30	27	25	21
6	62	50	42	37	57	47	40	34	40	34	30	33	29	26	27	24	22	19
7	58	45	38	32	53	42	35	30	36	30	26	30	26	23	25	22	19	17
8	54	41	33	28	49	38	31	27	33	27	23	28	23	20	23	20	17	15
9	50	38	30	25	46	35	28	24	30	25	21	25	21	18	21	18	16	13
10	47	34	27	22	43	32	26	21	28	22	19	23	19	16	20	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9821	9821	9821
5°	9896	9832	9795
10°	9872	9826	9798
15°	9820	9820	9811
20°	9755	9784	9784
25°	9663	9733	9704
30°	9546	9661	9619
35°	9404	9548	9481
40°	9249	9379	9283
45°	9080	9144	9003
50°	8843	8843	8701
55°	8562	8451	8324
60°	8149	7984	7857
65°	7532	7381	7316
70°	6596	6647	6620
75°	5304	5868	5903
80°	3772	4973	5026
85°	2297	4171	4171



TEST NUMBER: P561530

CATALOG NUMBER: SQ4-PC3-075U-075D-92765-1D-UNV-STD-W-4 (2700K)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	100.7	1.7
10°-20°	289.1	4.8
20°-30°	437.8	7.3
30°-40°	524.9	8.7
40°-50°	535.2	8.9
50°-60°	467.2	7.7
60°-70°	334.5	5.5
70°-80°	172.3	2.9
80°-90°	43.6	0.7
90°-100°	229.3	3.8
100°-110°	652.5	10.8
110°-120°	625.2	10.4
120°-130°	494.8	8.2
130°-140°	397.1	6.6
140°-150°	310.9	5.2
150°-160°	227.5	3.8
160°-170°	140.9	2.3
170°-180°	47.8	0.8
0°-30°	827.7	13.7
0°-40°	1352.6	22.4
0°-60°	2355.1	39.0
0°-90°	2905.4	48.2
90°-120°	1507.0	25.0
90°-150°	2709.8	44.9
90°-180°	3126.0	51.8
0°-180°	6031.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1064	1064	1064	1064	1064	
5°	1068	1058	1062	1059	1058	101
15°	1028	1019	1028	1028	1027	290
25°	949	942	956	953	953	437
35°	835	833	848	842	842	522
45°	696	694	701	692	690	536
55°	532	526	525	518	518	475
65°	345	337	338	335	335	341
75°	149	156	165	166	166	161
85°	22	33	39	40	39	29
90°	0	0	0	0	0	2
95°	25	99	444	154	95	28
105°	101	154	665	1174	1116	107
115°	188	228	504	1068	1254	186
125°	266	295	481	799	955	238
135°	325	352	476	675	762	251
145°	384	403	479	584	636	240
155°	438	448	491	528	549	203
165°	484	486	496	507	515	136
175°	507	504	502	499	496	48
180°	503	503	503	503	503	

TEST NUMBER: P561530

CATALOG NUMBER: SQ4-PC3-075U-075D-92765-1D-UNV-STD-W-4 (2700K)

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1064.5	1064.5	1064.5	1064.5	1064.5
2.5°	1070.9	1061.6	1064.5	1062.1	1058.2
5°	1068.5	1057.9	1061.6	1058.6	1057.6
7.5°	1060.8	1050.2	1055.1	1053.1	1052.1
10°	1053.7	1043.1	1048.8	1046.8	1045.8
12.5°	1044.2	1034.4	1040.9	1038.9	1038.7
15°	1028.1	1019.4	1028.1	1028.1	1027.1
17.5°	1007.8	999.9	1009.2	1009.7	1009.2
20°	993.6	984.9	996.5	995.6	996.5
22.5°	976.2	969.1	981.6	979.0	980.0
25°	949.2	942.5	956.1	953.2	953.2
27.5°	917.3	912.5	927.3	924.2	924.2
30°	896.0	891.2	906.8	902.9	902.9
32.5°	872.3	869.1	884.0	879.2	879.2
35°	834.9	833.0	847.7	841.8	841.8
37.5°	796.2	794.5	807.9	800.7	798.4
40°	767.9	766.9	778.7	770.8	770.8
42.5°	739.5	738.5	748.7	739.3	739.3
45°	695.9	694.0	700.8	691.9	690.0
47.5°	648.4	646.5	650.8	641.1	640.1
50°	616.1	614.1	616.1	607.2	606.2
52.5°	582.9	579.5	579.8	570.9	570.7
55°	532.3	525.5	525.4	517.5	517.5
57.5°	478.7	469.8	470.6	463.8	462.9
60°	441.6	432.0	432.7	426.8	425.8
62.5°	405.3	394.1	396.4	389.7	389.5
65°	345.0	337.3	338.1	335.1	335.1
67.5°	287.0	279.9	285.1	282.7	282.5
70°	244.5	239.6	246.4	246.4	245.4
72.5°	205.0	204.8	213.3	213.3	213.9
75°	148.8	155.6	164.6	165.6	165.6
77.5°	99.4	111.3	121.2	121.6	121.4
80°	71.0	84.5	93.6	95.6	94.6
82.5°	48.1	62.4	70.0	71.9	71.0
85°	21.7	33.3	39.4	40.4	39.4
87.5°	6.3	13.2	15.8	15.7	14.2
90°	0.0	0.0	0.0	0.0	0.0
92.5°	7.7	40.6	94.1	27.4	20.7
95°	24.9	98.8	443.9	153.7	94.7
97.5°	45.7	115.7	683.7	489.2	335.2
100°	60.3	125.8	735.7	745.2	574.0
102.5°	76.3	136.6	724.3	953.9	804.4
105°	101.4	153.8	664.9	1174.5	1116.5
107.5°	126.9	173.8	595.7	1236.7	1288.3
110°	144.5	188.4	555.9	1212.9	1328.9

TEST NUMBER: P561530

CATALOG NUMBER: SQ4-PC3-075U-075D-92765-1D-UNV-STD-W-4 (2700K)

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	161.3	203.0	529.1	1156.6	1322.0
115°	188.5	227.8	504.2	1068.1	1254.3
117.5°	212.4	249.3	489.5	971.4	1168.6
120°	231.5	262.4	487.9	916.1	1105.0
122.5°	246.8	277.7	484.1	867.5	1043.0
125°	266.0	295.0	481.2	798.6	954.8
127.5°	286.8	314.0	479.7	757.4	886.1
130°	297.5	324.7	477.4	728.7	841.0
132.5°	309.0	335.4	477.4	706.3	809.6
135°	325.3	352.4	475.5	674.6	762.5
137.5°	340.6	367.0	475.3	647.7	723.7
140°	352.1	379.2	474.5	625.5	698.4
142.5°	365.1	387.7	476.8	607.7	673.2
145°	383.7	403.3	479.3	583.8	636.2
147.5°	399.5	418.6	483.5	559.8	605.0
150°	413.3	426.4	485.1	551.8	583.6
152.5°	424.0	437.9	486.6	541.0	570.6
155°	438.2	448.5	490.8	527.7	549.2
157.5°	455.8	462.0	491.8	521.6	536.9
160°	465.0	469.7	495.6	516.9	530.0
162.5°	470.3	475.8	496.4	513.0	523.1
165°	484.1	486.0	496.5	507.2	514.7
167.5°	493.5	491.8	500.9	505.8	508.8
170°	496.5	495.6	499.4	500.5	504.2
172.5°	503.4	500.3	501.7	498.9	501.9
175°	507.1	504.3	502.3	499.3	495.6
177.5°	508.6	504.1	501.7	498.7	499.4
180°	503.2	503.2	503.2	503.2	503.2

(END OF REPORT)