

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P561558

Luminaire Tested: **SQ4-PC3-075U-125D-92765-1D-UNV-STD-W-4 (3500K)**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P561558
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2106-289-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PC3-075U-125D-92765-1D-UNV-STD-W-4 (3500K)
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 750 LUMENS PER FOOT
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8321.5 lumens
Efficiency: N/A
Efficacy: 104.7 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 79.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P561558
CATALOG NUMBER: SQ4-PC3-075U-125D-92765-1D-UNV-STD-W-4 (3500K)

Luminous Intensity Polar Plot





TEST NUMBER: P561558

CATALOG NUMBER: SQ4-PC3-075U-125D-92765-1D-UNV-STD-W-4 (3500K)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	89	89	89	77	77	77	66	66	66	61
1	100	96	92	88	94	90	86	83	78	76	74	68	66	64	58	57	56	51
2	91	84	78	72	85	79	73	68	69	65	61	60	57	54	51	49	47	43
3	83	74	66	60	78	69	63	57	61	56	51	53	49	46	46	43	40	36
4	76	65	57	51	71	61	54	48	54	48	44	47	43	39	41	37	34	31
5	70	58	50	44	65	55	47	42	48	42	38	42	38	34	37	33	30	27
6	64	52	44	38	60	49	42	36	43	37	33	38	33	30	33	29	26	24
7	60	47	39	33	56	44	37	32	39	33	29	35	30	26	30	26	23	21
8	55	43	35	29	52	40	33	28	36	30	26	32	27	23	28	24	21	19
9	52	39	31	26	48	37	30	25	33	27	23	29	24	21	26	22	19	17
10	48	36	29	24	45	34	27	23	30	25	21	27	22	19	24	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17086	17086	17086
5°	17214	17103	17040
10°	17173	17092	17044
15°	17082	17082	17066
20°	16970	17021	17021
25°	16810	16932	16879
30°	16606	16806	16733
35°	16359	16609	16494
40°	16088	16315	16150
45°	15796	15908	15661
50°	15383	15383	15136
55°	14893	14700	14480
60°	14175	13891	13670
65°	13101	12839	12728
70°	11470	11564	11519
75°	9229	10209	10270
80°	6562	8655	8745
85°	3991	7262	7262



TEST NUMBER: P561558

CATALOG NUMBER: SQ4-PC3-075U-125D-92765-1D-UNV-STD-W-4 (3500K)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	175.3	2.1
10°-20°	502.9	6.0
20°-30°	761.6	9.2
30°-40°	913.1	11.0
40°-50°	931.1	11.2
50°-60°	812.8	9.8
60°-70°	581.9	7.0
70°-80°	299.7	3.6
80°-90°	75.8	0.9
90°-100°	239.7	2.9
100°-110°	682.0	8.2
110°-120°	653.4	7.9
120°-130°	517.2	6.2
130°-140°	415.1	5.0
140°-150°	325.0	3.9
150°-160°	237.8	2.9
160°-170°	147.3	1.8
170°-180°	50.0	0.6
0°-30°	1439.9	17.3
0°-40°	2353.0	28.3
0°-60°	4096.8	49.2
0°-90°	5054.1	60.7
90°-120°	1575.1	18.9
90°-150°	2832.3	34.0
90°-180°	3267.0	39.3
0°-180°	8321.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1852	1852	1852	1852	1852	
5°	1859	1840	1847	1842	1840	176
15°	1788	1773	1788	1788	1787	504
25°	1651	1640	1663	1658	1658	760
35°	1452	1449	1475	1464	1464	908
45°	1211	1207	1219	1204	1200	932
55°	926	914	914	900	900	825
65°	600	587	588	583	583	594
75°	259	271	286	288	288	280
85°	38	58	69	70	69	51
90°	0	0	0	0	0	3
95°	26	103	464	161	99	30
105°	106	161	695	1228	1167	112
115°	197	238	527	1116	1311	194
125°	278	308	503	835	998	249
135°	340	368	497	705	797	262
145°	401	422	501	610	665	250
155°	458	469	513	552	574	212
165°	506	508	519	530	538	142
175°	530	527	525	522	518	50
180°	526	526	526	526	526	



TEST NUMBER: P561558

CATALOG NUMBER: SQ4-PC3-075U-125D-92765-1D-UNV-STD-W-4 (3500K)

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1851.9	1851.9	1851.9	1851.9	1851.9
2.5°	1862.9	1846.8	1851.9	1847.6	1840.9
5°	1858.7	1840.3	1846.7	1841.6	1839.9
7.5°	1845.4	1826.9	1835.4	1832.0	1830.3
10°	1833.0	1814.6	1824.4	1821.0	1819.3
12.5°	1816.6	1799.5	1810.7	1807.3	1807.0
15°	1788.4	1773.4	1788.4	1788.4	1786.7
17.5°	1753.1	1739.4	1755.5	1756.5	1755.5
20°	1728.4	1713.3	1733.6	1731.9	1733.6
22.5°	1698.2	1685.8	1707.5	1703.1	1704.8
25°	1651.3	1639.5	1663.3	1658.1	1658.1
27.5°	1595.7	1587.3	1613.2	1607.7	1607.7
30°	1558.7	1550.3	1577.5	1570.7	1570.7
32.5°	1517.5	1511.8	1537.8	1529.5	1529.5
35°	1452.4	1449.0	1474.6	1464.4	1464.4
37.5°	1385.1	1382.1	1405.4	1392.9	1388.9
40°	1335.8	1334.1	1354.6	1340.9	1340.9
42.5°	1286.4	1284.7	1302.5	1286.0	1286.0
45°	1210.6	1207.2	1219.2	1203.6	1200.3
47.5°	1127.9	1124.6	1132.1	1115.2	1113.5
50°	1071.7	1068.3	1071.7	1056.2	1054.5
52.5°	1014.1	1008.0	1008.6	993.2	992.8
55°	925.9	914.2	913.9	900.2	900.2
57.5°	832.7	817.2	818.6	806.9	805.2
60°	768.2	751.4	752.8	742.4	740.8
62.5°	705.1	685.6	689.7	678.0	677.7
65°	600.1	586.7	588.1	583.0	583.0
67.5°	499.3	486.9	495.9	491.8	491.4
70°	425.2	416.9	428.7	428.6	427.0
72.5°	356.7	356.3	371.1	371.1	372.1
75°	258.9	270.7	286.4	288.1	288.1
77.5°	172.8	193.6	210.9	211.6	211.3
80°	123.5	146.9	162.9	166.3	164.6
82.5°	83.7	108.5	121.7	125.1	123.5
85°	37.7	57.8	68.6	70.3	68.6
87.5°	11.0	23.0	27.4	27.4	24.7
90°	0.0	0.0	0.0	0.0	0.0
92.5°	8.0	42.4	98.4	28.6	21.6
95°	26.0	103.2	464.0	160.6	99.0
97.5°	47.8	120.9	714.6	511.3	350.4
100°	63.0	131.4	769.0	778.9	600.0
102.5°	79.8	142.8	757.0	997.0	840.8
105°	106.0	160.8	695.0	1227.6	1167.0
107.5°	132.6	181.7	622.6	1292.6	1346.6
110°	151.0	197.0	581.0	1267.8	1389.0

TEST NUMBER: P561558

CATALOG NUMBER: SQ4-PC3-075U-125D-92765-1D-UNV-STD-W-4 (3500K)

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	168.6	212.2	553.0	1208.9	1381.8
115°	197.0	238.1	527.0	1116.4	1311.0
117.5°	222.0	260.5	511.6	1015.3	1221.4
120°	242.0	274.3	510.0	957.5	1155.0
122.5°	258.0	290.3	506.0	906.8	1090.2
125°	278.0	308.3	503.0	834.7	998.0
127.5°	299.8	328.2	501.4	791.7	926.2
130°	311.0	339.4	499.0	761.7	879.0
132.5°	323.0	350.6	499.0	738.3	846.2
135°	340.0	368.4	497.0	705.1	797.0
137.5°	356.0	383.6	496.8	677.0	756.4
140°	368.0	396.4	496.0	653.7	730.0
142.5°	381.6	405.3	498.4	635.2	703.6
145°	401.0	421.5	501.0	610.2	665.0
147.5°	417.6	437.5	505.4	585.1	632.4
150°	432.0	445.7	507.0	576.8	610.0
152.5°	443.2	457.7	508.6	565.5	596.4
155°	458.0	468.8	513.0	551.5	574.0
157.5°	476.4	482.9	514.0	545.2	561.2
160°	486.0	490.9	518.0	540.3	554.0
162.5°	491.6	497.3	518.8	536.2	546.8
165°	506.0	508.0	519.0	530.2	538.0
167.5°	515.8	514.0	523.6	528.7	531.8
170°	519.0	518.0	522.0	523.1	527.0
172.5°	526.2	522.9	524.4	521.5	524.6
175°	530.0	527.1	525.0	521.9	518.0
177.5°	531.6	526.9	524.4	521.2	522.0
180°	526.0	526.0	526.0	526.0	526.0

(END OF REPORT)