

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P523675

Luminaire Tested: **SQ4-PP3-050U-050D-92765-1D-UNV-STD-W-4 (4500K)**

Issue Date: 5/24/2021

Test Information

Test Method: LM-79-2019
Report Number: P523675
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2103-172-1)
Test Lab: INNOVATION CENTER
Issue Date: 5/24/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PP3-050U-050D-92765-1D-UNV-STD-W-4 (4500K)
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS
DOWNLIGHT 500 LUMENS PER FOOT
UPLIGHT 500 LUMENS PER FOOT
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 4500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4336.8 lumens
Efficiency: N/A
Efficacy: 118.8 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 36.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P523675
CATALOG NUMBER: SQ4-PP3-050U-050D-92765-1D-UNV-STD-W-4 (4500K)

Luminous Intensity Polar Plot





TEST NUMBER: P523675

CATALOG NUMBER: SQ4-PP3-050U-050D-92765-1D-UNV-STD-W-4 (4500K)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	107	107	107	107	98	98	98	98	82	82	82	68	68	68	54	54	54	48				48
1	98	93	90	86	90	86	83	80	72	70	68	60	58	57	48	47	46				41	
2	89	82	76	71	82	75	70	66	64	60	56	53	50	48	43	41	39				34	
3	81	72	65	59	74	66	60	55	56	51	48	47	43	40	38	36	33				29	
4	74	64	56	50	68	59	52	47	50	45	41	42	38	35	34	31	29				25	
5	68	57	49	43	63	53	45	40	45	39	35	37	33	30	31	28	25				22	
6	63	51	43	37	58	47	40	35	40	35	31	34	30	26	28	25	22				19	
7	58	46	38	33	53	43	36	31	37	31	27	31	27	23	25	22	20				17	
8	54	42	34	29	50	39	32	27	33	28	24	28	24	21	23	20	18				15	
9	50	38	31	26	46	35	29	24	31	25	21	26	22	19	21	18	16				14	
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	20	17	15				13	

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7492	7492	7492
5°	7546	7501	7474
10°	7534	7481	7447
15°	7484	7444	7403
20°	7434	7392	7336
25°	7346	7295	7223
30°	7210	7172	7081
35°	7021	6973	6885
40°	6796	6754	6677
45°	6611	6564	6500
50°	6374	6333	6272
55°	6043	5964	5918
60°	5503	5344	5318
65°	4846	4646	4630
70°	4184	4011	4011
75°	3604	3550	3501
80°	3177	3214	3140
85°	2488	2710	2710



TEST NUMBER: P523675

CATALOG NUMBER: SQ4-PP3-050U-050D-92765-1D-UNV-STD-W-4 (4500K)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	76.8	1.8
10°-20°	219.2	5.1
20°-30°	328.4	7.6
30°-40°	385.2	8.9
40°-50°	386.4	8.9
50°-60°	329.6	7.6
60°-70°	215.0	5.0
70°-80°	107.9	2.5
80°-90°	29.9	0.7
90°-100°	165.7	3.8
100°-110°	471.4	10.9
110°-120°	451.7	10.4
120°-130°	357.5	8.2
130°-140°	286.9	6.6
140°-150°	224.6	5.2
150°-160°	164.4	3.8
160°-170°	101.8	2.3
170°-180°	34.5	0.8
0°-30°	624.4	14.4
0°-40°	1009.6	23.3
0°-60°	1725.6	39.8
0°-90°	2078.3	47.9
90°-120°	1088.8	25.1
90°-150°	1957.8	45.1
90°-180°	2259.0	52.1
0°-180°	4336.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	812	812	812	812	812	
5°	815	807	810	807	807	77
15°	784	776	779	776	775	221
25°	722	713	717	710	710	332
35°	623	617	619	612	611	389
45°	507	503	503	498	498	390
55°	376	374	371	369	368	334
65°	222	218	213	211	212	222
75°	101	101	100	99	98	110
85°	24	26	26	26	26	28
90°	0	0	0	0	0	2
95°	18	71	321	111	68	21
105°	73	111	480	849	807	78
115°	136	165	364	772	906	134
125°	192	213	348	577	690	172
135°	235	255	344	487	551	181
145°	277	291	346	422	460	173
155°	317	324	355	381	397	146
165°	350	351	359	366	372	98
175°	366	364	363	361	358	35
180°	364	364	364	364	364	



TEST NUMBER: P523675

CATALOG NUMBER: SQ4-PP3-050U-050D-92765-1D-UNV-STD-W-4 (4500K)

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	812.0	812.0	812.0	812.0	812.0
2.5°	817.1	810.4	812.0	810.8	807.4
5°	814.8	807.2	809.9	807.0	807.0
7.5°	809.3	800.9	803.6	800.7	800.6
10°	804.2	795.8	798.5	795.6	794.9
12.5°	796.8	788.4	791.6	788.2	788.1
15°	783.5	775.9	779.3	776.4	775.0
17.5°	768.6	760.2	764.3	760.3	759.8
20°	757.2	748.8	752.9	747.2	747.2
22.5°	743.5	735.2	739.8	732.4	732.4
25°	721.6	713.3	716.6	710.2	709.5
27.5°	695.6	687.4	690.9	683.6	683.5
30°	676.8	669.1	673.2	665.4	664.7
32.5°	656.3	649.2	652.2	644.3	643.6
35°	623.4	617.1	619.1	612.0	611.3
37.5°	588.8	582.4	584.7	578.6	578.3
40°	564.3	560.2	560.8	555.8	554.4
42.5°	541.6	536.8	537.4	532.4	532.2
45°	506.7	503.2	503.1	498.2	498.2
47.5°	469.7	467.0	466.3	462.1	462.0
50°	444.1	442.0	441.2	437.6	437.0
52.5°	417.3	416.3	413.9	410.9	410.8
55°	375.7	374.4	370.8	368.6	367.9
57.5°	330.6	327.8	323.8	320.7	321.2
60°	298.2	295.4	289.6	288.2	288.2
62.5°	266.9	263.5	257.8	255.8	256.9
65°	222.0	217.9	212.8	211.4	212.1
67.5°	181.3	177.6	172.1	172.1	171.5
70°	155.1	153.1	148.7	148.7	148.7
72.5°	131.8	130.8	127.7	127.7	127.1
75°	101.1	101.1	99.6	98.9	98.2
77.5°	75.7	76.0	75.3	74.6	73.3
80°	59.8	61.2	60.5	59.8	59.1
82.5°	45.0	46.4	46.3	45.0	44.8
85°	23.5	25.6	25.6	25.6	25.6
87.5°	6.3	8.5	9.1	9.1	9.7
90°	0.0	0.0	0.0	0.0	0.0
92.5°	5.5	29.3	68.0	19.8	14.9
95°	18.0	71.4	320.7	111.0	68.4
97.5°	33.0	83.6	494.0	353.5	242.2
100°	43.5	90.9	531.6	538.4	414.7
102.5°	55.2	98.7	523.3	689.2	581.2
105°	73.3	111.1	480.4	848.6	806.7
107.5°	91.7	125.6	430.4	893.5	930.8
110°	104.4	136.1	401.6	876.3	960.1

TEST NUMBER: P523675

CATALOG NUMBER: SQ4-PP3-050U-050D-92765-1D-UNV-STD-W-4 (4500K)

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	116.5	146.7	382.3	835.7	955.2
115°	136.2	164.6	364.3	771.7	906.2
117.5°	153.5	180.1	353.6	701.8	844.3
120°	167.3	189.6	352.5	661.9	798.4
122.5°	178.3	200.6	349.8	626.8	753.6
125°	192.2	213.1	347.7	577.0	689.9
127.5°	207.2	226.8	346.6	547.2	640.2
130°	215.0	234.6	344.9	526.5	607.6
132.5°	223.3	242.3	344.9	510.3	584.9
135°	235.0	254.6	343.5	487.4	550.9
137.5°	246.1	265.1	343.4	468.0	522.9
140°	254.4	274.0	342.9	451.9	504.6
142.5°	263.8	280.1	344.5	439.0	486.4
145°	277.2	291.4	346.3	421.8	459.7
147.5°	288.7	302.4	349.4	404.4	437.1
150°	298.6	308.1	350.5	398.7	421.7
152.5°	306.4	316.4	351.6	390.9	412.3
155°	316.6	324.0	354.6	381.2	396.8
157.5°	329.3	333.8	355.3	376.8	387.9
160°	335.9	339.3	358.1	373.5	382.9
162.5°	339.8	343.7	358.6	370.7	378.0
165°	349.8	351.1	358.8	366.5	371.9
167.5°	356.5	355.3	361.9	365.4	367.6
170°	358.8	358.1	360.8	361.6	364.3
172.5°	363.7	361.4	362.5	360.5	362.6
175°	366.4	364.3	362.9	360.8	358.1
177.5°	367.5	364.2	362.5	360.3	360.8
180°	363.6	363.6	363.6	363.6	363.6

(END OF REPORT)