

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: CORELITE

Report Number: P561660

Luminaire Tested: **SQ4-PC3-100U-125D-92765-1D-UNV-STD-W-4 (2700K)**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P561660
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2106-289-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PC3-100U-125D-92765-1D-UNV-STD-W-4 (2700K)
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 1000 LUMENS PER FOOT
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9018.8 lumens
Efficiency: N/A
Efficacy: 102.6 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 87.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P561660
CATALOG NUMBER: SQ4-PC3-100U-125D-92765-1D-UNV-STD-W-4 (2700K)

Luminous Intensity Polar Plot





TEST NUMBER: P561660

CATALOG NUMBER: SQ4-PC3-100U-125D-92765-1D-UNV-STD-W-4 (2700K)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20				
RC	80					70					50					30				
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	59	59	59	54		
1	99	94	90	87	91	88	84	81	75	73	70	63	62	60	53	51	50	45		
2	90	82	76	71	83	77	71	67	66	62	58	56	53	50	46	44	42	38		
3	82	72	65	59	76	67	61	56	58	53	49	49	45	42	41	38	36	32		
4	75	64	56	50	69	60	53	47	51	46	42	44	40	36	37	34	31	28		
5	69	57	49	43	63	53	46	40	46	40	36	39	35	31	33	30	27	24		
6	63	51	43	37	59	48	40	35	41	36	31	35	31	27	30	26	24	21		
7	59	46	38	33	54	43	36	31	38	32	28	32	28	24	27	24	21	18		
8	54	42	34	29	50	39	32	27	34	28	24	29	25	22	25	21	19	16		
9	51	38	31	26	47	36	29	24	31	26	22	27	23	19	23	20	17	15		
10	47	35	28	23	44	33	26	22	29	23	20	25	21	18	21	18	15	13		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16347	16347	16347
5°	16470	16363	16303
10°	16430	16353	16307
15°	16344	16344	16328
20°	16236	16285	16285
25°	16082	16199	16150
30°	15887	16079	16009
35°	15650	15891	15780
40°	15392	15609	15451
45°	15112	15219	14984
50°	14717	14717	14481
55°	14250	14065	13854
60°	13563	13289	13077
65°	12535	12284	12177
70°	10976	11063	11020
75°	8830	9767	9824
80°	6275	8278	8368
85°	3822	6944	6944



TEST NUMBER: P561660

CATALOG NUMBER: SQ4-PC3-100U-125D-92765-1D-UNV-STD-W-4 (2700K)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	167.7	1.9
10°-20°	481.2	5.3
20°-30°	728.7	8.1
30°-40°	873.6	9.7
40°-50°	890.8	9.9
50°-60°	777.6	8.6
60°-70°	556.7	6.2
70°-80°	286.7	3.2
80°-90°	72.5	0.8
90°-100°	306.9	3.4
100°-110°	873.2	9.7
110°-120°	836.6	9.3
120°-130°	662.1	7.3
130°-140°	531.5	5.9
140°-150°	416.1	4.6
150°-160°	304.4	3.4
160°-170°	188.6	2.1
170°-180°	64.0	0.7
0°-30°	1377.6	15.3
0°-40°	2251.2	25.0
0°-60°	3919.6	43.5
0°-90°	4835.5	53.6
90°-120°	2016.7	22.4
90°-150°	3626.3	40.2
90°-180°	4183.0	46.4
0°-180°	9018.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1772	1772	1772	1772	1772	
5°	1778	1761	1767	1762	1760	169
15°	1711	1697	1711	1711	1709	482
25°	1580	1569	1591	1586	1586	727
35°	1390	1386	1411	1401	1401	869
45°	1158	1155	1166	1152	1148	892
55°	886	875	874	861	861	790
65°	574	561	563	558	558	568
75°	248	259	274	276	276	268
85°	36	55	66	67	66	49
90°	0	0	0	0	0	3
95°	33	132	594	206	127	38
105°	136	206	890	1572	1494	144
115°	252	305	675	1429	1678	248
125°	356	395	644	1069	1278	319
135°	435	472	636	903	1020	336
145°	513	540	642	781	851	321
155°	586	600	657	706	735	271
165°	648	650	664	679	689	182
175°	679	675	672	668	663	64
180°	674	674	674	674	674	



TEST NUMBER: P561660

CATALOG NUMBER: SQ4-PC3-100U-125D-92765-1D-UNV-STD-W-4 (2700K)

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1771.8	1771.8	1771.8	1771.8	1771.8
2.5°	1782.3	1766.9	1771.8	1767.7	1761.3
5°	1778.3	1760.7	1766.8	1761.9	1760.3
7.5°	1765.5	1747.9	1756.0	1752.7	1751.1
10°	1753.7	1736.1	1745.5	1742.2	1740.6
12.5°	1738.0	1721.6	1732.4	1729.1	1728.8
15°	1711.1	1696.6	1711.1	1711.0	1709.4
17.5°	1677.3	1664.1	1679.6	1680.5	1679.6
20°	1653.6	1639.2	1658.6	1657.0	1658.6
22.5°	1624.8	1612.9	1633.6	1629.4	1631.0
25°	1579.8	1568.6	1591.3	1586.4	1586.4
27.5°	1526.7	1518.7	1543.4	1538.2	1538.2
30°	1491.2	1483.2	1509.3	1502.7	1502.7
32.5°	1451.9	1446.4	1471.2	1463.3	1463.3
35°	1389.5	1386.3	1410.9	1401.0	1401.0
37.5°	1325.2	1322.3	1344.6	1332.7	1328.8
40°	1278.0	1276.4	1296.0	1282.9	1282.9
42.5°	1230.7	1229.1	1246.1	1230.4	1230.4
45°	1158.2	1155.0	1166.4	1151.6	1148.4
47.5°	1079.1	1075.9	1083.1	1067.0	1065.4
50°	1025.3	1022.1	1025.3	1010.5	1008.9
52.5°	970.2	964.4	965.0	950.2	949.9
55°	885.9	874.7	874.4	861.3	861.3
57.5°	796.6	781.9	783.2	772.0	770.4
60°	735.0	718.9	720.2	710.3	708.7
62.5°	674.6	656.0	659.8	648.7	648.3
65°	574.2	561.4	562.7	557.8	557.8
67.5°	477.7	465.9	474.4	470.5	470.2
70°	406.9	398.8	410.1	410.1	408.5
72.5°	341.2	340.9	355.0	355.0	356.0
75°	247.7	258.9	274.0	275.6	275.6
77.5°	165.4	185.3	201.8	202.4	202.1
80°	118.1	140.6	155.8	159.1	157.5
82.5°	80.1	103.8	116.5	119.7	118.1
85°	36.1	55.3	65.6	67.2	65.6
87.5°	10.5	22.0	26.2	26.2	23.6
90°	0.0	0.0	0.0	0.0	0.0
92.5°	10.2	54.3	126.0	36.7	27.7
95°	33.3	132.2	594.1	205.6	126.8
97.5°	61.2	154.8	914.9	654.7	448.6
100°	80.7	168.3	984.6	997.3	768.2
102.5°	102.2	182.8	969.2	1276.6	1076.5
105°	135.7	205.8	889.8	1571.8	1494.2
107.5°	169.8	232.6	797.1	1655.0	1724.1
110°	193.3	252.2	743.9	1623.2	1778.4

TEST NUMBER: P561660

CATALOG NUMBER: SQ4-PC3-100U-125D-92765-1D-UNV-STD-W-4 (2700K)

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	215.9	271.7	708.0	1547.9	1769.2
115°	252.2	304.8	674.7	1429.4	1678.5
117.5°	284.2	333.6	655.0	1299.9	1563.8
120°	309.8	351.2	653.0	1225.9	1478.8
122.5°	330.3	371.6	647.9	1161.0	1395.8
125°	355.9	394.7	644.0	1068.7	1277.8
127.5°	383.8	420.2	642.0	1013.6	1185.9
130°	398.2	434.5	638.9	975.2	1125.4
132.5°	413.6	448.9	638.9	945.2	1083.4
135°	435.3	471.6	636.3	902.8	1020.4
137.5°	455.8	491.1	636.1	866.8	968.5
140°	471.2	507.5	635.1	837.0	934.7
142.5°	488.6	518.9	638.1	813.2	900.9
145°	513.4	539.7	641.5	781.3	851.4
147.5°	534.7	560.2	647.1	749.1	809.7
150°	553.1	570.6	649.1	738.5	781.0
152.5°	567.5	586.0	651.2	724.0	763.6
155°	586.4	600.2	656.8	706.1	734.9
157.5°	610.0	618.2	658.1	698.0	718.5
160°	622.3	628.5	663.2	691.8	709.3
162.5°	629.4	636.7	664.2	686.6	700.1
165°	647.9	650.4	664.5	678.8	688.8
167.5°	660.4	658.2	670.4	676.9	680.9
170°	664.5	663.3	668.3	669.7	674.7
172.5°	673.7	669.5	671.4	667.7	671.7
175°	678.6	674.8	672.2	668.2	663.2
177.5°	680.6	674.6	671.4	667.3	668.3
180°	673.5	673.5	673.5	673.5	673.5

(END OF REPORT)