

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P523686

Luminaire Tested: **SQ4-PP3-050U-075D-92765-1D-UNV-STD-W-4 (3500K)**

Issue Date: 5/24/2021

Test Information

Test Method: LM-79-2019
Report Number: P523686
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2103-172-1)
Test Lab: INNOVATION CENTER
Issue Date: 5/24/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PP3-050U-075D-92765-1D-UNV-STD-W-4 (3500K)
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 500 LUMENS PER FOOT
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5190.7 lumens
Efficiency: N/A
Efficacy: 108.8 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 47.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P523686

CATALOG NUMBER: SQ4-PP3-050U-075D-92765-1D-UNV-STD-W-4 (3500K)

Luminous Intensity Polar Plot





TEST NUMBER: P523686

CATALOG NUMBER: SQ4-PP3-050U-075D-92765-1D-UNV-STD-W-4 (3500K)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	102	102	102	102	88	88	88	75	75	75	63	63	63	58
1	100	96	92	88	93	89	86	83	77	75	73	66	65	63	56	55	54	49
2	91	84	78	72	85	78	73	68	68	64	61	59	56	53	50	48	46	42
3	83	74	66	61	77	69	63	57	60	55	51	52	48	45	44	42	39	35
4	76	65	57	51	71	61	54	49	54	48	44	46	42	39	40	37	34	31
5	70	58	50	44	65	55	47	42	48	42	38	42	37	34	36	32	30	27
6	65	52	44	38	60	49	42	37	43	37	33	38	33	30	33	29	26	23
7	60	47	39	34	56	45	37	32	39	33	29	34	30	26	30	26	23	21
8	55	43	35	30	52	41	33	29	36	30	26	31	27	23	27	24	21	19
9	52	39	32	27	48	37	30	26	33	27	23	29	24	21	25	22	19	17
10	48	36	29	24	45	34	27	23	30	25	21	27	22	19	23	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10844	10844	10844
5°	10923	10856	10817
10°	10904	10827	10778
15°	10833	10773	10714
20°	10760	10700	10619
25°	10632	10559	10454
30°	10435	10381	10249
35°	10163	10093	9966
40°	9837	9776	9664
45°	9569	9501	9407
50°	9225	9166	9077
55°	8749	8631	8565
60°	7964	7735	7698
65°	7017	6724	6700
70°	6056	5808	5808
75°	5215	5140	5065
80°	4596	4654	4543
85°	3599	3927	3927



TEST NUMBER: P523686

CATALOG NUMBER: SQ4-PP3-050U-075D-92765-1D-UNV-STD-W-4 (3500K)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	111.1	2.1
10°-20°	317.3	6.1
20°-30°	475.3	9.2
30°-40°	557.5	10.7
40°-50°	559.2	10.8
50°-60°	477.1	9.2
60°-70°	311.1	6.0
70°-80°	156.1	3.0
80°-90°	43.2	0.8
90°-100°	160.1	3.1
100°-110°	455.6	8.8
110°-120°	436.5	8.4
120°-130°	345.5	6.7
130°-140°	277.3	5.3
140°-150°	217.1	4.2
150°-160°	158.8	3.1
160°-170°	98.4	1.9
170°-180°	33.4	0.6
0°-30°	903.7	17.4
0°-40°	1461.2	28.2
0°-60°	2497.6	48.1
0°-90°	3008.0	57.9
90°-120°	1052.2	20.3
90°-150°	1892.1	36.5
90°-180°	2183.0	42.1
0°-180°	5190.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1175	1175	1175	1175	1175	
5°	1179	1168	1172	1168	1168	112
15°	1134	1123	1128	1124	1122	320
25°	1044	1032	1037	1028	1027	480
35°	902	893	896	886	885	564
45°	733	728	728	721	721	565
55°	544	542	537	534	532	483
65°	321	315	308	306	307	321
75°	146	146	144	143	142	159
85°	34	37	37	37	37	40
90°	0	0	0	0	0	2
95°	17	69	310	107	66	20
105°	71	107	464	820	780	75
115°	132	159	352	746	876	130
125°	186	206	336	558	667	166
135°	227	246	332	471	532	175
145°	268	282	335	408	444	167
155°	306	313	343	368	384	141
165°	338	339	347	354	359	95
175°	354	352	351	349	346	34
180°	351	351	351	351	351	

TEST NUMBER: P523686

CATALOG NUMBER: SQ4-PP3-050U-075D-92765-1D-UNV-STD-W-4 (3500K)

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1175.3	1175.3	1175.3	1175.3	1175.3
2.5°	1182.7	1173.0	1175.3	1173.5	1168.7
5°	1179.4	1168.3	1172.2	1168.0	1168.0
7.5°	1171.3	1159.3	1163.1	1159.0	1158.8
10°	1163.9	1151.8	1155.7	1151.5	1150.5
12.5°	1153.2	1141.1	1145.8	1140.8	1140.6
15°	1134.1	1123.0	1127.9	1123.7	1121.7
17.5°	1112.4	1100.3	1106.2	1100.5	1099.6
20°	1095.9	1083.9	1089.8	1081.5	1081.5
22.5°	1076.2	1064.1	1070.8	1060.1	1060.1
25°	1044.4	1032.4	1037.2	1027.9	1026.9
27.5°	1006.7	994.9	999.9	989.4	989.2
30°	979.5	968.5	974.4	963.0	962.0
32.5°	949.9	939.6	943.9	932.6	931.5
35°	902.3	893.2	896.1	885.8	884.8
37.5°	852.2	843.0	846.3	837.4	837.0
40°	816.8	810.8	811.7	804.4	802.4
42.5°	783.8	777.0	777.9	770.7	770.2
45°	733.4	728.3	728.2	721.0	721.0
47.5°	679.8	676.0	674.9	668.9	668.7
50°	642.7	639.7	638.6	633.4	632.4
52.5°	604.0	602.6	599.1	594.7	594.5
55°	543.9	541.8	536.6	533.5	532.5
57.5°	478.5	474.5	468.7	464.1	465.0
60°	431.6	427.5	419.2	417.2	417.2
62.5°	386.3	381.4	373.1	370.2	371.8
65°	321.4	315.3	308.0	305.9	306.9
67.5°	262.4	257.0	249.1	249.0	248.2
70°	224.5	221.5	215.3	215.3	215.3
72.5°	190.8	189.3	184.8	184.8	184.0
75°	146.3	146.3	144.2	143.1	142.1
77.5°	109.6	110.0	109.0	107.9	106.1
80°	86.5	88.5	87.6	86.5	85.5
82.5°	65.1	67.1	67.0	65.1	64.9
85°	34.0	37.0	37.1	37.1	37.1
87.5°	9.1	12.3	13.2	13.2	14.0
90°	0.0	0.0	0.0	0.0	0.0
92.5°	5.3	28.3	65.7	19.1	14.4
95°	17.4	69.0	310.0	107.3	66.1
97.5°	31.9	80.8	477.4	341.6	234.1
100°	42.1	87.8	513.7	520.4	400.8
102.5°	53.3	95.4	505.7	666.1	561.7
105°	70.8	107.4	464.3	820.1	779.6
107.5°	88.6	121.4	415.9	863.5	899.6
110°	100.9	131.6	388.1	846.9	927.9

TEST NUMBER: P523686

CATALOG NUMBER: SQ4-PP3-050U-075D-92765-1D-UNV-STD-W-4 (3500K)

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	112.6	141.8	369.4	807.6	923.1
115°	131.6	159.0	352.1	745.8	875.8
117.5°	148.3	174.0	341.8	678.3	815.9
120°	161.7	183.2	340.7	639.6	771.6
122.5°	172.4	193.9	338.0	605.8	728.3
125°	185.7	206.0	336.0	557.6	666.7
127.5°	200.3	219.2	335.0	528.9	618.7
130°	207.8	226.7	333.4	508.8	587.2
132.5°	215.8	234.2	333.4	493.2	565.3
135°	227.1	246.1	332.0	471.0	532.4
137.5°	237.8	256.2	331.9	452.3	505.3
140°	245.8	264.8	331.3	436.7	487.7
142.5°	254.9	270.7	333.0	424.3	470.0
145°	267.9	281.6	334.7	407.7	444.2
147.5°	279.0	292.3	337.6	390.9	422.5
150°	288.6	297.7	338.7	385.3	407.5
152.5°	296.1	305.7	339.8	377.8	398.4
155°	306.0	313.1	342.7	368.4	383.5
157.5°	318.3	322.6	343.4	364.2	374.9
160°	324.7	327.9	346.0	361.0	370.1
162.5°	328.4	332.2	346.6	358.2	365.3
165°	338.0	339.3	346.7	354.2	359.4
167.5°	344.6	343.4	349.8	353.2	355.3
170°	346.7	346.1	348.7	349.4	352.1
172.5°	351.5	349.3	350.3	348.4	350.5
175°	354.1	352.1	350.7	348.7	346.0
177.5°	355.1	352.0	350.3	348.2	348.7
180°	351.4	351.4	351.4	351.4	351.4

(END OF REPORT)