

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P561666

Luminaire Tested: **SQ4-PC3-100U-125D-92765-1D-UNV-STD-W-4 (5700K)**

Issue Date: 7/30/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P561666  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2106-289-1)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/30/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PC3-100U-125D-92765-1D-UNV-STD-W-4 (5700K)  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS  
DOWNLIGHT 1250 LUMENS PER FOOT  
UPLIGHT 1000 LUMENS PER FOOT  
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 5700K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 10002.4 lumens  
Efficiency: N/A  
Efficacy: 113.8 lumens/watt  
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37  
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 87.9  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P561666  
CATALOG NUMBER: SQ4-PC3-100U-125D-92765-1D-UNV-STD-W-4 (5700K)

### Luminous Intensity Polar Plot





TEST NUMBER: P561666

CATALOG NUMBER: SQ4-PC3-100U-125D-92765-1D-UNV-STD-W-4 (5700K)

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	59	59	59	54
1	99	94	90	87	91	88	84	81	75	73	70	63	62	60	53	51	50	45
2	90	82	76	71	83	77	71	67	66	62	58	56	53	50	46	44	42	38
3	82	72	65	59	76	67	61	56	58	53	49	49	45	42	41	38	36	32
4	75	64	56	50	69	60	53	47	51	46	42	44	40	36	37	34	31	28
5	69	57	49	43	63	53	46	40	46	40	36	39	35	31	33	30	27	24
6	63	51	43	37	59	48	40	35	41	36	31	35	31	27	30	26	24	21
7	59	46	38	33	54	43	36	31	38	32	28	32	28	24	27	24	21	18
8	54	42	34	29	50	39	32	27	34	28	24	29	25	22	25	21	19	16
9	51	38	31	26	47	36	29	24	31	26	22	27	23	19	23	20	17	15
10	47	35	28	23	44	33	26	22	29	23	20	25	21	18	21	18	15	13

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	18129	18129	18129
5°	18266	18148	18080
10°	18222	18137	18085
15°	18126	18126	18108
20°	18007	18060	18060
25°	17836	17966	17911
30°	17620	17833	17755
35°	17358	17623	17501
40°	17070	17311	17136
45°	16760	16879	16618
50°	16321	16321	16060
55°	15804	15600	15365
60°	15041	14738	14504
65°	13902	13625	13505
70°	12171	12271	12220
75°	9792	10830	10897
80°	6960	9181	9282
85°	4234	7707	7707



TEST NUMBER: P561666

CATALOG NUMBER: SQ4-PC3-100U-125D-92765-1D-UNV-STD-W-4 (5700K)

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	186.0	1.9
10°-20°	533.7	5.3
20°-30°	808.2	8.1
30°-40°	968.9	9.7
40°-50°	987.9	9.9
50°-60°	862.4	8.6
60°-70°	617.4	6.2
70°-80°	318.0	3.2
80°-90°	80.4	0.8
90°-100°	340.3	3.4
100°-110°	968.4	9.7
110°-120°	927.8	9.3
120°-130°	734.4	7.3
130°-140°	589.4	5.9
140°-150°	461.5	4.6
150°-160°	337.6	3.4
160°-170°	209.1	2.1
170°-180°	71.0	0.7
0°-30°	1527.8	15.3
0°-40°	2496.7	25.0
0°-60°	4347.0	43.5
0°-90°	5362.8	53.6
90°-120°	2236.6	22.4
90°-150°	4021.8	40.2
90°-180°	4640.0	46.4
0°-180°	10002.4	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1965	1965	1965	1965	1965	
5°	1972	1953	1960	1954	1952	187
15°	1898	1882	1898	1898	1896	535
25°	1752	1740	1765	1759	1759	806
35°	1541	1538	1565	1554	1554	964
45°	1284	1281	1294	1277	1274	989
55°	982	970	970	955	955	876
65°	637	623	624	619	619	630
75°	275	287	304	306	306	297
85°	40	61	73	75	73	54
90°	0	0	0	0	0	3
95°	37	147	659	228	141	42
105°	150	228	987	1743	1657	159
115°	280	338	748	1585	1862	275
125°	395	438	714	1185	1417	353
135°	483	523	706	1001	1132	373
145°	569	599	711	866	944	356
155°	650	666	728	783	815	301
165°	718	721	737	753	764	202
175°	753	748	746	741	736	71
180°	747	747	747	747	747	

TEST NUMBER: P561666

CATALOG NUMBER: SQ4-PC3-100U-125D-92765-1D-UNV-STD-W-4 (5700K)

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1965.0	1965.0	1965.0	1965.0	1965.0
2.5°	1976.6	1959.5	1965.0	1960.5	1953.3
5°	1972.3	1952.7	1959.5	1954.0	1952.2
7.5°	1958.1	1938.5	1947.5	1943.8	1942.1
10°	1945.0	1925.4	1935.9	1932.2	1930.4
12.5°	1927.5	1909.4	1921.3	1917.7	1917.3
15°	1897.7	1881.7	1897.7	1897.6	1895.8
17.5°	1860.2	1845.6	1862.7	1863.8	1862.7
20°	1834.0	1818.0	1839.4	1837.7	1839.4
22.5°	1802.0	1788.8	1811.8	1807.1	1808.9
25°	1752.1	1739.7	1764.8	1759.4	1759.4
27.5°	1693.2	1684.3	1711.7	1705.9	1705.9
30°	1653.9	1645.0	1673.9	1666.6	1666.6
32.5°	1610.2	1604.1	1631.7	1622.9	1622.9
35°	1541.1	1537.5	1564.7	1553.8	1553.8
37.5°	1469.7	1466.5	1491.2	1478.0	1473.7
40°	1417.3	1415.6	1437.3	1422.8	1422.8
42.5°	1364.9	1363.2	1382.0	1364.6	1364.6
45°	1284.5	1281.0	1293.6	1277.2	1273.6
47.5°	1196.8	1193.3	1201.2	1183.3	1181.5
50°	1137.1	1133.6	1137.1	1120.7	1118.9
52.5°	1076.0	1069.6	1070.2	1053.8	1053.4
55°	982.5	970.0	969.8	955.2	955.2
57.5°	883.5	867.1	868.6	856.2	854.4
60°	815.1	797.3	798.7	787.8	786.0
62.5°	748.1	727.5	731.8	719.4	719.0
65°	636.8	622.6	624.1	618.6	618.6
67.5°	529.8	516.7	526.2	521.8	521.4
70°	451.2	442.3	454.9	454.8	453.0
72.5°	378.4	378.1	393.7	393.7	394.8
75°	274.7	287.2	303.8	305.7	305.7
77.5°	183.4	205.5	223.8	224.5	224.2
80°	131.0	155.9	172.8	176.4	174.7
82.5°	88.8	115.1	129.2	132.8	131.0
85°	40.0	61.4	72.8	74.6	72.8
87.5°	11.6	24.5	29.1	29.0	26.2
90°	0.0	0.0	0.0	0.0	0.0
92.5°	11.4	60.2	139.7	40.7	30.7
95°	36.9	146.6	658.9	228.0	140.6
97.5°	67.9	171.7	1014.7	726.1	497.6
100°	89.5	186.6	1092.0	1106.1	852.0
102.5°	113.3	202.7	1074.9	1415.8	1193.9
105°	150.5	228.3	986.9	1743.2	1657.1
107.5°	188.3	258.0	884.1	1835.5	1912.1
110°	214.4	279.7	825.0	1800.2	1972.3



TEST NUMBER: P561666

CATALOG NUMBER: SQ4-PC3-100U-125D-92765-1D-UNV-STD-W-4 (5700K)

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	239.4	301.3	785.2	1716.7	1962.1
115°	279.7	338.0	748.3	1585.3	1861.6
117.5°	315.2	369.9	726.5	1441.7	1734.4
120°	343.6	389.5	724.2	1359.6	1640.1
122.5°	366.4	412.2	718.5	1287.6	1548.1
125°	394.8	437.8	714.2	1185.3	1417.1
127.5°	425.7	466.0	712.0	1124.1	1315.2
130°	441.6	481.9	708.6	1081.5	1248.2
132.5°	458.7	497.8	708.6	1048.3	1201.6
135°	482.8	523.1	705.7	1001.2	1131.7
137.5°	505.5	544.7	705.4	961.3	1074.1
140°	522.6	562.8	704.3	928.3	1036.6
142.5°	541.9	575.5	707.7	901.9	999.1
145°	569.4	598.6	711.4	866.5	944.3
147.5°	593.0	621.3	717.7	830.8	898.0
150°	613.4	632.9	719.9	819.0	866.2
152.5°	629.3	649.9	722.2	803.0	846.9
155°	650.3	665.6	728.4	783.1	815.1
157.5°	676.5	685.6	729.9	774.1	796.9
160°	690.1	697.1	735.5	767.2	786.7
162.5°	698.1	706.1	736.7	761.4	776.4
165°	718.5	721.3	737.0	752.8	763.9
167.5°	732.4	729.9	743.5	750.7	755.1
170°	737.0	735.6	741.2	742.8	748.3
172.5°	747.2	742.5	744.6	740.5	744.9
175°	752.6	748.4	745.5	741.1	735.5
177.5°	754.9	748.2	744.6	740.1	741.2
180°	746.9	746.9	746.9	746.9	746.9

(END OF REPORT)