

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P561667

Luminaire Tested: **SQ4-PC3-100U-125D-92765-1D-UNV-STD-W-4 (6500K)**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P561667
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2106-289-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PC3-100U-125D-92765-1D-UNV-STD-W-4 (6500K)
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 1000 LUMENS PER FOOT
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 6500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 10097.2 lumens
Efficiency: N/A
Efficacy: 115.3 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 87.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P561667
CATALOG NUMBER: SQ4-PC3-100U-125D-92765-1D-UNV-STD-W-4 (6500K)

Luminous Intensity Polar Plot





TEST NUMBER: P561667

CATALOG NUMBER: SQ4-PC3-100U-125D-92765-1D-UNV-STD-W-4 (6500K)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	59	59	59	54				
1	99	94	90	87	91	88	84	81	75	73	70	63	62	60	53	51	50	45				
2	90	82	76	71	83	77	71	67	66	62	58	56	53	50	46	44	42	38				
3	82	72	65	59	76	67	61	56	58	53	49	49	45	42	41	38	36	32				
4	75	64	56	50	69	60	53	47	51	46	42	44	40	36	37	34	31	28				
5	69	57	49	43	63	53	46	40	46	40	36	39	35	31	33	30	27	24				
6	63	51	43	37	59	48	40	35	41	36	31	35	31	27	30	26	24	21				
7	59	46	38	33	54	43	36	31	38	32	28	32	28	24	27	24	21	18				
8	54	42	34	29	50	39	32	27	34	28	24	29	25	22	25	21	19	16				
9	51	38	31	26	47	36	29	24	31	26	22	27	23	19	23	20	17	15				
10	47	35	28	23	44	33	26	22	29	23	20	25	21	18	21	18	15	13				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	18301	18301	18301
5°	18440	18320	18252
10°	18394	18308	18256
15°	18298	18298	18280
20°	18178	18232	18232
25°	18005	18137	18081
30°	17786	18001	17923
35°	17522	17790	17666
40°	17232	17476	17299
45°	16919	17039	16776
50°	16476	16476	16214
55°	15953	15746	15511
60°	15183	14878	14640
65°	14033	13754	13633
70°	12287	12387	12336
75°	9885	10933	11001
80°	7024	9271	9367
85°	4277	7781	7781



TEST NUMBER: P561667

CATALOG NUMBER: SQ4-PC3-100U-125D-92765-1D-UNV-STD-W-4 (6500K)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	187.7	1.9
10°-20°	538.7	5.3
20°-30°	815.8	8.1
30°-40°	978.1	9.7
40°-50°	997.3	9.9
50°-60°	870.6	8.6
60°-70°	623.3	6.2
70°-80°	321.0	3.2
80°-90°	81.2	0.8
90°-100°	343.6	3.4
100°-110°	977.6	9.7
110°-120°	936.6	9.3
120°-130°	741.3	7.3
130°-140°	595.0	5.9
140°-150°	465.8	4.6
150°-160°	340.8	3.4
160°-170°	211.1	2.1
170°-180°	71.6	0.7
0°-30°	1542.3	15.3
0°-40°	2520.4	25.0
0°-60°	4388.2	43.5
0°-90°	5413.7	53.6
90°-120°	2257.8	22.4
90°-150°	4059.9	40.2
90°-180°	4684.0	46.4
0°-180°	10097.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1984	1984	1984	1984	1984	
5°	1991	1971	1978	1973	1971	189
15°	1916	1900	1916	1916	1914	540
25°	1769	1756	1782	1776	1776	814
35°	1556	1552	1580	1568	1568	973
45°	1297	1293	1306	1289	1286	998
55°	992	979	979	964	964	884
65°	643	628	630	624	624	636
75°	277	290	307	309	309	300
85°	40	62	74	75	74	55
90°	0	0	0	0	0	3
95°	37	148	665	230	142	43
105°	152	230	996	1760	1673	161
115°	282	341	755	1600	1879	278
125°	398	442	721	1196	1431	357
135°	487	528	712	1011	1142	376
145°	575	604	718	875	953	359
155°	656	672	735	791	823	303
165°	725	728	744	760	771	204
175°	760	756	753	748	742	72
180°	754	754	754	754	754	

TEST NUMBER: P561667

CATALOG NUMBER: SQ4-PC3-100U-125D-92765-1D-UNV-STD-W-4 (6500K)

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1983.6	1983.6	1983.6	1983.6	1983.6
2.5°	1995.4	1978.1	1983.6	1979.0	1971.9
5°	1991.0	1971.2	1978.1	1972.6	1970.8
7.5°	1976.6	1956.9	1966.0	1962.3	1960.5
10°	1963.4	1943.7	1954.2	1950.5	1948.7
12.5°	1945.8	1927.5	1939.5	1935.9	1935.5
15°	1915.7	1899.5	1915.7	1915.6	1913.8
17.5°	1877.8	1863.1	1880.4	1881.5	1880.4
20°	1851.4	1835.2	1856.9	1855.1	1856.9
22.5°	1819.0	1805.8	1829.0	1824.2	1826.0
25°	1768.7	1756.2	1781.6	1776.1	1776.1
27.5°	1709.2	1700.2	1727.9	1722.1	1722.1
30°	1669.5	1660.6	1689.7	1682.4	1682.4
32.5°	1625.5	1619.4	1647.1	1638.3	1638.3
35°	1555.7	1552.1	1579.5	1568.5	1568.5
37.5°	1483.7	1480.4	1505.3	1492.0	1487.7
40°	1430.8	1429.0	1451.0	1436.3	1436.3
42.5°	1377.9	1376.1	1395.1	1377.5	1377.5
45°	1296.7	1293.1	1305.9	1289.3	1285.7
47.5°	1208.2	1204.6	1212.6	1194.5	1192.7
50°	1147.9	1144.3	1147.9	1131.4	1129.6
52.5°	1086.2	1079.7	1080.3	1063.8	1063.4
55°	991.8	979.2	978.9	964.3	964.3
57.5°	891.9	875.4	876.8	864.3	862.5
60°	822.8	804.9	806.3	795.2	793.4
62.5°	755.2	734.4	738.7	726.2	725.9
65°	642.8	628.5	630.0	624.5	624.5
67.5°	534.8	521.6	531.2	526.8	526.4
70°	455.5	446.5	459.2	459.1	457.3
72.5°	382.0	381.7	397.5	397.5	398.6
75°	277.3	289.9	306.7	308.6	308.6
77.5°	185.1	207.4	225.9	226.6	226.3
80°	132.2	157.4	174.5	178.1	176.3
82.5°	89.6	116.2	130.4	134.0	132.2
85°	40.4	62.0	73.5	75.3	73.5
87.5°	11.8	24.7	29.4	29.3	26.4
90°	0.0	0.0	0.0	0.0	0.0
92.5°	11.5	60.8	141.1	41.1	31.0
95°	37.3	148.0	665.1	230.2	141.9
97.5°	68.5	173.4	1024.3	733.0	502.3
100°	90.3	188.4	1102.3	1116.6	860.1
102.5°	114.4	204.7	1085.1	1429.2	1205.2
105°	151.9	230.4	996.2	1759.7	1672.8
107.5°	190.1	260.4	892.5	1852.9	1930.3
110°	216.4	282.3	832.8	1817.3	1991.1



TEST NUMBER: P561667

CATALOG NUMBER: SQ4-PC3-100U-125D-92765-1D-UNV-STD-W-4 (6500K)

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	241.7	304.2	792.7	1732.9	1980.7
115°	282.4	341.3	755.4	1600.3	1879.2
117.5°	318.2	373.4	733.3	1455.4	1750.8
120°	346.9	393.1	731.1	1372.5	1655.6
122.5°	369.8	416.1	725.3	1299.8	1562.7
125°	398.5	441.9	721.0	1196.5	1430.6
127.5°	429.7	470.4	718.7	1134.8	1327.7
130°	445.8	486.4	715.3	1091.8	1260.0
132.5°	463.0	502.5	715.3	1058.2	1213.0
135°	487.4	528.0	712.4	1010.7	1142.5
137.5°	510.3	549.8	712.1	970.4	1084.3
140°	527.5	568.2	711.0	937.1	1046.4
142.5°	547.0	580.9	714.4	910.5	1008.6
145°	574.8	604.2	718.2	874.7	953.2
147.5°	598.6	627.2	724.5	838.7	906.5
150°	619.2	638.9	726.8	826.7	874.4
152.5°	635.3	656.0	729.0	810.6	854.9
155°	656.5	671.9	735.4	790.6	822.8
157.5°	682.9	692.1	736.8	781.5	804.4
160°	696.7	703.7	742.5	774.5	794.1
162.5°	704.7	712.8	743.7	768.7	783.8
165°	725.3	728.1	744.0	760.0	771.2
167.5°	739.4	736.8	750.6	757.8	762.3
170°	744.0	742.6	748.3	749.8	755.4
172.5°	754.3	749.5	751.7	747.5	752.0
175°	759.7	755.5	752.6	748.1	742.5
177.5°	762.0	755.3	751.7	747.1	748.3
180°	754.0	754.0	754.0	754.0	754.0

(END OF REPORT)