

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P561692

Luminaire Tested: **SQ4-PC3-125U-075D-92765-1D-UNV-STD-W-4 (5700K)**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P561692
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2106-289-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PC3-125U-075D-92765-1D-UNV-STD-W-4 (5700K)
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 1250 LUMENS PER FOOT
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 5700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9049.5 lumens
Efficiency: N/A
Efficacy: 123.6 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 73.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P561692
CATALOG NUMBER: SQ4-PC3-125U-075D-92765-1D-UNV-STD-W-4 (5700K)

Luminous Intensity Polar Plot





TEST NUMBER: P561692

CATALOG NUMBER: SQ4-PC3-125U-075D-92765-1D-UNV-STD-W-4 (5700K)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	75	75	75	58	58	58	43	43	43	36
1	95	90	87	83	85	82	79	76	66	64	62	51	50	49	38	37	36	30
2	86	79	73	68	78	72	67	62	58	54	51	45	43	41	33	32	31	25
3	79	69	62	56	71	63	57	52	51	47	43	40	37	34	30	28	26	21
4	72	61	54	48	65	56	49	44	45	40	36	35	32	29	26	24	22	18
5	66	54	46	41	59	50	43	38	40	35	31	32	28	25	24	21	19	16
6	60	49	41	35	55	44	37	32	36	31	27	29	25	22	21	19	17	14
7	56	44	36	31	50	40	33	28	33	28	24	26	22	19	20	17	15	12
8	52	40	32	27	47	36	30	25	30	25	21	24	20	17	18	15	13	11
9	48	36	29	24	43	33	27	22	27	22	19	22	18	15	17	14	12	10
10	45	33	26	21	41	30	24	20	25	20	17	20	16	14	15	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10892	10892	10892
5°	10975	10904	10864
10°	10948	10897	10867
15°	10891	10891	10880
20°	10819	10851	10851
25°	10716	10795	10761
30°	10586	10714	10668
35°	10429	10588	10515
40°	10257	10401	10296
45°	10070	10142	9984
50°	9806	9806	9650
55°	9495	9373	9231
60°	9036	8855	8715
65°	8353	8187	8115
70°	7313	7372	7343
75°	5885	6509	6548
80°	4181	5520	5574
85°	2551	4626	4626



TEST NUMBER: P561692

CATALOG NUMBER: SQ4-PC3-125U-075D-92765-1D-UNV-STD-W-4 (5700K)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	111.7	1.2
10°-20°	320.6	3.5
20°-30°	485.6	5.4
30°-40°	582.1	6.4
40°-50°	593.6	6.6
50°-60°	518.2	5.7
60°-70°	371.0	4.1
70°-80°	191.1	2.1
80°-90°	48.3	0.5
90°-100°	427.5	4.7
100°-110°	1216.3	13.4
110°-120°	1165.4	12.9
120°-130°	922.3	10.2
130°-140°	740.3	8.2
140°-150°	579.6	6.4
150°-160°	424.1	4.7
160°-170°	262.7	2.9
170°-180°	89.1	1.0
0°-30°	918.0	10.1
0°-40°	1500.1	16.6
0°-60°	2611.9	28.9
0°-90°	3222.2	35.6
90°-120°	2809.1	31.0
90°-150°	5051.4	55.8
90°-180°	5827.0	64.4
0°-180°	9049.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1181	1181	1181	1181	1181	
5°	1185	1173	1177	1174	1173	112
15°	1140	1131	1140	1140	1139	321
25°	1053	1045	1060	1057	1057	484
35°	926	924	940	934	934	579
45°	772	770	777	767	765	594
55°	590	583	583	574	574	526
65°	383	374	375	372	372	378
75°	165	173	183	184	184	178
85°	24	37	44	45	44	33
90°	0	0	0	0	0	3
95°	46	184	828	286	177	53
105°	189	287	1240	2189	2081	200
115°	351	425	940	1991	2338	346
125°	496	550	897	1489	1780	444
135°	606	657	886	1258	1421	468
145°	715	752	894	1088	1186	447
155°	817	836	915	984	1024	378
165°	902	906	926	946	960	254
175°	945	940	936	931	924	90
180°	938	938	938	938	938	

TEST NUMBER: P561692

CATALOG NUMBER: SQ4-PC3-125U-075D-92765-1D-UNV-STD-W-4 (5700K)

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1180.6	1180.6	1180.6	1180.6	1180.6
2.5°	1187.6	1177.4	1180.6	1177.9	1173.6
5°	1185.0	1173.3	1177.4	1174.1	1173.0
7.5°	1176.5	1164.7	1170.1	1167.9	1166.9
10°	1168.6	1156.9	1163.1	1160.9	1159.9
12.5°	1158.1	1147.2	1154.4	1152.2	1152.0
15°	1140.2	1130.6	1140.2	1140.2	1139.1
17.5°	1117.7	1108.9	1119.2	1119.8	1119.2
20°	1101.9	1092.3	1105.2	1104.1	1105.2
22.5°	1082.7	1074.8	1088.6	1085.8	1086.8
25°	1052.7	1045.3	1060.4	1057.1	1057.1
27.5°	1017.3	1012.0	1028.5	1025.0	1025.0
30°	993.7	988.4	1005.7	1001.4	1001.4
32.5°	967.5	963.8	980.4	975.1	975.1
35°	925.9	923.8	940.1	933.6	933.6
37.5°	883.1	881.1	896.0	888.0	885.5
40°	851.6	850.5	863.6	854.9	854.9
42.5°	820.1	819.0	830.4	819.9	819.9
45°	771.8	769.6	777.3	767.4	765.2
47.5°	719.1	717.0	721.7	711.0	709.9
50°	683.2	681.1	683.2	673.4	672.3
52.5°	646.5	642.7	643.0	633.2	633.0
55°	590.3	582.8	582.7	573.9	573.9
57.5°	530.8	521.0	521.9	514.4	513.4
60°	489.7	479.1	479.9	473.3	472.3
62.5°	449.5	437.1	439.7	432.2	432.0
65°	382.6	374.1	375.0	371.7	371.7
67.5°	318.3	310.4	316.1	313.5	313.3
70°	271.1	265.8	273.3	273.3	272.2
72.5°	227.4	227.2	236.6	236.6	237.2
75°	165.1	172.6	182.6	183.7	183.7
77.5°	110.2	123.4	134.5	134.9	134.7
80°	78.7	93.7	103.9	106.0	104.9
82.5°	53.3	69.2	77.6	79.8	78.7
85°	24.1	36.9	43.7	44.8	43.7
87.5°	7.0	14.7	17.5	17.5	15.7
90°	0.0	0.0	0.0	0.0	0.0
92.5°	14.3	75.7	175.5	51.1	38.5
95°	46.4	184.1	827.5	286.4	176.6
97.5°	85.2	215.7	1274.5	912.0	624.9
100°	112.4	234.4	1371.5	1389.2	1070.1
102.5°	142.3	254.6	1350.1	1778.2	1499.5
105°	189.0	286.7	1239.5	2189.4	2081.3
107.5°	236.5	324.0	1110.4	2305.4	2401.6
110°	269.3	351.3	1036.2	2261.0	2477.2



TEST NUMBER: P561692

CATALOG NUMBER: SQ4-PC3-125U-075D-92765-1D-UNV-STD-W-4 (5700K)

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	300.7	378.5	986.3	2156.1	2464.4
115°	351.3	424.6	939.9	1991.1	2338.1
117.5°	395.9	464.6	912.4	1810.7	2178.3
120°	431.6	489.1	909.6	1707.7	2059.9
122.5°	460.1	517.7	902.4	1617.2	1944.3
125°	495.8	549.9	897.1	1488.7	1779.9
127.5°	534.7	585.3	894.2	1411.9	1651.8
130°	554.7	605.2	890.0	1358.4	1567.7
132.5°	576.1	625.2	890.0	1316.7	1509.2
135°	606.4	657.0	886.4	1257.5	1421.4
137.5°	634.9	684.1	886.0	1207.4	1349.0
140°	656.3	706.9	884.6	1165.9	1301.9
142.5°	680.6	722.8	888.9	1132.8	1254.8
145°	715.2	751.8	893.5	1088.4	1186.0
147.5°	744.8	780.4	901.4	1043.5	1127.9
150°	770.5	794.9	904.2	1028.6	1087.9
152.5°	790.4	816.2	907.1	1008.6	1063.7
155°	816.8	836.0	914.9	983.6	1023.7
157.5°	849.6	861.2	916.7	972.3	1000.9
160°	866.8	875.5	923.8	963.6	988.0
162.5°	876.8	886.9	925.3	956.4	975.2
165°	902.4	905.9	925.6	945.6	959.5
167.5°	919.9	916.8	933.8	942.9	948.4
170°	925.6	923.9	931.0	932.9	939.9
172.5°	938.5	932.5	935.3	930.0	935.6
175°	945.2	940.0	936.3	930.8	923.8
177.5°	948.1	939.7	935.3	929.6	931.0
180°	938.1	938.1	938.1	938.1	938.1

(END OF REPORT)