

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P523724

Luminaire Tested: **SQ4-PP3-075U-050D-92765-1D-UNV-STD-W-4 (3000K)**

Issue Date: 5/24/2021

Test Information

Test Method: LM-79-2019
Report Number: P523724
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2103-172-1)
Test Lab: INNOVATION CENTER
Issue Date: 5/24/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PP3-075U-050D-92765-1D-UNV-STD-W-4 (3000K)
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS
DOWNLIGHT 500 LUMENS PER FOOT
UPLIGHT 750 LUMENS PER FOOT
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5152.2 lumens
Efficiency: N/A
Efficacy: 116.0 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 44.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P523724

CATALOG NUMBER: SQ4-PP3-075U-050D-92765-1D-UNV-STD-W-4 (3000K)

Luminous Intensity Polar Plot





TEST NUMBER: P523724

CATALOG NUMBER: SQ4-PP3-075U-050D-92765-1D-UNV-STD-W-4 (3000K)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	95	95	95	95	77	77	77	60	60	60	45	45	45	38
1	95	91	87	84	86	83	80	77	67	65	63	53	52	50	40	39	38	32
2	87	80	74	69	79	73	68	63	59	56	53	47	44	42	35	34	33	27
3	79	70	63	57	72	64	58	53	52	48	44	42	38	36	32	30	28	23
4	72	62	54	48	66	57	50	45	46	42	38	37	34	31	28	26	24	20
5	66	55	47	41	60	50	44	38	42	36	32	33	30	27	25	23	21	17
6	61	49	42	36	55	45	38	33	37	32	28	30	26	23	23	20	18	15
7	57	45	37	31	51	41	34	29	34	29	25	27	23	21	21	18	16	14
8	52	40	33	28	47	37	30	26	31	26	22	25	21	18	19	17	15	12
9	49	37	29	25	44	34	27	23	28	23	20	23	19	16	18	15	13	11
10	45	34	27	22	41	31	25	20	26	21	18	21	17	15	16	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7071	7071	7071
5°	7122	7079	7054
10°	7111	7060	7028
15°	7063	7025	6986
20°	7016	6977	6924
25°	6934	6886	6817
30°	6804	6769	6683
35°	6627	6581	6498
40°	6415	6375	6301
45°	6239	6196	6135
50°	6016	5977	5919
55°	5704	5628	5585
60°	5193	5045	5019
65°	4576	4384	4371
70°	3949	3787	3787
75°	3401	3351	3305
80°	2997	3034	2959
85°	2350	2562	2562



TEST NUMBER: P523724

CATALOG NUMBER: SQ4-PP3-075U-050D-92765-1D-UNV-STD-W-4 (3000K)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	72.5	1.4
10°-20°	206.9	4.0
20°-30°	309.9	6.0
30°-40°	363.5	7.1
40°-50°	364.7	7.1
50°-60°	311.1	6.0
60°-70°	202.9	3.9
70°-80°	101.8	2.0
80°-90°	28.2	0.5
90°-100°	234.1	4.5
100°-110°	666.0	12.9
110°-120°	638.1	12.4
120°-130°	505.0	9.8
130°-140°	405.4	7.9
140°-150°	317.4	6.2
150°-160°	232.2	4.5
160°-170°	143.8	2.8
170°-180°	48.8	0.9
0°-30°	589.3	11.4
0°-40°	952.8	18.5
0°-60°	1628.6	31.6
0°-90°	1961.4	38.1
90°-120°	1538.2	29.9
90°-150°	2766.0	53.7
90°-180°	3191.0	61.9
0°-180°	5152.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	766	766	766	766	766	
5°	769	762	764	762	762	73
15°	740	732	736	733	731	209
25°	681	673	676	670	670	313
35°	588	582	584	578	577	368
45°	478	475	475	470	470	368
55°	355	353	350	348	347	315
65°	210	206	201	200	200	209
75°	95	95	94	93	93	103
85°	22	24	24	24	24	26
90°	0	0	0	0	0	2
95°	25	101	453	157	97	29
105°	104	157	679	1199	1140	110
115°	192	232	515	1090	1280	189
125°	272	301	491	815	975	243
135°	332	360	485	689	778	256
145°	392	412	489	596	649	245
155°	447	458	501	539	560	207
165°	494	496	507	518	525	139
175°	518	515	513	510	506	49
180°	514	514	514	514	514	

TEST NUMBER: P523724

CATALOG NUMBER: SQ4-PP3-075U-050D-92765-1D-UNV-STD-W-4 (3000K)

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	766.4	766.4	766.4	766.4	766.4
2.5°	771.2	764.9	766.4	765.2	762.1
5°	769.0	761.8	764.3	761.6	761.6
7.5°	763.8	755.9	758.4	755.7	755.6
10°	759.0	751.1	753.6	750.9	750.2
12.5°	752.0	744.1	747.1	743.9	743.8
15°	739.5	732.3	735.5	732.7	731.4
17.5°	725.4	717.5	721.4	717.6	717.1
20°	714.6	706.8	710.6	705.2	705.2
22.5°	701.7	693.9	698.2	691.3	691.3
25°	681.1	673.2	676.4	670.3	669.6
27.5°	656.5	648.7	652.0	645.2	645.1
30°	638.7	631.5	635.4	628.0	627.3
32.5°	619.4	612.7	615.5	608.1	607.4
35°	588.4	582.5	584.3	577.6	576.9
37.5°	555.7	549.7	551.8	546.0	545.8
40°	532.6	528.7	529.3	524.5	523.2
42.5°	511.1	506.7	507.2	502.5	502.3
45°	478.2	474.9	474.9	470.2	470.2
47.5°	443.3	440.8	440.1	436.2	436.0
50°	419.1	417.1	416.4	413.0	412.4
52.5°	393.9	392.9	390.6	387.8	387.7
55°	354.6	353.3	349.9	347.9	347.2
57.5°	312.0	309.4	305.6	302.7	303.2
60°	281.4	278.8	273.4	272.0	272.0
62.5°	251.9	248.7	243.3	241.4	242.5
65°	209.6	205.6	200.8	199.5	200.2
67.5°	171.1	167.6	162.4	162.4	161.9
70°	146.4	144.4	140.4	140.4	140.4
72.5°	124.4	123.5	120.5	120.5	120.0
75°	95.4	95.4	94.0	93.3	92.7
77.5°	71.5	71.7	71.1	70.4	69.2
80°	56.4	57.7	57.1	56.4	55.7
82.5°	42.4	43.8	43.7	42.4	42.3
85°	22.2	24.1	24.2	24.2	24.2
87.5°	5.9	8.0	8.6	8.6	9.1
90°	0.0	0.0	0.0	0.0	0.0
92.5°	7.8	41.4	96.1	28.0	21.1
95°	25.4	100.8	453.1	156.8	96.7
97.5°	46.7	118.1	697.9	499.4	342.2
100°	61.5	128.4	751.0	760.7	585.9
102.5°	77.9	139.4	739.3	973.7	821.1
105°	103.5	157.0	678.7	1198.9	1139.7
107.5°	129.5	177.4	608.0	1262.3	1315.0
110°	147.5	192.3	567.4	1238.0	1356.5

TEST NUMBER: P523724

CATALOG NUMBER: SQ4-PP3-075U-050D-92765-1D-UNV-STD-W-4 (3000K)

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	164.6	207.2	540.0	1180.6	1349.4
115°	192.4	232.5	514.7	1090.3	1280.3
117.5°	216.8	254.4	499.6	991.5	1192.8
120°	236.3	267.8	498.0	935.1	1127.9
122.5°	252.0	283.5	494.1	885.5	1064.7
125°	271.5	301.1	491.2	815.2	974.6
127.5°	292.8	320.5	489.7	773.1	904.5
130°	303.7	331.4	487.3	743.8	858.4
132.5°	315.4	342.4	487.3	721.0	826.4
135°	332.0	359.7	485.4	688.6	778.3
137.5°	347.7	374.6	485.2	661.1	738.7
140°	359.4	387.1	484.4	638.4	712.9
142.5°	372.7	395.8	486.7	620.3	687.1
145°	391.6	411.7	489.3	595.9	649.4
147.5°	407.8	427.3	493.6	571.4	617.6
150°	421.9	435.2	495.1	563.2	595.7
152.5°	432.8	446.9	496.7	552.3	582.4
155°	447.3	457.8	501.0	538.6	560.5
157.5°	465.2	471.5	502.0	532.4	548.0
160°	474.6	479.4	505.9	527.6	541.0
162.5°	480.1	485.6	506.6	523.7	534.0
165°	494.1	496.1	506.8	517.8	525.4
167.5°	503.7	502.0	511.3	516.3	519.3
170°	506.8	505.9	509.8	510.8	514.7
172.5°	513.9	510.6	512.1	509.3	512.3
175°	517.6	514.7	512.7	509.7	505.9
177.5°	519.1	514.6	512.1	509.0	509.8
180°	513.7	513.7	513.7	513.7	513.7

(END OF REPORT)