

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P523737

Luminaire Tested: **SQ4-PP3-075U-075D-92765-1D-UNV-STD-W-4 (3000K)**

Issue Date: 5/24/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P523737  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2103-172-1)  
Test Lab: INNOVATION CENTER  
Issue Date: 5/24/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PP3-075U-075D-92765-1D-UNV-STD-W-4 (3000K)  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS  
DOWNLIGHT 750 LUMENS PER FOOT  
UPLIGHT 750 LUMENS PER FOOT  
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 3000K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6128.3 lumens  
Efficiency: N/A  
Efficacy: 110.2 lumens/watt  
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33  
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 55.6  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P523737

CATALOG NUMBER: SQ4-PP3-075U-075D-92765-1D-UNV-STD-W-4 (3000K)

### Luminous Intensity Polar Plot





TEST NUMBER: P523737

CATALOG NUMBER: SQ4-PP3-075U-075D-92765-1D-UNV-STD-W-4 (3000K)

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	107	107	107	107	98	98	98	98	82	82	82	68	68	68	54	54	54	48	48	48	48	48	48	48		
1	98	93	90	86	90	86	83	80	72	70	68	60	58	57	48	47	46	41	41	41	41	41	41	41		
2	89	82	76	71	82	75	70	66	64	60	56	53	50	48	43	41	39	34	34	34	34	34	34	34		
3	81	72	65	59	74	66	60	55	56	52	48	47	43	40	38	36	33	29	29	29	29	29	29	29		
4	74	64	56	50	68	59	52	47	50	45	41	42	38	35	34	31	29	25	25	25	25	25	25	25		
5	68	57	49	43	63	53	45	40	45	39	35	37	33	30	31	28	25	22	22	22	22	22	22	22		
6	63	51	43	37	58	47	40	35	40	35	31	34	30	26	28	25	22	19	19	19	19	19	19	19		
7	58	46	38	33	53	43	36	31	37	31	27	31	27	23	25	22	20	17	17	17	17	17	17	17		
8	54	42	34	29	50	39	32	27	33	28	24	28	24	21	23	20	18	15	15	15	15	15	15	15		
9	50	38	31	26	46	35	29	24	31	25	21	26	22	19	21	18	16	14	14	14	14	14	14	14		
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	20	17	15	13	13	13	13	13	13	13		

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	10589	10589	10589
5°	10666	10602	10565
10°	10648	10573	10526
15°	10578	10520	10463
20°	10509	10449	10370
25°	10384	10311	10210
30°	10191	10138	10009
35°	9925	9856	9732
40°	9607	9546	9438
45°	9345	9280	9187
50°	9010	8951	8865
55°	8543	8430	8364
60°	7778	7554	7518
65°	6851	6567	6545
70°	5916	5670	5670
75°	5090	5019	4948
80°	4490	4543	4436
85°	3515	3832	3832



TEST NUMBER: P523737

CATALOG NUMBER: SQ4-PP3-075U-075D-92765-1D-UNV-STD-W-4 (3000K)

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	108.5	1.8
10°-20°	309.9	5.1
20°-30°	464.2	7.6
30°-40°	544.4	8.9
40°-50°	546.1	8.9
50°-60°	465.9	7.6
60°-70°	303.8	5.0
70°-80°	152.4	2.5
80°-90°	42.2	0.7
90°-100°	234.1	3.8
100°-110°	666.0	10.9
110°-120°	638.1	10.4
120°-130°	505.0	8.2
130°-140°	405.4	6.6
140°-150°	317.4	5.2
150°-160°	232.2	3.8
160°-170°	143.8	2.3
170°-180°	48.8	0.8
0°-30°	882.6	14.4
0°-40°	1427.0	23.3
0°-60°	2439.0	39.8
0°-90°	2937.5	47.9
90°-120°	1538.2	25.1
90°-150°	2766.0	45.1
90°-180°	3191.0	52.1
0°-180°	6128.3	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1148	1148	1148	1148	1148	
5°	1152	1141	1145	1141	1141	109
15°	1108	1097	1101	1097	1095	312
25°	1020	1008	1013	1004	1003	469
35°	881	872	875	865	864	550
45°	716	711	711	704	704	551
55°	531	529	524	521	520	472
65°	314	308	301	299	300	313
75°	143	143	141	140	139	155
85°	33	36	36	36	36	39
90°	0	0	0	0	0	2
95°	25	101	453	157	97	29
105°	104	157	679	1199	1140	110
115°	192	232	515	1090	1280	189
125°	272	301	491	815	975	243
135°	332	360	485	689	778	256
145°	392	412	489	596	649	245
155°	447	458	501	539	560	207
165°	494	496	507	518	525	139
175°	518	515	513	510	506	49
180°	514	514	514	514	514	

TEST NUMBER: P523737

CATALOG NUMBER: SQ4-PP3-075U-075D-92765-1D-UNV-STD-W-4 (3000K)

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1147.7	1147.7	1147.7	1147.7	1147.7
2.5°	1155.0	1145.5	1147.7	1146.0	1141.3
5°	1151.7	1140.9	1144.7	1140.7	1140.7
7.5°	1143.9	1132.1	1135.8	1131.8	1131.6
10°	1136.6	1124.8	1128.6	1124.6	1123.6
12.5°	1126.2	1114.4	1118.9	1114.1	1113.9
15°	1107.5	1096.7	1101.4	1097.4	1095.4
17.5°	1086.4	1074.6	1080.3	1074.7	1073.9
20°	1070.3	1058.5	1064.2	1056.2	1056.2
22.5°	1050.9	1039.1	1045.7	1035.3	1035.3
25°	1020.0	1008.2	1012.9	1003.8	1002.9
27.5°	983.1	971.5	976.5	966.2	966.0
30°	956.6	945.8	951.6	940.5	939.5
32.5°	927.6	917.6	921.8	910.7	909.7
35°	881.2	872.3	875.1	865.0	864.1
37.5°	832.3	823.2	826.4	817.8	817.4
40°	797.7	791.8	792.6	785.5	783.6
42.5°	765.5	758.8	759.6	752.6	752.2
45°	716.2	711.3	711.2	704.1	704.1
47.5°	663.9	660.1	659.1	653.2	653.0
50°	627.7	624.7	623.6	618.6	617.6
52.5°	589.8	588.5	585.0	580.8	580.6
55°	531.1	529.1	524.1	521.0	520.0
57.5°	467.3	463.4	457.7	453.3	454.1
60°	421.5	417.5	409.4	407.4	407.4
62.5°	377.2	372.5	364.3	361.5	363.1
65°	313.8	307.9	300.8	298.8	299.8
67.5°	256.3	251.0	243.2	243.2	242.4
70°	219.3	216.3	210.2	210.2	210.2
72.5°	186.3	184.9	180.5	180.4	179.7
75°	142.8	142.8	140.8	139.8	138.8
77.5°	107.0	107.4	106.4	105.4	103.6
80°	84.5	86.5	85.5	84.5	83.5
82.5°	63.6	65.5	65.4	63.6	63.4
85°	33.2	36.1	36.2	36.2	36.2
87.5°	8.9	12.0	12.9	12.9	13.7
90°	0.0	0.0	0.0	0.0	0.0
92.5°	7.8	41.4	96.1	28.0	21.1
95°	25.4	100.8	453.1	156.8	96.7
97.5°	46.7	118.1	697.9	499.4	342.2
100°	61.5	128.4	751.0	760.7	585.9
102.5°	77.9	139.4	739.3	973.7	821.1
105°	103.5	157.0	678.7	1198.9	1139.7
107.5°	129.5	177.4	608.0	1262.3	1315.0
110°	147.5	192.3	567.4	1238.0	1356.5

TEST NUMBER: P523737

CATALOG NUMBER: SQ4-PP3-075U-075D-92765-1D-UNV-STD-W-4 (3000K)

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	164.6	207.2	540.0	1180.6	1349.4
115°	192.4	232.5	514.7	1090.3	1280.3
117.5°	216.8	254.4	499.6	991.5	1192.8
120°	236.3	267.8	498.0	935.1	1127.9
122.5°	252.0	283.5	494.1	885.5	1064.7
125°	271.5	301.1	491.2	815.2	974.6
127.5°	292.8	320.5	489.7	773.1	904.5
130°	303.7	331.4	487.3	743.8	858.4
132.5°	315.4	342.4	487.3	721.0	826.4
135°	332.0	359.7	485.4	688.6	778.3
137.5°	347.7	374.6	485.2	661.1	738.7
140°	359.4	387.1	484.4	638.4	712.9
142.5°	372.7	395.8	486.7	620.3	687.1
145°	391.6	411.7	489.3	595.9	649.4
147.5°	407.8	427.3	493.6	571.4	617.6
150°	421.9	435.2	495.1	563.2	595.7
152.5°	432.8	446.9	496.7	552.3	582.4
155°	447.3	457.8	501.0	538.6	560.5
157.5°	465.2	471.5	502.0	532.4	548.0
160°	474.6	479.4	505.9	527.6	541.0
162.5°	480.1	485.6	506.6	523.7	534.0
165°	494.1	496.1	506.8	517.8	525.4
167.5°	503.7	502.0	511.3	516.3	519.3
170°	506.8	505.9	509.8	510.8	514.7
172.5°	513.9	510.6	512.1	509.3	512.3
175°	517.6	514.7	512.7	509.7	505.9
177.5°	519.1	514.6	512.1	509.0	509.8
180°	513.7	513.7	513.7	513.7	513.7

(END OF REPORT)