

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P523749

Luminaire Tested: **SQ4-PP3-075U-100D-92765-1D-UNV-STD-W-4 (2700K)**

Issue Date: 5/24/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P523749  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2103-172-1)  
Test Lab: INNOVATION CENTER  
Issue Date: 5/24/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PP3-075U-100D-92765-1D-UNV-STD-W-4 (2700K)  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS  
DOWNLIGHT 1000 LUMENS PER FOOT  
UPLIGHT 750 LUMENS PER FOOT  
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 2700K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6909.1 lumens  
Efficiency: N/A  
Efficacy: 104.8 lumens/watt  
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33  
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 65.9  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P523749

CATALOG NUMBER: SQ4-PP3-075U-100D-92765-1D-UNV-STD-W-4 (2700K)

### Luminous Intensity Polar Plot





TEST NUMBER: P523749

CATALOG NUMBER: SQ4-PP3-075U-100D-92765-1D-UNV-STD-W-4 (2700K)

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	86	86	86	73	73	73	60	60	60	55
1	99	95	91	88	92	88	85	82	76	73	71	64	63	61	54	53	52	47
2	90	83	77	72	84	77	72	68	67	63	59	57	54	51	48	46	44	39
3	83	73	66	60	76	68	62	57	59	54	50	50	47	44	42	40	37	34
4	76	65	57	51	70	61	54	48	52	47	43	45	41	37	38	35	32	29
5	69	58	50	44	64	54	47	41	47	41	37	40	36	33	34	31	28	25
6	64	52	44	38	59	49	41	36	42	37	32	36	32	29	31	28	25	22
7	59	47	39	33	55	44	37	32	38	33	28	33	29	25	28	25	22	20
8	55	43	35	29	51	40	33	28	35	29	25	30	26	23	26	22	20	18
9	51	39	31	26	48	37	30	25	32	27	23	28	23	20	24	20	18	16
10	48	36	28	24	44	34	27	23	30	24	20	26	21	18	22	19	16	14

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	13637	13637	13637
5°	13738	13653	13605
10°	13715	13617	13556
15°	13624	13549	13475
20°	13534	13457	13355
25°	13372	13280	13148
30°	13125	13056	12891
35°	12781	12694	12534
40°	12373	12294	12155
45°	12035	11950	11832
50°	11603	11529	11417
55°	11002	10856	10772
60°	10016	9728	9682
65°	8824	8455	8427
70°	7618	7302	7302
75°	6559	6466	6374
80°	5781	5850	5712
85°	4520	4933	4933



TEST NUMBER: P523749

CATALOG NUMBER: SQ4-PP3-075U-100D-92765-1D-UNV-STD-W-4 (2700K)

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	139.8	2.0
10°-20°	399.1	5.8
20°-30°	597.8	8.7
30°-40°	701.2	10.1
40°-50°	703.4	10.2
50°-60°	600.0	8.7
60°-70°	391.3	5.7
70°-80°	196.3	2.8
80°-90°	54.3	0.8
90°-100°	229.3	3.3
100°-110°	652.5	9.4
110°-120°	625.2	9.0
120°-130°	494.8	7.2
130°-140°	397.1	5.7
140°-150°	310.9	4.5
150°-160°	227.5	3.3
160°-170°	140.9	2.0
170°-180°	47.8	0.7
0°-30°	1136.6	16.5
0°-40°	1837.8	26.6
0°-60°	3141.2	45.5
0°-90°	3783.1	54.8
90°-120°	1507.0	21.8
90°-150°	2709.8	39.2
90°-180°	3126.0	45.2
0°-180°	6909.1	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1478	1478	1478	1478	1478	
5°	1483	1469	1474	1469	1469	141
15°	1426	1412	1418	1413	1411	402
25°	1314	1298	1304	1293	1292	604
35°	1135	1123	1127	1114	1113	709
45°	922	916	916	907	907	710
55°	684	682	675	671	670	608
65°	404	397	387	385	386	403
75°	184	184	181	180	179	200
85°	43	46	47	47	47	50
90°	0	0	0	0	0	3
95°	25	99	444	154	95	28
105°	101	154	665	1174	1116	107
115°	188	228	504	1068	1254	186
125°	266	295	481	799	955	238
135°	325	352	476	675	762	251
145°	384	403	479	584	636	240
155°	438	448	491	528	549	203
165°	484	486	496	507	515	136
175°	507	504	502	499	496	48
180°	503	503	503	503	503	

TEST NUMBER: P523749

CATALOG NUMBER: SQ4-PP3-075U-100D-92765-1D-UNV-STD-W-4 (2700K)

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1478.1	1478.1	1478.1	1478.1	1478.1
2.5°	1487.4	1475.3	1478.1	1475.9	1469.8
5°	1483.3	1469.4	1474.2	1469.0	1469.0
7.5°	1473.2	1458.0	1462.8	1457.6	1457.4
10°	1463.9	1448.7	1453.5	1448.3	1447.0
12.5°	1450.4	1435.2	1441.1	1434.8	1434.6
15°	1426.3	1412.4	1418.5	1413.3	1410.7
17.5°	1399.1	1383.9	1391.3	1384.0	1383.0
20°	1378.4	1363.2	1370.6	1360.2	1360.2
22.5°	1353.5	1338.3	1346.8	1333.3	1333.3
25°	1313.6	1298.4	1304.5	1292.8	1291.6
27.5°	1266.2	1251.2	1257.6	1244.4	1244.2
30°	1232.0	1218.0	1225.5	1211.2	1210.0
32.5°	1194.7	1181.7	1187.2	1172.9	1171.6
35°	1134.8	1123.4	1127.0	1114.1	1112.8
37.5°	1071.9	1060.2	1064.3	1053.2	1052.7
40°	1027.3	1019.7	1020.8	1011.7	1009.2
42.5°	985.8	977.2	978.3	969.2	968.7
45°	922.4	916.0	915.9	906.8	906.8
47.5°	855.0	850.2	848.8	841.3	841.0
50°	808.4	804.6	803.2	796.7	795.4
52.5°	759.7	757.9	753.4	748.0	747.7
55°	684.0	681.5	674.9	671.0	669.7
57.5°	601.9	596.8	589.4	583.8	584.8
60°	542.8	537.7	527.2	524.7	524.7
62.5°	485.8	479.7	469.2	465.6	467.7
65°	404.2	396.6	387.3	384.8	386.0
67.5°	330.1	323.2	313.2	313.2	312.2
70°	282.4	278.6	270.7	270.7	270.7
72.5°	239.9	238.1	232.4	232.4	231.4
75°	184.0	184.0	181.4	180.0	178.8
77.5°	137.8	138.3	137.1	135.7	133.4
80°	108.8	111.4	110.1	108.8	107.5
82.5°	81.9	84.4	84.2	81.9	81.6
85°	42.7	46.5	46.6	46.6	46.6
87.5°	11.4	15.5	16.6	16.6	17.6
90°	0.0	0.0	0.0	0.0	0.0
92.5°	7.7	40.6	94.1	27.4	20.7
95°	24.9	98.8	443.9	153.7	94.7
97.5°	45.7	115.7	683.7	489.2	335.2
100°	60.3	125.8	735.7	745.2	574.0
102.5°	76.3	136.6	724.3	953.9	804.4
105°	101.4	153.8	664.9	1174.5	1116.5
107.5°	126.9	173.8	595.7	1236.7	1288.3
110°	144.5	188.4	555.9	1212.9	1328.9

TEST NUMBER: P523749

CATALOG NUMBER: SQ4-PP3-075U-100D-92765-1D-UNV-STD-W-4 (2700K)

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	161.3	203.0	529.1	1156.6	1322.0
115°	188.5	227.8	504.2	1068.1	1254.3
117.5°	212.4	249.3	489.5	971.4	1168.6
120°	231.5	262.4	487.9	916.1	1105.0
122.5°	246.8	277.7	484.1	867.5	1043.0
125°	266.0	295.0	481.2	798.6	954.8
127.5°	286.8	314.0	479.7	757.4	886.1
130°	297.5	324.7	477.4	728.7	841.0
132.5°	309.0	335.4	477.4	706.3	809.6
135°	325.3	352.4	475.5	674.6	762.5
137.5°	340.6	367.0	475.3	647.7	723.7
140°	352.1	379.2	474.5	625.5	698.4
142.5°	365.1	387.7	476.8	607.7	673.2
145°	383.7	403.3	479.3	583.8	636.2
147.5°	399.5	418.6	483.5	559.8	605.0
150°	413.3	426.4	485.1	551.8	583.6
152.5°	424.0	437.9	486.6	541.0	570.6
155°	438.2	448.5	490.8	527.7	549.2
157.5°	455.8	462.0	491.8	521.6	536.9
160°	465.0	469.7	495.6	516.9	530.0
162.5°	470.3	475.8	496.4	513.0	523.1
165°	484.1	486.0	496.5	507.2	514.7
167.5°	493.5	491.8	500.9	505.8	508.8
170°	496.5	495.6	499.4	500.5	504.2
172.5°	503.4	500.3	501.7	498.9	501.9
175°	507.1	504.3	502.3	499.3	495.6
177.5°	508.6	504.1	501.7	498.7	499.4
180°	503.2	503.2	503.2	503.2	503.2

(END OF REPORT)