

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P523751

Luminaire Tested: **SQ4-PP3-075U-100D-92765-1D-UNV-STD-W-4 (3500K)**

Issue Date: 5/24/2021

Test Information

Test Method: LM-79-2019
Report Number: P523751
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2103-172-1)
Test Lab: INNOVATION CENTER
Issue Date: 5/24/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PP3-075U-100D-92765-1D-UNV-STD-W-4 (3500K)
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS
DOWNLIGHT 1000 LUMENS PER FOOT
UPLIGHT 750 LUMENS PER FOOT
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7221.6 lumens
Efficiency: N/A
Efficacy: 109.3 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 66.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P523751

CATALOG NUMBER: SQ4-PP3-075U-100D-92765-1D-UNV-STD-W-4 (3500K)

Luminous Intensity Polar Plot





TEST NUMBER: P523751

CATALOG NUMBER: SQ4-PP3-075U-100D-92765-1D-UNV-STD-W-4 (3500K)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	86	86	86	73	73	73	60	60	60	55
1	99	95	91	88	92	88	85	82	76	73	71	64	63	61	54	53	52	47
2	90	83	77	72	84	77	72	68	67	63	59	57	54	51	48	46	44	39
3	83	73	66	60	76	68	62	57	59	54	50	50	47	44	42	40	37	34
4	76	65	57	51	70	61	54	48	52	47	43	45	41	37	38	35	32	29
5	69	58	50	44	64	54	47	41	47	41	37	40	36	33	34	31	28	25
6	64	52	44	38	59	49	41	36	42	37	32	36	32	29	31	28	25	22
7	59	47	39	33	55	44	37	32	38	33	28	33	29	25	28	25	22	20
8	55	43	35	29	51	40	33	28	35	29	25	30	26	23	26	22	20	18
9	51	39	31	26	48	37	30	25	32	27	23	28	23	20	24	20	18	16
10	48	36	28	24	44	34	27	23	30	24	20	26	21	18	22	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	14254	14254	14254
5°	14359	14271	14221
10°	14335	14233	14170
15°	14240	14162	14084
20°	14145	14066	13959
25°	13977	13880	13743
30°	13719	13646	13473
35°	13359	13268	13100
40°	12932	12851	12704
45°	12579	12491	12367
50°	12127	12050	11933
55°	11499	11348	11260
60°	10468	10169	10119
65°	9224	8839	8809
70°	7963	7634	7634
75°	6855	6759	6662
80°	6041	6115	5972
85°	4732	5155	5155



TEST NUMBER: P523751

CATALOG NUMBER: SQ4-PP3-075U-100D-92765-1D-UNV-STD-W-4 (3500K)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	146.1	2.0
10°-20°	417.1	5.8
20°-30°	624.8	8.7
30°-40°	732.9	10.1
40°-50°	735.2	10.2
50°-60°	627.2	8.7
60°-70°	409.0	5.7
70°-80°	205.2	2.8
80°-90°	56.8	0.8
90°-100°	239.7	3.3
100°-110°	682.0	9.4
110°-120°	653.4	9.0
120°-130°	517.2	7.2
130°-140°	415.1	5.7
140°-150°	325.0	4.5
150°-160°	237.8	3.3
160°-170°	147.3	2.0
170°-180°	50.0	0.7
0°-30°	1188.0	16.5
0°-40°	1920.9	26.6
0°-60°	3283.2	45.5
0°-90°	3954.2	54.8
90°-120°	1575.1	21.8
90°-150°	2832.3	39.2
90°-180°	3267.0	45.2
0°-180°	7221.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1545	1545	1545	1545	1545	
5°	1550	1536	1541	1536	1536	147
15°	1491	1476	1483	1477	1474	421
25°	1373	1357	1364	1351	1350	631
35°	1186	1174	1178	1164	1163	741
45°	964	958	957	948	948	742
55°	715	712	706	701	700	635
65°	422	414	405	402	404	422
75°	192	192	190	188	187	209
85°	45	49	49	49	49	52
90°	0	0	0	0	0	3
95°	26	103	464	161	99	30
105°	106	161	695	1228	1167	112
115°	197	238	527	1116	1311	194
125°	278	308	503	835	998	249
135°	340	368	497	705	797	262
145°	401	422	501	610	665	250
155°	458	469	513	552	574	212
165°	506	508	519	530	538	142
175°	530	527	525	522	518	50
180°	526	526	526	526	526	

TEST NUMBER: P523751

CATALOG NUMBER: SQ4-PP3-075U-100D-92765-1D-UNV-STD-W-4 (3500K)

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1545.0	1545.0	1545.0	1545.0	1545.0
2.5°	1554.7	1542.0	1545.0	1542.6	1536.3
5°	1550.4	1535.8	1540.9	1535.5	1535.5
7.5°	1539.8	1523.9	1529.0	1523.6	1523.3
10°	1530.1	1514.2	1519.2	1513.8	1512.5
12.5°	1516.0	1500.1	1506.2	1499.7	1499.5
15°	1490.8	1476.2	1482.7	1477.2	1474.5
17.5°	1462.4	1446.5	1454.2	1446.6	1445.6
20°	1440.7	1424.8	1432.6	1421.7	1421.7
22.5°	1414.7	1398.8	1407.7	1393.6	1393.6
25°	1373.0	1357.1	1363.5	1351.3	1350.0
27.5°	1323.4	1307.8	1314.5	1300.7	1300.4
30°	1287.7	1273.1	1280.9	1266.0	1264.7
32.5°	1248.7	1235.2	1240.8	1225.9	1224.6
35°	1186.1	1174.2	1178.0	1164.4	1163.1
37.5°	1120.3	1108.1	1112.5	1100.8	1100.3
40°	1073.7	1065.8	1067.0	1057.4	1054.8
42.5°	1030.4	1021.4	1022.6	1013.1	1012.5
45°	964.1	957.5	957.3	947.8	947.8
47.5°	893.7	888.6	887.2	879.3	879.0
50°	844.9	840.9	839.5	832.7	831.4
52.5°	794.0	792.2	787.5	781.8	781.5
55°	714.9	712.3	705.5	701.4	700.0
57.5°	629.1	623.8	616.1	610.2	611.2
60°	567.3	562.0	551.1	548.4	548.4
62.5°	507.8	501.4	490.4	486.7	488.8
65°	422.5	414.5	404.9	402.2	403.5
67.5°	345.0	337.9	327.4	327.4	326.3
70°	295.2	291.2	283.0	283.0	283.0
72.5°	250.8	248.9	242.9	242.9	241.8
75°	192.3	192.3	189.6	188.2	186.9
77.5°	144.1	144.6	143.3	141.8	139.5
80°	113.7	116.4	115.1	113.7	112.4
82.5°	85.6	88.2	88.0	85.6	85.3
85°	44.7	48.7	48.7	48.7	48.7
87.5°	11.9	16.2	17.3	17.4	18.4
90°	0.0	0.0	0.0	0.0	0.0
92.5°	8.0	42.4	98.4	28.6	21.6
95°	26.0	103.2	464.0	160.6	99.0
97.5°	47.8	120.9	714.6	511.3	350.4
100°	63.0	131.4	769.0	778.9	600.0
102.5°	79.8	142.8	757.0	997.0	840.8
105°	106.0	160.8	695.0	1227.6	1167.0
107.5°	132.6	181.7	622.6	1292.6	1346.6
110°	151.0	197.0	581.0	1267.8	1389.0

TEST NUMBER: P523751

CATALOG NUMBER: SQ4-PP3-075U-100D-92765-1D-UNV-STD-W-4 (3500K)

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	168.6	212.2	553.0	1208.9	1381.8
115°	197.0	238.1	527.0	1116.4	1311.0
117.5°	222.0	260.5	511.6	1015.3	1221.4
120°	242.0	274.3	510.0	957.5	1155.0
122.5°	258.0	290.3	506.0	906.8	1090.2
125°	278.0	308.3	503.0	834.7	998.0
127.5°	299.8	328.2	501.4	791.7	926.2
130°	311.0	339.4	499.0	761.7	879.0
132.5°	323.0	350.6	499.0	738.3	846.2
135°	340.0	368.4	497.0	705.1	797.0
137.5°	356.0	383.6	496.8	677.0	756.4
140°	368.0	396.4	496.0	653.7	730.0
142.5°	381.6	405.3	498.4	635.2	703.6
145°	401.0	421.5	501.0	610.2	665.0
147.5°	417.6	437.5	505.4	585.1	632.4
150°	432.0	445.7	507.0	576.8	610.0
152.5°	443.2	457.7	508.6	565.5	596.4
155°	458.0	468.8	513.0	551.5	574.0
157.5°	476.4	482.9	514.0	545.2	561.2
160°	486.0	490.9	518.0	540.3	554.0
162.5°	491.6	497.3	518.8	536.2	546.8
165°	506.0	508.0	519.0	530.2	538.0
167.5°	515.8	514.0	523.6	528.7	531.8
170°	519.0	518.0	522.0	523.1	527.0
172.5°	526.2	522.9	524.4	521.5	524.6
175°	530.0	527.1	525.0	521.9	518.0
177.5°	531.6	526.9	524.4	521.2	522.0
180°	526.0	526.0	526.0	526.0	526.0

(END OF REPORT)