

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P561712

Luminaire Tested: **SQ4-PC3-125U-125D-92765-1D-UNV-STD-W-4 (2700K)**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P561712
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2106-289-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PC3-125U-125D-92765-1D-UNV-STD-W-4 (2700K)
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 1250 LUMENS PER FOOT
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 10089.8 lumens
Efficiency: N/A
Efficacy: 104.0 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 97
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P561712
CATALOG NUMBER: SQ4-PC3-125U-125D-92765-1D-UNV-STD-W-4 (2700K)

Luminous Intensity Polar Plot





TEST NUMBER: P561712

CATALOG NUMBER: SQ4-PC3-125U-125D-92765-1D-UNV-STD-W-4 (2700K)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	98	98	98	98	82	82	82	68	68	68	54	54	54	48
1	97	93	89	86	89	86	83	80	72	70	68	60	58	56	48	47	46	41
2	89	81	75	70	81	75	70	65	63	59	56	52	50	47	42	40	39	34
3	81	71	64	58	74	66	60	54	56	51	47	46	43	40	37	35	33	29
4	74	63	55	49	68	58	51	46	49	44	40	41	37	34	33	31	28	25
5	68	56	48	42	62	52	45	40	44	39	34	37	33	29	30	27	25	21
6	62	50	42	36	57	47	40	34	40	34	30	33	29	26	27	24	22	19
7	58	45	37	32	53	42	35	30	36	30	26	30	26	23	25	22	19	17
8	53	41	33	28	49	38	31	27	33	27	23	28	23	20	23	20	17	15
9	50	38	30	25	46	35	28	24	30	25	21	25	21	18	21	18	15	13
10	46	34	27	22	43	32	26	21	28	22	19	23	19	16	19	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16347	16347	16347
5°	16470	16363	16303
10°	16430	16353	16307
15°	16344	16344	16328
20°	16236	16285	16285
25°	16082	16199	16150
30°	15887	16079	16009
35°	15650	15891	15780
40°	15392	15609	15451
45°	15112	15219	14984
50°	14717	14717	14481
55°	14250	14065	13854
60°	13563	13289	13077
65°	12535	12284	12177
70°	10976	11063	11020
75°	8830	9767	9824
80°	6275	8278	8368
85°	3822	6944	6944



TEST NUMBER: P561712

CATALOG NUMBER: SQ4-PC3-125U-125D-92765-1D-UNV-STD-W-4 (2700K)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	167.7	1.7
10°-20°	481.2	4.8
20°-30°	728.7	7.2
30°-40°	873.6	8.7
40°-50°	890.8	8.8
50°-60°	777.6	7.7
60°-70°	556.7	5.5
70°-80°	286.7	2.8
80°-90°	72.5	0.7
90°-100°	385.4	3.8
100°-110°	1096.7	10.9
110°-120°	1050.8	10.4
120°-130°	831.6	8.2
130°-140°	667.5	6.6
140°-150°	522.6	5.2
150°-160°	382.4	3.8
160°-170°	236.8	2.3
170°-180°	80.4	0.8
0°-30°	1377.6	13.7
0°-40°	2251.2	22.3
0°-60°	3919.6	38.8
0°-90°	4835.5	47.9
90°-120°	2532.9	25.1
90°-150°	4554.7	45.1
90°-180°	5254.0	52.1
0°-180°	10089.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1772	1772	1772	1772	1772	
5°	1778	1761	1767	1762	1760	169
15°	1711	1697	1711	1711	1709	482
25°	1580	1569	1591	1586	1586	727
35°	1390	1386	1411	1401	1401	869
45°	1158	1155	1166	1152	1148	892
55°	886	875	874	861	861	790
65°	574	561	563	558	558	568
75°	248	259	274	276	276	268
85°	36	55	66	67	66	49
90°	0	0	0	0	0	3
95°	42	166	746	258	159	48
105°	170	258	1118	1974	1877	180
115°	317	383	848	1795	2108	312
125°	447	496	809	1342	1605	400
135°	547	592	799	1134	1282	422
145°	645	678	806	981	1069	403
155°	736	754	825	887	923	340
165°	814	817	835	853	865	229
175°	852	848	844	839	833	81
180°	846	846	846	846	846	

TEST NUMBER: P561712

CATALOG NUMBER: SQ4-PC3-125U-125D-92765-1D-UNV-STD-W-4 (2700K)

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1771.8	1771.8	1771.8	1771.8	1771.8
2.5°	1782.3	1766.9	1771.8	1767.7	1761.3
5°	1778.3	1760.7	1766.8	1761.9	1760.3
7.5°	1765.5	1747.9	1756.0	1752.7	1751.1
10°	1753.7	1736.1	1745.5	1742.2	1740.6
12.5°	1738.0	1721.6	1732.4	1729.1	1728.8
15°	1711.1	1696.6	1711.1	1711.0	1709.4
17.5°	1677.3	1664.1	1679.6	1680.5	1679.6
20°	1653.6	1639.2	1658.6	1657.0	1658.6
22.5°	1624.8	1612.9	1633.6	1629.4	1631.0
25°	1579.8	1568.6	1591.3	1586.4	1586.4
27.5°	1526.7	1518.7	1543.4	1538.2	1538.2
30°	1491.2	1483.2	1509.3	1502.7	1502.7
32.5°	1451.9	1446.4	1471.2	1463.3	1463.3
35°	1389.5	1386.3	1410.9	1401.0	1401.0
37.5°	1325.2	1322.3	1344.6	1332.7	1328.8
40°	1278.0	1276.4	1296.0	1282.9	1282.9
42.5°	1230.7	1229.1	1246.1	1230.4	1230.4
45°	1158.2	1155.0	1166.4	1151.6	1148.4
47.5°	1079.1	1075.9	1083.1	1067.0	1065.4
50°	1025.3	1022.1	1025.3	1010.5	1008.9
52.5°	970.2	964.4	965.0	950.2	949.9
55°	885.9	874.7	874.4	861.3	861.3
57.5°	796.6	781.9	783.2	772.0	770.4
60°	735.0	718.9	720.2	710.3	708.7
62.5°	674.6	656.0	659.8	648.7	648.3
65°	574.2	561.4	562.7	557.8	557.8
67.5°	477.7	465.9	474.4	470.5	470.2
70°	406.9	398.8	410.1	410.1	408.5
72.5°	341.2	340.9	355.0	355.0	356.0
75°	247.7	258.9	274.0	275.6	275.6
77.5°	165.4	185.3	201.8	202.4	202.1
80°	118.1	140.6	155.8	159.1	157.5
82.5°	80.1	103.8	116.5	119.7	118.1
85°	36.1	55.3	65.6	67.2	65.6
87.5°	10.5	22.0	26.2	26.2	23.6
90°	0.0	0.0	0.0	0.0	0.0
92.5°	12.9	68.2	158.2	46.1	34.7
95°	41.8	166.0	746.2	258.3	159.2
97.5°	76.9	194.5	1149.2	822.3	563.5
100°	101.3	211.4	1236.6	1252.6	964.9
102.5°	128.3	229.6	1217.3	1603.4	1352.1
105°	170.5	258.5	1117.6	1974.1	1876.7
107.5°	213.2	292.2	1001.2	2078.7	2165.5
110°	242.8	316.7	934.3	2038.7	2233.7

TEST NUMBER: P561712

CATALOG NUMBER: SQ4-PC3-125U-125D-92765-1D-UNV-STD-W-4 (2700K)

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	271.1	341.3	889.3	1944.1	2222.1
115°	316.8	382.8	847.5	1795.3	2108.2
117.5°	357.0	419.0	822.7	1632.7	1964.1
120°	389.2	441.0	820.1	1539.7	1857.4
122.5°	414.9	466.8	813.7	1458.2	1753.2
125°	447.1	495.8	808.9	1342.3	1604.9
127.5°	482.1	527.7	806.3	1273.1	1489.4
130°	500.1	545.7	802.4	1224.8	1413.5
132.5°	519.4	563.8	802.4	1187.2	1360.8
135°	546.8	592.4	799.2	1133.9	1281.7
137.5°	572.5	616.8	798.9	1088.7	1216.4
140°	591.8	637.4	797.6	1051.3	1173.9
142.5°	613.7	651.7	801.5	1021.4	1131.5
145°	644.8	677.9	805.7	981.3	1069.4
147.5°	671.5	703.6	812.7	940.9	1017.0
150°	694.7	716.7	815.3	927.5	980.9
152.5°	712.7	736.0	817.9	909.4	959.1
155°	736.5	753.8	825.0	886.9	923.1
157.5°	766.1	776.5	826.6	876.7	902.5
160°	781.5	789.4	833.0	868.9	890.9
162.5°	790.5	799.7	834.3	862.3	879.3
165°	813.7	816.8	834.6	852.6	865.2
167.5°	829.5	826.6	842.0	850.2	855.2
170°	834.6	833.0	839.4	841.2	847.5
172.5°	846.2	840.8	843.3	838.6	843.6
175°	852.3	847.6	844.3	839.3	833.0
177.5°	854.9	847.3	843.3	838.2	839.4
180°	845.9	845.9	845.9	845.9	845.9

(END OF REPORT)