

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P561727

Luminaire Tested: **SQ4-PC3-150U-050D-92765-1D-UNV-STD-W-4 (3500K)**

Issue Date: 7/30/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P561727  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2106-289-1)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/30/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PC3-150U-050D-92765-1D-UNV-STD-W-4 (3500K)  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS  
DOWNLIGHT 500 LUMENS PER FOOT  
UPLIGHT 1500 LUMENS PER FOOT  
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 3500K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 8646.2 lumens  
Efficiency: N/A  
Efficacy: 120.3 lumens/watt  
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37  
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 71.9  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P561727

CATALOG NUMBER: SQ4-PC3-150U-050D-92765-1D-UNV-STD-W-4 (3500K)

### Luminous Intensity Polar Plot





TEST NUMBER: P561727

CATALOG NUMBER: SQ4-PC3-150U-050D-92765-1D-UNV-STD-W-4 (3500K)

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	90	90	90	90	69	69	69	49	49	49	32	32	32	23
1	92	88	84	81	81	78	75	72	60	58	56	43	42	41	28	27	27	20
2	84	77	71	66	74	68	63	59	53	49	46	38	36	34	25	24	23	17
3	76	67	60	55	67	60	54	49	46	42	39	34	31	29	22	20	19	14
4	70	59	52	46	62	53	47	42	41	37	33	30	27	25	19	18	16	12
5	64	53	45	39	56	47	40	36	36	32	28	27	24	21	17	16	14	10
6	59	47	39	34	52	42	35	31	33	28	24	24	21	18	16	14	12	9
7	54	42	35	29	48	38	31	27	30	25	21	22	19	16	14	12	11	8
8	50	38	31	26	44	34	28	23	27	22	19	20	17	14	13	11	10	7
9	46	35	28	23	41	31	25	21	24	20	17	18	15	13	12	10	9	6
10	43	32	25	20	38	28	22	18	22	18	15	17	14	11	11	9	8	6

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	6855	6855	6855
5°	6906	6862	6836
10°	6890	6858	6838
15°	6853	6853	6847
20°	6808	6829	6829
25°	6744	6793	6772
30°	6662	6743	6713
35°	6563	6663	6617
40°	6454	6546	6480
45°	6337	6382	6283
50°	6172	6172	6073
55°	5976	5899	5810
60°	5687	5573	5484
65°	5257	5152	5106
70°	4602	4640	4621
75°	3704	4096	4121
80°	2630	3475	3507
85°	1598	2911	2911



TEST NUMBER: P561727

CATALOG NUMBER: SQ4-PC3-150U-050D-92765-1D-UNV-STD-W-4 (3500K)

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	70.3	0.8
10°-20°	201.8	2.3
20°-30°	305.6	3.5
30°-40°	366.3	4.2
40°-50°	373.5	4.3
50°-60°	326.1	3.8
60°-70°	233.4	2.7
70°-80°	120.2	1.4
80°-90°	30.4	0.4
90°-100°	485.5	5.6
100°-110°	1381.5	16.0
110°-120°	1323.6	15.3
120°-130°	1047.6	12.1
130°-140°	840.8	9.7
140°-150°	658.3	7.6
150°-160°	481.7	5.6
160°-170°	298.3	3.5
170°-180°	101.2	1.2
0°-30°	577.7	6.7
0°-40°	944.0	10.9
0°-60°	1643.6	19.0
0°-90°	2027.7	23.5
90°-120°	3190.6	36.9
90°-150°	5737.2	66.4
90°-180°	6618.0	76.5
0°-180°	8646.2	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	743	743	743	743	743	
5°	746	738	741	739	738	71
15°	718	712	718	718	717	202
25°	662	658	667	665	665	305
35°	583	581	592	588	588	364
45°	486	484	489	483	482	374
55°	372	367	367	361	361	331
65°	241	235	236	234	234	238
75°	104	109	115	116	116	112
85°	15	23	28	28	28	21
90°	0	0	0	0	0	3
95°	53	209	940	325	200	60
105°	215	326	1408	2487	2364	227
115°	399	482	1068	2262	2656	393
125°	563	624	1019	1691	2022	504
135°	689	746	1007	1428	1614	531
145°	812	854	1015	1236	1347	507
155°	928	950	1039	1117	1163	429
165°	1025	1029	1051	1074	1090	288
175°	1074	1068	1064	1057	1049	102
180°	1066	1066	1066	1066	1066	

TEST NUMBER: P561727

CATALOG NUMBER: SQ4-PC3-150U-050D-92765-1D-UNV-STD-W-4 (3500K)

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	743.0	743.0	743.0	743.0	743.0
2.5°	747.4	740.9	743.0	741.3	738.6
5°	745.7	738.3	740.9	738.8	738.1
7.5°	740.3	732.9	736.4	735.0	734.3
10°	735.4	728.0	732.0	730.6	729.9
12.5°	728.8	721.9	726.5	725.1	724.9
15°	717.5	711.5	717.5	717.5	716.8
17.5°	703.3	697.8	704.3	704.7	704.3
20°	693.4	687.4	695.5	694.8	695.5
22.5°	681.3	676.3	685.0	683.3	683.9
25°	662.5	657.8	667.3	665.2	665.2
27.5°	640.2	636.8	647.2	645.0	645.0
30°	625.3	622.0	632.9	630.1	630.1
32.5°	608.8	606.5	616.9	613.6	613.6
35°	582.7	581.3	591.6	587.5	587.5
37.5°	555.7	554.5	563.8	558.8	557.2
40°	535.9	535.2	543.5	538.0	538.0
42.5°	516.1	515.4	522.6	515.9	515.9
45°	485.7	484.3	489.1	482.9	481.5
47.5°	452.5	451.2	454.2	447.4	446.7
50°	430.0	428.6	430.0	423.7	423.1
52.5°	406.8	404.4	404.6	398.4	398.3
55°	371.5	366.8	366.7	361.2	361.2
57.5°	334.1	327.9	328.4	323.7	323.1
60°	308.2	301.5	302.0	297.9	297.2
62.5°	282.9	275.1	276.7	272.0	271.9
65°	240.8	235.4	236.0	233.9	233.9
67.5°	200.3	195.3	198.9	197.3	197.2
70°	170.6	167.2	172.0	172.0	171.3
72.5°	143.1	143.0	148.9	148.9	149.3
75°	103.9	108.6	114.9	115.6	115.6
77.5°	69.3	77.7	84.6	84.9	84.8
80°	49.5	58.9	65.4	66.7	66.0
82.5°	33.6	43.5	48.8	50.2	49.5
85°	15.1	23.2	27.5	28.2	27.5
87.5°	4.4	9.2	11.0	11.0	9.9
90°	0.0	0.0	0.0	0.0	0.0
92.5°	16.2	85.9	199.3	58.0	43.8
95°	52.7	209.1	939.9	325.3	200.5
97.5°	96.8	245.0	1447.5	1035.8	709.8
100°	127.6	266.3	1557.7	1577.8	1215.4
102.5°	161.6	289.2	1533.4	2019.7	1703.2
105°	214.7	325.6	1407.8	2486.7	2363.9
107.5°	268.6	368.0	1261.2	2618.4	2727.7
110°	305.9	399.0	1176.9	2568.0	2813.6

TEST NUMBER: P561727

CATALOG NUMBER: SQ4-PC3-150U-050D-92765-1D-UNV-STD-W-4 (3500K)

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	341.5	429.9	1120.2	2448.9	2799.0
115°	399.1	482.2	1067.5	2261.5	2655.6
117.5°	449.7	527.7	1036.3	2056.6	2474.1
120°	490.2	555.6	1033.1	1939.5	2339.6
122.5°	522.6	588.0	1025.0	1836.8	2208.4
125°	563.1	624.5	1018.9	1690.8	2021.6
127.5°	607.3	664.7	1015.7	1603.6	1876.1
130°	630.0	687.4	1010.8	1542.9	1780.5
132.5°	654.3	710.1	1010.8	1495.4	1714.1
135°	688.7	746.2	1006.7	1428.3	1614.4
137.5°	721.1	777.0	1006.3	1371.4	1532.2
140°	745.4	802.9	1004.7	1324.2	1478.7
142.5°	773.0	820.9	1009.6	1286.6	1425.2
145°	812.3	853.9	1014.8	1236.1	1347.0
147.5°	845.9	886.3	1023.8	1185.2	1281.0
150°	875.1	902.8	1027.0	1168.3	1235.6
152.5°	897.8	927.1	1030.2	1145.5	1208.1
155°	927.7	949.5	1039.2	1117.2	1162.7
157.5°	965.0	978.1	1041.2	1104.3	1136.8
160°	984.5	994.4	1049.3	1094.5	1122.2
162.5°	995.8	1007.3	1050.9	1086.2	1107.6
165°	1025.0	1028.9	1051.3	1073.9	1089.8
167.5°	1044.8	1041.3	1060.6	1070.9	1077.2
170°	1051.3	1049.3	1057.4	1059.6	1067.5
172.5°	1065.9	1059.2	1062.2	1056.3	1062.6
175°	1073.6	1067.6	1063.5	1057.2	1049.3
177.5°	1076.8	1067.3	1062.2	1055.8	1057.4
180°	1065.5	1065.5	1065.5	1065.5	1065.5

(END OF REPORT)