

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P523776

Luminaire Tested: **SQ4-PP3-0U-050D-92765-1D-UNV-STD-W-4 (3000K)**

Issue Date: 5/24/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P523776  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2103-172-1)  
Test Lab: INNOVATION CENTER  
Issue Date: 5/24/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PP3-0U-050D-92765-1D-UNV-STD-W-4 (3000K)  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS  
DOWNLIGHT 500 LUMENS PER FOOT  
DIRECT ONLY  
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 3000K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1961.4 lumens  
Efficiency: N/A  
Efficacy: 94.8 lumens/watt  
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33  
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')  
CIE Type: Direct


Input Watts (W): 20.7  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P523776

CATALOG NUMBER: SQ4-PP3-0U-050D-92765-1D-UNV-STD-W-4 (3000K)

### Luminous Intensity Polar Plot





TEST NUMBER: P523776

CATALOG NUMBER: SQ4-PP3-0U-050D-92765-1D-UNV-STD-W-4 (3000K)

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				
1	109	105	101	97	107	103	99	96	98	95	93	95	92	90	91	89	87	85				
2	100	92	86	80	97	90	84	79	87	82	77	84	79	76	81	77	74	72				
3	92	81	74	67	89	80	73	67	77	71	66	74	69	64	72	67	63	61				
4	84	72	64	57	82	71	63	57	69	62	56	66	60	56	64	59	55	53				
5	77	65	56	50	75	64	56	49	62	54	49	60	53	48	58	52	48	46				
6	72	59	50	44	70	58	49	43	56	49	43	54	48	43	53	47	42	40				
7	66	53	45	39	65	52	44	39	51	44	38	49	43	38	48	42	38	36				
8	62	49	40	35	60	48	40	34	47	39	34	45	39	34	44	38	34	32				
9	58	45	37	31	56	44	36	31	43	36	31	42	35	31	41	35	31	29				
10	54	41	34	28	53	41	33	28	40	33	28	39	33	28	38	32	28	26				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	7071	7071	7071
5°	7122	7079	7054
10°	7111	7060	7028
15°	7063	7025	6986
20°	7016	6977	6924
25°	6934	6886	6817
30°	6804	6769	6683
35°	6627	6581	6498
40°	6415	6375	6301
45°	6239	6196	6135
50°	6016	5977	5919
55°	5704	5628	5585
60°	5193	5045	5019
65°	4576	4384	4371
70°	3949	3787	3787
75°	3401	3351	3305
80°	2997	3034	2959
85°	2350	2562	2562



TEST NUMBER: P523776

CATALOG NUMBER: SQ4-PP3-0U-050D-92765-1D-UNV-STD-W-4 (3000K)

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	72.5	3.7
10°-20°	206.9	10.5
20°-30°	309.9	15.8
30°-40°	363.5	18.5
40°-50°	364.7	18.6
50°-60°	311.1	15.9
60°-70°	202.9	10.3
70°-80°	101.8	5.2
80°-90°	28.2	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	589.3	30.0
0°-40°	952.8	48.6
0°-60°	1628.6	83.0
0°-90°	1961.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1961.4	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	766	766	766	766	766	
5°	769	762	764	762	762	73
15°	740	732	736	733	731	209
25°	681	673	676	670	670	313
35°	588	582	584	578	577	368
45°	478	475	475	470	470	368
55°	355	353	350	348	347	315
65°	210	206	201	200	200	209
75°	95	95	94	93	93	103
85°	22	24	24	24	24	27
90°	0	0	0	0	0	



TEST NUMBER: P523776

CATALOG NUMBER: SQ4-PP3-OU-050D-92765-1D-UNV-STD-W-4 (3000K)

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	766.4	766.4	766.4	766.4	766.4
2.5°	771.2	764.9	766.4	765.2	762.1
5°	769.0	761.8	764.3	761.6	761.6
7.5°	763.8	755.9	758.4	755.7	755.6
10°	759.0	751.1	753.6	750.9	750.2
12.5°	752.0	744.1	747.1	743.9	743.8
15°	739.5	732.3	735.5	732.7	731.4
17.5°	725.4	717.5	721.4	717.6	717.1
20°	714.6	706.8	710.6	705.2	705.2
22.5°	701.7	693.9	698.2	691.3	691.3
25°	681.1	673.2	676.4	670.3	669.6
27.5°	656.5	648.7	652.0	645.2	645.1
30°	638.7	631.5	635.4	628.0	627.3
32.5°	619.4	612.7	615.5	608.1	607.4
35°	588.4	582.5	584.3	577.6	576.9
37.5°	555.7	549.7	551.8	546.0	545.8
40°	532.6	528.7	529.3	524.5	523.2
42.5°	511.1	506.7	507.2	502.5	502.3
45°	478.2	474.9	474.9	470.2	470.2
47.5°	443.3	440.8	440.1	436.2	436.0
50°	419.1	417.1	416.4	413.0	412.4
52.5°	393.9	392.9	390.6	387.8	387.7
55°	354.6	353.3	349.9	347.9	347.2
57.5°	312.0	309.4	305.6	302.7	303.2
60°	281.4	278.8	273.4	272.0	272.0
62.5°	251.9	248.7	243.3	241.4	242.5
65°	209.6	205.6	200.8	199.5	200.2
67.5°	171.1	167.6	162.4	162.4	161.9
70°	146.4	144.4	140.4	140.4	140.4
72.5°	124.4	123.5	120.5	120.5	120.0
75°	95.4	95.4	94.0	93.3	92.7
77.5°	71.5	71.7	71.1	70.4	69.2
80°	56.4	57.7	57.1	56.4	55.7
82.5°	42.4	43.8	43.7	42.4	42.3
85°	22.2	24.1	24.2	24.2	24.2
87.5°	5.9	8.0	8.6	8.6	9.1
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)