

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P561739

Luminaire Tested: **SQ4-PC3-150U-075D-92765-1D-UNV-STD-W-4 (3000K)**

Issue Date: 7/30/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P561739  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2106-289-1)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/30/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PC3-150U-075D-92765-1D-UNV-STD-W-4 (3000K)  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS  
DOWNLIGHT 750 LUMENS PER FOOT  
UPLIGHT 1500 LUMENS PER FOOT  
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 3000K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 9428.9 lumens  
Efficiency: N/A  
Efficacy: 113.5 lumens/watt  
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37  
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')  
CIE Type: Semi-Indirect

Input Watts (W): 83.1  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P561739  
CATALOG NUMBER: SQ4-PC3-150U-075D-92765-1D-UNV-STD-W-4 (3000K)

### Luminous Intensity Polar Plot





TEST NUMBER: P561739

CATALOG NUMBER: SQ4-PC3-150U-075D-92765-1D-UNV-STD-W-4 (3000K)

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	92	92	92	92	73	73	73	55	55	55	39	39	39	31
1	94	89	86	82	84	81	77	75	64	62	60	49	47	46	35	34	33	27
2	85	78	72	67	76	70	65	61	56	53	50	43	40	38	30	29	28	22
3	78	69	62	56	70	62	56	51	49	45	42	38	35	32	27	25	24	19
4	71	61	53	47	64	55	48	43	44	39	35	34	30	28	24	22	20	16
5	65	54	46	40	58	49	42	37	39	34	30	30	27	24	22	19	18	14
6	60	48	40	35	54	44	37	32	35	30	26	27	24	21	20	17	15	12
7	55	43	36	30	49	39	33	28	32	27	23	25	21	18	18	15	14	11
8	51	39	32	26	46	36	29	24	29	24	20	22	19	16	16	14	12	10
9	47	36	28	23	43	32	26	22	26	21	18	20	17	14	15	13	11	9
10	44	33	26	21	40	30	23	19	24	19	16	19	15	13	14	12	10	8

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	10025	10025	10025
5°	10101	10036	9999
10°	10076	10029	10001
15°	10024	10024	10014
20°	9958	9987	9987
25°	9863	9935	9904
30°	9744	9861	9818
35°	9598	9746	9677
40°	9440	9573	9476
45°	9268	9334	9190
50°	9025	9025	8882
55°	8739	8627	8496
60°	8316	8150	8019
65°	7687	7534	7468
70°	6730	6784	6757
75°	5415	5989	6024
80°	3847	5079	5133
85°	2339	4256	4256



TEST NUMBER: P561739

CATALOG NUMBER: SQ4-PC3-150U-075D-92765-1D-UNV-STD-W-4 (3000K)

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	102.8	1.1
10°-20°	295.1	3.1
20°-30°	446.9	4.7
30°-40°	535.8	5.7
40°-50°	546.3	5.8
50°-60°	476.9	5.1
60°-70°	341.4	3.6
70°-80°	175.8	1.9
80°-90°	44.5	0.5
90°-100°	474.1	5.0
100°-110°	1349.1	14.3
110°-120°	1292.6	13.7
120°-130°	1023.0	10.8
130°-140°	821.1	8.7
140°-150°	642.8	6.8
150°-160°	470.4	5.0
160°-170°	291.4	3.1
170°-180°	98.9	1.0
0°-30°	844.9	9.0
0°-40°	1380.6	14.6
0°-60°	2403.8	25.5
0°-90°	2965.6	31.5
90°-120°	3115.8	33.0
90°-150°	5602.8	59.4
90°-180°	6463.0	68.5
0°-180°	9428.9	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1087	1087	1087	1087	1087	
5°	1091	1080	1084	1081	1080	104
15°	1049	1040	1049	1049	1048	296
25°	969	962	976	973	973	446
35°	852	850	865	859	859	533
45°	710	708	715	706	704	547
55°	543	536	536	528	528	484
65°	352	344	345	342	342	348
75°	152	159	168	169	169	164
85°	22	34	40	41	40	30
90°	0	0	0	0	0	3
95°	51	204	918	318	196	59
105°	210	318	1375	2428	2308	222
115°	390	471	1042	2208	2593	384
125°	550	610	995	1651	1974	492
135°	673	729	983	1395	1577	519
145°	793	834	991	1207	1316	496
155°	906	927	1015	1091	1136	419
165°	1001	1005	1027	1049	1064	281
175°	1048	1043	1038	1032	1025	99
180°	1040	1040	1040	1040	1040	



TEST NUMBER: P561739

CATALOG NUMBER: SQ4-PC3-150U-075D-92765-1D-UNV-STD-W-4 (3000K)

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1086.6	1086.6	1086.6	1086.6	1086.6
2.5°	1093.0	1083.6	1086.6	1084.1	1080.2
5°	1090.6	1079.8	1083.6	1080.6	1079.6
7.5°	1082.8	1072.0	1077.0	1074.9	1073.9
10°	1075.5	1064.7	1070.5	1068.5	1067.5
12.5°	1065.9	1055.8	1062.5	1060.4	1060.2
15°	1049.4	1040.5	1049.4	1049.4	1048.4
17.5°	1028.7	1020.6	1030.1	1030.7	1030.1
20°	1014.2	1005.3	1017.2	1016.2	1017.2
22.5°	996.5	989.2	1001.9	999.3	1000.3
25°	968.9	962.0	975.9	972.9	972.9
27.5°	936.3	931.4	946.6	943.3	943.3
30°	914.6	909.6	925.6	921.6	921.6
32.5°	890.4	887.1	902.3	897.5	897.5
35°	852.2	850.2	865.3	859.2	859.2
37.5°	812.7	811.0	824.6	817.3	815.0
40°	783.8	782.8	794.8	786.8	786.8
42.5°	754.8	753.8	764.2	754.6	754.6
45°	710.3	708.4	715.4	706.3	704.3
47.5°	661.8	659.9	664.2	654.4	653.4
50°	628.8	626.9	628.8	619.7	618.8
52.5°	595.0	591.5	591.8	582.7	582.5
55°	543.3	536.4	536.3	528.2	528.2
57.5°	488.6	479.5	480.3	473.5	472.5
60°	450.7	440.9	441.7	435.6	434.6
62.5°	413.7	402.3	404.7	397.8	397.6
65°	352.1	344.3	345.1	342.1	342.1
67.5°	293.0	285.7	291.0	288.6	288.4
70°	249.5	244.6	251.5	251.5	250.5
72.5°	209.3	209.1	217.7	217.7	218.3
75°	151.9	158.8	168.0	169.0	169.0
77.5°	101.4	113.6	123.8	124.2	124.0
80°	72.4	86.2	95.6	97.6	96.6
82.5°	49.1	63.7	71.4	73.4	72.4
85°	22.1	33.9	40.2	41.2	40.2
87.5°	6.4	13.5	16.1	16.1	14.5
90°	0.0	0.0	0.0	0.0	0.0
92.5°	15.8	83.9	194.7	56.7	42.7
95°	51.4	204.2	917.9	317.7	195.8
97.5°	94.6	239.2	1413.6	1011.5	693.2
100°	124.6	260.0	1521.2	1540.9	1186.9
102.5°	157.9	282.4	1497.5	1972.3	1663.2
105°	209.7	318.0	1374.8	2428.4	2308.5
107.5°	262.3	359.4	1231.6	2557.0	2663.8
110°	298.7	389.6	1149.3	2507.8	2747.7

TEST NUMBER: P561739

CATALOG NUMBER: SQ4-PC3-150U-075D-92765-1D-UNV-STD-W-4 (3000K)

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	333.5	419.8	1093.9	2391.5	2733.4
115°	389.7	470.9	1042.5	2208.5	2593.4
117.5°	439.2	515.4	1012.0	2008.4	2416.1
120°	478.7	542.5	1008.9	1894.1	2284.8
122.5°	510.4	574.2	1001.0	1793.7	2156.6
125°	549.9	609.9	995.0	1651.2	1974.2
127.5°	593.1	649.1	991.9	1566.0	1832.2
130°	615.2	671.3	987.1	1506.7	1738.8
132.5°	638.9	693.5	987.1	1460.4	1673.9
135°	672.6	728.7	983.2	1394.8	1576.6
137.5°	704.2	758.8	982.8	1339.2	1496.3
140°	728.0	784.1	981.2	1293.2	1444.1
142.5°	754.9	801.7	985.9	1256.4	1391.8
145°	793.2	833.9	991.1	1207.2	1315.5
147.5°	826.1	865.5	999.8	1157.4	1251.0
150°	854.6	881.6	1002.9	1140.9	1206.7
152.5°	876.7	905.4	1006.1	1118.7	1179.8
155°	906.0	927.3	1014.8	1091.0	1135.5
157.5°	942.4	955.2	1016.8	1078.4	1110.1
160°	961.4	971.1	1024.7	1068.8	1095.9
162.5°	972.5	983.7	1026.3	1060.8	1081.7
165°	1001.0	1004.8	1026.7	1048.8	1064.3
167.5°	1020.3	1016.9	1035.8	1045.8	1052.0
170°	1026.7	1024.7	1032.6	1034.8	1042.5
172.5°	1040.9	1034.3	1037.4	1031.6	1037.7
175°	1048.4	1042.6	1038.5	1032.4	1024.7
177.5°	1051.6	1042.3	1037.4	1031.1	1032.6
180°	1040.5	1040.5	1040.5	1040.5	1040.5

(END OF REPORT)