

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P561751

Luminaire Tested: **SQ4-PC3-150U-100D-92765-1D-UNV-STD-W-4 (2700K)**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P561751
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2106-289-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PC3-150U-100D-92765-1D-UNV-STD-W-4 (2700K)
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS
DOWNLIGHT 1000 LUMENS PER FOOT
UPLIGHT 1500 LUMENS PER FOOT
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 10151.4 lumens
Efficiency: N/A
Efficacy: 108.8 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 93.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P561751
CATALOG NUMBER: SQ4-PC3-150U-100D-92765-1D-UNV-STD-W-4 (2700K)

Luminous Intensity Polar Plot





TEST NUMBER: P561751

CATALOG NUMBER: SQ4-PC3-150U-100D-92765-1D-UNV-STD-W-4 (2700K)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	95	95	95	95	76	76	76	60	60	60	45	45	45	38
1	95	91	87	84	86	83	79	76	67	65	63	53	51	50	40	39	38	32
2	87	79	73	68	78	72	67	63	59	55	52	46	44	42	35	33	32	27
3	79	70	62	57	71	63	57	52	52	47	44	41	38	35	31	29	27	23
4	72	62	54	48	65	56	49	44	46	41	37	36	33	30	28	25	23	19
5	66	55	47	41	60	50	43	38	41	36	32	33	29	26	25	22	20	17
6	61	49	41	35	55	45	38	33	37	32	28	29	26	23	22	20	18	15
7	56	44	36	31	51	40	33	29	33	28	24	27	23	20	20	18	16	13
8	52	40	32	27	47	37	30	25	30	25	21	24	21	18	19	16	14	12
9	48	36	29	24	44	33	27	22	28	23	19	22	19	16	17	15	13	10
10	45	33	26	21	41	31	24	20	25	21	17	21	17	14	16	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12911	12911	12911
5°	13009	12924	12877
10°	12977	12916	12880
15°	12909	12909	12897
20°	12824	12862	12862
25°	12703	12795	12756
30°	12548	12700	12645
35°	12361	12552	12464
40°	12157	12329	12204
45°	11936	12021	11834
50°	11625	11625	11438
55°	11255	11109	10943
60°	10712	10496	10330
65°	9900	9702	9619
70°	8667	8737	8702
75°	6976	7714	7760
80°	4957	6540	6610
85°	3017	5483	5483



TEST NUMBER: P561751

CATALOG NUMBER: SQ4-PC3-150U-100D-92765-1D-UNV-STD-W-4 (2700K)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	132.4	1.3
10°-20°	380.1	3.7
20°-30°	575.6	5.7
30°-40°	690.0	6.8
40°-50°	703.6	6.9
50°-60°	614.2	6.1
60°-70°	439.7	4.3
70°-80°	226.5	2.2
80°-90°	57.3	0.6
90°-100°	464.5	4.6
100°-110°	1321.7	13.0
110°-120°	1266.3	12.5
120°-130°	1002.2	9.9
130°-140°	804.5	7.9
140°-150°	629.8	6.2
150°-160°	460.8	4.5
160°-170°	285.4	2.8
170°-180°	96.9	1.0
0°-30°	1088.1	10.7
0°-40°	1778.1	17.5
0°-60°	3095.9	30.5
0°-90°	3819.3	37.6
90°-120°	3052.5	30.1
90°-150°	5489.0	54.1
90°-180°	6332.0	62.4
0°-180°	10151.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1399	1399	1399	1399	1399	
5°	1405	1391	1396	1392	1390	133
15°	1352	1340	1352	1351	1350	381
25°	1248	1239	1257	1253	1253	574
35°	1098	1095	1114	1107	1107	686
45°	915	912	921	910	907	704
55°	700	691	691	680	680	624
65°	454	443	444	441	441	449
75°	196	204	216	218	218	211
85°	28	44	52	53	52	39
90°	0	0	0	0	0	3
95°	50	200	899	311	192	58
105°	205	312	1347	2379	2262	217
115°	382	461	1021	2164	2541	376
125°	539	598	975	1618	1934	482
135°	659	714	963	1366	1545	508
145°	777	817	971	1183	1289	485
155°	888	908	994	1069	1112	410
165°	981	984	1006	1028	1043	276
175°	1027	1022	1018	1012	1004	97
180°	1019	1019	1019	1019	1019	

TEST NUMBER: P561751

CATALOG NUMBER: SQ4-PC3-150U-100D-92765-1D-UNV-STD-W-4 (2700K)

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1399.4	1399.4	1399.4	1399.4	1399.4
2.5°	1407.7	1395.6	1399.4	1396.2	1391.1
5°	1404.6	1390.7	1395.5	1391.6	1390.4
7.5°	1394.5	1380.6	1387.0	1384.4	1383.1
10°	1385.2	1371.2	1378.7	1376.1	1374.8
12.5°	1372.7	1359.8	1368.3	1365.7	1365.5
15°	1351.5	1340.1	1351.5	1351.4	1350.2
17.5°	1324.8	1314.4	1326.6	1327.4	1326.6
20°	1306.1	1294.7	1310.0	1308.7	1310.0
22.5°	1283.3	1273.9	1290.3	1287.0	1288.2
25°	1247.8	1238.9	1256.9	1253.0	1253.0
27.5°	1205.8	1199.5	1219.1	1214.9	1214.9
30°	1177.8	1171.5	1192.1	1186.9	1186.9
32.5°	1146.7	1142.4	1162.0	1155.8	1155.8
35°	1097.5	1095.0	1114.4	1106.6	1106.6
37.5°	1046.7	1044.4	1062.0	1052.6	1049.6
40°	1009.4	1008.1	1023.7	1013.3	1013.3
42.5°	972.1	970.8	984.3	971.8	971.8
45°	914.8	912.3	921.3	909.6	907.0
47.5°	852.4	849.8	855.5	842.7	841.5
50°	809.9	807.3	809.9	798.2	796.9
52.5°	766.3	761.8	762.2	750.5	750.2
55°	699.7	690.8	690.6	680.3	680.3
57.5°	629.2	617.6	618.6	609.8	608.5
60°	580.5	567.8	568.8	561.0	559.8
62.5°	532.8	518.1	521.2	512.3	512.1
65°	453.5	443.4	444.4	440.6	440.6
67.5°	377.3	367.9	374.7	371.6	371.4
70°	321.3	315.0	323.9	323.9	322.6
72.5°	269.5	269.3	280.4	280.4	281.2
75°	195.7	204.5	216.4	217.7	217.7
77.5°	130.6	146.3	159.4	159.9	159.6
80°	93.3	111.0	123.1	125.7	124.4
82.5°	63.2	82.0	92.0	94.6	93.3
85°	28.5	43.7	51.8	53.1	51.8
87.5°	8.3	17.4	20.7	20.7	18.7
90°	0.0	0.0	0.0	0.0	0.0
92.5°	15.5	82.2	190.7	55.5	41.9
95°	50.4	200.1	899.2	311.2	191.9
97.5°	92.6	234.4	1384.9	991.0	679.1
100°	122.1	254.7	1490.3	1509.6	1162.8
102.5°	154.7	276.7	1467.1	1932.3	1629.5
105°	205.4	311.5	1346.9	2379.1	2261.7
107.5°	257.0	352.1	1206.6	2505.1	2609.7
110°	292.6	381.7	1126.0	2456.9	2691.9

TEST NUMBER: P561751

CATALOG NUMBER: SQ4-PC3-150U-100D-92765-1D-UNV-STD-W-4 (2700K)

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	326.7	411.3	1071.7	2342.9	2677.9
115°	381.8	461.4	1021.3	2163.6	2540.7
117.5°	430.2	504.9	991.5	1967.6	2367.1
120°	469.0	531.5	988.4	1855.6	2238.4
122.5°	500.0	562.5	980.6	1757.3	2112.8
125°	538.8	597.5	974.8	1617.7	1934.1
127.5°	581.0	636.0	971.7	1534.2	1795.0
130°	602.7	657.7	967.1	1476.1	1703.5
132.5°	626.0	679.4	967.1	1430.7	1639.9
135°	658.9	713.9	963.2	1366.5	1544.6
137.5°	689.9	743.4	962.8	1312.0	1465.9
140°	713.2	768.1	961.3	1266.9	1414.7
142.5°	739.5	785.4	965.9	1230.9	1363.6
145°	777.1	816.9	970.9	1182.7	1288.8
147.5°	809.3	848.0	979.5	1133.9	1225.6
150°	837.2	863.7	982.6	1117.8	1182.2
152.5°	858.9	887.0	985.7	1095.9	1155.8
155°	887.6	908.5	994.2	1068.8	1112.4
157.5°	923.3	935.8	996.1	1056.5	1087.6
160°	941.9	951.3	1003.9	1047.1	1073.7
162.5°	952.7	963.7	1005.4	1039.2	1059.7
165°	980.6	984.4	1005.8	1027.5	1042.6
167.5°	999.6	996.2	1014.7	1024.6	1030.6
170°	1005.8	1003.9	1011.6	1013.7	1021.3
172.5°	1019.8	1013.3	1016.3	1010.6	1016.7
175°	1027.1	1021.5	1017.5	1011.5	1003.9
177.5°	1030.2	1021.1	1016.3	1010.1	1011.6
180°	1019.4	1019.4	1019.4	1019.4	1019.4

(END OF REPORT)