

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P561770

Luminaire Tested: **SQ4-PC3-150U-125D-92765-1D-UNV-STD-W-4 (5700K)**

Issue Date: 7/30/2021

Test Information

Test Method: LM-79-2019
Report Number: P561770
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2106-289-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/30/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PC3-150U-125D-92765-1D-UNV-STD-W-4 (5700K)
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 1500 LUMENS PER FOOT
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 5700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 12385.5 lumens
Efficiency: N/A
Efficacy: 116.2 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 106.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P561770

CATALOG NUMBER: SQ4-PC3-150U-125D-92765-1D-UNV-STD-W-4 (5700K)

Luminous Intensity Polar Plot





TEST NUMBER: P561770

CATALOG NUMBER: SQ4-PC3-150U-125D-92765-1D-UNV-STD-W-4 (5700K)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	96	96	96	96	80	80	80	64	64	64	50	50	50	43
1	96	92	88	85	88	84	81	78	70	68	65	57	55	54	44	43	42	37
2	88	80	74	69	80	74	69	64	61	57	54	50	47	45	39	37	36	31
3	80	71	63	58	73	65	59	54	54	49	45	44	41	38	34	32	30	26
4	73	62	55	49	67	57	51	45	48	43	39	39	35	32	31	28	26	22
5	67	56	48	42	61	51	44	39	43	37	33	35	31	28	28	25	23	19
6	62	50	42	36	56	46	39	34	38	33	29	32	27	24	25	22	20	17
7	57	45	37	31	52	41	34	29	35	29	25	29	25	21	23	20	18	15
8	53	41	33	28	48	38	31	26	32	26	23	26	22	19	21	18	16	13
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	19	16	14	12
10	46	34	27	22	42	31	25	21	27	22	18	22	18	15	18	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	18129	18129	18129
5°	18266	18148	18080
10°	18222	18137	18085
15°	18126	18126	18108
20°	18007	18060	18060
25°	17836	17966	17911
30°	17620	17833	17755
35°	17358	17623	17501
40°	17070	17311	17136
45°	16760	16879	16618
50°	16321	16321	16060
55°	15804	15600	15365
60°	15041	14738	14504
65°	13902	13625	13505
70°	12171	12271	12220
75°	9792	10830	10897
80°	6960	9181	9282
85°	4234	7707	7707



TEST NUMBER: P561770

CATALOG NUMBER: SQ4-PC3-150U-125D-92765-1D-UNV-STD-W-4 (5700K)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	186.0	1.5
10°-20°	533.7	4.3
20°-30°	808.2	6.5
30°-40°	968.9	7.8
40°-50°	987.9	8.0
50°-60°	862.4	7.0
60°-70°	617.4	5.0
70°-80°	318.0	2.6
80°-90°	80.4	0.6
90°-100°	515.2	4.2
100°-110°	1465.8	11.8
110°-120°	1404.4	11.3
120°-130°	1111.5	9.0
130°-140°	892.2	7.2
140°-150°	698.5	5.6
150°-160°	511.1	4.1
160°-170°	316.6	2.6
170°-180°	107.4	0.9
0°-30°	1527.8	12.3
0°-40°	2496.7	20.2
0°-60°	4347.0	35.1
0°-90°	5362.8	43.3
90°-120°	3385.4	27.3
90°-150°	6087.6	49.2
90°-180°	7023.0	56.7
0°-180°	12385.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1965	1965	1965	1965	1965	
5°	1972	1953	1960	1954	1952	187
15°	1898	1882	1898	1898	1896	535
25°	1752	1740	1765	1759	1759	806
35°	1541	1538	1565	1554	1554	964
45°	1284	1281	1294	1277	1274	989
55°	982	970	970	955	955	876
65°	637	623	624	619	619	630
75°	275	287	304	306	306	297
85°	40	61	73	75	73	54
90°	0	0	0	0	0	4
95°	56	222	997	345	213	64
105°	228	346	1494	2639	2508	241
115°	423	512	1133	2400	2818	417
125°	598	663	1081	1794	2145	535
135°	731	792	1068	1516	1713	564
145°	862	906	1077	1312	1429	538
155°	984	1008	1103	1185	1234	455
165°	1088	1092	1116	1140	1156	306
175°	1139	1133	1128	1122	1113	108
180°	1131	1131	1131	1131	1131	

TEST NUMBER: P561770

CATALOG NUMBER: SQ4-PC3-150U-125D-92765-1D-UNV-STD-W-4 (5700K)

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1965.0	1965.0	1965.0	1965.0	1965.0
2.5°	1976.6	1959.5	1965.0	1960.5	1953.3
5°	1972.3	1952.7	1959.5	1954.0	1952.2
7.5°	1958.1	1938.5	1947.5	1943.8	1942.1
10°	1945.0	1925.4	1935.9	1932.2	1930.4
12.5°	1927.5	1909.4	1921.3	1917.7	1917.3
15°	1897.7	1881.7	1897.7	1897.6	1895.8
17.5°	1860.2	1845.6	1862.7	1863.8	1862.7
20°	1834.0	1818.0	1839.4	1837.7	1839.4
22.5°	1802.0	1788.8	1811.8	1807.1	1808.9
25°	1752.1	1739.7	1764.8	1759.4	1759.4
27.5°	1693.2	1684.3	1711.7	1705.9	1705.9
30°	1653.9	1645.0	1673.9	1666.6	1666.6
32.5°	1610.2	1604.1	1631.7	1622.9	1622.9
35°	1541.1	1537.5	1564.7	1553.8	1553.8
37.5°	1469.7	1466.5	1491.2	1478.0	1473.7
40°	1417.3	1415.6	1437.3	1422.8	1422.8
42.5°	1364.9	1363.2	1382.0	1364.6	1364.6
45°	1284.5	1281.0	1293.6	1277.2	1273.6
47.5°	1196.8	1193.3	1201.2	1183.3	1181.5
50°	1137.1	1133.6	1137.1	1120.7	1118.9
52.5°	1076.0	1069.6	1070.2	1053.8	1053.4
55°	982.5	970.0	969.8	955.2	955.2
57.5°	883.5	867.1	868.6	856.2	854.4
60°	815.1	797.3	798.7	787.8	786.0
62.5°	748.1	727.5	731.8	719.4	719.0
65°	636.8	622.6	624.1	618.6	618.6
67.5°	529.8	516.7	526.2	521.8	521.4
70°	451.2	442.3	454.9	454.8	453.0
72.5°	378.4	378.1	393.7	393.7	394.8
75°	274.7	287.2	303.8	305.7	305.7
77.5°	183.4	205.5	223.8	224.5	224.2
80°	131.0	155.9	172.8	176.4	174.7
82.5°	88.8	115.1	129.2	132.8	131.0
85°	40.0	61.4	72.8	74.6	72.8
87.5°	11.6	24.5	29.1	29.0	26.2
90°	0.0	0.0	0.0	0.0	0.0
92.5°	17.2	91.2	211.5	61.6	46.4
95°	55.9	221.9	997.3	345.2	212.8
97.5°	102.7	259.9	1535.9	1099.1	753.1
100°	135.4	282.5	1652.8	1674.2	1289.6
102.5°	171.5	306.9	1627.1	2143.0	1807.2
105°	227.8	345.5	1493.8	2638.6	2508.3
107.5°	285.0	390.5	1338.2	2778.3	2894.3
110°	324.6	423.3	1248.8	2724.8	2985.4

TEST NUMBER: P561770

CATALOG NUMBER: SQ4-PC3-150U-125D-92765-1D-UNV-STD-W-4 (5700K)

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	362.4	456.1	1188.6	2598.4	2970.0
115°	423.4	511.7	1132.7	2399.6	2817.8
117.5°	477.2	560.0	1099.6	2182.2	2625.2
120°	520.1	589.5	1096.2	2058.0	2482.5
122.5°	554.5	623.9	1087.6	1949.0	2343.2
125°	597.5	662.7	1081.1	1794.1	2145.0
127.5°	644.4	705.3	1077.7	1701.5	1990.7
130°	668.4	729.4	1072.5	1637.1	1889.3
132.5°	694.2	753.5	1072.5	1586.8	1818.8
135°	730.8	791.7	1068.2	1515.5	1713.0
137.5°	765.2	824.4	1067.8	1455.1	1625.8
140°	791.0	851.9	1066.1	1405.1	1569.0
142.5°	820.2	871.0	1071.2	1365.2	1512.3
145°	861.9	906.0	1076.8	1311.6	1429.3
147.5°	897.6	940.4	1086.3	1257.5	1359.2
150°	928.5	957.9	1089.7	1239.6	1311.1
152.5°	952.6	983.7	1093.2	1215.5	1281.9
155°	984.4	1007.5	1102.6	1185.4	1233.7
157.5°	1023.9	1037.8	1104.8	1171.7	1206.2
160°	1044.6	1055.1	1113.4	1161.3	1190.7
162.5°	1056.6	1068.8	1115.1	1152.6	1175.3
165°	1087.6	1091.8	1115.5	1139.5	1156.3
167.5°	1108.6	1104.8	1125.4	1136.3	1143.0
170°	1115.5	1113.4	1122.0	1124.3	1132.7
172.5°	1131.0	1123.8	1127.1	1120.8	1127.5
175°	1139.2	1132.8	1128.4	1121.8	1113.4
177.5°	1142.6	1132.5	1127.1	1120.3	1122.0
180°	1130.6	1130.6	1130.6	1130.6	1130.6

(END OF REPORT)