

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P523621

Luminaire Tested: **SQ4-PP3-025U-050D-92765-1D-UNV-STD-W-4 (3500K)**

Issue Date: 5/24/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P523621  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2103-172-1)  
Test Lab: INNOVATION CENTER  
Issue Date: 5/24/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PP3-025U-050D-92765-1D-UNV-STD-W-4 (3500K)  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS  
DOWNLIGHT 500 LUMENS PER FOOT  
UPLIGHT 250 LUMENS PER FOOT  
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 3500K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 3945.3 lumens  
Efficiency: N/A  
Efficacy: 113.7 lumens/watt  
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33  
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 34.7  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P523621  
CATALOG NUMBER: SQ4-PP3-025U-050D-92765-1D-UNV-STD-W-4 (3500K)

### Luminous Intensity Polar Plot





TEST NUMBER: P523621

CATALOG NUMBER: SQ4-PP3-025U-050D-92765-1D-UNV-STD-W-4 (3500K)

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20									
RC	80					70					50					30					10				
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0				
RCR																									
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	51							
1	98	94	90	87	91	87	84	81	74	71	69	62	60	59	51	50	49	43							
2	90	82	76	71	83	76	71	67	65	61	58	54	52	49	45	43	41	37							
3	82	72	65	59	75	67	61	56	57	53	49	48	45	42	40	37	35	31							
4	75	64	56	50	69	60	53	47	51	46	42	43	39	36	36	33	30	27							
5	69	57	49	43	63	53	46	41	46	40	36	39	34	31	32	29	27	23							
6	63	51	43	37	58	48	41	35	41	36	31	35	31	27	29	26	23	21							
7	59	46	38	33	54	43	36	31	37	32	28	32	27	24	27	23	21	18							
8	54	42	34	29	50	39	32	28	34	29	25	29	25	22	24	21	19	16							
9	51	38	31	26	47	36	29	25	31	26	22	27	22	19	23	19	17	15							
10	47	35	28	23	44	33	26	22	29	23	20	25	21	18	21	18	15	13							

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	7240	7240	7240
5°	7293	7249	7223
10°	7281	7230	7197
15°	7233	7193	7154
20°	7185	7145	7091
25°	7100	7051	6980
30°	6968	6931	6844
35°	6786	6740	6654
40°	6569	6528	6453
45°	6390	6345	6281
50°	6160	6120	6061
55°	5841	5763	5720
60°	5318	5165	5139
65°	4685	4488	4475
70°	4044	3876	3876
75°	3483	3433	3383
80°	3071	3108	3034
85°	2403	2625	2625



TEST NUMBER: P523621

CATALOG NUMBER: SQ4-PP3-025U-050D-92765-1D-UNV-STD-W-4 (3500K)

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	74.2	1.9
10°-20°	211.9	5.4
20°-30°	317.4	8.0
30°-40°	372.3	9.4
40°-50°	373.4	9.5
50°-60°	318.5	8.1
60°-70°	207.7	5.3
70°-80°	104.2	2.6
80°-90°	28.9	0.7
90°-100°	142.1	3.6
100°-110°	404.2	10.2
110°-120°	387.3	9.8
120°-130°	306.6	7.8
130°-140°	246.0	6.2
140°-150°	192.6	4.9
150°-160°	140.9	3.6
160°-170°	87.3	2.2
170°-180°	29.6	0.8
0°-30°	603.5	15.3
0°-40°	975.7	24.7
0°-60°	1667.7	42.3
0°-90°	2008.5	50.9
90°-120°	933.6	23.7
90°-150°	1678.9	42.6
90°-180°	1937.0	49.1
0°-180°	3945.3	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	785	785	785	785	785	
5°	788	780	783	780	780	75
15°	757	750	753	750	749	214
25°	697	689	693	686	686	321
35°	602	596	598	592	591	376
45°	490	486	486	481	481	377
55°	363	362	358	356	356	323
65°	215	210	206	204	205	214
75°	98	98	96	96	95	106
85°	23	25	25	25	25	27
90°	0	0	0	0	0	1
95°	15	61	275	95	59	18
105°	63	95	412	728	692	66
115°	117	141	312	662	777	115
125°	165	183	298	495	592	147
135°	202	218	295	418	472	156
145°	238	250	297	362	394	148
155°	272	278	304	327	340	126
165°	300	301	308	314	319	84
175°	314	312	311	309	307	30
180°	312	312	312	312	312	

TEST NUMBER: P523621

CATALOG NUMBER: SQ4-PP3-025U-050D-92765-1D-UNV-STD-W-4 (3500K)

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	784.7	784.7	784.7	784.7	784.7
2.5°	789.7	783.2	784.7	783.6	780.3
5°	787.5	780.1	782.7	779.9	779.9
7.5°	782.1	774.1	776.6	773.9	773.7
10°	777.2	769.1	771.7	768.9	768.2
12.5°	770.0	762.0	765.1	761.8	761.6
15°	757.2	749.8	753.1	750.3	749.0
17.5°	742.8	734.7	738.7	734.8	734.3
20°	731.8	723.7	727.7	722.2	722.2
22.5°	718.6	710.5	715.0	707.8	707.8
25°	697.4	689.3	692.6	686.4	685.7
27.5°	672.2	664.3	667.7	660.7	660.5
30°	654.1	646.7	650.6	643.0	642.4
32.5°	634.3	627.4	630.3	622.7	622.0
35°	602.5	596.4	598.4	591.5	590.8
37.5°	569.1	562.9	565.1	559.1	558.9
40°	545.4	541.4	542.0	537.1	535.8
42.5°	523.4	518.8	519.4	514.6	514.3
45°	489.7	486.3	486.3	481.4	481.4
47.5°	453.9	451.4	450.6	446.6	446.5
50°	429.2	427.1	426.4	423.0	422.3
52.5°	403.3	402.4	400.0	397.1	397.0
55°	363.1	361.8	358.3	356.2	355.6
57.5°	319.5	316.8	312.9	309.9	310.5
60°	288.2	285.5	279.9	278.5	278.5
62.5°	257.9	254.7	249.1	247.2	248.3
65°	214.6	210.5	205.6	204.3	205.0
67.5°	175.2	171.6	166.3	166.3	165.8
70°	149.9	147.9	143.7	143.7	143.7
72.5°	127.4	126.4	123.4	123.4	122.8
75°	97.7	97.7	96.3	95.6	94.9
77.5°	73.2	73.4	72.8	72.1	70.8
80°	57.8	59.1	58.5	57.8	57.1
82.5°	43.5	44.8	44.7	43.5	43.3
85°	22.7	24.7	24.8	24.8	24.8
87.5°	6.1	8.2	8.8	8.8	9.4
90°	0.0	0.0	0.0	0.0	0.0
92.5°	4.7	25.1	58.3	17.0	12.8
95°	15.4	61.2	275.0	95.2	58.7
97.5°	28.3	71.7	423.6	303.1	207.7
100°	37.3	77.9	455.8	461.7	355.7
102.5°	47.3	84.6	448.7	591.0	498.4
105°	62.8	95.3	412.0	727.7	691.7
107.5°	78.6	107.7	369.0	766.2	798.2
110°	89.5	116.7	344.4	751.5	823.3

TEST NUMBER: P523621

CATALOG NUMBER: SQ4-PP3-025U-050D-92765-1D-UNV-STD-W-4 (3500K)

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	99.9	125.8	327.8	716.6	819.1
115°	116.8	141.1	312.4	661.8	777.1
117.5°	131.6	154.4	303.3	601.8	724.0
120°	143.4	162.6	302.3	567.6	684.6
122.5°	152.9	172.1	299.9	537.5	646.2
125°	164.8	182.8	298.2	494.8	591.6
127.5°	177.7	194.5	297.2	469.3	549.0
130°	184.3	201.2	295.8	451.5	521.0
132.5°	191.5	207.8	295.8	437.6	501.6
135°	201.5	218.3	294.6	417.9	472.4
137.5°	211.0	227.4	294.5	401.3	448.4
140°	218.1	234.9	294.0	387.5	432.7
142.5°	226.2	240.2	295.4	376.5	417.1
145°	237.7	249.9	297.0	361.7	394.2
147.5°	247.5	259.4	299.6	346.8	374.9
150°	256.1	264.2	300.5	341.9	361.6
152.5°	262.7	271.3	301.5	335.2	353.5
155°	271.5	277.9	304.1	326.9	340.2
157.5°	282.4	286.2	304.7	323.1	332.7
160°	288.1	291.0	307.0	320.3	328.4
162.5°	291.4	294.8	307.5	317.9	324.1
165°	299.9	301.1	307.6	314.3	318.9
167.5°	305.7	304.7	310.4	313.4	315.2
170°	307.6	307.1	309.4	310.1	312.4
172.5°	311.9	309.9	310.8	309.1	311.0
175°	314.2	312.4	311.2	309.4	307.0
177.5°	315.1	312.3	310.8	309.0	309.4
180°	311.8	311.8	311.8	311.8	311.8

(END OF REPORT)