

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: CORELITE

Report Number: P523827

Luminaire Tested: **SQ4-PP3-100U-050D-92765-1D-UNV-STD-W-4 (2700K)**

Issue Date: 5/24/2021

Test Information

Test Method: LM-79-2019
Report Number: P523827
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2103-172-1)
Test Lab: INNOVATION CENTER
Issue Date: 5/24/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PP3-100U-050D-92765-1D-UNV-STD-W-4 (2700K)
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS
DOWNLIGHT 500 LUMENS PER FOOT
UPLIGHT 1000 LUMENS PER FOOT
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6104.9 lumens
Efficiency: N/A
Efficacy: 115.4 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 52.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P523827

CATALOG NUMBER: SQ4-PP3-100U-050D-92765-1D-UNV-STD-W-4 (2700K)

Luminous Intensity Polar Plot





TEST NUMBER: P523827

CATALOG NUMBER: SQ4-PP3-100U-050D-92765-1D-UNV-STD-W-4 (2700K)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	92	92	92	92	73	73	73	55	55	55	39	39	39	31
1	94	90	86	83	84	81	78	75	64	62	60	49	47	46	35	34	33	27
2	85	78	72	68	77	71	66	62	56	53	50	43	41	39	31	29	28	23
3	78	69	62	56	70	62	56	51	50	45	42	38	35	33	27	26	24	19
4	71	61	53	48	64	55	49	44	44	39	36	34	31	28	24	22	21	17
5	65	54	46	41	59	49	42	37	39	34	31	30	27	24	22	20	18	14
6	60	48	41	35	54	44	37	32	35	30	27	27	24	21	20	18	16	13
7	55	44	36	31	50	40	33	28	32	27	23	25	21	19	18	16	14	11
8	51	39	32	27	46	36	29	25	29	24	21	23	19	17	17	14	13	10
9	48	36	29	24	43	33	26	22	27	22	18	21	17	15	15	13	11	9
10	45	33	26	21	40	30	24	20	24	20	16	19	16	13	14	12	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6927	6927	6927
5°	6978	6935	6911
10°	6966	6917	6886
15°	6920	6882	6845
20°	6874	6836	6783
25°	6792	6745	6678
30°	6667	6632	6548
35°	6492	6448	6366
40°	6285	6245	6174
45°	6113	6070	6010
50°	5894	5856	5799
55°	5588	5514	5472
60°	5087	4942	4918
65°	4482	4294	4281
70°	3868	3709	3709
75°	3329	3283	3237
80°	2938	2970	2901
85°	2297	2509	2509



TEST NUMBER: P523827

CATALOG NUMBER: SQ4-PP3-100U-050D-92765-1D-UNV-STD-W-4 (2700K)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	71.0	1.2
10°-20°	202.7	3.3
20°-30°	303.6	5.0
30°-40°	356.1	5.8
40°-50°	357.3	5.9
50°-60°	304.8	5.0
60°-70°	198.8	3.3
70°-80°	99.7	1.6
80°-90°	27.6	0.5
90°-100°	306.9	5.0
100°-110°	873.2	14.3
110°-120°	836.6	13.7
120°-130°	662.1	10.8
130°-140°	531.5	8.7
140°-150°	416.1	6.8
150°-160°	304.4	5.0
160°-170°	188.6	3.1
170°-180°	64.0	1.0
0°-30°	577.3	9.5
0°-40°	933.5	15.3
0°-60°	1595.5	26.1
0°-90°	1921.6	31.5
90°-120°	2016.7	33.0
90°-150°	3626.3	59.4
90°-180°	4183.0	68.5
0°-180°	6104.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	751	751	751	751	751	
5°	753	746	749	746	746	72
15°	724	717	720	718	717	204
25°	667	660	663	657	656	307
35°	576	571	572	566	565	360
45°	468	465	465	461	461	361
55°	347	346	343	341	340	309
65°	205	201	197	195	196	205
75°	93	93	92	91	91	101
85°	22	24	24	24	24	26
90°	0	0	0	0	0	2
95°	33	132	594	206	127	38
105°	136	206	890	1572	1494	144
115°	252	305	675	1429	1678	248
125°	356	395	644	1069	1278	319
135°	435	472	636	903	1020	336
145°	513	540	642	781	851	321
155°	586	600	657	706	735	271
165°	648	650	664	679	689	182
175°	679	675	672	668	663	64
180°	674	674	674	674	674	

TEST NUMBER: P523827

CATALOG NUMBER: SQ4-PP3-100U-050D-92765-1D-UNV-STD-W-4 (2700K)

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	750.8	750.8	750.8	750.8	750.8
2.5°	755.5	749.4	750.8	749.7	746.6
5°	753.4	746.3	748.8	746.2	746.2
7.5°	748.3	740.6	743.0	740.4	740.3
10°	743.6	735.8	738.3	735.6	735.0
12.5°	736.7	729.0	732.0	728.8	728.7
15°	724.5	717.4	720.5	717.9	716.6
17.5°	710.7	702.9	706.7	703.0	702.5
20°	700.1	692.4	696.2	690.9	690.9
22.5°	687.5	679.8	684.1	677.2	677.2
25°	667.2	659.5	662.6	656.7	656.0
27.5°	643.1	635.5	638.8	632.1	632.0
30°	625.8	618.7	622.5	615.2	614.6
32.5°	606.8	600.3	603.0	595.7	595.1
35°	576.4	570.6	572.5	565.9	565.2
37.5°	544.4	538.5	540.6	535.0	534.7
40°	521.8	517.9	518.5	513.9	512.6
42.5°	500.7	496.4	496.9	492.3	492.1
45°	468.5	465.3	465.2	460.6	460.6
47.5°	434.3	431.8	431.1	427.3	427.2
50°	410.6	408.7	408.0	404.7	404.0
52.5°	385.9	385.0	382.7	379.9	379.8
55°	347.4	346.1	342.8	340.8	340.2
57.5°	305.7	303.1	299.4	296.5	297.0
60°	275.7	273.1	267.8	266.5	266.5
62.5°	246.8	243.7	238.3	236.5	237.5
65°	205.3	201.4	196.7	195.4	196.1
67.5°	167.7	164.2	159.1	159.1	158.6
70°	143.4	141.5	137.5	137.5	137.5
72.5°	121.9	121.0	118.0	118.0	117.5
75°	93.4	93.4	92.1	91.4	90.8
77.5°	70.0	70.3	69.6	68.9	67.8
80°	55.3	56.6	55.9	55.3	54.6
82.5°	41.6	42.9	42.8	41.6	41.5
85°	21.7	23.6	23.7	23.7	23.7
87.5°	5.8	7.8	8.4	8.4	8.9
90°	0.0	0.0	0.0	0.0	0.0
92.5°	10.2	54.3	126.0	36.7	27.7
95°	33.3	132.2	594.1	205.6	126.8
97.5°	61.2	154.8	914.9	654.7	448.6
100°	80.7	168.3	984.6	997.3	768.2
102.5°	102.2	182.8	969.2	1276.6	1076.5
105°	135.7	205.8	889.8	1571.8	1494.2
107.5°	169.8	232.6	797.1	1655.0	1724.1
110°	193.3	252.2	743.9	1623.2	1778.4

TEST NUMBER: P523827

CATALOG NUMBER: SQ4-PP3-100U-050D-92765-1D-UNV-STD-W-4 (2700K)

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	215.9	271.7	708.0	1547.9	1769.2
115°	252.2	304.8	674.7	1429.4	1678.5
117.5°	284.2	333.6	655.0	1299.9	1563.8
120°	309.8	351.2	653.0	1225.9	1478.8
122.5°	330.3	371.6	647.9	1161.0	1395.8
125°	355.9	394.7	644.0	1068.7	1277.8
127.5°	383.8	420.2	642.0	1013.6	1185.9
130°	398.2	434.5	638.9	975.2	1125.4
132.5°	413.6	448.9	638.9	945.2	1083.4
135°	435.3	471.6	636.3	902.8	1020.4
137.5°	455.8	491.1	636.1	866.8	968.5
140°	471.2	507.5	635.1	837.0	934.7
142.5°	488.6	518.9	638.1	813.2	900.9
145°	513.4	539.7	641.5	781.3	851.4
147.5°	534.7	560.2	647.1	749.1	809.7
150°	553.1	570.6	649.1	738.5	781.0
152.5°	567.5	586.0	651.2	724.0	763.6
155°	586.4	600.2	656.8	706.1	734.9
157.5°	610.0	618.2	658.1	698.0	718.5
160°	622.3	628.5	663.2	691.8	709.3
162.5°	629.4	636.7	664.2	686.6	700.1
165°	647.9	650.4	664.5	678.8	688.8
167.5°	660.4	658.2	670.4	676.9	680.9
170°	664.5	663.3	668.3	669.7	674.7
172.5°	673.7	669.5	671.4	667.7	671.7
175°	678.6	674.8	672.2	668.2	663.2
177.5°	680.6	674.6	671.4	667.3	668.3
180°	673.5	673.5	673.5	673.5	673.5

(END OF REPORT)