

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P523830

Luminaire Tested: **SQ4-PP3-100U-050D-92765-1D-UNV-STD-W-4 (4000K)**

Issue Date: 5/24/2021

Test Information

Test Method: LM-79-2019
Report Number: P523830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2103-172-1)
Test Lab: INNOVATION CENTER
Issue Date: 5/24/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PP3-100U-050D-92765-1D-UNV-STD-W-4 (4000K)
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS
DOWNLIGHT 500 LUMENS PER FOOT
UPLIGHT 1000 LUMENS PER FOOT
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6497.7 lumens
Efficiency: N/A
Efficacy: 122.4 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 53.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P523830
CATALOG NUMBER: SQ4-PP3-100U-050D-92765-1D-UNV-STD-W-4 (4000K)

Luminous Intensity Polar Plot





TEST NUMBER: P523830

CATALOG NUMBER: SQ4-PP3-100U-050D-92765-1D-UNV-STD-W-4 (4000K)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	92	92	92	92	73	73	73	55	55	55	39	39	39	31
1	94	90	86	83	84	81	78	75	64	62	60	49	47	46	35	34	33	27
2	85	78	72	68	77	71	66	62	56	53	50	43	41	39	31	29	28	23
3	78	69	62	56	70	62	56	51	50	45	42	38	35	33	27	26	24	19
4	71	61	53	48	64	55	49	44	44	39	36	34	31	28	24	22	21	17
5	65	54	46	41	59	49	42	37	39	34	31	30	27	24	22	20	18	14
6	60	48	41	35	54	44	37	32	35	30	27	27	24	21	20	18	16	13
7	55	44	36	31	50	40	33	28	32	27	23	25	21	19	18	16	14	11
8	51	39	32	27	46	36	29	25	29	24	21	23	19	17	17	14	13	10
9	48	36	29	24	43	33	26	22	27	22	18	21	17	15	15	13	11	9
10	45	33	26	21	40	30	24	20	24	20	16	19	16	13	14	12	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7373	7373	7373
5°	7427	7381	7355
10°	7414	7362	7329
15°	7365	7325	7285
20°	7317	7275	7220
25°	7230	7180	7108
30°	7095	7058	6968
35°	6910	6863	6776
40°	6689	6647	6571
45°	6506	6460	6396
50°	6272	6232	6172
55°	5948	5870	5825
60°	5414	5259	5233
65°	4770	4571	4556
70°	4119	3949	3949
75°	3543	3493	3444
80°	3124	3161	3087
85°	2445	2668	2668



TEST NUMBER: P523830

CATALOG NUMBER: SQ4-PP3-100U-050D-92765-1D-UNV-STD-W-4 (4000K)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	75.6	1.2
10°-20°	215.8	3.3
20°-30°	323.2	5.0
30°-40°	379.1	5.8
40°-50°	380.2	5.9
50°-60°	324.4	5.0
60°-70°	211.5	3.3
70°-80°	106.1	1.6
80°-90°	29.4	0.5
90°-100°	326.6	5.0
100°-110°	929.4	14.3
110°-120°	890.4	13.7
120°-130°	704.7	10.8
130°-140°	565.7	8.7
140°-150°	442.8	6.8
150°-160°	324.0	5.0
160°-170°	200.7	3.1
170°-180°	68.1	1.0
0°-30°	614.5	9.5
0°-40°	993.6	15.3
0°-60°	1698.2	26.1
0°-90°	2045.2	31.5
90°-120°	2146.4	33.0
90°-150°	3859.7	59.4
90°-180°	4453.0	68.5
0°-180°	6497.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	799	799	799	799	799	
5°	802	794	797	794	794	76
15°	771	764	767	764	763	218
25°	710	702	705	699	698	327
35°	614	607	609	602	602	383
45°	499	495	495	490	490	384
55°	370	368	365	363	362	329
65°	218	214	209	208	209	218
75°	99	99	98	97	97	108
85°	23	25	25	25	25	27
90°	0	0	0	0	0	2
95°	35	141	632	219	135	40
105°	144	219	947	1673	1590	153
115°	268	324	718	1521	1786	264
125°	379	420	686	1138	1360	339
135°	463	502	677	961	1086	358
145°	546	574	683	832	906	341
155°	624	639	699	752	782	289
165°	690	692	707	722	733	194
175°	722	718	715	711	706	68
180°	717	717	717	717	717	

TEST NUMBER: P523830

CATALOG NUMBER: SQ4-PP3-100U-050D-92765-1D-UNV-STD-W-4 (4000K)

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	799.1	799.1	799.1	799.1	799.1
2.5°	804.1	797.6	799.1	797.9	794.6
5°	801.9	794.4	797.0	794.2	794.2
7.5°	796.4	788.2	790.8	788.0	787.9
10°	791.4	783.2	785.8	783.0	782.3
12.5°	784.1	775.9	779.1	775.7	775.6
15°	771.1	763.6	766.9	764.0	762.7
17.5°	756.4	748.2	752.2	748.2	747.7
20°	745.2	737.0	741.0	735.4	735.4
22.5°	731.7	723.5	728.1	720.8	720.8
25°	710.2	701.9	705.3	698.9	698.2
27.5°	684.5	676.4	679.9	672.8	672.6
30°	666.0	658.5	662.5	654.8	654.1
32.5°	645.9	638.9	641.8	634.1	633.4
35°	613.5	607.3	609.3	602.3	601.6
37.5°	579.5	573.2	575.4	569.4	569.1
40°	555.4	551.3	551.9	546.9	545.6
42.5°	533.0	528.3	528.9	524.0	523.7
45°	498.6	495.2	495.1	490.2	490.2
47.5°	462.2	459.6	458.9	454.8	454.7
50°	437.0	435.0	434.2	430.7	430.0
52.5°	410.7	409.7	407.3	404.4	404.2
55°	369.8	368.4	364.9	362.8	362.1
57.5°	325.4	322.6	318.7	315.6	316.1
60°	293.4	290.7	285.0	283.6	283.6
62.5°	262.6	259.3	253.7	251.7	252.8
65°	218.5	214.4	209.4	208.0	208.7
67.5°	178.4	174.8	169.3	169.3	168.8
70°	152.7	150.6	146.4	146.4	146.4
72.5°	129.7	128.7	125.6	125.6	125.1
75°	99.4	99.4	98.0	97.3	96.6
77.5°	74.5	74.8	74.1	73.4	72.1
80°	58.8	60.2	59.5	58.8	58.1
82.5°	44.3	45.6	45.5	44.3	44.1
85°	23.1	25.2	25.2	25.2	25.2
87.5°	6.2	8.4	9.0	9.0	9.5
90°	0.0	0.0	0.0	0.0	0.0
92.5°	10.9	57.8	134.1	39.0	29.4
95°	35.4	140.7	632.3	218.9	134.9
97.5°	65.1	164.8	973.8	696.8	477.5
100°	85.9	179.1	1047.9	1061.5	817.6
102.5°	108.7	194.6	1031.6	1358.7	1145.8
105°	144.4	219.1	947.1	1672.9	1590.3
107.5°	180.7	247.6	848.4	1761.5	1835.1
110°	205.8	268.4	791.7	1727.6	1892.8



TEST NUMBER: P523830

CATALOG NUMBER: SQ4-PP3-100U-050D-92765-1D-UNV-STD-W-4 (4000K)

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	229.8	289.2	753.6	1647.4	1883.0
115°	268.5	324.4	718.2	1521.4	1786.5
117.5°	302.5	355.0	697.2	1383.6	1664.4
120°	329.8	373.8	695.0	1304.8	1574.0
122.5°	351.6	395.6	689.5	1235.7	1485.7
125°	378.8	420.1	685.5	1137.5	1360.0
127.5°	408.5	447.2	683.3	1078.8	1262.2
130°	423.8	462.5	680.0	1037.9	1197.8
132.5°	440.2	477.7	680.0	1006.0	1153.1
135°	463.3	502.0	677.3	960.8	1086.1
137.5°	485.1	522.7	677.0	922.6	1030.8
140°	501.5	540.1	675.9	890.9	994.8
142.5°	520.0	552.3	679.2	865.5	958.8
145°	546.5	574.4	682.7	831.6	906.2
147.5°	569.1	596.3	688.7	797.3	861.8
150°	588.7	607.4	690.9	786.0	831.3
152.5°	604.0	623.7	693.1	770.6	812.7
155°	624.1	638.8	699.1	751.6	782.2
157.5°	649.2	658.0	700.4	742.9	764.8
160°	662.3	668.9	705.9	736.3	755.0
162.5°	669.9	677.6	707.0	730.8	745.1
165°	689.5	692.2	707.3	722.5	733.1
167.5°	702.9	700.5	713.5	720.4	724.7
170°	707.3	705.9	711.3	712.8	718.2
172.5°	717.1	712.5	714.6	710.6	714.9
175°	722.2	718.3	715.4	711.2	705.9
177.5°	724.4	718.0	714.6	710.3	711.3
180°	716.8	716.8	716.8	716.8	716.8

(END OF REPORT)