

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P523645

Luminaire Tested: **SQ4-PP3-025U-100D-92765-1D-UNV-STD-W-4 (2700K)**

Issue Date: 5/24/2021

Test Information

Test Method: LM-79-2019
Report Number: P523645
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2103-172-1)
Test Lab: INNOVATION CENTER
Issue Date: 5/24/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PP3-025U-100D-92765-1D-UNV-STD-W-4 (2700K)
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS
DOWNLIGHT 1000 LUMENS PER FOOT
UPLIGHT 250 LUMENS PER FOOT
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5636.1 lumens
Efficiency: N/A
Efficacy: 100.1 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 56.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P523645
CATALOG NUMBER: SQ4-PP3-025U-100D-92765-1D-UNV-STD-W-4 (2700K)

Luminous Intensity Polar Plot





TEST NUMBER: P523645

CATALOG NUMBER: SQ4-PP3-025U-100D-92765-1D-UNV-STD-W-4 (2700K)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	105	105	105	105	93	93	93	82	82	82	72	72	72	67
1	102	98	94	90	96	92	89	86	82	79	77	73	71	69	64	63	61	57
2	93	86	79	74	87	81	75	71	72	68	64	64	61	58	57	54	52	48
3	85	75	68	62	80	71	65	59	64	59	54	57	53	49	50	47	44	41
4	78	67	59	53	73	63	56	51	57	51	46	51	46	42	45	41	38	35
5	72	60	51	45	67	57	49	44	51	45	40	46	41	37	41	37	34	31
6	66	54	45	40	62	51	44	38	46	40	35	41	36	32	37	33	30	27
7	61	49	40	35	58	46	39	34	42	36	31	38	33	29	34	30	26	24
8	57	44	36	31	54	42	35	30	38	32	28	35	29	26	31	27	24	21
9	53	40	33	28	50	39	32	27	35	29	25	32	27	23	29	24	21	19
10	50	37	30	25	47	36	29	24	32	27	23	29	24	21	27	22	19	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13637	13637	13637
5°	13738	13653	13605
10°	13715	13617	13556
15°	13624	13549	13475
20°	13534	13457	13355
25°	13372	13280	13148
30°	13125	13056	12891
35°	12781	12694	12534
40°	12373	12294	12155
45°	12035	11950	11832
50°	11603	11529	11417
55°	11002	10856	10772
60°	10016	9728	9682
65°	8824	8455	8427
70°	7618	7302	7302
75°	6559	6466	6374
80°	5781	5850	5712
85°	4520	4933	4933



TEST NUMBER: P523645

CATALOG NUMBER: SQ4-PP3-025U-100D-92765-1D-UNV-STD-W-4 (2700K)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	139.8	2.5
10°-20°	399.1	7.1
20°-30°	597.8	10.6
30°-40°	701.2	12.4
40°-50°	703.4	12.5
50°-60°	600.0	10.6
60°-70°	391.3	6.9
70°-80°	196.3	3.5
80°-90°	54.3	1.0
90°-100°	135.9	2.4
100°-110°	386.8	6.9
110°-120°	370.6	6.6
120°-130°	293.3	5.2
130°-140°	235.4	4.2
140°-150°	184.3	3.3
150°-160°	134.8	2.4
160°-170°	83.5	1.5
170°-180°	28.3	0.5
0°-30°	1136.6	20.2
0°-40°	1837.8	32.6
0°-60°	3141.2	55.7
0°-90°	3783.1	67.1
90°-120°	893.2	15.8
90°-150°	1606.2	28.5
90°-180°	1853.0	32.9
0°-180°	5636.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1478	1478	1478	1478	1478	
5°	1483	1469	1474	1469	1469	141
15°	1426	1412	1418	1413	1411	402
25°	1314	1298	1304	1293	1292	604
35°	1135	1123	1127	1114	1113	709
45°	922	916	916	907	907	710
55°	684	682	675	671	670	608
65°	404	397	387	385	386	403
75°	184	184	181	180	179	200
85°	43	46	47	47	47	50
90°	0	0	0	0	0	2
95°	15	59	263	91	56	17
105°	60	91	394	696	662	64
115°	112	135	299	633	744	110
125°	158	175	285	473	566	141
135°	193	209	282	400	452	149
145°	227	239	284	346	377	142
155°	260	266	291	313	326	120
165°	287	288	294	301	305	81
175°	301	299	298	296	294	28
180°	298	298	298	298	298	

TEST NUMBER: P523645

CATALOG NUMBER: SQ4-PP3-025U-100D-92765-1D-UNV-STD-W-4 (2700K)

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1478.1	1478.1	1478.1	1478.1	1478.1
2.5°	1487.4	1475.3	1478.1	1475.9	1469.8
5°	1483.3	1469.4	1474.2	1469.0	1469.0
7.5°	1473.2	1458.0	1462.8	1457.6	1457.4
10°	1463.9	1448.7	1453.5	1448.3	1447.0
12.5°	1450.4	1435.2	1441.1	1434.8	1434.6
15°	1426.3	1412.4	1418.5	1413.3	1410.7
17.5°	1399.1	1383.9	1391.3	1384.0	1383.0
20°	1378.4	1363.2	1370.6	1360.2	1360.2
22.5°	1353.5	1338.3	1346.8	1333.3	1333.3
25°	1313.6	1298.4	1304.5	1292.8	1291.6
27.5°	1266.2	1251.2	1257.6	1244.4	1244.2
30°	1232.0	1218.0	1225.5	1211.2	1210.0
32.5°	1194.7	1181.7	1187.2	1172.9	1171.6
35°	1134.8	1123.4	1127.0	1114.1	1112.8
37.5°	1071.9	1060.2	1064.3	1053.2	1052.7
40°	1027.3	1019.7	1020.8	1011.7	1009.2
42.5°	985.8	977.2	978.3	969.2	968.7
45°	922.4	916.0	915.9	906.8	906.8
47.5°	855.0	850.2	848.8	841.3	841.0
50°	808.4	804.6	803.2	796.7	795.4
52.5°	759.7	757.9	753.4	748.0	747.7
55°	684.0	681.5	674.9	671.0	669.7
57.5°	601.9	596.8	589.4	583.8	584.8
60°	542.8	537.7	527.2	524.7	524.7
62.5°	485.8	479.7	469.2	465.6	467.7
65°	404.2	396.6	387.3	384.8	386.0
67.5°	330.1	323.2	313.2	313.2	312.2
70°	282.4	278.6	270.7	270.7	270.7
72.5°	239.9	238.1	232.4	232.4	231.4
75°	184.0	184.0	181.4	180.0	178.8
77.5°	137.8	138.3	137.1	135.7	133.4
80°	108.8	111.4	110.1	108.8	107.5
82.5°	81.9	84.4	84.2	81.9	81.6
85°	42.7	46.5	46.6	46.6	46.6
87.5°	11.4	15.5	16.6	16.6	17.6
90°	0.0	0.0	0.0	0.0	0.0
92.5°	4.5	24.1	55.8	16.2	12.2
95°	14.7	58.6	263.1	91.1	56.1
97.5°	27.1	68.6	405.3	290.0	198.7
100°	35.7	74.5	436.1	441.7	340.3
102.5°	45.3	81.0	429.3	565.4	476.8
105°	60.1	91.2	394.1	696.2	661.8
107.5°	75.2	103.0	353.1	733.1	763.7
110°	85.6	111.7	329.5	719.0	787.7

TEST NUMBER: P523645

CATALOG NUMBER: SQ4-PP3-025U-100D-92765-1D-UNV-STD-W-4 (2700K)

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	95.6	120.3	313.6	685.6	783.6
115°	111.7	135.0	298.9	633.1	743.5
117.5°	125.9	147.7	290.1	575.8	692.7
120°	137.2	155.5	289.2	543.0	655.0
122.5°	146.3	164.6	287.0	514.2	618.3
125°	157.7	174.8	285.3	473.4	566.0
127.5°	170.0	186.1	284.3	449.0	525.3
130°	176.4	192.5	283.0	431.9	498.5
132.5°	183.2	198.8	283.0	418.7	479.9
135°	192.8	208.9	281.9	399.9	452.0
137.5°	201.9	217.5	281.7	383.9	429.0
140°	208.7	224.8	281.3	370.7	414.0
142.5°	216.4	229.8	282.6	360.2	399.0
145°	227.4	239.1	284.1	346.1	377.1
147.5°	236.8	248.1	286.6	331.8	358.6
150°	245.0	252.8	287.5	327.1	345.9
152.5°	251.3	259.6	288.4	320.7	338.2
155°	259.7	265.8	290.9	312.8	325.5
157.5°	270.2	273.8	291.5	309.2	318.3
160°	275.6	278.4	293.8	306.4	314.2
162.5°	278.8	282.0	294.2	304.1	310.1
165°	287.0	288.1	294.3	300.7	305.1
167.5°	292.5	291.5	296.9	299.8	301.6
170°	294.3	293.8	296.0	296.6	298.9
172.5°	298.4	296.5	297.4	295.7	297.5
175°	300.6	298.9	297.7	296.0	293.8
177.5°	301.5	298.8	297.4	295.6	296.0
180°	298.3	298.3	298.3	298.3	298.3

(END OF REPORT)