

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P523833

Luminaire Tested: **SQ4-PP3-100U-050D-92765-1D-UNV-STD-W-4 (5700K)**

Issue Date: 5/24/2021

Test Information

Test Method: LM-79-2019
Report Number: P523833
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2103-172-1)
Test Lab: INNOVATION CENTER
Issue Date: 5/24/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PP3-100U-050D-92765-1D-UNV-STD-W-4 (5700K)
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS
DOWNLIGHT 500 LUMENS PER FOOT
UPLIGHT 1000 LUMENS PER FOOT
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 5700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6770.7 lumens
Efficiency: N/A
Efficacy: 128.0 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 52.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P523833

CATALOG NUMBER: SQ4-PP3-100U-050D-92765-1D-UNV-STD-W-4 (5700K)

Luminous Intensity Polar Plot





TEST NUMBER: P523833

CATALOG NUMBER: SQ4-PP3-100U-050D-92765-1D-UNV-STD-W-4 (5700K)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	92	92	92	92	73	73	73	55	55	55	39	39	39	31
1	94	90	86	83	84	81	78	75	64	62	60	49	47	46	35	34	33	27
2	85	78	72	68	77	71	66	62	56	53	50	43	41	39	31	29	28	23
3	78	69	62	56	70	62	56	51	50	45	42	38	35	33	27	26	24	19
4	71	61	53	48	64	55	49	44	44	39	36	34	31	28	24	22	21	17
5	65	54	46	41	59	49	42	37	39	34	31	30	27	24	22	20	18	14
6	60	48	41	35	54	44	37	32	35	30	27	27	24	21	20	18	16	13
7	55	44	36	31	50	40	33	28	32	27	23	25	21	19	18	16	14	11
8	51	39	32	27	46	36	29	25	29	24	21	23	19	17	17	14	13	10
9	48	36	29	24	43	33	26	22	27	22	18	21	17	15	15	13	11	9
10	45	33	26	21	40	30	24	20	24	20	16	19	16	13	14	12	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7683	7683	7683
5°	7739	7692	7665
10°	7725	7671	7637
15°	7675	7633	7591
20°	7624	7581	7524
25°	7533	7481	7407
30°	7394	7355	7261
35°	7201	7151	7061
40°	6970	6926	6847
45°	6780	6731	6665
50°	6537	6495	6432
55°	6198	6116	6069
60°	5643	5480	5455
65°	4971	4764	4748
70°	4292	4114	4114
75°	3693	3643	3590
80°	3257	3294	3220
85°	2551	2784	2784



TEST NUMBER: P523833

CATALOG NUMBER: SQ4-PP3-100U-050D-92765-1D-UNV-STD-W-4 (5700K)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	78.7	1.2
10°-20°	224.8	3.3
20°-30°	336.8	5.0
30°-40°	395.0	5.8
40°-50°	396.2	5.9
50°-60°	338.0	5.0
60°-70°	220.4	3.3
70°-80°	110.6	1.6
80°-90°	30.6	0.5
90°-100°	340.3	5.0
100°-110°	968.4	14.3
110°-120°	927.8	13.7
120°-130°	734.4	10.8
130°-140°	589.4	8.7
140°-150°	461.5	6.8
150°-160°	337.6	5.0
160°-170°	209.1	3.1
170°-180°	71.0	1.0
0°-30°	640.3	9.5
0°-40°	1035.3	15.3
0°-60°	1769.5	26.1
0°-90°	2131.1	31.5
90°-120°	2236.6	33.0
90°-150°	4021.8	59.4
90°-180°	4640.0	68.5
0°-180°	6770.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	833	833	833	833	833	
5°	836	828	830	828	828	79
15°	804	796	799	796	795	227
25°	740	731	735	728	728	340
35°	639	633	635	628	627	399
45°	520	516	516	511	511	400
55°	385	384	380	378	377	342
65°	228	223	218	217	218	227
75°	104	104	102	101	101	112
85°	24	26	26	26	26	28
90°	0	0	0	0	0	2
95°	37	147	659	228	141	42
105°	150	228	987	1743	1657	159
115°	280	338	748	1585	1862	275
125°	395	438	714	1185	1417	353
135°	483	523	706	1001	1132	373
145°	569	599	711	866	944	356
155°	650	666	728	783	815	301
165°	718	721	737	753	764	202
175°	753	748	746	741	736	71
180°	747	747	747	747	747	



TEST NUMBER: P523833

CATALOG NUMBER: SQ4-PP3-100U-050D-92765-1D-UNV-STD-W-4 (5700K)

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	832.7	832.7	832.7	832.7	832.7
2.5°	837.9	831.1	832.7	831.4	828.0
5°	835.6	827.7	830.5	827.6	827.6
7.5°	829.9	821.3	824.1	821.1	821.0
10°	824.6	816.1	818.8	815.9	815.2
12.5°	817.0	808.5	811.8	808.3	808.1
15°	803.5	795.6	799.1	796.1	794.7
17.5°	788.1	779.6	783.8	779.7	779.1
20°	776.5	767.9	772.1	766.3	766.3
22.5°	762.5	753.9	758.7	751.1	751.1
25°	740.0	731.4	734.9	728.3	727.6
27.5°	713.3	704.9	708.5	701.0	700.9
30°	694.0	686.2	690.4	682.3	681.6
32.5°	673.0	665.7	668.8	660.7	660.0
35°	639.3	632.9	634.9	627.6	626.9
37.5°	603.8	597.2	599.6	593.3	593.0
40°	578.7	574.4	575.1	569.9	568.5
42.5°	555.4	550.5	551.1	546.0	545.7
45°	519.6	516.0	515.9	510.8	510.8
47.5°	481.6	478.9	478.1	473.9	473.8
50°	455.4	453.2	452.5	448.8	448.1
52.5°	427.9	426.9	424.4	421.4	421.2
55°	385.3	383.9	380.2	378.0	377.3
57.5°	339.1	336.2	332.0	328.8	329.4
60°	305.8	302.9	297.0	295.6	295.6
62.5°	273.7	270.2	264.3	262.3	263.4
65°	227.7	223.4	218.2	216.8	217.5
67.5°	185.9	182.1	176.5	176.4	175.9
70°	159.1	156.9	152.5	152.5	152.5
72.5°	135.2	134.2	130.9	130.9	130.3
75°	103.6	103.6	102.2	101.4	100.7
77.5°	77.6	77.9	77.2	76.5	75.2
80°	61.3	62.7	62.0	61.3	60.6
82.5°	46.1	47.5	47.4	46.1	46.0
85°	24.1	26.2	26.3	26.3	26.3
87.5°	6.4	8.7	9.3	9.4	9.9
90°	0.0	0.0	0.0	0.0	0.0
92.5°	11.4	60.2	139.7	40.7	30.7
95°	36.9	146.6	658.9	228.0	140.6
97.5°	67.9	171.7	1014.7	726.1	497.6
100°	89.5	186.6	1092.0	1106.1	852.0
102.5°	113.3	202.7	1074.9	1415.8	1193.9
105°	150.5	228.3	986.9	1743.2	1657.1
107.5°	188.3	258.0	884.1	1835.5	1912.1
110°	214.4	279.7	825.0	1800.2	1972.3

TEST NUMBER: P523833

CATALOG NUMBER: SQ4-PP3-100U-050D-92765-1D-UNV-STD-W-4 (5700K)

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	239.4	301.3	785.2	1716.7	1962.1
115°	279.7	338.0	748.3	1585.3	1861.6
117.5°	315.2	369.9	726.5	1441.7	1734.4
120°	343.6	389.5	724.2	1359.6	1640.1
122.5°	366.4	412.2	718.5	1287.6	1548.1
125°	394.8	437.8	714.2	1185.3	1417.1
127.5°	425.7	466.0	712.0	1124.1	1315.2
130°	441.6	481.9	708.6	1081.5	1248.2
132.5°	458.7	497.8	708.6	1048.3	1201.6
135°	482.8	523.1	705.7	1001.2	1131.7
137.5°	505.5	544.7	705.4	961.3	1074.1
140°	522.6	562.8	704.3	928.3	1036.6
142.5°	541.9	575.5	707.7	901.9	999.1
145°	569.4	598.6	711.4	866.5	944.3
147.5°	593.0	621.3	717.7	830.8	898.0
150°	613.4	632.9	719.9	819.0	866.2
152.5°	629.3	649.9	722.2	803.0	846.9
155°	650.3	665.6	728.4	783.1	815.1
157.5°	676.5	685.6	729.9	774.1	796.9
160°	690.1	697.1	735.5	767.2	786.7
162.5°	698.1	706.1	736.7	761.4	776.4
165°	718.5	721.3	737.0	752.8	763.9
167.5°	732.4	729.9	743.5	750.7	755.1
170°	737.0	735.6	741.2	742.8	748.3
172.5°	747.2	742.5	744.6	740.5	744.9
175°	752.6	748.4	745.5	741.1	735.5
177.5°	754.9	748.2	744.6	740.1	741.2
180°	746.9	746.9	746.9	746.9	746.9

(END OF REPORT)