

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P523842

Luminaire Tested: **SQ4-PP3-100U-075D-92765-1D-UNV-STD-W-4 (3500K)**

Issue Date: 5/24/2021

Test Information

Test Method: LM-79-2019
Report Number: P523842
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2103-172-1)
Test Lab: INNOVATION CENTER
Issue Date: 5/24/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PP3-100U-075D-92765-1D-UNV-STD-W-4 (3500K)
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 1000 LUMENS PER FOOT
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7380.5 lumens
Efficiency: N/A
Efficacy: 114.8 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 64.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P523842

CATALOG NUMBER: SQ4-PP3-100U-075D-92765-1D-UNV-STD-W-4 (3500K)

Luminous Intensity Polar Plot





TEST NUMBER: P523842

CATALOG NUMBER: SQ4-PP3-100U-075D-92765-1D-UNV-STD-W-4 (3500K)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	105	105	105	105	96	96	96	96	78	78	78	62	62	62	48	48	48	41				41
1	96	92	88	85	87	84	81	78	69	67	64	55	54	52	42	41	41	35				35
2	87	80	74	69	79	73	68	64	60	57	54	48	46	44	37	36	34	29				29
3	80	71	63	58	72	65	58	53	53	49	45	43	40	37	33	31	29	25				25
4	73	62	55	49	66	57	51	45	47	42	39	38	35	32	30	27	25	21				21
5	67	56	48	42	61	51	44	39	42	37	33	34	31	28	27	24	22	19				19
6	62	50	42	36	56	46	39	34	38	33	29	31	27	24	24	22	19	16				16
7	57	45	37	32	52	41	34	30	35	29	25	28	24	21	22	19	17	15				15
8	53	41	33	28	48	38	31	26	31	26	23	26	22	19	20	18	15	13				13
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	19	16	14	12				12
10	46	34	27	22	42	31	25	21	26	21	18	22	18	15	17	15	13	11				11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10844	10844	10844
5°	10923	10856	10817
10°	10904	10827	10778
15°	10833	10773	10714
20°	10760	10700	10619
25°	10632	10559	10454
30°	10435	10381	10249
35°	10163	10093	9966
40°	9837	9776	9664
45°	9569	9501	9407
50°	9225	9166	9077
55°	8749	8631	8565
60°	7964	7735	7698
65°	7017	6724	6700
70°	6056	5808	5808
75°	5215	5140	5065
80°	4596	4654	4543
85°	3599	3927	3927



TEST NUMBER: P523842

CATALOG NUMBER: SQ4-PP3-100U-075D-92765-1D-UNV-STD-W-4 (3500K)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	111.1	1.5
10°-20°	317.3	4.3
20°-30°	475.3	6.4
30°-40°	557.5	7.6
40°-50°	559.2	7.6
50°-60°	477.1	6.5
60°-70°	311.1	4.2
70°-80°	156.1	2.1
80°-90°	43.2	0.6
90°-100°	320.7	4.3
100°-110°	912.7	12.4
110°-120°	874.4	11.8
120°-130°	692.1	9.4
130°-140°	555.5	7.5
140°-150°	434.9	5.9
150°-160°	318.2	4.3
160°-170°	197.1	2.7
170°-180°	66.9	0.9
0°-30°	903.7	12.2
0°-40°	1461.2	19.8
0°-60°	2497.6	33.8
0°-90°	3008.0	40.8
90°-120°	2107.9	28.6
90°-150°	3790.4	51.4
90°-180°	4373.0	59.3
0°-180°	7380.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1175	1175	1175	1175	1175	
5°	1179	1168	1172	1168	1168	112
15°	1134	1123	1128	1124	1122	320
25°	1044	1032	1037	1028	1027	480
35°	902	893	896	886	885	564
45°	733	728	728	721	721	565
55°	544	542	537	534	532	483
65°	321	315	308	306	307	321
75°	146	146	144	143	142	159
85°	34	37	37	37	37	40
90°	0	0	0	0	0	3
95°	35	138	621	215	132	40
105°	142	215	930	1643	1562	150
115°	264	319	705	1494	1754	260
125°	372	413	673	1117	1336	333
135°	455	493	665	944	1067	351
145°	537	564	670	817	890	335
155°	613	627	686	738	768	283
165°	677	680	695	710	720	190
175°	709	705	703	698	693	67
180°	704	704	704	704	704	

TEST NUMBER: P523842

CATALOG NUMBER: SQ4-PP3-100U-075D-92765-1D-UNV-STD-W-4 (3500K)

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1175.3	1175.3	1175.3	1175.3	1175.3
2.5°	1182.7	1173.0	1175.3	1173.5	1168.7
5°	1179.4	1168.3	1172.2	1168.0	1168.0
7.5°	1171.3	1159.3	1163.1	1159.0	1158.8
10°	1163.9	1151.8	1155.7	1151.5	1150.5
12.5°	1153.2	1141.1	1145.8	1140.8	1140.6
15°	1134.1	1123.0	1127.9	1123.7	1121.7
17.5°	1112.4	1100.3	1106.2	1100.5	1099.6
20°	1095.9	1083.9	1089.8	1081.5	1081.5
22.5°	1076.2	1064.1	1070.8	1060.1	1060.1
25°	1044.4	1032.4	1037.2	1027.9	1026.9
27.5°	1006.7	994.9	999.9	989.4	989.2
30°	979.5	968.5	974.4	963.0	962.0
32.5°	949.9	939.6	943.9	932.6	931.5
35°	902.3	893.2	896.1	885.8	884.8
37.5°	852.2	843.0	846.3	837.4	837.0
40°	816.8	810.8	811.7	804.4	802.4
42.5°	783.8	777.0	777.9	770.7	770.2
45°	733.4	728.3	728.2	721.0	721.0
47.5°	679.8	676.0	674.9	668.9	668.7
50°	642.7	639.7	638.6	633.4	632.4
52.5°	604.0	602.6	599.1	594.7	594.5
55°	543.9	541.8	536.6	533.5	532.5
57.5°	478.5	474.5	468.7	464.1	465.0
60°	431.6	427.5	419.2	417.2	417.2
62.5°	386.3	381.4	373.1	370.2	371.8
65°	321.4	315.3	308.0	305.9	306.9
67.5°	262.4	257.0	249.1	249.0	248.2
70°	224.5	221.5	215.3	215.3	215.3
72.5°	190.8	189.3	184.8	184.8	184.0
75°	146.3	146.3	144.2	143.1	142.1
77.5°	109.6	110.0	109.0	107.9	106.1
80°	86.5	88.5	87.6	86.5	85.5
82.5°	65.1	67.1	67.0	65.1	64.9
85°	34.0	37.0	37.1	37.1	37.1
87.5°	9.1	12.3	13.2	13.2	14.0
90°	0.0	0.0	0.0	0.0	0.0
92.5°	10.7	56.8	131.7	38.3	28.9
95°	34.8	138.2	620.9	214.9	132.5
97.5°	64.0	161.8	956.3	684.3	468.9
100°	84.3	175.9	1029.1	1042.4	802.9
102.5°	106.8	191.1	1013.1	1334.3	1125.2
105°	141.9	215.1	930.1	1642.9	1561.7
107.5°	177.5	243.1	833.2	1729.9	1802.1
110°	202.1	263.6	777.5	1696.6	1858.8



TEST NUMBER: P523842

CATALOG NUMBER: SQ4-PP3-100U-075D-92765-1D-UNV-STD-W-4 (3500K)

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	225.6	284.0	740.1	1617.8	1849.2
115°	263.6	318.6	705.3	1494.1	1754.4
117.5°	297.1	348.6	684.6	1358.7	1634.5
120°	323.9	367.0	682.5	1281.4	1545.7
122.5°	345.3	388.4	677.2	1213.5	1459.0
125°	372.0	412.6	673.1	1117.1	1335.6
127.5°	401.2	439.2	671.0	1059.4	1239.5
130°	416.2	454.1	667.8	1019.3	1176.3
132.5°	432.3	469.2	667.8	988.0	1132.4
135°	455.0	493.0	665.1	943.6	1066.6
137.5°	476.4	513.3	664.8	906.0	1012.3
140°	492.5	530.4	663.8	874.9	976.9
142.5°	510.7	542.3	667.0	850.0	941.6
145°	536.6	564.1	670.5	816.7	889.9
147.5°	558.9	585.5	676.4	783.0	846.3
150°	578.1	596.4	678.5	771.8	816.3
152.5°	593.1	612.5	680.6	756.8	798.1
155°	612.9	627.3	686.5	738.1	768.2
157.5°	637.5	646.2	687.9	729.6	751.0
160°	650.4	656.9	693.2	723.1	741.4
162.5°	657.9	665.5	694.3	717.6	731.8
165°	677.2	679.8	694.6	709.5	720.0
167.5°	690.3	687.9	700.7	707.5	711.7
170°	694.6	693.2	698.6	700.0	705.3
172.5°	704.2	699.7	701.8	697.9	702.0
175°	709.3	705.3	702.6	698.4	693.2
177.5°	711.4	705.1	701.8	697.5	698.6
180°	703.9	703.9	703.9	703.9	703.9

(END OF REPORT)