

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P523701

Luminaire Tested: **SQ4-PP3-050U-100D-92765-1D-UNV-STD-W-4 (4500K)**

Issue Date: 5/24/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P523701  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2103-172-1)  
Test Lab: INNOVATION CENTER  
Issue Date: 5/24/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PP3-050U-100D-92765-1D-UNV-STD-W-4 (4500K)  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS  
DOWNLIGHT 1000 LUMENS PER FOOT  
UPLIGHT 500 LUMENS PER FOOT  
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 4500K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6350.0 lumens  
Efficiency: N/A  
Efficacy: 109.3 lumens/watt  
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33  
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 58.1  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P523701

CATALOG NUMBER: SQ4-PP3-050U-100D-92765-1D-UNV-STD-W-4 (4500K)

### Luminous Intensity Polar Plot





TEST NUMBER: P523701

CATALOG NUMBER: SQ4-PP3-050U-100D-92765-1D-UNV-STD-W-4 (4500K)

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	104	104	104	104	91	91	91	80	80	80	69	69	69	64
1	101	97	93	90	95	91	88	85	81	78	76	71	69	67	62	60	59	55
2	92	85	79	74	87	80	75	70	71	67	63	62	59	57	55	52	50	46
3	84	75	67	62	79	71	64	59	63	58	53	55	51	48	49	46	43	39
4	77	66	58	52	72	63	56	50	56	50	46	49	45	41	44	40	37	34
5	71	59	51	45	67	56	49	43	50	44	39	44	40	36	39	35	32	30
6	66	53	45	39	61	51	43	38	45	39	35	40	35	32	36	32	29	26
7	61	48	40	34	57	46	38	33	41	35	31	37	32	28	33	29	25	23
8	56	44	36	31	53	42	34	29	38	32	27	34	29	25	30	26	23	21
9	53	40	33	27	49	38	31	26	34	29	24	31	26	23	28	24	21	19
10	49	37	30	25	46	35	28	24	32	26	22	29	24	20	26	22	19	17

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	14749	14749	14749
5°	14857	14766	14715
10°	14832	14727	14662
15°	14734	14653	14573
20°	14636	14554	14444
25°	14463	14363	14219
30°	14195	14120	13941
35°	13823	13729	13555
40°	13381	13297	13145
45°	13015	12924	12796
50°	12549	12467	12347
55°	11900	11741	11651
60°	10832	10522	10470
65°	9542	9145	9114
70°	8238	7898	7898
75°	7090	6990	6891
80°	6254	6328	6179
85°	4891	5335	5335



TEST NUMBER: P523701

CATALOG NUMBER: SQ4-PP3-050U-100D-92765-1D-UNV-STD-W-4 (4500K)

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	151.2	2.4
10°-20°	431.6	6.8
20°-30°	646.5	10.2
30°-40°	758.3	11.9
40°-50°	760.7	12.0
50°-60°	648.9	10.2
60°-70°	423.2	6.7
70°-80°	212.3	3.3
80°-90°	58.8	0.9
90°-100°	165.7	2.6
100°-110°	471.4	7.4
110°-120°	451.7	7.1
120°-130°	357.5	5.6
130°-140°	286.9	4.5
140°-150°	224.6	3.5
150°-160°	164.4	2.6
160°-170°	101.8	1.6
170°-180°	34.5	0.5
0°-30°	1229.3	19.4
0°-40°	1987.6	31.3
0°-60°	3397.2	53.5
0°-90°	4091.5	64.4
90°-120°	1088.8	17.1
90°-150°	1957.8	30.8
90°-180°	2259.0	35.6
0°-180°	6350.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1599	1599	1599	1599	1599	
5°	1604	1589	1594	1589	1589	152
15°	1543	1528	1534	1528	1526	435
25°	1421	1404	1411	1398	1397	653
35°	1227	1215	1219	1205	1204	767
45°	998	991	990	981	981	768
55°	740	737	730	726	724	657
65°	437	429	419	416	418	436
75°	199	199	196	195	193	216
85°	46	50	50	50	50	54
90°	0	0	0	0	0	2
95°	18	71	321	111	68	21
105°	73	111	480	849	807	78
115°	136	165	364	772	906	134
125°	192	213	348	577	690	172
135°	235	255	344	487	551	181
145°	277	291	346	422	460	173
155°	317	324	355	381	397	146
165°	350	351	359	366	372	98
175°	366	364	363	361	358	35
180°	364	364	364	364	364	

TEST NUMBER: P523701

CATALOG NUMBER: SQ4-PP3-050U-100D-92765-1D-UNV-STD-W-4 (4500K)

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1598.6	1598.6	1598.6	1598.6	1598.6
2.5°	1608.7	1595.5	1598.6	1596.2	1589.6
5°	1604.2	1589.1	1594.4	1588.8	1588.8
7.5°	1593.3	1576.8	1582.1	1576.4	1576.2
10°	1583.2	1566.7	1572.0	1566.3	1565.0
12.5°	1568.6	1552.2	1558.5	1551.8	1551.5
15°	1542.6	1527.5	1534.1	1528.5	1525.7
17.5°	1513.1	1496.7	1504.7	1496.9	1495.8
20°	1490.7	1474.3	1482.3	1471.1	1471.1
22.5°	1463.8	1447.4	1456.5	1442.0	1442.0
25°	1420.7	1404.2	1410.9	1398.2	1396.8
27.5°	1369.4	1353.2	1360.1	1345.8	1345.6
30°	1332.4	1317.3	1325.4	1309.9	1308.6
32.5°	1292.0	1278.1	1283.9	1268.5	1267.1
35°	1227.3	1215.0	1218.9	1204.9	1203.5
37.5°	1159.2	1146.6	1151.1	1139.0	1138.5
40°	1111.0	1102.8	1104.0	1094.2	1091.4
42.5°	1066.2	1056.9	1058.1	1048.2	1047.7
45°	997.5	990.7	990.5	980.7	980.7
47.5°	924.7	919.5	918.0	909.8	909.6
50°	874.3	870.1	868.6	861.6	860.2
52.5°	821.6	819.7	814.8	809.0	808.7
55°	739.8	737.0	729.9	725.7	724.3
57.5°	650.9	645.4	637.5	631.3	632.4
60°	587.0	581.6	570.2	567.4	567.4
62.5°	525.4	518.8	507.5	503.6	505.8
65°	437.1	428.9	418.9	416.1	417.5
67.5°	357.0	349.6	338.8	338.7	337.7
70°	305.4	301.3	292.8	292.8	292.8
72.5°	259.5	257.6	251.3	251.3	250.2
75°	198.9	198.9	196.1	194.7	193.3
77.5°	149.1	149.6	148.2	146.8	144.3
80°	117.7	120.4	119.1	117.7	116.3
82.5°	88.5	91.3	91.1	88.5	88.3
85°	46.2	50.3	50.4	50.4	50.4
87.5°	12.3	16.7	17.9	18.0	19.1
90°	0.0	0.0	0.0	0.0	0.0
92.5°	5.5	29.3	68.0	19.8	14.9
95°	18.0	71.4	320.7	111.0	68.4
97.5°	33.0	83.6	494.0	353.5	242.2
100°	43.5	90.9	531.6	538.4	414.7
102.5°	55.2	98.7	523.3	689.2	581.2
105°	73.3	111.1	480.4	848.6	806.7
107.5°	91.7	125.6	430.4	893.5	930.8
110°	104.4	136.1	401.6	876.3	960.1

TEST NUMBER: P523701

CATALOG NUMBER: SQ4-PP3-050U-100D-92765-1D-UNV-STD-W-4 (4500K)

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	116.5	146.7	382.3	835.7	955.2
115°	136.2	164.6	364.3	771.7	906.2
117.5°	153.5	180.1	353.6	701.8	844.3
120°	167.3	189.6	352.5	661.9	798.4
122.5°	178.3	200.6	349.8	626.8	753.6
125°	192.2	213.1	347.7	577.0	689.9
127.5°	207.2	226.8	346.6	547.2	640.2
130°	215.0	234.6	344.9	526.5	607.6
132.5°	223.3	242.3	344.9	510.3	584.9
135°	235.0	254.6	343.5	487.4	550.9
137.5°	246.1	265.1	343.4	468.0	522.9
140°	254.4	274.0	342.9	451.9	504.6
142.5°	263.8	280.1	344.5	439.0	486.4
145°	277.2	291.4	346.3	421.8	459.7
147.5°	288.7	302.4	349.4	404.4	437.1
150°	298.6	308.1	350.5	398.7	421.7
152.5°	306.4	316.4	351.6	390.9	412.3
155°	316.6	324.0	354.6	381.2	396.8
157.5°	329.3	333.8	355.3	376.8	387.9
160°	335.9	339.3	358.1	373.5	382.9
162.5°	339.8	343.7	358.6	370.7	378.0
165°	349.8	351.1	358.8	366.5	371.9
167.5°	356.5	355.3	361.9	365.4	367.6
170°	358.8	358.1	360.8	361.6	364.3
172.5°	363.7	361.4	362.5	360.5	362.6
175°	366.4	364.3	362.9	360.8	358.1
177.5°	367.5	364.2	362.5	360.3	360.8
180°	363.6	363.6	363.6	363.6	363.6

(END OF REPORT)