

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P523859

Luminaire Tested: **SQ4-PP3-100U-100D-92765-1D-UNV-STD-W-4 (5700K)**

Issue Date: 5/24/2021

Test Information

Test Method: LM-79-2019
Report Number: P523859
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2103-172-1)
Test Lab: INNOVATION CENTER
Issue Date: 5/24/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PP3-100U-100D-92765-1D-UNV-STD-W-4 (5700K)
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS
DOWNLIGHT 1000 LUMENS PER FOOT
UPLIGHT 1000 LUMENS PER FOOT
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 5700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8835.3 lumens
Efficiency: N/A
Efficacy: 118.4 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 74.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P523859

CATALOG NUMBER: SQ4-PP3-100U-100D-92765-1D-UNV-STD-W-4 (5700K)

Luminous Intensity Polar Plot





TEST NUMBER: P523859

CATALOG NUMBER: SQ4-PP3-100U-100D-92765-1D-UNV-STD-W-4 (5700K)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	107	107	107	107	98	98	98	98	82	82	82	67	67	67	54	54	54	47				47
1	97	93	89	86	89	86	83	80	72	70	68	60	58	56	48	47	46				40	
2	89	82	76	71	81	75	70	66	63	60	56	52	50	47	42	41	39				34	
3	81	72	65	59	74	66	60	55	56	51	47	46	43	40	38	35	33				29	
4	74	64	56	50	68	59	52	47	50	45	41	41	38	35	34	31	29				25	
5	68	57	49	43	62	52	45	40	45	39	35	37	33	30	30	27	25				22	
6	63	51	43	37	58	47	40	35	40	35	31	34	29	26	28	24	22				19	
7	58	46	38	32	53	43	36	31	36	31	27	31	26	23	25	22	20				17	
8	54	42	34	29	49	39	32	27	33	28	24	28	24	21	23	20	18				15	
9	50	38	31	26	46	35	29	24	30	25	21	26	22	19	21	18	16				14	
10	47	35	28	23	43	32	26	22	28	23	19	24	20	17	20	17	14				12	

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	15125	15125	15125
5°	15235	15142	15089
10°	15210	15102	15035
15°	15109	15027	14945
20°	15009	14925	14812
25°	14830	14728	14582
30°	14556	14479	14296
35°	14176	14079	13900
40°	13722	13635	13480
45°	13347	13254	13122
50°	12868	12786	12661
55°	12202	12040	11948
60°	11108	10789	10737
65°	9787	9379	9346
70°	8449	8101	8101
75°	7272	7169	7069
80°	6413	6487	6333
85°	5018	5473	5473



TEST NUMBER: P523859

CATALOG NUMBER: SQ4-PP3-100U-100D-92765-1D-UNV-STD-W-4 (5700K)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	155.0	1.8
10°-20°	442.6	5.0
20°-30°	663.0	7.5
30°-40°	777.6	8.8
40°-50°	780.0	8.8
50°-60°	665.5	7.5
60°-70°	434.0	4.9
70°-80°	217.7	2.5
80°-90°	60.2	0.7
90°-100°	340.3	3.9
100°-110°	968.4	11.0
110°-120°	927.8	10.5
120°-130°	734.4	8.3
130°-140°	589.4	6.7
140°-150°	461.5	5.2
150°-160°	337.6	3.8
160°-170°	209.1	2.4
170°-180°	71.0	0.8
0°-30°	1260.6	14.3
0°-40°	2038.2	23.1
0°-60°	3483.7	39.4
0°-90°	4195.7	47.5
90°-120°	2236.6	25.3
90°-150°	4021.8	45.5
90°-180°	4640.0	52.5
0°-180°	8835.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1639	1639	1639	1639	1639	
5°	1645	1630	1635	1629	1629	156
15°	1582	1566	1573	1567	1565	446
25°	1457	1440	1447	1434	1432	670
35°	1259	1246	1250	1236	1234	786
45°	1023	1016	1016	1006	1006	788
55°	759	756	748	744	743	674
65°	448	440	430	427	428	447
75°	204	204	201	200	198	221
85°	47	52	52	52	52	56
90°	0	0	0	0	0	3
95°	37	147	659	228	141	42
105°	150	228	987	1743	1657	159
115°	280	338	748	1585	1862	275
125°	395	438	714	1185	1417	353
135°	483	523	706	1001	1132	373
145°	569	599	711	866	944	356
155°	650	666	728	783	815	301
165°	718	721	737	753	764	202
175°	753	748	746	741	736	71
180°	747	747	747	747	747	

TEST NUMBER: P523859

CATALOG NUMBER: SQ4-PP3-100U-100D-92765-1D-UNV-STD-W-4 (5700K)

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1639.3	1639.3	1639.3	1639.3	1639.3
2.5°	1649.6	1636.2	1639.3	1636.9	1630.1
5°	1645.0	1629.6	1635.0	1629.2	1629.2
7.5°	1633.8	1617.0	1622.3	1616.6	1616.3
10°	1623.5	1606.6	1612.0	1606.2	1604.8
12.5°	1608.6	1591.7	1598.2	1591.3	1591.0
15°	1581.8	1566.4	1573.2	1567.4	1564.6
17.5°	1551.7	1534.8	1543.0	1535.0	1533.8
20°	1528.7	1511.8	1520.1	1508.6	1508.6
22.5°	1501.1	1484.2	1493.6	1478.7	1478.7
25°	1456.8	1440.0	1446.8	1433.8	1432.4
27.5°	1404.3	1387.7	1394.8	1380.1	1379.8
30°	1366.3	1350.9	1359.1	1343.3	1341.9
32.5°	1324.9	1310.6	1316.6	1300.8	1299.4
35°	1258.6	1245.9	1250.0	1235.6	1234.1
37.5°	1188.7	1175.8	1180.4	1168.0	1167.5
40°	1139.3	1130.9	1132.1	1122.0	1119.2
42.5°	1093.3	1083.8	1085.0	1074.9	1074.4
45°	1022.9	1015.9	1015.8	1005.7	1005.7
47.5°	948.2	942.9	941.3	933.0	932.7
50°	896.5	892.3	890.8	883.6	882.1
52.5°	842.5	840.5	835.6	829.6	829.3
55°	758.6	755.8	748.5	744.2	742.8
57.5°	667.5	661.9	653.7	647.4	648.5
60°	602.0	596.4	584.7	581.9	581.9
62.5°	538.8	532.0	520.4	516.4	518.7
65°	448.3	439.8	429.6	426.7	428.1
67.5°	366.1	358.5	347.4	347.4	346.3
70°	313.2	309.0	300.3	300.3	300.3
72.5°	266.1	264.1	257.7	257.7	256.6
75°	204.0	204.0	201.1	199.7	198.3
77.5°	152.9	153.4	152.0	150.5	148.0
80°	120.7	123.5	122.1	120.7	119.2
82.5°	90.8	93.6	93.4	90.8	90.5
85°	47.4	51.6	51.7	51.7	51.7
87.5°	12.6	17.1	18.4	18.4	19.5
90°	0.0	0.0	0.0	0.0	0.0
92.5°	11.4	60.2	139.7	40.7	30.7
95°	36.9	146.6	658.9	228.0	140.6
97.5°	67.9	171.7	1014.7	726.1	497.6
100°	89.5	186.6	1092.0	1106.1	852.0
102.5°	113.3	202.7	1074.9	1415.8	1193.9
105°	150.5	228.3	986.9	1743.2	1657.1
107.5°	188.3	258.0	884.1	1835.5	1912.1
110°	214.4	279.7	825.0	1800.2	1972.3

TEST NUMBER: P523859

CATALOG NUMBER: SQ4-PP3-100U-100D-92765-1D-UNV-STD-W-4 (5700K)

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	239.4	301.3	785.2	1716.7	1962.1
115°	279.7	338.0	748.3	1585.3	1861.6
117.5°	315.2	369.9	726.5	1441.7	1734.4
120°	343.6	389.5	724.2	1359.6	1640.1
122.5°	366.4	412.2	718.5	1287.6	1548.1
125°	394.8	437.8	714.2	1185.3	1417.1
127.5°	425.7	466.0	712.0	1124.1	1315.2
130°	441.6	481.9	708.6	1081.5	1248.2
132.5°	458.7	497.8	708.6	1048.3	1201.6
135°	482.8	523.1	705.7	1001.2	1131.7
137.5°	505.5	544.7	705.4	961.3	1074.1
140°	522.6	562.8	704.3	928.3	1036.6
142.5°	541.9	575.5	707.7	901.9	999.1
145°	569.4	598.6	711.4	866.5	944.3
147.5°	593.0	621.3	717.7	830.8	898.0
150°	613.4	632.9	719.9	819.0	866.2
152.5°	629.3	649.9	722.2	803.0	846.9
155°	650.3	665.6	728.4	783.1	815.1
157.5°	676.5	685.6	729.9	774.1	796.9
160°	690.1	697.1	735.5	767.2	786.7
162.5°	698.1	706.1	736.7	761.4	776.4
165°	718.5	721.3	737.0	752.8	763.9
167.5°	732.4	729.9	743.5	750.7	755.1
170°	737.0	735.6	741.2	742.8	748.3
172.5°	747.2	742.5	744.6	740.5	744.9
175°	752.6	748.4	745.5	741.1	735.5
177.5°	754.9	748.2	744.6	740.1	741.2
180°	746.9	746.9	746.9	746.9	746.9

(END OF REPORT)