

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: CORELITE

Report Number: P523713

Luminaire Tested: **SQ4-PP3-050U-125D-92765-1D-UNV-STD-W-4 (4000K)**

Issue Date: 5/24/2021

Test Information

Test Method: LM-79-2019
Report Number: P523713
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2103-172-1)
Test Lab: INNOVATION CENTER
Issue Date: 5/24/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PP3-050U-125D-92765-1D-UNV-STD-W-4 (4000K)
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 500 LUMENS PER FOOT
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7320.6 lumens
Efficiency: N/A
Efficacy: 102.2 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 71.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P523713

CATALOG NUMBER: SQ4-PP3-050U-125D-92765-1D-UNV-STD-W-4 (4000K)

Luminous Intensity Polar Plot





TEST NUMBER: P523713

CATALOG NUMBER: SQ4-PP3-050U-125D-92765-1D-UNV-STD-W-4 (4000K)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	112	112	112	112	106	106	106	106	94	94	94	84	84	84	74	74	74	74	74	74	70	
1	102	98	94	91	97	93	90	86	83	81	78	74	72	71	66	65	63	63	63	63	59	
2	94	86	80	75	88	82	76	71	73	69	65	66	62	59	58	56	54	54	54	54	50	
3	86	76	68	62	81	72	65	60	65	59	55	58	54	50	52	49	46	46	46	46	43	
4	78	67	59	53	74	64	57	51	58	52	47	52	47	43	47	43	40	40	40	40	37	
5	72	60	52	46	68	57	50	44	52	46	41	47	42	38	42	38	35	35	35	35	32	
6	66	54	46	40	63	52	44	38	47	40	36	42	37	33	38	34	31	31	31	31	28	
7	62	49	41	35	58	47	39	34	43	36	32	39	33	29	35	31	27	27	27	27	25	
8	57	45	37	31	54	43	35	30	39	33	28	35	30	26	32	28	24	24	24	24	22	
9	53	41	33	28	50	39	32	27	36	30	25	33	27	24	30	25	22	22	22	22	20	
10	50	38	30	25	47	36	29	24	33	27	23	30	25	22	27	23	20	20	20	20	18	

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	18377	18377	18377
5°	18512	18399	18334
10°	18480	18349	18268
15°	18358	18258	18158
20°	18237	18133	17996
25°	18020	17895	17717
30°	17686	17593	17371
35°	17224	17105	16889
40°	16672	16568	16379
45°	16217	16104	15944
50°	15635	15535	15384
55°	14826	14630	14517
60°	13496	13110	13046
65°	11889	11396	11357
70°	10267	9841	9841
75°	8837	8712	8587
80°	7789	7885	7699
85°	6097	6648	6648



TEST NUMBER: P523713

CATALOG NUMBER: SQ4-PP3-050U-125D-92765-1D-UNV-STD-W-4 (4000K)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	188.3	2.6
10°-20°	537.8	7.3
20°-30°	805.5	11.0
30°-40°	944.8	12.9
40°-50°	947.8	12.9
50°-60°	808.5	11.0
60°-70°	527.3	7.2
70°-80°	264.5	3.6
80°-90°	73.2	1.0
90°-100°	163.0	2.2
100°-110°	463.9	6.3
110°-120°	444.5	6.1
120°-130°	351.8	4.8
130°-140°	282.4	3.9
140°-150°	221.1	3.0
150°-160°	161.8	2.2
160°-170°	100.2	1.4
170°-180°	34.0	0.5
0°-30°	1531.7	20.9
0°-40°	2476.5	33.8
0°-60°	4232.8	57.8
0°-90°	5097.9	69.6
90°-120°	1071.5	14.6
90°-150°	1926.7	26.3
90°-180°	2223.0	30.4
0°-180°	7320.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1992	1992	1992	1992	1992	
5°	1999	1980	1987	1980	1980	190
15°	1922	1903	1912	1904	1901	542
25°	1770	1750	1758	1742	1740	814
35°	1529	1514	1519	1501	1500	955
45°	1243	1234	1234	1222	1222	957
55°	922	918	910	904	902	819
65°	545	534	522	518	520	544
75°	248	248	244	243	241	269
85°	58	63	63	63	63	68
90°	0	0	0	0	0	3
95°	18	70	316	109	67	20
105°	72	109	473	835	794	76
115°	134	162	358	760	892	132
125°	189	210	342	568	679	169
135°	231	251	338	480	542	178
145°	273	287	341	415	452	170
155°	312	319	349	375	390	144
165°	344	346	353	361	366	97
175°	360	358	357	355	352	34
180°	358	358	358	358	358	

TEST NUMBER: P523713

CATALOG NUMBER: SQ4-PP3-050U-125D-92765-1D-UNV-STD-W-4 (4000K)

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1991.8	1991.8	1991.8	1991.8	1991.8
2.5°	2004.4	1988.0	1991.8	1988.8	1980.6
5°	1998.8	1980.0	1986.6	1979.6	1979.6
7.5°	1985.2	1964.7	1971.2	1964.2	1963.9
10°	1972.6	1952.1	1958.6	1951.6	1949.9
12.5°	1954.4	1934.0	1941.9	1933.5	1933.1
15°	1922.0	1903.2	1911.5	1904.4	1901.0
17.5°	1885.3	1864.8	1874.8	1865.0	1863.7
20°	1857.4	1836.9	1846.9	1832.9	1832.9
22.5°	1823.9	1803.4	1814.8	1796.6	1796.6
25°	1770.1	1749.6	1757.9	1742.1	1740.4
27.5°	1706.2	1686.1	1694.7	1676.9	1676.5
30°	1660.1	1641.4	1651.4	1632.2	1630.5
32.5°	1609.9	1592.4	1599.7	1580.5	1578.8
35°	1529.2	1513.8	1518.7	1501.2	1499.5
37.5°	1444.4	1428.7	1434.2	1419.2	1418.5
40°	1384.3	1374.1	1375.6	1363.3	1359.9
42.5°	1328.5	1316.8	1318.3	1306.1	1305.4
45°	1242.9	1234.4	1234.2	1222.0	1222.0
47.5°	1152.1	1145.7	1143.8	1133.6	1133.3
50°	1089.3	1084.2	1082.3	1073.5	1071.8
52.5°	1023.7	1021.3	1015.3	1007.9	1007.6
55°	921.7	918.3	909.5	904.2	902.5
57.5°	811.0	804.2	794.3	786.6	788.0
60°	731.4	724.6	710.5	707.0	707.0
62.5°	654.6	646.4	632.3	627.5	630.2
65°	544.6	534.4	522.0	518.5	520.2
67.5°	444.8	435.6	422.1	422.1	420.7
70°	380.6	375.4	364.8	364.8	364.8
72.5°	323.3	320.9	313.2	313.1	311.8
75°	247.9	247.9	244.4	242.6	240.9
77.5°	185.7	186.4	184.7	182.9	179.8
80°	146.6	150.0	148.4	146.6	144.9
82.5°	110.3	113.7	113.5	110.3	110.0
85°	57.6	62.7	62.8	62.8	62.8
87.5°	15.4	20.8	22.3	22.4	23.7
90°	0.0	0.0	0.0	0.0	0.0
92.5°	5.4	28.9	66.9	19.5	14.7
95°	17.7	70.2	315.6	109.3	67.3
97.5°	32.5	82.3	486.1	347.8	238.4
100°	42.9	89.4	523.1	529.9	408.2
102.5°	54.3	97.1	515.0	678.3	572.0
105°	72.1	109.4	472.8	835.1	793.9
107.5°	90.2	123.6	423.5	879.3	916.0
110°	102.7	134.0	395.2	862.4	944.9

TEST NUMBER: P523713

CATALOG NUMBER: SQ4-PP3-050U-125D-92765-1D-UNV-STD-W-4 (4000K)

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	114.7	144.4	376.2	822.4	940.0
115°	134.0	161.9	358.5	759.5	891.8
117.5°	151.0	177.2	348.0	690.7	830.9
120°	164.6	186.6	346.9	651.3	785.7
122.5°	175.5	197.5	344.2	616.8	741.6
125°	189.1	209.7	342.2	567.8	678.9
127.5°	203.9	223.2	341.1	538.5	630.1
130°	211.6	230.9	339.5	518.1	598.0
132.5°	219.7	238.5	339.5	502.2	575.6
135°	231.3	250.6	338.1	479.6	542.2
137.5°	242.2	260.9	338.0	460.5	514.6
140°	250.3	269.6	337.4	444.7	496.6
142.5°	259.6	275.7	339.0	432.1	478.6
145°	272.8	286.8	340.8	415.1	452.4
147.5°	284.1	297.6	343.8	398.0	430.2
150°	293.9	303.2	344.9	392.3	415.0
152.5°	301.5	311.3	346.0	384.7	405.7
155°	311.6	318.9	349.0	375.2	390.5
157.5°	324.1	328.5	349.7	370.9	381.8
160°	330.6	333.9	352.4	367.6	376.9
162.5°	334.4	338.3	352.9	364.8	372.0
165°	344.2	345.5	353.1	360.7	366.0
167.5°	350.9	349.7	356.2	359.6	361.8
170°	353.1	352.4	355.1	355.8	358.5
172.5°	358.0	355.7	356.7	354.7	356.9
175°	360.5	358.5	357.1	355.0	352.4
177.5°	361.6	358.4	356.7	354.6	355.1
180°	357.8	357.8	357.8	357.8	357.8

(END OF REPORT)