

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P523715

Luminaire Tested: **SQ4-PP3-050U-125D-92765-1D-UNV-STD-W-4 (5000K)**

Issue Date: 5/24/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P523715  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2103-172-1)  
Test Lab: INNOVATION CENTER  
Issue Date: 5/24/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PP3-050U-125D-92765-1D-UNV-STD-W-4 (5000K)  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS  
DOWNLIGHT 1250 LUMENS PER FOOT  
UPLIGHT 500 LUMENS PER FOOT  
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 5000K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7520.9 lumens  
Efficiency: N/A  
Efficacy: 105.2 lumens/watt  
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33  
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 71.5  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P523715

CATALOG NUMBER: SQ4-PP3-050U-125D-92765-1D-UNV-STD-W-4 (5000K)

### Luminous Intensity Polar Plot





TEST NUMBER: P523715

CATALOG NUMBER: SQ4-PP3-050U-125D-92765-1D-UNV-STD-W-4 (5000K)

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	112	112	112	112	106	106	106	106	94	94	94	84	84	84	74	74	74	70
1	102	98	94	91	97	93	90	86	83	81	78	74	72	71	66	65	63	59
2	94	86	80	75	88	82	76	71	73	69	65	66	62	59	58	56	54	50
3	86	76	68	62	81	72	65	60	65	59	55	58	54	50	52	49	46	43
4	78	67	59	53	74	64	57	51	58	52	47	52	47	43	47	43	40	37
5	72	60	52	46	68	57	50	44	52	46	41	47	42	38	42	38	35	32
6	66	54	46	40	63	52	44	38	47	40	36	42	37	33	38	34	31	28
7	62	49	41	35	58	47	39	34	43	36	32	39	33	29	35	31	27	25
8	57	45	37	31	54	43	35	30	39	33	28	35	30	26	32	28	24	22
9	53	41	33	28	50	39	32	27	36	30	25	33	27	24	30	25	22	20
10	50	38	30	25	47	36	29	24	33	27	23	30	25	22	27	23	20	18

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	18880	18880	18880
5°	19018	18902	18836
10°	18986	18852	18768
15°	18861	18758	18655
20°	18735	18630	18489
25°	18513	18385	18203
30°	18171	18075	17846
35°	17695	17574	17352
40°	17129	17021	16827
45°	16661	16545	16380
50°	16063	15960	15806
55°	15231	15030	14914
60°	13867	13468	13402
65°	12217	11706	11667
70°	10547	10110	10110
75°	9079	8951	8823
80°	8002	8097	7911
85°	6267	6838	6838



TEST NUMBER: P523715

CATALOG NUMBER: SQ4-PP3-050U-125D-92765-1D-UNV-STD-W-4 (5000K)

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	193.5	2.6
10°-20°	552.5	7.3
20°-30°	827.6	11.0
30°-40°	970.7	12.9
40°-50°	973.7	12.9
50°-60°	830.7	11.0
60°-70°	541.7	7.2
70°-80°	271.8	3.6
80°-90°	75.2	1.0
90°-100°	167.5	2.2
100°-110°	476.6	6.3
110°-120°	456.7	6.1
120°-130°	361.4	4.8
130°-140°	290.1	3.9
140°-150°	227.1	3.0
150°-160°	166.2	2.2
160°-170°	102.9	1.4
170°-180°	34.9	0.5
0°-30°	1573.6	20.9
0°-40°	2544.3	33.8
0°-60°	4348.7	57.8
0°-90°	5237.4	69.6
90°-120°	1100.8	14.6
90°-150°	1979.5	26.3
90°-180°	2283.0	30.4
0°-180°	7520.9	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	2046	2046	2046	2046	2046	
5°	2054	2034	2041	2034	2034	195
15°	1975	1955	1964	1957	1953	557
25°	1819	1798	1806	1790	1788	836
35°	1571	1555	1560	1542	1541	981
45°	1277	1268	1268	1255	1255	983
55°	947	943	934	929	927	842
65°	560	549	536	533	534	558
75°	255	255	251	249	248	276
85°	59	64	65	65	65	70
90°	0	0	0	0	0	3
95°	18	72	324	112	69	21
105°	74	112	486	858	816	78
115°	138	166	368	780	916	136
125°	194	216	352	583	698	174
135°	238	257	347	493	557	183
145°	280	295	350	426	465	175
155°	320	328	358	385	401	148
165°	354	355	363	370	376	99
175°	370	368	367	365	362	35
180°	368	368	368	368	368	

TEST NUMBER: P523715

CATALOG NUMBER: SQ4-PP3-050U-125D-92765-1D-UNV-STD-W-4 (5000K)

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	2046.3	2046.3	2046.3	2046.3	2046.3
2.5°	2059.2	2042.4	2046.3	2043.3	2034.8
5°	2053.5	2034.2	2040.9	2033.8	2033.8
7.5°	2039.5	2018.5	2025.2	2018.0	2017.6
10°	2026.6	2005.6	2012.3	2005.0	2003.3
12.5°	2007.9	1986.9	1995.0	1986.4	1986.1
15°	1974.6	1955.3	1963.8	1956.6	1953.1
17.5°	1936.9	1915.9	1926.2	1916.1	1914.7
20°	1908.2	1887.2	1897.5	1883.1	1883.1
22.5°	1873.8	1852.8	1864.5	1845.8	1845.8
25°	1818.6	1797.5	1806.0	1789.8	1788.1
27.5°	1752.9	1732.2	1741.1	1722.8	1722.4
30°	1705.6	1686.3	1696.6	1676.8	1675.1
32.5°	1653.9	1636.0	1643.5	1623.7	1622.0
35°	1571.1	1555.3	1560.3	1542.3	1540.6
37.5°	1483.9	1467.8	1473.5	1458.1	1457.4
40°	1422.2	1411.7	1413.2	1400.6	1397.1
42.5°	1364.8	1352.9	1354.4	1341.8	1341.1
45°	1276.9	1268.2	1268.0	1255.4	1255.4
47.5°	1183.7	1177.0	1175.1	1164.7	1164.3
50°	1119.1	1113.9	1111.9	1102.9	1101.2
52.5°	1051.7	1049.2	1043.1	1035.5	1035.2
55°	946.9	943.4	934.4	929.0	927.2
57.5°	833.2	826.2	816.0	808.2	809.6
60°	751.5	744.4	729.9	726.3	726.3
62.5°	672.5	664.1	649.6	644.6	647.4
65°	559.6	549.0	536.2	532.7	534.4
67.5°	457.0	447.5	433.7	433.6	432.2
70°	391.0	385.7	374.8	374.8	374.8
72.5°	332.1	329.7	321.7	321.7	320.3
75°	254.7	254.7	251.1	249.2	247.5
77.5°	190.8	191.5	189.7	187.9	184.7
80°	150.6	154.2	152.4	150.6	148.9
82.5°	113.3	116.9	116.6	113.3	113.0
85°	59.2	64.4	64.6	64.6	64.6
87.5°	15.8	21.4	23.0	23.0	24.4
90°	0.0	0.0	0.0	0.0	0.0
92.5°	5.6	29.6	68.8	20.0	15.1
95°	18.2	72.2	324.3	112.2	69.2
97.5°	33.4	84.5	499.4	357.4	244.9
100°	44.0	91.9	537.4	544.4	419.3
102.5°	55.8	99.8	529.1	696.8	587.6
105°	74.1	112.3	485.7	858.0	815.6
107.5°	92.7	127.0	435.1	903.4	941.1
110°	105.5	137.6	406.1	886.0	970.8

TEST NUMBER: P523715

CATALOG NUMBER: SQ4-PP3-050U-125D-92765-1D-UNV-STD-W-4 (5000K)

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	117.8	148.3	386.5	844.9	965.7
115°	137.7	166.4	368.3	780.3	916.2
117.5°	155.2	182.1	357.6	709.6	853.6
120°	169.1	191.7	356.4	669.2	807.2
122.5°	180.3	202.9	353.6	633.7	761.9
125°	194.3	215.5	351.5	583.4	697.5
127.5°	209.5	229.3	350.4	553.3	647.3
130°	217.4	237.2	348.7	532.3	614.3
132.5°	225.7	245.0	348.7	516.0	591.4
135°	237.6	257.4	347.3	492.8	557.0
137.5°	248.8	268.1	347.2	473.1	528.6
140°	257.2	277.0	346.6	456.9	510.2
142.5°	266.7	283.2	348.3	443.9	491.7
145°	280.3	294.6	350.1	426.5	464.8
147.5°	291.9	305.8	353.2	408.9	442.0
150°	301.9	311.5	354.3	403.1	426.3
152.5°	309.7	319.9	355.5	395.2	416.8
155°	320.1	327.6	358.5	385.4	401.2
157.5°	332.9	337.5	359.2	381.0	392.2
160°	339.7	343.1	362.0	377.6	387.2
162.5°	343.6	347.5	362.6	374.8	382.2
165°	353.6	355.0	362.7	370.5	376.0
167.5°	360.5	359.3	365.9	369.5	371.7
170°	362.7	362.0	364.8	365.6	368.3
172.5°	367.8	365.4	366.5	364.4	366.6
175°	370.4	368.4	366.9	364.8	362.0
177.5°	371.5	368.2	366.5	364.3	364.8
180°	367.6	367.6	367.6	367.6	367.6

(END OF REPORT)