

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: CORELITE

Report Number: P523893

Luminaire Tested: **SQ4-PP3-125U-075D-92765-1D-UNV-STD-W-4 (3000K)**

Issue Date: 5/24/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P523893  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2103-172-1)  
Test Lab: INNOVATION CENTER  
Issue Date: 5/24/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PP3-125U-075D-92765-1D-UNV-STD-W-4 (3000K)  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS  
DOWNLIGHT 750 LUMENS PER FOOT  
UPLIGHT 1250 LUMENS PER FOOT  
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 3000K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 8300.7 lumens  
Efficiency: N/A  
Efficacy: 113.1 lumens/watt  
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33  
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')  
CIE Type: Semi-Indirect

Input Watts (W): 73.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P523893  
CATALOG NUMBER: SQ4-PP3-125U-075D-92765-1D-UNV-STD-W-4 (3000K)

### Luminous Intensity Polar Plot





TEST NUMBER: P523893

CATALOG NUMBER: SQ4-PP3-125U-075D-92765-1D-UNV-STD-W-4 (3000K)

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	75	75	75	58	58	58	43	43	43	35
1	95	91	87	83	85	82	79	76	66	64	62	51	50	49	38	37	36	30
2	86	79	73	68	78	72	67	63	58	54	51	45	43	41	34	32	31	25
3	79	70	63	57	71	63	57	52	51	47	43	40	37	35	30	28	26	22
4	72	62	54	48	65	56	49	44	45	41	37	36	32	30	27	24	23	19
5	66	55	47	41	59	50	43	38	41	36	32	32	28	26	24	22	20	16
6	61	49	41	36	55	45	38	33	37	31	28	29	25	22	22	19	17	14
7	56	44	36	31	51	40	34	29	33	28	24	26	23	20	20	17	15	13
8	52	40	32	27	47	37	30	25	30	25	21	24	20	18	18	16	14	11
9	48	36	29	24	44	33	27	23	28	23	19	22	18	16	17	14	12	10
10	45	33	26	22	41	31	24	20	25	20	17	20	17	14	16	13	11	9

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	10589	10589	10589
5°	10666	10602	10565
10°	10648	10573	10526
15°	10578	10520	10463
20°	10509	10449	10370
25°	10384	10311	10210
30°	10191	10138	10009
35°	9925	9856	9732
40°	9607	9546	9438
45°	9345	9280	9187
50°	9010	8951	8865
55°	8543	8430	8364
60°	7778	7554	7518
65°	6851	6567	6545
70°	5916	5670	5670
75°	5090	5019	4948
80°	4490	4543	4436
85°	3515	3832	3832



TEST NUMBER: P523893

CATALOG NUMBER: SQ4-PP3-125U-075D-92765-1D-UNV-STD-W-4 (3000K)

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	108.5	1.3
10°-20°	309.9	3.7
20°-30°	464.2	5.6
30°-40°	544.4	6.6
40°-50°	546.1	6.6
50°-60°	465.9	5.6
60°-70°	303.8	3.7
70°-80°	152.4	1.8
80°-90°	42.2	0.5
90°-100°	393.4	4.7
100°-110°	1119.5	13.5
110°-120°	1072.5	12.9
120°-130°	848.9	10.2
130°-140°	681.4	8.2
140°-150°	533.4	6.4
150°-160°	390.3	4.7
160°-170°	241.8	2.9
170°-180°	82.0	1.0
0°-30°	882.6	10.6
0°-40°	1427.0	17.2
0°-60°	2439.0	29.4
0°-90°	2937.5	35.4
90°-120°	2585.4	31.1
90°-150°	4649.1	56.0
90°-180°	5363.0	64.6
0°-180°	8300.7	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1148	1148	1148	1148	1148	
5°	1152	1141	1145	1141	1141	109
15°	1108	1097	1101	1097	1095	312
25°	1020	1008	1013	1004	1003	469
35°	881	872	875	865	864	550
45°	716	711	711	704	704	551
55°	531	529	524	521	520	472
65°	314	308	301	299	300	313
75°	143	143	141	140	139	155
85°	33	36	36	36	36	39
90°	0	0	0	0	0	3
95°	43	170	762	264	162	49
105°	174	264	1141	2015	1916	184
115°	323	391	865	1832	2152	318
125°	456	506	826	1370	1638	408
135°	558	605	816	1157	1308	431
145°	658	692	822	1002	1092	411
155°	752	769	842	905	942	348
165°	831	834	852	870	883	234
175°	870	865	862	857	850	82
180°	863	863	863	863	863	

TEST NUMBER: P523893

CATALOG NUMBER: SQ4-PP3-125U-075D-92765-1D-UNV-STD-W-4 (3000K)

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1147.7	1147.7	1147.7	1147.7	1147.7
2.5°	1155.0	1145.5	1147.7	1146.0	1141.3
5°	1151.7	1140.9	1144.7	1140.7	1140.7
7.5°	1143.9	1132.1	1135.8	1131.8	1131.6
10°	1136.6	1124.8	1128.6	1124.6	1123.6
12.5°	1126.2	1114.4	1118.9	1114.1	1113.9
15°	1107.5	1096.7	1101.4	1097.4	1095.4
17.5°	1086.4	1074.6	1080.3	1074.7	1073.9
20°	1070.3	1058.5	1064.2	1056.2	1056.2
22.5°	1050.9	1039.1	1045.7	1035.3	1035.3
25°	1020.0	1008.2	1012.9	1003.8	1002.9
27.5°	983.1	971.5	976.5	966.2	966.0
30°	956.6	945.8	951.6	940.5	939.5
32.5°	927.6	917.6	921.8	910.7	909.7
35°	881.2	872.3	875.1	865.0	864.1
37.5°	832.3	823.2	826.4	817.8	817.4
40°	797.7	791.8	792.6	785.5	783.6
42.5°	765.5	758.8	759.6	752.6	752.2
45°	716.2	711.3	711.2	704.1	704.1
47.5°	663.9	660.1	659.1	653.2	653.0
50°	627.7	624.7	623.6	618.6	617.6
52.5°	589.8	588.5	585.0	580.8	580.6
55°	531.1	529.1	524.1	521.0	520.0
57.5°	467.3	463.4	457.7	453.3	454.1
60°	421.5	417.5	409.4	407.4	407.4
62.5°	377.2	372.5	364.3	361.5	363.1
65°	313.8	307.9	300.8	298.8	299.8
67.5°	256.3	251.0	243.2	243.2	242.4
70°	219.3	216.3	210.2	210.2	210.2
72.5°	186.3	184.9	180.5	180.4	179.7
75°	142.8	142.8	140.8	139.8	138.8
77.5°	107.0	107.4	106.4	105.4	103.6
80°	84.5	86.5	85.5	84.5	83.5
82.5°	63.6	65.5	65.4	63.6	63.4
85°	33.2	36.1	36.2	36.2	36.2
87.5°	8.9	12.0	12.9	12.9	13.7
90°	0.0	0.0	0.0	0.0	0.0
92.5°	13.1	69.6	161.5	47.0	35.5
95°	42.7	169.5	761.6	263.6	162.5
97.5°	78.5	198.5	1173.0	839.3	575.2
100°	103.4	215.8	1262.3	1278.6	984.9
102.5°	131.0	234.3	1242.6	1636.6	1380.1
105°	174.0	263.9	1140.8	2015.1	1915.6
107.5°	217.7	298.2	1022.0	2121.8	2210.4
110°	247.9	323.3	953.7	2080.9	2279.9

TEST NUMBER: P523893

CATALOG NUMBER: SQ4-PP3-125U-075D-92765-1D-UNV-STD-W-4 (3000K)

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	276.7	348.3	907.7	1984.4	2268.1
115°	323.4	390.8	865.0	1832.5	2151.9
117.5°	364.4	427.6	839.8	1666.5	2004.8
120°	397.2	450.2	837.1	1571.7	1895.9
122.5°	423.5	476.5	830.6	1488.4	1789.5
125°	456.3	506.1	825.6	1370.1	1638.1
127.5°	492.1	538.6	823.0	1299.5	1520.3
130°	510.5	557.0	819.1	1250.2	1442.8
132.5°	530.2	575.4	819.1	1211.8	1389.0
135°	558.1	604.6	815.8	1157.4	1308.2
137.5°	584.3	629.6	815.5	1111.3	1241.6
140°	604.0	650.6	814.2	1073.1	1198.2
142.5°	626.4	665.2	818.1	1042.6	1154.9
145°	658.2	691.9	822.4	1001.7	1091.6
147.5°	685.5	718.2	829.6	960.4	1038.0
150°	709.1	731.6	832.2	946.7	1001.3
152.5°	727.5	751.2	834.8	928.2	978.9
155°	751.8	769.4	842.1	905.3	942.2
157.5°	782.0	792.6	843.7	894.9	921.2
160°	797.7	805.8	850.3	886.9	909.4
162.5°	806.9	816.2	851.6	880.2	897.5
165°	830.6	833.8	851.9	870.3	883.1
167.5°	846.7	843.8	859.5	867.8	872.9
170°	851.9	850.3	856.8	858.6	865.0
172.5°	863.7	858.3	860.8	856.0	861.1
175°	870.0	865.1	861.8	856.7	850.3
177.5°	872.6	864.9	860.8	855.5	856.8
180°	863.4	863.4	863.4	863.4	863.4

(END OF REPORT)