

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P523912

Luminaire Tested: **SQ4-PP3-125U-100D-92765-1D-UNV-STD-W-4 (6500K)**

Issue Date: 5/24/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P523912  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2103-172-1)  
Test Lab: INNOVATION CENTER  
Issue Date: 5/24/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PP3-125U-100D-92765-1D-UNV-STD-W-4 (6500K)  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS  
DOWNLIGHT 1000 LUMENS PER FOOT  
UPLIGHT 1250 LUMENS PER FOOT  
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 6500K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 10118.0 lumens  
Efficiency: N/A  
Efficacy: 121.5 lumens/watt  
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33  
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 83.3  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P523912

CATALOG NUMBER: SQ4-PP3-125U-100D-92765-1D-UNV-STD-W-4 (6500K)

### Luminous Intensity Polar Plot





TEST NUMBER: P523912

CATALOG NUMBER: SQ4-PP3-125U-100D-92765-1D-UNV-STD-W-4 (6500K)

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	49	49	49	42				
1	96	92	88	85	88	84	81	78	69	67	65	56	54	53	43	42	41	36				
2	88	80	74	69	80	74	69	64	61	57	54	49	47	44	38	37	35	30				
3	80	71	64	58	73	65	59	54	54	49	46	44	40	38	34	32	30	26				
4	73	63	55	49	67	58	51	46	48	43	39	39	35	32	30	28	26	22				
5	67	56	48	42	61	51	44	39	43	38	33	35	31	28	27	25	23	19				
6	62	50	42	36	56	46	39	34	38	33	29	31	28	24	25	22	20	17				
7	57	45	37	32	52	42	35	30	35	30	26	29	25	22	23	20	18	15				
8	53	41	33	28	48	38	31	26	32	26	23	26	22	19	21	18	16	13				
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	19	16	14	12				
10	46	34	27	22	42	32	25	21	27	22	18	22	18	16	18	15	13	11				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	15268	15268	15268
5°	15380	15286	15232
10°	15354	15245	15177
15°	15252	15169	15086
20°	15152	15066	14952
25°	14972	14868	14720
30°	14694	14617	14431
35°	14310	14212	14032
40°	13852	13765	13607
45°	13473	13379	13246
50°	12990	12907	12782
55°	12318	12154	12061
60°	11214	10892	10839
65°	9879	9468	9435
70°	8530	8176	8176
75°	7340	7236	7133
80°	6471	6551	6397
85°	5071	5526	5526



TEST NUMBER: P523912

CATALOG NUMBER: SQ4-PP3-125U-100D-92765-1D-UNV-STD-W-4 (6500K)

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	156.5	1.5
10°-20°	446.8	4.4
20°-30°	669.3	6.6
30°-40°	785.0	7.8
40°-50°	787.4	7.8
50°-60°	671.8	6.6
60°-70°	438.1	4.3
70°-80°	219.8	2.2
80°-90°	60.8	0.6
90°-100°	431.5	4.3
100°-110°	1227.8	12.1
110°-120°	1176.4	11.6
120°-130°	931.1	9.2
130°-140°	747.3	7.4
140°-150°	585.1	5.8
150°-160°	428.1	4.2
160°-170°	265.2	2.6
170°-180°	90.0	0.9
0°-30°	1272.5	12.6
0°-40°	2057.5	20.3
0°-60°	3516.8	34.8
0°-90°	4235.5	41.9
90°-120°	2835.8	28.0
90°-150°	5099.2	50.4
90°-180°	5882.0	58.1
0°-180°	10118.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1655	1655	1655	1655	1655	
5°	1661	1645	1650	1645	1645	158
15°	1597	1581	1588	1582	1579	451
25°	1471	1454	1460	1447	1446	676
35°	1270	1258	1262	1247	1246	794
45°	1033	1026	1025	1015	1015	795
55°	766	763	756	751	750	681
65°	452	444	434	431	432	452
75°	206	206	203	202	200	223
85°	48	52	52	52	52	56
90°	0	0	0	0	0	4
95°	47	186	835	289	178	54
105°	191	289	1251	2210	2101	202
115°	355	429	949	2010	2360	349
125°	500	555	906	1503	1797	448
135°	612	663	895	1269	1435	472
145°	722	759	902	1099	1197	451
155°	825	844	924	993	1033	381
165°	911	914	934	954	969	256
175°	954	949	945	940	933	90
180°	947	947	947	947	947	

TEST NUMBER: P523912

CATALOG NUMBER: SQ4-PP3-125U-100D-92765-1D-UNV-STD-W-4 (6500K)

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1654.8	1654.8	1654.8	1654.8	1654.8
2.5°	1665.3	1651.7	1654.8	1652.4	1645.6
5°	1660.6	1645.0	1650.5	1644.7	1644.7
7.5°	1649.3	1632.3	1637.7	1631.9	1631.6
10°	1638.9	1621.9	1627.3	1621.5	1620.0
12.5°	1623.8	1606.8	1613.4	1606.4	1606.1
15°	1596.8	1581.2	1588.1	1582.3	1579.4
17.5°	1566.4	1549.4	1557.7	1549.5	1548.4
20°	1543.2	1526.2	1534.5	1522.9	1522.9
22.5°	1515.3	1498.3	1507.8	1492.7	1492.7
25°	1470.7	1453.6	1460.5	1447.4	1446.0
27.5°	1417.6	1400.8	1408.0	1393.2	1392.9
30°	1379.3	1363.7	1372.0	1356.0	1354.6
32.5°	1337.5	1323.0	1329.1	1313.1	1311.7
35°	1270.5	1257.7	1261.8	1247.3	1245.8
37.5°	1200.0	1187.0	1191.6	1179.1	1178.6
40°	1150.1	1141.6	1142.9	1132.7	1129.8
42.5°	1103.7	1094.1	1095.3	1085.1	1084.6
45°	1032.6	1025.6	1025.4	1015.2	1015.2
47.5°	957.2	951.8	950.3	941.8	941.6
50°	905.0	900.8	899.2	891.9	890.5
52.5°	850.5	848.5	843.5	837.4	837.1
55°	765.8	762.9	755.6	751.2	749.8
57.5°	673.8	668.2	659.9	653.6	654.7
60°	607.7	602.0	590.3	587.4	587.4
62.5°	543.9	537.1	525.3	521.3	523.6
65°	452.5	444.0	433.7	430.8	432.2
67.5°	369.5	361.9	350.7	350.7	349.5
70°	316.2	311.9	303.1	303.1	303.1
72.5°	268.6	266.6	260.2	260.2	259.0
75°	205.9	205.9	203.0	201.6	200.1
77.5°	154.3	154.9	153.4	151.9	149.4
80°	121.8	124.7	123.3	121.8	120.4
82.5°	91.7	94.5	94.3	91.7	91.4
85°	47.9	52.1	52.2	52.2	52.2
87.5°	12.8	17.3	18.6	18.6	19.7
90°	0.0	0.0	0.0	0.0	0.0
92.5°	14.4	76.4	177.2	51.6	38.9
95°	46.8	185.9	835.4	289.1	178.2
97.5°	86.1	217.7	1286.6	920.6	630.9
100°	113.4	236.6	1384.5	1402.4	1080.2
102.5°	143.7	257.0	1362.9	1795.1	1513.8
105°	190.8	289.4	1251.3	2210.2	2101.0
107.5°	238.7	327.1	1120.9	2327.2	2424.4
110°	271.9	354.6	1046.0	2282.4	2500.7

TEST NUMBER: P523912

CATALOG NUMBER: SQ4-PP3-125U-100D-92765-1D-UNV-STD-W-4 (6500K)

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	303.5	382.1	995.6	2176.5	2487.8
115°	354.7	428.6	948.8	2010.0	2360.3
117.5°	399.7	469.0	921.1	1827.9	2199.0
120°	435.7	493.8	918.2	1723.8	2079.4
122.5°	464.5	522.6	911.0	1632.5	1962.8
125°	500.5	555.1	905.6	1502.8	1796.8
127.5°	539.8	590.8	902.7	1425.3	1667.5
130°	559.9	611.0	898.4	1371.3	1582.5
132.5°	581.5	631.2	898.4	1329.1	1523.5
135°	612.1	663.2	894.8	1269.4	1434.9
137.5°	640.9	690.6	894.4	1218.9	1361.8
140°	662.5	713.6	893.0	1177.0	1314.3
142.5°	687.0	729.6	897.3	1143.5	1266.7
145°	722.0	758.9	902.0	1098.7	1197.3
147.5°	751.8	787.8	909.9	1053.4	1138.6
150°	777.8	802.4	912.8	1038.4	1098.2
152.5°	797.9	824.0	915.7	1018.1	1073.7
155°	824.6	843.9	923.6	992.9	1033.4
157.5°	857.7	869.3	925.4	981.5	1010.4
160°	875.0	883.8	932.6	972.8	997.4
162.5°	885.1	895.3	934.0	965.4	984.4
165°	911.0	914.5	934.4	954.5	968.6
167.5°	928.6	925.5	942.7	951.8	957.4
170°	934.4	932.6	939.8	941.8	948.8
172.5°	947.4	941.4	944.1	938.8	944.5
175°	954.2	948.9	945.2	939.6	932.6
177.5°	957.1	948.6	944.1	938.4	939.8
180°	947.0	947.0	947.0	947.0	947.0

(END OF REPORT)