

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P523933

Luminaire Tested: **SQ4-PP3-150U-050D-92765-1D-UNV-STD-W-4 (3500K)**

Issue Date: 5/24/2021

Test Information

Test Method: LM-79-2019
Report Number: P523933
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2103-172-1)
Test Lab: INNOVATION CENTER
Issue Date: 5/24/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PP3-150U-050D-92765-1D-UNV-STD-W-4 (3500K)
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS
DOWNLIGHT 500 LUMENS PER FOOT
UPLIGHT 1500 LUMENS PER FOOT
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8627.0 lumens
Efficiency: N/A
Efficacy: 120.0 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 71.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P523933
CATALOG NUMBER: SQ4-PP3-150U-050D-92765-1D-UNV-STD-W-4 (3500K)

Luminous Intensity Polar Plot





TEST NUMBER: P523933

CATALOG NUMBER: SQ4-PP3-150U-050D-92765-1D-UNV-STD-W-4 (3500K)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	90	90	90	90	68	68	68	49	49	49	32	32	32	23
1	92	88	84	81	82	78	75	72	60	58	56	43	42	41	28	27	27	20
2	84	77	71	66	74	68	63	59	53	49	47	38	36	34	25	24	23	17
3	76	67	60	55	68	60	54	50	46	42	39	34	31	29	22	21	19	14
4	70	60	52	46	62	53	47	42	41	37	33	30	27	25	20	18	17	12
5	64	53	45	39	57	47	41	36	37	32	29	27	24	21	18	16	15	11
6	59	47	40	34	52	42	36	31	33	28	25	24	21	19	16	14	13	9
7	54	42	35	30	48	38	32	27	30	25	22	22	19	16	15	13	11	8
8	50	38	31	26	44	34	28	24	27	22	19	20	17	15	13	11	10	7
9	47	35	28	23	41	31	25	21	25	20	17	18	15	13	12	10	9	7
10	43	32	25	20	38	29	23	19	23	18	15	17	14	12	11	10	8	6

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7240	7240	7240
5°	7293	7249	7223
10°	7281	7230	7197
15°	7233	7193	7154
20°	7185	7145	7091
25°	7100	7051	6980
30°	6968	6931	6844
35°	6786	6740	6654
40°	6569	6528	6453
45°	6390	6345	6281
50°	6160	6120	6061
55°	5841	5763	5720
60°	5318	5165	5139
65°	4685	4488	4475
70°	4044	3876	3876
75°	3483	3433	3383
80°	3071	3108	3034
85°	2403	2625	2625



TEST NUMBER: P523933

CATALOG NUMBER: SQ4-PP3-150U-050D-92765-1D-UNV-STD-W-4 (3500K)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	74.2	0.9
10°-20°	211.9	2.5
20°-30°	317.4	3.7
30°-40°	372.3	4.3
40°-50°	373.4	4.3
50°-60°	318.5	3.7
60°-70°	207.7	2.4
70°-80°	104.2	1.2
80°-90°	28.9	0.3
90°-100°	485.5	5.6
100°-110°	1381.5	16.0
110°-120°	1323.6	15.3
120°-130°	1047.6	12.1
130°-140°	840.8	9.7
140°-150°	658.3	7.6
150°-160°	481.7	5.6
160°-170°	298.3	3.5
170°-180°	101.2	1.2
0°-30°	603.5	7.0
0°-40°	975.7	11.3
0°-60°	1667.7	19.3
0°-90°	2008.5	23.3
90°-120°	3190.6	37.0
90°-150°	5737.2	66.5
90°-180°	6618.0	76.7
0°-180°	8627.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	785	785	785	785	785	
5°	788	780	783	780	780	75
15°	757	750	753	750	749	214
25°	697	689	693	686	686	321
35°	602	596	598	592	591	376
45°	490	486	486	481	481	377
55°	363	362	358	356	356	323
65°	215	210	206	204	205	214
75°	98	98	96	96	95	106
85°	23	25	25	25	25	27
90°	0	0	0	0	0	3
95°	53	209	940	325	200	60
105°	215	326	1408	2487	2364	227
115°	399	482	1068	2262	2656	393
125°	563	624	1019	1691	2022	504
135°	689	746	1007	1428	1614	531
145°	812	854	1015	1236	1347	507
155°	928	950	1039	1117	1163	429
165°	1025	1029	1051	1074	1090	288
175°	1074	1068	1064	1057	1049	102
180°	1066	1066	1066	1066	1066	

TEST NUMBER: P523933

CATALOG NUMBER: SQ4-PP3-150U-050D-92765-1D-UNV-STD-W-4 (3500K)

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	784.7	784.7	784.7	784.7	784.7
2.5°	789.7	783.2	784.7	783.6	780.3
5°	787.5	780.1	782.7	779.9	779.9
7.5°	782.1	774.1	776.6	773.9	773.7
10°	777.2	769.1	771.7	768.9	768.2
12.5°	770.0	762.0	765.1	761.8	761.6
15°	757.2	749.8	753.1	750.3	749.0
17.5°	742.8	734.7	738.7	734.8	734.3
20°	731.8	723.7	727.7	722.2	722.2
22.5°	718.6	710.5	715.0	707.8	707.8
25°	697.4	689.3	692.6	686.4	685.7
27.5°	672.2	664.3	667.7	660.7	660.5
30°	654.1	646.7	650.6	643.0	642.4
32.5°	634.3	627.4	630.3	622.7	622.0
35°	602.5	596.4	598.4	591.5	590.8
37.5°	569.1	562.9	565.1	559.1	558.9
40°	545.4	541.4	542.0	537.1	535.8
42.5°	523.4	518.8	519.4	514.6	514.3
45°	489.7	486.3	486.3	481.4	481.4
47.5°	453.9	451.4	450.6	446.6	446.5
50°	429.2	427.1	426.4	423.0	422.3
52.5°	403.3	402.4	400.0	397.1	397.0
55°	363.1	361.8	358.3	356.2	355.6
57.5°	319.5	316.8	312.9	309.9	310.5
60°	288.2	285.5	279.9	278.5	278.5
62.5°	257.9	254.7	249.1	247.2	248.3
65°	214.6	210.5	205.6	204.3	205.0
67.5°	175.2	171.6	166.3	166.3	165.8
70°	149.9	147.9	143.7	143.7	143.7
72.5°	127.4	126.4	123.4	123.4	122.8
75°	97.7	97.7	96.3	95.6	94.9
77.5°	73.2	73.4	72.8	72.1	70.8
80°	57.8	59.1	58.5	57.8	57.1
82.5°	43.5	44.8	44.7	43.5	43.3
85°	22.7	24.7	24.8	24.8	24.8
87.5°	6.1	8.2	8.8	8.8	9.4
90°	0.0	0.0	0.0	0.0	0.0
92.5°	16.2	85.9	199.3	58.0	43.8
95°	52.7	209.1	939.9	325.3	200.5
97.5°	96.8	245.0	1447.5	1035.8	709.8
100°	127.6	266.3	1557.7	1577.8	1215.4
102.5°	161.6	289.2	1533.4	2019.7	1703.2
105°	214.7	325.6	1407.8	2486.7	2363.9
107.5°	268.6	368.0	1261.2	2618.4	2727.7
110°	305.9	399.0	1176.9	2568.0	2813.6

TEST NUMBER: P523933

CATALOG NUMBER: SQ4-PP3-150U-050D-92765-1D-UNV-STD-W-4 (3500K)

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	341.5	429.9	1120.2	2448.9	2799.0
115°	399.1	482.2	1067.5	2261.5	2655.6
117.5°	449.7	527.7	1036.3	2056.6	2474.1
120°	490.2	555.6	1033.1	1939.5	2339.6
122.5°	522.6	588.0	1025.0	1836.8	2208.4
125°	563.1	624.5	1018.9	1690.8	2021.6
127.5°	607.3	664.7	1015.7	1603.6	1876.1
130°	630.0	687.4	1010.8	1542.9	1780.5
132.5°	654.3	710.1	1010.8	1495.4	1714.1
135°	688.7	746.2	1006.7	1428.3	1614.4
137.5°	721.1	777.0	1006.3	1371.4	1532.2
140°	745.4	802.9	1004.7	1324.2	1478.7
142.5°	773.0	820.9	1009.6	1286.6	1425.2
145°	812.3	853.9	1014.8	1236.1	1347.0
147.5°	845.9	886.3	1023.8	1185.2	1281.0
150°	875.1	902.8	1027.0	1168.3	1235.6
152.5°	897.8	927.1	1030.2	1145.5	1208.1
155°	927.7	949.5	1039.2	1117.2	1162.7
157.5°	965.0	978.1	1041.2	1104.3	1136.8
160°	984.5	994.4	1049.3	1094.5	1122.2
162.5°	995.8	1007.3	1050.9	1086.2	1107.6
165°	1025.0	1028.9	1051.3	1073.9	1089.8
167.5°	1044.8	1041.3	1060.6	1070.9	1077.2
170°	1051.3	1049.3	1057.4	1059.6	1067.5
172.5°	1065.9	1059.2	1062.2	1056.3	1062.6
175°	1073.6	1067.6	1063.5	1057.2	1049.3
177.5°	1076.8	1067.3	1062.2	1055.8	1057.4
180°	1065.5	1065.5	1065.5	1065.5	1065.5

(END OF REPORT)