

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P523726

Luminaire Tested: **SQ4-PP3-075U-050D-92765-1D-UNV-STD-W-4 (4000K)**

Issue Date: 5/24/2021

Test Information

Test Method: LM-79-2019
Report Number: P523726
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2103-172-1)
Test Lab: INNOVATION CENTER
Issue Date: 5/24/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4-PP3-075U-050D-92765-1D-UNV-STD-W-4 (4000K)
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS
DOWNLIGHT 500 LUMENS PER FOOT
UPLIGHT 750 LUMENS PER FOOT
Light Source: 2700K/65000K CCT, 90 CRI LEDS, TUNED TO 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5372.4 lumens
Efficiency: N/A
Efficacy: 121.0 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 44.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P523726

CATALOG NUMBER: SQ4-PP3-075U-050D-92765-1D-UNV-STD-W-4 (4000K)

Luminous Intensity Polar Plot





TEST NUMBER: P523726

CATALOG NUMBER: SQ4-PP3-075U-050D-92765-1D-UNV-STD-W-4 (4000K)

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	95	95	95	95	77	77	77	60	60	60	45	45	45	38
1	95	91	87	84	86	83	80	77	67	65	63	53	52	50	40	39	38	32
2	87	80	74	69	79	73	68	63	59	56	53	47	44	42	35	34	33	27
3	79	70	63	57	72	64	58	53	52	48	44	42	38	36	32	30	28	23
4	72	62	54	48	66	57	50	45	46	42	38	37	34	31	28	26	24	20
5	66	55	47	41	60	50	44	38	42	36	32	33	30	27	25	23	21	17
6	61	49	42	36	55	45	38	33	37	32	28	30	26	23	23	20	18	15
7	57	45	37	31	51	41	34	29	34	29	25	27	23	21	21	18	16	14
8	52	40	33	28	47	37	30	26	31	26	22	25	21	18	19	17	15	12
9	49	37	29	25	44	34	27	23	28	23	20	23	19	16	18	15	13	11
10	45	34	27	22	41	31	25	20	26	21	18	21	17	15	16	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7373	7373	7373
5°	7427	7381	7355
10°	7414	7362	7329
15°	7365	7325	7285
20°	7317	7275	7220
25°	7230	7180	7108
30°	7095	7058	6968
35°	6910	6863	6776
40°	6689	6647	6571
45°	6506	6460	6396
50°	6272	6232	6172
55°	5948	5870	5825
60°	5414	5259	5233
65°	4770	4571	4556
70°	4119	3949	3949
75°	3543	3493	3444
80°	3124	3161	3087
85°	2445	2668	2668



TEST NUMBER: P523726

CATALOG NUMBER: SQ4-PP3-075U-050D-92765-1D-UNV-STD-W-4 (4000K)

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	75.6	1.4
10°-20°	215.8	4.0
20°-30°	323.2	6.0
30°-40°	379.1	7.1
40°-50°	380.2	7.1
50°-60°	324.4	6.0
60°-70°	211.5	3.9
70°-80°	106.1	2.0
80°-90°	29.4	0.5
90°-100°	244.1	4.5
100°-110°	694.5	12.9
110°-120°	665.4	12.4
120°-130°	526.6	9.8
130°-140°	422.7	7.9
140°-150°	330.9	6.2
150°-160°	242.1	4.5
160°-170°	150.0	2.8
170°-180°	50.9	0.9
0°-30°	614.5	11.4
0°-40°	993.6	18.5
0°-60°	1698.2	31.6
0°-90°	2045.2	38.1
90°-120°	1603.9	29.9
90°-150°	2884.1	53.7
90°-180°	3327.0	61.9
0°-180°	5372.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	799	799	799	799	799	
5°	802	794	797	794	794	76
15°	771	764	767	764	763	218
25°	710	702	705	699	698	327
35°	614	607	609	602	602	383
45°	499	495	495	490	490	384
55°	370	368	365	363	362	329
65°	218	214	209	208	209	218
75°	99	99	98	97	97	108
85°	23	25	25	25	25	27
90°	0	0	0	0	0	2
95°	26	105	472	164	101	30
105°	108	164	708	1250	1188	114
115°	201	242	537	1137	1335	198
125°	283	314	512	850	1016	253
135°	346	375	506	718	812	267
145°	408	429	510	621	677	255
155°	466	477	522	562	584	216
165°	515	517	528	540	548	145
175°	540	537	535	532	528	51
180°	536	536	536	536	536	



TEST NUMBER: P523726

CATALOG NUMBER: SQ4-PP3-075U-050D-92765-1D-UNV-STD-W-4 (4000K)

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	799.1	799.1	799.1	799.1	799.1
2.5°	804.1	797.6	799.1	797.9	794.6
5°	801.9	794.4	797.0	794.2	794.2
7.5°	796.4	788.2	790.8	788.0	787.9
10°	791.4	783.2	785.8	783.0	782.3
12.5°	784.1	775.9	779.1	775.7	775.6
15°	771.1	763.6	766.9	764.0	762.7
17.5°	756.4	748.2	752.2	748.2	747.7
20°	745.2	737.0	741.0	735.4	735.4
22.5°	731.7	723.5	728.1	720.8	720.8
25°	710.2	701.9	705.3	698.9	698.2
27.5°	684.5	676.4	679.9	672.8	672.6
30°	666.0	658.5	662.5	654.8	654.1
32.5°	645.9	638.9	641.8	634.1	633.4
35°	613.5	607.3	609.3	602.3	601.6
37.5°	579.5	573.2	575.4	569.4	569.1
40°	555.4	551.3	551.9	546.9	545.6
42.5°	533.0	528.3	528.9	524.0	523.7
45°	498.6	495.2	495.1	490.2	490.2
47.5°	462.2	459.6	458.9	454.8	454.7
50°	437.0	435.0	434.2	430.7	430.0
52.5°	410.7	409.7	407.3	404.4	404.2
55°	369.8	368.4	364.9	362.8	362.1
57.5°	325.4	322.6	318.7	315.6	316.1
60°	293.4	290.7	285.0	283.6	283.6
62.5°	262.6	259.3	253.7	251.7	252.8
65°	218.5	214.4	209.4	208.0	208.7
67.5°	178.4	174.8	169.3	169.3	168.8
70°	152.7	150.6	146.4	146.4	146.4
72.5°	129.7	128.7	125.6	125.6	125.1
75°	99.4	99.4	98.0	97.3	96.6
77.5°	74.5	74.8	74.1	73.4	72.1
80°	58.8	60.2	59.5	58.8	58.1
82.5°	44.3	45.6	45.5	44.3	44.1
85°	23.1	25.2	25.2	25.2	25.2
87.5°	6.2	8.4	9.0	9.0	9.5
90°	0.0	0.0	0.0	0.0	0.0
92.5°	8.1	43.2	100.2	29.2	22.0
95°	26.5	105.1	472.5	163.5	100.8
97.5°	48.7	123.2	727.7	520.7	356.8
100°	64.2	133.8	783.1	793.2	611.0
102.5°	81.3	145.4	770.8	1015.3	856.2
105°	107.9	163.7	707.7	1250.1	1188.4
107.5°	135.0	185.0	634.0	1316.3	1371.2
110°	153.8	200.6	591.6	1290.9	1414.4



TEST NUMBER: P523726

CATALOG NUMBER: SQ4-PP3-075U-050D-92765-1D-UNV-STD-W-4 (4000K)

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	171.7	216.1	563.1	1231.0	1407.1
115°	200.6	242.4	536.6	1136.8	1335.0
117.5°	226.1	265.3	521.0	1033.9	1243.7
120°	246.4	279.3	519.3	975.0	1176.1
122.5°	262.7	295.6	515.3	923.4	1110.1
125°	283.1	314.0	512.2	850.0	1016.3
127.5°	305.3	334.2	510.6	806.1	943.1
130°	316.7	345.6	508.1	775.6	895.1
132.5°	328.9	357.0	508.1	751.8	861.7
135°	346.2	375.1	506.1	718.0	811.6
137.5°	362.5	390.6	505.9	689.4	770.2
140°	374.7	403.6	505.1	665.7	743.4
142.5°	388.6	412.7	507.5	646.8	716.5
145°	408.3	429.2	510.2	621.4	677.2
147.5°	425.2	445.6	514.6	595.8	644.0
150°	439.9	453.8	516.3	587.3	621.2
152.5°	451.3	466.0	517.9	575.8	607.3
155°	466.4	477.3	522.4	561.6	584.5
157.5°	485.1	491.7	523.4	555.1	571.5
160°	494.9	499.9	527.5	550.2	564.1
162.5°	500.6	506.4	528.3	546.1	556.8
165°	515.3	517.2	528.5	539.9	547.8
167.5°	525.2	523.4	533.2	538.3	541.5
170°	528.5	527.5	531.5	532.7	536.6
172.5°	535.8	532.4	534.0	531.0	534.2
175°	539.7	536.7	534.6	531.5	527.5
177.5°	541.3	536.5	534.0	530.8	531.5
180°	535.6	535.6	535.6	535.6	535.6

(END OF REPORT)